PRIVATE LABEL BRANDS VOLUME 5

FERGUSON®


WOLSELEY Canada



FERGUSON® | WOLSELEY Canada

PRIVATE LABEL BRANDS

BATHING // BATH FAUCETS // KITCHEN & BAR FAUCETS // FIXTURES // ROUGH PLUMBING
COMMERCIAL/INDUSTRIAL // WATERWORKS // HVAC // TOOLS // FASTENERS & INSTALLATION



Introducing Ferguson Mobile

With Ferguson's new mobile website, you can check pricing and availability, download photos and spec sheets and quickly place orders. You can also see your order status or manage your account, whenever and wherever you want.

Try it now at **Ferguson.com.**

FERGUSON®

FOR OUR CANADIAN CUSTOMERS...
Shop Online at **WolseleyExpress.com** & get access to your account.



work on-the-go
with Wolseley Express

PLUMBING HVAC/R

Wolseley Canada is the country's leading national distributor of plumbing, hydronics, HVAC/R and PVF products and solutions to professional contractors, retailers, and industrial users.

Our associates have proven industry expertise and can provide the resources and products you need at over 220 branches across Canada.

National reach for products when and where you need them.

WOLSELEY
The best local distributor



FNW · MONOGRAM BRASS · PROFLO · PROSELECT · RAPTOR

TABLE OF CONTENTS

- BATHING . . . . . 5 - 16
- BATH FAUCETS . . . . . 17 - 38
- KITCHEN & BAR FAUCETS . . . . . 39 - 44
- FIXTURES . . . . . 45 - 76
- ROUGH PLUMBING . . . . . 77 - 166
- COMMERCIAL/INDUSTRIAL . . . . . 167 - 178
- WATERWORKS . . . . . 179 - 188
- HVAC . . . . . 189 - 212
- TOOLS . . . . . 213 - 226
- FASTENERS & INSTALLATION SUPPLIES . . . . . 227 - 236
- INDEX . . . . . 238 - 252











CONTACT US

Contact the Private Label Assistance Center for parts, warranty or troubleshooting needs (8am-8pm EST):

Phone Number:
(800) 221-3379

EMAIL:
PLAC@FERGUSON.COM

For more information on each brand, and to view available products, visit our Private Label websites:

FNW.COM
MONOGRAMBRASS.COM
PROFLO.COM
PROSELECTPRODUCTS.COM
RAPTORTOOL.COM

ICON LEGEND

ADA
Product complies with the Americans with Disabilities Act.

Low Lead
Product is defined as "lead free" as pursuant to US Federal and other applicable law.

Non-Potable
Do not use product in connection with drinking water.

WaterSense
Product meets the EPA's criteria for water conservation.

Available in Canada



Style that makes a statement, quality that backs it up. Elevate your home with beautiful solutions from Ferguson® brands.

Mirabelle®

MIRABELLEPRODUCTS.COM

PARK HARBOR®

PARKHARBORLIGHTING.COM

Bath Faucets: Mirabelle® Rigi & Custom Showering Collections | **Bath Tub:** Mirabelle® Sitka Collection | **Lighting:** Park Harbor® Willow Hill Exterior Collection

WORK LIKE A BEAST



Wanna' tear through stuff with the destructive force of a wild animal? Of course you do.

Beef up your tool arsenal with our new and improved Raptor RAW Premium Cutting Hole Saw & Reciprocating Saw Blades.



RAPTOR®

RAW™

Premium Cutting

RAPTORTOOL.COM

Made in U.S.A.

Copyright © 2016 Ferguson Enterprises, Inc. 05/14 20917

Made in/Fabriqué à/Hecho en USA



What can we help you find?

Whirlpools 5-8
Baths/Soakers 8-11
Shower Bases 12
Bathing Accessories 12-16

Drop-In Whirlpools



- 72" x 42" x 19 1/2"
- 55 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR
  6' removable skirt: PFSK72

SKU	Color/Finish
PFWPLUSA7242BS	Biscuit
PFWPLUSA7242WH	White

Drop-In Whirlpools



- 72" x 36" x 19 1/2"
- 50 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR
  6' removable skirt: PFSK72

SKU	Color/Finish
PFWPLUSA7236BS	Biscuit
PFWPLUSA7236WH	White

Drop-In Whirlpools



- 70" x 40" x 20 1/2"
- 50 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 6 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Color/Finish
PFWPLUSA7040BS	Biscuit
PFWPLUSA7040WH	White

Drop-In Whirlpools



- 60" x 36" x 19 1/2"
- 45 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Color/Finish
PFWPLUSA6036BS	Biscuit
PFWPLUSA6036WH	White

Drop-In Whirlpools



- 58" x 38" x 20 1/2"
- 40 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 6 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Color/Finish
PFWPLUSA5838BS	Biscuit
PFWPLUSA5838WH	White

Drop-In Whirlpools



- 60" x 42" x 19 1/2"
- 45 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Color/Finish
PFWPLUSA6042BS	Biscuit
PFWPLUSA6042WH	White

Drop-In Whirlpools



- 60" x 32" x 19 1/2"
- 40 gal capacity
- Drop-in installation
- End drain
- On/Off low-profile air switch
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Color/Finish
PFWPLUSA6032BS	Biscuit
PFWPLUSA6032WH	White

Alcove Whirlpools



- 72" x 42" x 19 3/4"
- 55 gal capacity
- Alcove installation
- End drain
- On/Off low-profile air switch
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Drain Location	Color/Finish
PFW7242ALSKWH	Left	White
PFW7242ALSKBS	Left	Biscuit
PFW7242ARSKWH	Right	White
PFW7242ARSKBS	Right	Biscuit

Alcove Whirlpools



- 72" x 36" x 19 3/4"
- 50 gal capacity
- Alcove installation
- End drain
- On/Off low-profile air switch
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Drain Location	Color/Finish
PFW7236ALSKBS	Left	Biscuit
PFW7236ALSKWH	Left	White
PFW7236ARSKBS	Right	Biscuit
PFW7236ARSKWH	Right	White

Alcove Whirlpools



- 66" x 36" x 19 3/4"
- 40 gal capacity
- Alcove installation
- End drain
- On/Off low-profile air switch
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- Features an integral skirt and integral tile flange
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Drain Location	Color/Finish
PFW6636ALSKBS	Left	Biscuit
PFW6636ALSKWH	Left	White
PFW6636ARSKBS	Right	Biscuit
PFW6636ARSKWH	Right	White

Alcove Whirlpools



- 60" x 42" x 19 3/4"
- 55 gal capacity
- Alcove installation
- End drain
- On/Off low-profile air switch
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Drain Location	Color/Finish
PFW6042ALSKWH	Left	White
PFW6042ARSKWH	Right	White
PFW6042ALSKBS	Left	Biscuit
PFW6042ARSKBS	Right	Biscuit

Alcove Whirlpools



- 60" x 36" x 19 3/4"
- 40 gal capacity
- Alcove installation
- End drain
- On/Off low-profile air switch
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Drain Location	Color/Finish
PFW6036ALSKBS	Left	Biscuit
PFW6036ALSKWH	Left	White
PFW6036ARSKBS	Right	Biscuit
PFW6036ARSKWH	Right	White



Alcove Whirlpools



- 60" x 32" x 19 3/4"
- 40 gal capacity
- Alcove installation
- End drain
- On/Off low-profile air switch
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Drain Location	Color/Finish
PFW6032ALSKBS	Left	Biscuit
PFW6032ALSKWH	Left	White
PFW6032ARSKBS	Right	Biscuit
PFW6032ARSKWH	Right	White

Whirlpools



- 60" x 60" x 21"
- 72 gal capacity
- Corner installation
- Center drain
- On/Off low-profile air switch
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Acrylic construction
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR
  Removable skirt: PFSK6060

SKU	Drain Location	Color/Finish
PFWPLUSA6060LBS	Left	Biscuit
PFWPLUSA6060LWH	Left	White
PFWPLUSA6060RBS	Right	Biscuit
PFWPLUSA6060RWH	Right	White

Whirlpools



- 60" x 60" x 21"
- 60 gal capacity
- Corner installation
- Center drain
- Pump Location: Left
- On/Off low-profile air switch
- 8 high-flow quarter-turn directional and volume adjustable color matched whirlpool jets
- Features an integral skirt and integral tile flange
- Textured slip-resistant bottom
- Silent air induction for quiet operation
- Safety suction return
- Requires a single 115V/20A GFCI circuit for whirlpool
- **Optional accessories:**
  In-line heater: MIRPRESSHTR

SKU	Color/Finish
PFW6060SKPLABS	Biscuit
PFW6060SKPLAWH	White

Drop-In Soakers



- 72" x 42" x 19 1/2"
- 55 gal capacity
- Drop-in installation
- End drain
- Integral arm rests
- Textured slip-resistant bottom
- **Optional accessories:**
  6' removable skirt: PFSK72

SKU	Color/Finish
PFS7242ABS	Biscuit
PFS7242AWH	White

Drop-In Soakers



- 72" x 36" x 19 1/2"
- 50 gal capacity
- Drop-in installation
- End drain
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- **Optional accessories:**
  6' removable skirt: PFSK72

SKU	Color/Finish
PFS7236ABS	Biscuit
PFS7236AWH	White

Drop-In Soakers



- 70" x 40" x 20 1/2"
- 50 gal capacity
- Drop-in installation
- End drain
- Textured slip-resistant bottom

SKU	Color/Finish
PFS7040BS	Biscuit
PFS7040WH	White

Drop-In Soakers



- 60" x 42" x 19 1/2"
- 45 gal capacity
- Drop-in installation
- End drain
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- **Optional accessories:**
  5' removable skirt: PFSK60

SKU	Color/Finish
PFS6042ABS	Biscuit
PFS6042AWH	White

Drop-In Soakers



- 60" x 36" x 19 1/2"
- 45 gal capacity
- Drop-in installation
- End drain
- Integral arm rests
- Acrylic construction
- Textured slip-resistant bottom
- **Optional accessories:**
  5' removable skirt: PFSK60

SKU	Color/Finish
PFS6036ABS	Biscuit
PFS6036AWH	White

Drop-In Soakers



- 60" x 32" x 19 1/2"
- 40 gal capacity
- Drop-in installation
- End drain
- Integral arm rests
- Textured slip-resistant bottom
- **Optional accessories:**
  5' removable skirt: PFSK60

SKU	Color/Finish
PFS6032AWH	White
PFS6032ABS	Biscuit

Drop-In Soakers



- 58" x 38" x 20 1/2"
- 40 gal capacity
- Drop-in installation
- End drain
- Acrylic construction
- Textured slip-resistant bottom

SKU	Color/Finish
PFS5838BS	Biscuit
PFS5838WH	White

Alcove Soakers



- 72" x 42" x 19 3/4"
- 55 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Textured slip-resistant bottom

SKU	Drain Location	Color/Finish
PFS7242LSKWH	Left	White
PFS7242LSKBS	Left	Biscuit
PFS7242RSKWH	Right	White
PFS7242RSKBS	Right	Biscuit

Alcove Soakers



- 72" x 36" x 19 3/4"
- 50 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom

SKU	Drain Location	Color/Finish
PFS7236LSKBS	Left	Biscuit
PFS7236LSKWH	Left	White
PFS7236RSKBS	Right	Biscuit
PFS7236RSKWH	Right	White

Alcove Soakers



- 66" x 36" x 19 3/4"
- 40 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom

SKU	Drain Location	Color/Finish
PFS6636LSKBS	Left	Biscuit
PFS6636LSKWH	Left	White
PFS6636RSKBS	Right	Biscuit
PFS6636RSKWH	Right	White

Alcove Soakers



- 60" x 36" x 19 3/4"
- 40 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom

SKU	Drain Location	Color/Finish
PFS6036LSKBS	Left	Biscuit
PFS6036LSKWH	Left	White
PFS6036RSKBS	Right	Biscuit
PFS6036RSKWH	Right	White

Alcove Soakers



- 60" x 30" x 15 1/2"
- 33 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Textured slip-resistant bottom
- Acrylic construction
- End drain

SKU	Drain Location	Color/Finish
PFS6030LSKBS	Left	Biscuit
PFS6030LSKWH	Left	White
PFS6030RSKBS	Right	Biscuit
PFS6030RSKWH	Right	White

Soakers



- 60" x 60" x 21"
- 60 gal capacity
- Corner installation
- Center drain
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom

SKU	Color/Finish
PFS6060SKWH	White
PFS6060SKBS	Biscuit

Alcove Soakers



- 60" x 42" x 19 3/4"
- 55 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom

SKU	Drain Location	Color/Finish
PFS6042LSKBS	Left	Biscuit
PFS6042LSKWH	Left	White
PFS6042RSKBS	Right	Biscuit
PFS6042RSKWH	Right	White

Alcove Soakers



- 60" x 32" x 19 3/4"
- 40 gal capacity
- Alcove installation
- Features an integral skirt and integral tile flange
- Acrylic construction
- Textured slip-resistant bottom

SKU	Drain Location	Color/Finish
PFS6032LSKBS	Left	Biscuit
PFS6032LSKWH	Left	White
PFS6032RSKBS	Right	Biscuit
PFS6032RSKWH	Right	White

Soakers



- 60" x 60" x 21"
- 60 gal capacity
- Corner installation
- Center drain
- Acrylic construction
- Textured slip-resistant bottom
- **Optional accessories:**
  Removable apron: PFSK6060

SKU	Color/Finish
PFS6060BS	Biscuit
PFS6060WH	White

Steel Tubs - Basic Series



- Enameled Steel
- Soaker
- 60" x 30" x 16 5/8"
- Alcove installation
- Above floor rough-in
- Full length tile flange

SKU	Drain Location	Color/Finish
PFB16LBS	Left	Biscuit
PFB16LWH	Left	White
PFB16RBS	Right	Biscuit
PFB16RWH	Right	White

Steel Tubs - Basic Series



- Enameled Steel
- Soaker
- 60" x 30" x 14 1/4"
- Alcove installation
- Standard rough-in
- 40° lumbar support
- Full length tile flange

SKU	Drain Location	Color/Finish
PFB14CLBS	Left	Biscuit
PFB14CLWH	Left	White
PFB14CRBS	Right	Biscuit
PFB14CRWH	Right	White

Steel Tubs - S Series



- Enameled Steel
- Soaker
- 60" x 30" x 14 1/4"
- Alcove installation
- Standard rough-in
- Elastomer backing deadens noise, retains heat and resists impact damage
- Full length tile flange
- Integral molded leveling feet
- Non-skid bottom surface
- High gloss, stain resistant porcelain finish

SKU	Drain Location	Color/Finish
PFB14LSBS	Left	Biscuit
PFB14LSWH	Left	White
PFB14RSBS	Right	Biscuit
PFB14RSWH	Right	White

Steel Tubs - S2 Series



- Enameled Steel
- Soaker
- 60" x 30" x 14 1/4"
- Alcove installation
- Standard rough-in
- High-density molded backing for sound deadening and heat retention
- Full length tile flange
- Integral molded leveling feet
- Non-skid bottom surface
- High gloss, stain resistant porcelain finish

SKU	Drain Location	Color/Finish
PFB14LS2BS	Left	Biscuit
PFB14LS2WH	Left	White
PFB14RS2BS	Right	Biscuit
PFB14RS2WH	Right	White

Steel Tubs - S Series



- Enameled Steel
- Soaker
- 60" x 30" x 16 5/8"
- Alcove installation
- Above floor rough-in
- Elastomer backing deadens noise, retains heat and resists impact damage
- Full length tile flange

SKU	Drain Location	Color/Finish
PFB16LSBS	Left	Biscuit
PFB16LSWH	Left	White
PFB16RSBS	Right	Biscuit
PFB16RSWH	Right	White

Steel Tubs - S2 Series



- Enameled Steel
- Soaker
- 60" x 30" x 16 1/4"
- Alcove installation
- Above floor rough-in
- Elastomer backing deadens noise, retains heat and resists impact damage
- Full length tile flange
- Integral molded leveling feet
- Non-skid bottom surface
- High gloss, stain resistant porcelain finish

SKU	Drain Location	Color/Finish
PFB16LS2BS	Left	Biscuit
PFB16LS2WH	Left	White
PFB16RS2BS	Right	Biscuit
PFB16RS2WH	Right	White

Steel Tubs - Basic Series



- Enameled Steel
- Soaker
- 54" x 30" x 15 1/4"
- Alcove installation
- Designed for space-saving convenience
- Standard rough-in
- Full length tile flange
- Color/Finish: White

SKU	Drain Location
PFB54LWH	Left
PFB54RWH	Right

Steel Tubs

Item Attributes	Basic	S Series	S2 Series
Standard Rough-in	PFB14CR/L	PFB14RS/LS	PFB14RS2/LS2
Above Floor Rough-in	PFB16R/L	PFB16RS/LS	PFB16RS2/LS2
Insulated Backing	No	Standard	High Density
Sound Deadening	Low	Mid	High
Heat Retention	Low	Mid	High
Impact Resistance	Low	Mid	High
Source	Factory Direct	Factory Direct	Factory Direct

Shower Bases



- One-piece unit molded of durable composite
- Non-porous surface is stain, thermal and shock resistant
- Includes integrally molded drain with compression gasket and strainer
- Slip-resistant surface
- Color/Finish: White
- **Optional accessories:**
  Replacement white strainer: PFSBSTR
  Replacement drain gasket: PFSBGSKT

SKU	Size	Shower Base Shape
PFSB3232WH	32" x 32"	Square
PFSB3434WH	34" x 34"	Square
PFSB3636NEOWH	36" x 36"	Neo-Angle
PFSB3636WH	36" x 36"	Square
PFSB4234WH	42" x 34"	Rectangle
PFSB4242WH	42" x 42"	Square
PFSB4832WH	48" x 32"	Rectangle
PFSB4834WH	48" x 34"	Rectangle
PFSB5434WH	54" x 34"	Rectangle
PFSB6034WH	60" x 34"	Rectangle

Cable Drains



- For tub depths 23" - 27"
- Less piping
- Includes trim kit
- PVC construction

SKU	Color/Finish
MB642BN	Brushed Nickel
MB642CP	Chrome
MB642ORB	Oil Rubbed Bronze

Cable Drains



- For tub depths 17" - 22"
- Less piping
- Includes trim kit
- ABS construction

SKU	Color/Finish
MB643BN	Brushed Nickel
MB643CP	Chrome
MB643ORB	Oil Rubbed Bronze
MB643PN	Polished Nickel

Cable Drains



- For tub depths 17" - 22"
- Less piping
- Includes trim kit
- PVC construction

SKU	Color/Finish
MB644BN	Brushed Nickel
MB644CP	Chrome
MB644ORB	Oil Rubbed Bronze
MB644PN	Polished Nickel

Lift & Turn 1/2 Kits



- Plastic drain and overflow elbows
- One hole face plate
- 1 1/2" threaded shoe
- Half kit that does not include pipe
- **Optional accessories:**
  Test kit: PFTK

SKU	Material	Color/Finish
PFWO320	ABS Body with Zinc Drain	Chrome
PFWO350	PVC Body with Zinc Drain	Chrome
PFWO322	ABS Body with Brass Drain	Chrome
PFWO354	PVC Body with Brass Drain	Brushed Nickel
PFWO355	PVC Body with Brass Drain	Chrome
PFWO357	PVC Body with Brass Drain	Oil Rubbed Bronze

Test Kits



- Includes: overflow test cap and test plug
- For PROFLO half kits

SKU
PFTK

Toe Tap 1/2 Kits



- Plastic drain and overflow elbows
- One hole face plate
- 1 1/2" threaded shoe
- Half kit that does not include pipe
- **Optional accessories:**
  Test kit: PFTK

SKU	Material	Color/Finish
PFWO321	ABS Body with Brass Drain	Chrome
PFWO351	PVC Body with Brass Drain	Brushed Nickel
PFWO352	PVC Body with Brass Drain	Chrome

Lift & Turn Trim Kits



- Brass construction

SKU	Color/Finish
PFWO502	Brushed Nickel
PFWO503	Oil Rubbed Bronze

Lift & Turn Trim Kits



- Lift & turn stopper
- 2 hole overflow plate
- With 1 3/5" x 1 3/5" TPI ID
- Color/Finish: Chrome

SKU
PFWO505

Lift & Turn Tub Drain Kits



- Fits Pipe Size: 1 1/2"
- Fits most 18" – 24" tubs
- 17 gauge brass construction
- Color/Finish: Chrome

SKU
PFWO251

Lift & Turn Tub Waste Kits



- 17 gauge brass construction
- Two hole face plate
- 1 1/2" threaded shoe
- Fits most 14" – 16" high tubs
- Includes plastic and brass washers
- Color/Finish: Chrome

SKU
PFWO101

Lift & Turn Tub Waste Kits



- Full plastic drain including piping
- Two hole face plate
- 1 1/2" threaded shoe
- PVC body with zinc drain spud
- Color/Finish: Chrome

SKU	Pipe Material
PFWO304	SCH40
PFWO400	Tubular

Push Pull Tub Waste Kits



- Full plastic drain including SCH 40 piping
- Two hole face plate
- 1 1/2" threaded shoe
- PVC body with brass drain spud
- Color/Finish: Chrome

SKU
PFWO305

Toe Tap Tub Waste Kits



- Full plastic drain including SCH 40 piping
- Two hole face plate
- 1 1/2" threaded shoe
- PVC body with zinc drain spud
- Color/Finish: Chrome
- LA Code approved

SKU
PFWO300

Trip Lever Trim Kits



- Brass construction

SKU	Color/Finish
PFWO210	Brushed Nickel
PFWO215	Oil Rubbed Bronze

Trip Lever Tub Waste Kits



- 17 gauge brass construction
- Two hole face plate
- 1 1/2" threaded shoe
- Fits most 14" – 16" high tubs
- Includes plastic and brass washers
- Color/Finish: Chrome

SKU
PFWO201

Trip Lever Tub Waste Kits



- Fits Pipe Size: 1 1/2"
- Fits most 18" – 24" tubs
- 17 gauge brass construction
- Color/Finish: Chrome

SKU
PFWO250

Trip Lever Tub Waste Kits



- Full plastic tubular drain
- Includes TPR washer
- Color/Finish: Chrome

SKU	Material
PFWO401	Plastic Body with Brass Drain Spud
PFWO402	Plastic Body with Zinc Drain Spud

Waste & Overflow Trim Kits



- Trim kit only
- Lift & turn design stopper
- One hole face plate
- Zinc construction
- Color/Finish: Chrome
- **Required accessories:**
  Waste & overflow kit: PFWO500

SKU
PFWO501

Drain Kits



- Includes gasket
- Brass construction
- Compatible with lift & turn style stopper only
- Color/Finish: Chrome

SKU
PFWO904

Cover Plates



- One hole plate with screw
- Brass construction

SKU	Color/Finish
MB631BN	Brushed Nickel
MB631CP	Chrome
MB631ORB	Oil Rubbed Bronze
MB631PB	Polished Brass
MB631PN	Polished Nickel

Cover Plates



- Two hole plate with screws
- Brass construction

SKU	Color/Finish
MB632BN	Brushed Nickel
MB632CP	Chrome
MB632ORB	Oil Rubbed Bronze
MB632PB	Polished Brass
MB632PN	Polished Nickel

Cover Plates



- Trip lever design
- Two hole
- Includes brass screws
- Color/Finish: Chrome

SKU
PF400

Cover Plates



- Two hole
- Includes brass screws
- Color/Finish: Chrome

SKU
PF401

Cover Plates



- One hole
- Includes brass screws
- Color/Finish: Chrome

SKU
PF402

Stoppers



- Lift & turn design
- 3/8" post connection
- Brass construction
- Color/Finish: Chrome

SKU
PFWO900

Stoppers



- Toe tap design
- 3/8" post connection
- Plastic construction
- Color/Finish: Chrome

SKU
PFWO901

Stoppers



- Push/pull design
- Brass construction
- Color/Finish: Chrome

SKU	Connection
PFWO902	3/8" Post
PFWO903	3/8" & 5/16" Post

Drain Conversion Kits



- Trip waste shoe strainer
- Brass trip plate with handle
- Brass drain body
- Stainless steel strainer
- Plastic bushing

SKU	Color/Finish
MB621BN	Brushed Nickel
MB621CP	Chrome
MB621ORB	Oil Rubbed Bronze
MB621PN	Polished Nickel

Drain Conversion Kits



- Rapid Fit™ style tub stopper
- Two to one hole converter bracket
- Brass one hole plate and drain body

SKU	Color/Finish
MB622BN	Brushed Nickel
MB622CP	Chrome
MB622ORB	Oil Rubbed Bronze
MB622PN	Polished Nickel

Drains



- Trip lever design
- Trip plate with handle and brass screws
- Brass construction

SKU	Color/Finish
MB633BN	Brushed Nickel
MB633ORB	Oil Rubbed Bronze
MB633PB	Polished Brass
MB633PN	Polished Nickel

Drains



MONOGRAM BRASS™

- Lift & turn style
- Fits 1 1/4" & 1 1/2" drains
- Brass body and plastic bushing

SKU	Color/Finish
MB612BN	Brushed Nickel
MB612CP	Chrome
MB612ORB	Oil Rubbed Bronze
MB612PB	Polished Brass
MB612PN	Polished Nickel

Waste & Overflow Components



- Connection: 3/4" NPT
- Top elbow including condensate drain connection
- PVC construction

SKU
PFWO950

Waste & Overflow Components



- Adapter bar for overflow plate
- Includes brass screws and aluminum bar

SKU
PF402BS

Waste & Overflow Rough-in Kits



- Rough-in portion only
- Plastic drain and overflow elbows
- 1 1/2" threaded shoe
- PVC construction
- **Required accessories:**
  Drain kit: PFWO501

SKU
PFWO500

Waste & Overflow Rough-in Kits



- ABS construction

SKU
PFWO600

Shower Cock Elbows



- Connection: 1/2" MIP
- Sold as a pair
- Brass construction
- Color/Finish: Chrome

SKU
PFBCE

Shower Elbows



- Connection: 1/2" SWT or 1/2" MIP x 1/2" FIP
- For fiberglass showers
- Includes rigid nut for easy tightening
- Secures shower arms to stall
- Color/Finish: Rough Brass

SKU
PF18012



What can we help you find?

Lavatory Faucets 17-20
Shower Only Faucets 21-22
Tub & Shower Faucets 23-24
Showerheads 25-26
Shower Arms 26
Tup Spouts 27-28
Tub & Shower Valves 28-29
Handshowers & Accessories 29-32
Roman Tub Faucets 33
Bath Faucet Accessories 34-35
Bath Hardware 35-37

Single Handle Lavatory Faucets



- Spout Height: 2 5/16"
- Spout Reach: 6 3/8"
- 4" centerset installation
- Lever metal handle
- Ceramic disc cartridge
- Less pop-up
- Color/Finish: Chrome

SKU	Flow Rate
PFWSC30065CP	0.5 gpm
PFWSC3006CP	1.2 gpm

Single Handle Lavatory Faucets



- Spout Height: 2 5/16"
- Spout Reach: 6 1/2"
- 4" centerset installation
- Metal lever handle
- Ceramic disc cartridge
- Less drain
- Less pop-up

SKU	Flow Rate	Color/Finish
PFWSC47445CP	0.5 gpm	Chrome
PFWSC4744CP	1.2 gpm	Chrome
PFWSC4744BN	1.2 gpm	Brushed Nickel

Single Handle Lavatory Faucets



- Spout Height: 2 5/16"
- Spout Reach: 6 3/8"
- 4" centerset installation
- Lever metal handle
- Ceramic disc cartridge
- With 50/50 pop-up

SKU	Flow Rate	Color/Finish
PFWSC30165CP	0.5 gpm	Chrome
PFWSC3016CP	1.2 gpm	Chrome
PFWSC3016BN	1.2 gpm	Brushed Nickel
PFWSC3016ORB	1.2 gpm	Oil Rubbed Bronze

Single Handle Lavatory Faucets



- Spout Height: 2 5/16"
- Spout Reach: 6 1/2"
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handle
- Ceramic disc cartridge
- 30" flexible nylon supply lines
- Color/Finish: Chrome

SKU	Type
PFWSC4744SCP	Less Pop-up
PFWSC4746SCP	With Pop-up

Single Handle Lavatory Faucets



- Spout Height: 2 5/16"
- Spout Reach: 6 1/2"
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handle
- Ceramic disc cartridge
- Brass pop-up

SKU	Color/Finish
PFWSC4746BN	Brushed Nickel
PFWSC4746CP	Chrome

Single Handle Lavatory Faucets



- Spout Height: 2 1/4"
- Spout Reach: 4 5/8"
- 4" centerset installation
- Lever handle
- Ceramic cartridge with temperature limiting device
- One piece cast brass body
- Less pop-up
- Color/Finish: Chrome

SKU	Flow Rate
PFX3145L	0.5 gpm
PFX314L	1.5 gpm

Single Handle Lavatory Faucets



- Spout Height: 2 3/16"
- Spout Reach: 6 7/8"
- 1 or 3 hole installation (optional deck plate included)
- Flow Rate: 1.2 gpm
- Metal lever handle
- Ceramic disc cartridge
- With brass pop-up

SKU	Color/Finish
PFWSC6850BN	Brushed Nickel
PFWSC6850CP	Chrome

Two Handle Lavatory Faucets



- Spout Height: 3 1/16"
- Spout Reach: 5 5/8"
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Acrylic handles
- Ceramic disc cartridges
- Color/Finish: Chrome

SKU	Type
PFWSC1040ACP	With Plastic Pop-up
PFWSC1040CP	With Metal Pop-up

Single Handle Lavatory Faucets



- Spout Height: 7 3/16"
- Spout Reach: 5"
- 1 hole installation
- Flow Rate: 1.2 gpm
- Metal lever handle
- Ceramic disc cartridge

SKU	Color/Finish
PFWSC8851BN	Brushed Nickel
PFWSC8851CP	Chrome

Two Handle Lavatory Faucets



- Spout Height: 2 13/16"
- Spout Reach: 3 3/4"
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- Color/Finish: Chrome

SKU	Type
PFWSC1140CP	With Pop-up
PFWSC1140LCP	Less Pop-up

Two Handle Lavatory Faucets



- Spout Height: 3 1/4"
- Spout Reach: 5 3/4"
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handles
- Stainless disc cartridges

SKU	Type	Color/Finish
PFWSC1240ABN	Quick Connect ABS Pop-up	Brushed Nickel
PFWSC1240ACP	Quick Connect ABS Pop-up	Chrome
PFWSC1240BN	Metal Pop-up	Brushed Nickel
PFWSC1240CP	Metal Pop-up	Chrome

Two Handle Lavatory Faucets



- Spout Height: 5 7/8"
- Spout Reach: 7 5/16"
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC4840BN	Brushed Nickel
PFWSC4840CP	Chrome
PFWSC4840ORB	Oil Rubbed Bronze

Two Handle Lavatory Faucets



- 4" centerset installation
- Blade handles
- Ceramic disc cartridges
- Color/Finish: Chrome

SKU	Type	Flow Rate
PFWSC13405GCP	With Grid Drain	0.5 gpm
PFWSC13405LCP	Less Pop-up	0.5 gpm
PFWSC1340GCP	With Grid Drain	1.5 gpm
PFWSC1340LCP	Less Pop-up	1.5 gpm

Two Handle Lavatory Faucets



- Spout Height: 3 1/2"
- Spout Reach: 7"
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC5240BN	Brushed Nickel
PFWSC5240CP	Chrome
PFWSC5240ORB	Oil Rubbed Bronze

Two Handle Lavatory Faucets



- Spout Height: 8 1/8"
- Spout Reach: 6 7/8"
- Flow Rate: 1.2 gpm
- Lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC2840BN	Brushed Nickel
PFWSC2840CP	Chrome
PFWSC2840ORB	Oil Rubbed Bronze

Two Handle Lavatory Faucets



- Spout Height: 3 7/8"
- Spout Reach: 6 5/8"
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC6840BN	Brushed Nickel
PFWSC6840CP	Chrome

Two Handle Lavatory Faucets



- Spout Height: 1 5/8"
- Spout Reach: 4"
- 4" centerset installation
- Wrist blade handles
- Color-indexed caps on handles
- Ceramic disc cartridges
- Color/Finish: Chrome

SKU	Flow Rate
PFX3045	0.5 gpm
PFX304	1.5 gpm

Two Handle Lavatory Faucets



- Spout Height: 12 1/4"
- Spout Reach: 5 1/2"
- 8" centerset installation
- Wrist blade handles
- Color-indexed caps on handles
- Ceramic disc cartridges
- Color/Finish: Chrome

SKU	Flow Rate
PFX3085	0.5 gpm
PFX308	1.5 gpm

Widespread Lavatory Faucets



- Spout Height: 8"
- Spout Reach: 6 1/2"
- 8" centerset installation
- Flow Rate: 1.2 gpm
- Lever handles
- With brass pop-up
- Ceramic disc cartridges

SKU	Color/Finish
PFWSC2860BN	Brushed Nickel
PFWSC2860CP	Chrome
PFWSC2860ORB	Oil Rubbed Bronze

Widespread Lavatory Faucets



- Spout Height: 5 13/16"
- Spout Reach: 7 3/16"
- 8" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC4860BN	Brushed Nickel
PFWSC4860CP	Chrome
PFWSC4860ORB	Oil Rubbed Bronze

Widespread Lavatory Faucets



- Spout Height: 5 1/8"
- Spout Reach: 6 7/8"
- 8" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC5260BN	Brushed Nickel
PFWSC5260CP	Chrome
PFWSC5260ORB	Oil Rubbed Bronze

Widespread Lavatory Faucets



- Spout Height: 6 3/16"
- Spout Reach: 6 1/4"
- 8" centerset installation
- Flow Rate: 1.2 gpm
- Metal lever handles
- Ceramic disc cartridges
- With brass pop-up

SKU	Color/Finish
PFWSC6860BN	Brushed Nickel
PFWSC6860CP	Chrome

Pressure Balancing Valve Trim



PROFLO

- Trim only
- Handle Type: Lever
- Metal construction
- **Required accessories:**
  Rough-in valve: PF3001 or PF3001LS

SKU	Color/Finish
PF5200BN	Brushed Nickel
PF5200CP	Chrome
PF5200ORB	Oil Rubbed Bronze

Single Handle Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- Brass shower arm and flange
- **Required accessories:**
  Pressure balancing valve: PF3001

SKU	Color/Finish
PF2820BN	Brushed Nickel
PF2820CP	Chrome
PF2820ORB	Oil Rubbed Bronze

Single Handle Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Brass shower arm and flange
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF5220BN	Brushed Nickel
PF5220CP	Chrome
PF5220ORB	Oil Rubbed Bronze

Single Handle Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 1.75 gpm
- Handle Type: Lever
- Brass shower arm and flange
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF7610SBN	Brushed Nickel
PF7610SCP	Chrome

Single Handle Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Brass shower arm and flange
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF6820BN	Brushed Nickel
PF6820CP	Chrome

Single Handle Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF4820BN	Brushed Nickel
PF4820CP	Chrome
PF4820ORB	Oil Rubbed Bronze

Single Handle Shower Faucets Trim





PROFLO

- Trim only
- Flow Rate: 1.75 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF8820BN	Brushed Nickel
PF8820CP	Chrome

Two Handle Shower Faucets






PROFLO

- Flow Rate: 2.0 gpm
- Handle Type: Acrylic
- Showerhead, arm and flange
- Washerless non-pressure balance valve
- Color/Finish: Chrome

SKU
PF1020CP



Single Handle Tub/Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- Brass shower arms and flange
- Slip-fit diverter tub spout
- **Required accessories:**
  Rough-in valve: PF3001

SKU	Color/Finish
PF2830BN	Brushed Nickel
PF2830CP	Chrome
PF2830ORB	Oil Rubbed Bronze

Single Handle Tub/Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Brass shower arm and flange
- Slip-fit diverter tub spout
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF6830BN	Brushed Nickel
PF6830CP	Chrome

Single Handle Tub/Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- Slip-fit diverter tub spout
- **Optional accessories:**
  Extension kit: ACF3001EXT
- **Required accessories:**
  Rough-in valve: PF3001 or PF3001LS

SKU	Color/Finish
PF4830BN	Brushed Nickel
PF4830CP	Chrome
PF4830ORB	Oil Rubbed Bronze

Single Handle Tub/Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 1.75 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- Slip-fit diverter tub spout
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF7611SBN	Brushed Nickel
PF7611SCP	Chrome

Single Handle Tub/Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 2.0 gpm
- Handle Type: Lever
- Brass shower arm and flange
- Slip-fit diverter tub spout
- **Required accessories:**
  Pressure balancing valve: PF3001 or PF3001LS

SKU	Color/Finish
PF5230BN	Brushed Nickel
PF5230CP	Chrome
PF5230ORB	Oil Rubbed Bronze

Single Handle Tub/Shower Faucets Trim



PROFLO

- Trim only
- Flow Rate: 1.75 gpm
- Handle Type: Lever
- Showerhead with easy clean rubber nozzles
- Slip-fit diverter tub spout
- **Required accessories:**
  Rough-in valve: PF3001 or PF3001LS

SKU	Color/Finish
PF8830BN	Brushed Nickel
PF8830CP	Chrome

Two Handle Tub/Shower Faucets



PROFLO

- Flow Rate: 2.0 gpm
- Handle Type: Acrylic
- Showerhead, arm and flange
- Washerless non-pressure balance valve
- Tub spout with pull-up diverter
- Color/Finish: Chrome

SKU
PF1030CP

Three Handle Tub/Shower Faucets



PROFLO

- Flow Rate: 2.0 gpm
- Handle Type: Acrylic
- Showerhead, arm and flange
- Washerless non-pressure balance valve
- Color/Finish: Chrome

SKU
PF1033CP

Showerheads

SKU	Function	Easy Clean Nozzles	Flow Rate	Color/Finish
PFDCSHK	Adjustable		2.0 gpm	Chrome
PF110100	Single		2.0 gpm	Chrome
PFMSH	Single		2.0 gpm	Chrome
PFSHD15	Single	✓	1.5 gpm	Chrome
PF05316	Single	✓	2.0 gpm	Chrome, Brushed Nickel
PF05324	Single	✓	2.0 gpm	Chrome, Brushed Nickel
MB501	Single		2.0 gpm	Chrome, Brushed Nickel, Oil Rubbed Bronze
PF05509CP	Three	✓	1.5 gpm	Chrome
MB502	Three	✓	2.0 gpm	Chrome, Brushed Nickel, Oil Rubbed Bronze
MB503	Three		2.0 gpm	Chrome, Brushed Nickel, Oil Rubbed Bronze
PF5360	Five	✓	2.0 gpm	Chrome, Brushed Nickel

Showerheads



MONOGRAM BRASS™

- Single-Function Showerhead
- Connection: 1/2" NPT brass ball joint
- Flow Rate: 2.0 gpm
- Shower arm and flange sold separately

SKU	Color/Finish
MB501BN	Brushed Nickel
MB501CP	Chrome
MB501ORB	Oil Rubbed Bronze

Showerheads



MONOGRAM BRASS™

- Three-Function Showerhead
- Connection: 1/2" NPT brass ball joint
- Flow Rate: 2.0 gpm
- Shower arm and flange sold separately

SKU	Color/Finish
MB502BN	Brushed Nickel
MB502CP	Chrome
MB502ORB	Oil Rubbed Bronze

Showerheads



MONOGRAM BRASS™

- Three-Function Showerhead
- Connection: 1/2" NPSM brass ball joint
- Flow Rate: 2.0 gpm
- Shower arm and flange sold separately

SKU	Color/Finish
MB503BN	Brushed Nickel
MB503CP	Chrome
MB503ORB	Oil Rubbed Bronze

Showerheads



PROFLO

- MIXET®
- Diameter: 3 1/4"
- Connection: 1/2" NPT
- Flow Rate: 2.5 gpm
- Color/Finish: Black Chrome

SKU
PFMSH

Showerheads



PROFLO

- Single-Function Showerhead: Full spray
- Connection: 1/2" NPT
- Flow Rate: 2.0 gpm

SKU	Color/Finish
PF05316BN	Brushed Nickel
PF05316CP	Chrome

Showerheads



PROFLO

- Single-Function Showerhead: Full spray
- Connection: 1/2" NPT
- Flow Rate: 2.0 gpm

SKU	Color/Finish
PF05324BN	Brushed Nickel
PF05324CP	Chrome

Showerheads



PROFLO

- Five-Function Showerhead: Full spray, massage, bubble, spray+bubble and spray+massage
- Connection: 1/2" NPT
- Flow Rate: 2.0 gpm

SKU	Color/Finish
PF5360BN	Brushed Nickel
PF5360CP	Chrome

Showerheads



PROFLO

- Three-Function Showerhead: Full spray, massage and spray+massage
- Connection: 1/2" NPT
- Flow Rate: 1.5 gpm
- Color/Finish: Chrome

SKU
PF05509CP

Showerheads



PROFLO

- Single-Function Showerhead
- Flow Rate: 2.0 gpm
- Color/Finish: Chrome

SKU
PF110100

Showerheads



PROFLO

- Diameter: 2"
- Connection: 1/2" FIP
- Flow Rate: 2.0 gpm
- Adjustable spray
- Die cast construction
- Color/Finish: Chrome

SKU
PFDCSHK

Showerheads



PROFLO

- Single-Function Showerhead: Full spray
- Connection: 1/2" NPT
- Flow Rate: 1.5 gpm
- Easy clean rubber nozzles

SKU	Color/Finish
PFSHD15BN	Brushed Nickel
PFSHD15CP	Chrome
PFSHD15RB	Oil Rubbed Bronze

Shower Arms



MONOGRAM BRASS™

- Length: 6"
- Connection: 1/2" NPT
- Includes 1/2" IPS sure grip flange
- Brass construction

SKU	Color/Finish
MB551BN	Brushed Nickel
MB551ORB	Oil Rubbed Bronze
MB551PB	Polished Brass
MB551PN	Polished Nickel

Shower Arms



MONOGRAM BRASS™

- Length: 8"
- Height: 6"
- Connection: 1/2" NPT
- Includes 1/2" IPS sure grip flange
- Brass construction

SKU	Color/Finish
MB552BN	Brushed Nickel
MB552CP	Chrome
MB552ORB	Oil Rubbed Bronze

Shower Arms



MONOGRAM BRASS™

- Length: 7 1/2"
- Height: 11"
- Connection: 1/2" NPT
- Includes 1/2" IPS sure grip flange
- Brass construction

SKU	Color/Finish
MB553BN	Brushed Nickel
MB553CP	Chrome
MB553ORB	Oil Rubbed Bronze

Shower Arms



MONOGRAM BRASS™

- Adjustable 10" extension hi-low shower
- Allows 20" height and angle adjustment
- Connection: 1/2" NPT
- Brass construction
- Color/Finish: Chrome

SKU
MB554CP

Shower Arms



PROFLO

- Brass shower arms with stainless steel flange

SKU	Color/Finish	Size
PFS40	Chrome	1/2" x 6"
PFS41	Chrome	1/2" x 8"
PFPB41A	Polished Brass	1/2" x 8"

Tub Spouts



MONOGRAM BRASS™

- Diverter
- Connection: 1/2" NPT female
- Zinc construction

SKU	Color/Finish
MB562BN	Brushed Nickel
MB562ORB	Oil Rubbed Bronze

Tub Spouts



MONOGRAM BRASS™

- Diverter
- Connection: 1/2" NPT female
- Zinc construction

SKU	Color/Finish
MB563BN	Brushed Nickel
MB563ORB	Oil Rubbed Bronze
MB563PB	Polished Brass

Tub Spouts



MONOGRAM BRASS™

- Diverter
- Connection: 1/2" or 3/4" NPT female
- For use with handheld personal showers
- Zinc construction
- Color/Finish: Chrome

SKU
MB564CP

Tub Spouts



PROFLO

- Diverter
- Die cast construction
- Color/Finish: Chrome

SKU	Connection
PF1095	1/2" FIP
PF1096	1/2" Slip

Tub Spouts



PROFLO

- Diverter
- With 3/4" x 1/2" face bushing

SKU	Material	Color/Finish
PF1091	Die Cast	Polished Brass
PF1093	Die Cast	Chrome
PF1097	Brass	Chrome

Tub Spouts



PROFLO

- Diverter
- Connection: 1/2" CTS slip-fit
- Spout Reach: 7"
- Metal construction
- For applications where an extra long spout is required

SKU	Color/Finish
PFTS32BN	Brushed Nickel
PFTS32CP	Chrome

Tub Spouts



MONOGRAM BRASS™

- Non-diverter
- Connection: 1/2" NPT female
- Zinc construction

SKU	Color/Finish
MB561BN	Brushed Nickel
MB561ORB	Oil Rubbed Bronze

Tub Spouts



PROFLO

- Non-diverter
- Connection: 1/2" FIP
- Die cast construction
- Color/Finish: Chrome

SKU
PF1092

Tub Spouts



- Non-diverter
- Connection: 1/2" CTS slip-fit
- Spout Reach: 7"
- Metal construction
- For applications where an extra long spout is required

SKU	Color/Finish
PFTS33BN	Brushed Nickel
PFTS33CP	Chrome

Self-Closing Shower Valves



- 1/2"
- With pull chain
- Self-closing
- Brass construction
- Color/Finish: Chrome

SKU
PF20015

Tub Spouts

SKU	Type	Mount	Material	Length	Color/Finish
MB562	Diverter	1/2" CTS Slip Fit	Zinc	5"	Brushed Nickel, Oil Rubbed Bronze
PF1096	Diverter	1/2" CTS Slip Fit	Die Cast	5"	Chrome
PFTS32	Diverter	1/2" CTS Slip Fit	Die Cast	7"	Chrome, Brushed Nickel, Oil Rubbed Bronze
PF1095	Diverter	1/2" IPS	Die Cast	5"	Chrome
MB563	Diverter	1/2" IPS	Zinc	5"	Brushed Nickel, Oil Rubbed Bronze, Polished Brass
PF1097	Diverter	1/2" or 3/4" IPS	Brass	5"	Chrome
PF1091	Diverter	1/2" or 3/4" IPS	Die Cast	5"	Polished Brass
PF1093	Diverter	1/2" or 3/4" IPS	Die Cast	5"	Chrome
MB564CP	Diverter	1/2" or 3/4" IPS	Zinc	5"	Chrome
PFTS33	Non-Diverter	1/2" CTS Slip Fit	Die Cast	7"	Chrome, Brushed Nickel, Oil Rubbed Bronze
PF1092	Non-Diverter	1/2" IPS	Die Cast	5"	Chrome
MB561	Non-Diverter	1/2" IPS	Zinc	5"	Brushed Nickel, Oil Rubbed Bronze

Tub & Shower Rough-in Valves



- Pressure balance
- Ceramic cartridge
- Back-to-back capability
- Temperature limiting device
- Plaster guard included
- Finished sleeve cover and cap are packaged with trim
- **Optional accessories:**
  Air test cap: ACF3001AIR
  Plaster guard: ACF3001GRD
  Replacement cartridge: ACF3001LSCRT
  Extension kit: ACF3001EXTCP, ACF3001EXTBN or ACF3001EXTORB

SKU	Type
PF3001CLS	CPVC
PF3001FLS	Female IPS
PF3001LS	IPS and Sweat
PF3001PLS	PEX Crimp

Tub & Shower Rough-in Valves



- Pressure balance
- Ceramic cartridge
- Back-to-back capability
- Temperature limiting device
- Plaster guard included
- Finished sleeve cover and cap are packaged with trim
- Integral stops
- **Optional accessories:**
  Air test cap: ACF3001AIR
  Plaster guard: ACF3001GRD
  Replacement cartridge: ACF3001LSCRT
  Extension kit: ACF3001EXTCP, ACF3001EXTBN or ACF3001EXTORB

SKU	Type
PF3001C	CPVC
PF3001F	Female IPS
PF3001	IPS & Sweat
PF3001P	PEX Crimp

Handshowers



- Three-function handshower
- Flow Rate: 2.0 gpm
- Factory installed backflow prevention check valve

SKU	Color/Finish
MB512BN	Brushed Nickel
MB512CP	Chrome
MB512ORB	Oil Rubbed Bronze

Handshowers



- Single-function handshower
- Flow Rate: 1.75 gpm
- Connection: 1/2" NPSM
- Easy clean spray nozzles
- Material: ABS
- Color/Finish: White

SKU
PF05417WH

Handshowers



- Five-function handshower
- Flow Rate: 2.0 gpm
- Factory installed backflow prevention check valve

SKU	Color/Finish
MB511BN	Brushed Nickel
MB511CP	Chrome
MB511ORB	Oil Rubbed Bronze

Handshowers



- Single-function handshower
- Flow Rate: 1.75 gpm
- Connection: 1/2" NPSM
- Easy clean spray nozzles
- Push button pause control
- Material: ABS
- Color/Finish: Chrome

SKU
PF05786CP

Handshowers



- Five-function handshower
- Flow Rate: 1.75 gpm
- Connection: 1/2" NPSM
- Easy clean spray nozzles
- Material: ABS

SKU	Color/Finish
PF05464BN	Brushed Nickel
PF05464CP	Chrome

Handshower Kits



- Five-function handshower
- Flow Rate: 1.75 gpm
- Connection: 1/2" NPT
- Easy clean spray nozzles
- Includes handshower, hose and shower arms mount
- Material: Metal and ABS construction

SKU	Color/Finish
PF05844BN	Brushed Nickel
PF05844CP	Chrome

Handshower Kits



- Single-function handshower
- Flow Rate: 1.75 gpm
- 60" vinyl hose
- Easy clean nozzles
- Set includes mounting hardware, hand spray and hose
- Color/Finish: White

SKU
PF14110WH

Handshower Kits



- Three-function handshower
- Flow Rate: 1.75 gpm
- Connection: 1/2"
- Set includes handshower, hose and shower arms mount
- Color/Finish: Chrome

SKU
PF05615CP

Handshowers

SKU	Type	Function	Easy Clean	Flow Rate	Color/Finish
PF05786CP	Handshower	Single - On/Off	✓	1.75 gpm	Chrome
PF05417WH	Handshower	Single	✓	1.75 gpm	White
MB512	Handshower	Three	✓	2.0 gpm	Chrome, Brushed Nickel, Oil Rubbed Bronze
PF05464	Handshower	Five	✓	1.75 gpm	Chrome, Brushed Nickel
MB511	Handshower	Five	✓	2.0 gpm	Chrome, Brushed Nickel, Oil Rubbed Bronze
PF14110WH	Kit	Single	✓	1.75 gpm	White
PF05615CP	Kit	Three	✓	1.75 gpm	Chrome
PF05844	Kit	Five	✓	1.75 gpm	Chrome, Brushed Nickel

Shower Hoses



MONOGRAM BRASS™

- Length: 60"
- Connection: 1/2" FPT
- Material: Stainless Steel

SKU	Color/Finish
MB531BN	Brushed Nickel
MB531CP	Chrome
MB531ORB	Oil Rubbed Bronze

Shower Hoses



PROFLO

- Hose stretches from 60" to 82" for ease of use
- Connection: 1/2" NPSM
- Material: Metal

SKU	Color/Finish
PF05289BN	Brushed Nickel
PF05289CP	Chrome

Mounting Accessories



MONOGRAM BRASS™

- Wall supply elbow
- Connection: 1/2" NPT
- Brass construction

SKU	Color/Finish
MB542BN	Brushed Nickel
MB542CP	Chrome
MB542ORB	Oil Rubbed Bronze

Mounting Accessories



MONOGRAM BRASS™

- Shower arm bracket
- Adjustable angle
- Installs on shower arm for handshower mounting
- ABS body

SKU	Color/Finish
MB543BN	Brushed Nickel
MB543CP	Chrome
MB543ORB	Oil Rubbed Bronze

Mounting Accessories



MONOGRAM BRASS™

- Adjustable wall mount bracket
- ABS body

SKU	Color/Finish
MB544BN	Brushed Nickel
MB544CP	Chrome
MB544ORB	Oil Rubbed Bronze

Mounting Accessories



PROFLO

- Holds handshower in a fixed wall mount position
- Material: ABS

SKU	Color/Finish
PF05688BN	Brushed Nickel
PF05688CP	Chrome

Mounting Accessories



PROFLO

- Connection: 1/2" NPT
- Adjustable mount
- Material: Brass and ABS

SKU	Color/Finish
PF05738BN	Brushed Nickel
PF05738CP	Chrome

Mounting Accessories



PROFLO

- Wall mounted
- Connection: 1/2"
- Supply flow from an in-wall diverter to a handshower
- Material: Brass

SKU	Color/Finish
PF05143BN	Brushed Nickel
PF05143CP	Chrome

Shower Switches



PROFLO

- Shower on/off switch
- Color/Finish: Chrome

SKU
PF05516CP

Shower Arm Diverters



MONOGRAM BRASS™

- Shower arm diverter for handshower
- Connection: 1/2" FIP inlet x 1/2" MIP outlets
- Brass construction

SKU	Color/Finish
MB541BN	Brushed Nickel
MB541CP	Chrome
MB541ORB	Oil Rubbed Bronze

Shower Arm Diverters



PROFLO

- Connection: 1/2" NPT
- Push button in line shower diverter
- Diverts flow to showerhead or handshower
- Brass construction

SKU	Color/Finish
PF05128BN	Brushed Nickel
PF05128CP	Chrome

Vacuum Breakers



PROFLO

- Connection: 1/2" NPSM
- Prevents backflow in handshower systems
- Material: Brass and ABS

SKU	Color/Finish
PF05036BN	Brushed Nickel
PF05036CP	Chrome

Slide Bars



MONOGRAM BRASS™

- Length: 27"
- Adjustable angle for handshower mount
- Metal bars and mounting posts

SKU	Color/Finish
MB521BN	Brushed Nickel
MB521CP	Chrome
MB521ORB	Oil Rubbed Bronze

Slide Bars



MONOGRAM BRASS™

- Length: 27"
- Adjustable angle for handshower mount
- Zinc slider and lateral holder

SKU	Color/Finish
MB522BN	Brushed Nickel
MB522CP	Chrome

Slide Bars



PROFLO

- Length: 30"
- Includes friction mount holder
- Allows handshower to be used at varying heights

SKU	Color/Finish
PF05130BN	Brushed Nickel
PF05130CP	Chrome

Slide Bars



PROFLO

- Length: 24"
- Allows handshower to be used at varying heights

SKU	Color/Finish
PF14BSBN	Brushed Nickel
PF14BSCP	Chrome

Roman Tub Faucets



- 6" - 12" installation
- Flow Rate: 7.5 gpm
- Metal lever handles
- Ceramic disc cartridges
- Complete rough-in and trim kit included

SKU	Color/Finish
PF5270BN	Brushed Nickel
PF5270CP	Chrome
PF5270ORB	Oil Rubbed Bronze

Roman Tub Faucets Trim



- Trim only
- 8" - 16" installation
- Metal lever handles
- **Required accessories:**
  Rough-in valve: PF674163

SKU	Color/Finish
PF4870BN	Brushed Nickel
PF4870CP	Chrome
PF4870ORB	Oil Rubbed Bronze

Roman Tub Faucets Trim



- Trim only
- 8" - 16" installation
- Metal lever handles
- **Required accessories:**
  Rough-in valve: PF674163

SKU	Color/Finish
PF6870BN	Brushed Nickel
PF6870CP	Chrome

Roman Tub Faucets Trim



- Trim only
- 8" - 16" installation
- Flow Rate: 7.5 gpm
- Metal lever handles
- Ceramic disc cartridges
- **Required accessories:**
  Rough-in valve: PF674163

SKU	Color/Finish
PF2870BN	Brushed Nickel
PF2870CP	Chrome
PF2870ORB	Oil Rubbed Bronze

Aerators

SKU	Thread Type	Flow Rate	Package Quantity	Color/Finish
PFX113175	Dual	1.5 gpm	6	Chrome
PFX113174	Dual	2.2 gpm	6	Chrome
PFX5061C	Dual	2.0 gpm	Single Pack	Chrome
PFX277	Male	2.0 gpm	Single Pack	Chrome
PFX143128PK	Female	2.0 gpm	Single Pack	Chrome

Aerators



- For PROFLO kitchen and lavatory faucets
- 55/64" 27 TPI female connection
- Flow Rate: 2.0 gpm
- Anti-clogging dome screen filters sediment and particles
- Color/Finish: Chrome

SKU
PFX143128PK

Aerators



- Male connection
- Flow Rate: 2.0 gpm
- Standard faucet aerator size
- Color/Finish: Chrome

SKU
PFX277

Aerators



- Dual connection
- Flow Rate: 2.0 gpm
- Standard faucet aerator size
- Color/Finish: Chrome

SKU
PFX5061C

Aerators



- Patented three-screen slotted design provides a splash-free stream, well aerated and soft touch
- Standard flow
- 15/16" MIP x 55/64" FIP
- Package Quantity: 6

SKU	Flow Rate
PFX113175	1.5 gpm
PFX113174	2.2 gpm

Cartridges



- Pressure balance tub and shower valve
- Ceramic cartridge

SKU	Type
ACF3001CRT	With Stops
ACF3001LSCRT	Less Stops

Cartridges



- Ceramic cartridge
- For PROFLO single handle lavatory and kitchen faucets

SKU
PF141555PK

Cartridges



- For tub/shower faucets
- Ceramic disc
- Fits PF9091B, PF9293B, PFLL51SACP, PFLL51SAPB, PFLL51ACP, PFLL51APB, PFLL51SMCP, PFLL51SMPB, PFLL51MCP and PFLL51MPB

SKU
PF141558PK

Cartridges



- For two-handle decorative lever kitchen gooseneck faucets
- Less spray

SKU
PFX141199PK

Diverter Stems



- With gasket
- For PFLL43A

SKU
PF141566PK

Faucet Balls



- Stem assembly for metal lever handle
- Fits: PFLL1001M, PFLL1011M, PFLL2011M, PFLL2001M, PFLL2021M, PF2011M, PF2001M, PF1011M, PF1001M, PFLL41M, PFLL41SM, PFLL1011WFM, PFLL2011WFM, PFLL1011M30

SKU
PFX141137PK

Stems



- For PF1118 service faucet

SKU
PF141554PK

Knob Handles



- For use with PF7651CP and PF7650CP
- Handle Material: Acrylic
- Color/Finish: Clear

SKU
PF141548PK

Plug Buttons



- Fits: PFLL1012A, PFLL1022A, PFLL2012A, PFLL2002A, PFLL6002A, PF7002A, PF333A, PF2002A, PF2012A, PFLL2112A, PFLL2122A, PF1012A, PFLL1112A, PFLL42A, PFLL1012APB, PFLL42SA, PFLL43A and PFLL53A

SKU
PF141344PK

Plug Buttons



- Fits: PF80ATSTRM, PF80ASTRM and PF141548PK
- For use with single handle tub and shower faucet
- Hot and cold indicator
- Material: Acrylic

SKU
PF141570PK

Double Robe Hooks



- Zinc die-cast posts
- Metal bars and rings

SKU	Color/Finish
PF6741BN	Brushed Nickel
PF6741CP	Chrome
PF6741RB	Oil Rubbed Bronze

Double Robe Hooks



- Concealed screw
- Color/Finish: Chrome

SKU
PFLLDRHCP

Robe Hooks



- Zinc alloy die-cast posts
- Metal bars and rings
- Mounting hardware included

SKU	Color/Finish
PF2841BN	Brushed Nickel
PF2841CP	Chrome
PF2841ORB	Oil Rubbed Bronze

Shower Rod Holders



- Adjustable design
- Rod sold separately
- Color/Finish: Chrome

SKU	Material
PFC71F	Die cast
PFC71FB	Plastic

Shower Rods



- 5' curved shower rod
- Made of 22 gauge 445 stainless steel
- Fits all standard shower curtains
- Heavy duty flange kit includes installation hardware

SKU	Color/Finish
PFCSRH60BN	Brushed Nickel
PFCSRH60CP	Chrome

Shower Rods



- Made of aluminum alloy to prevent rusting
- Fits all standard shower curtains
- Flanges not included
- Color/Finish: Chrome
- **Required accessories:**
  Shower rod flange: PFSRFCP, PFC71F or PFC71FB

SKU	Length
PFSCR60	5'
PFSCR72	6'

Shower Rod Flange Kits



- Rod sold separately
- Color/Finish: Chrome

SKU
PFSRFCP

Soap Dishes



- Requires a recess wall bracket for installation (not included)
- Removable soap dish
- Color/Finish: Chrome

SKU
PFLLRSHCP

Soap Dishes



- Concealed screw
- Color/Finish: Chrome

SKU
PFLLSDCP

Recessed Toilet Tissue Holders



- Requires a recess wall bracket for installation (not included)
- With white plastic roller
- Color/Finish: Chrome

SKU
PFLLRTPHCP

Toilet Tissue Holders



- Width: 8"
- Zinc alloy die-cast posts
- Metal bars and rings
- Mounting hardware included

SKU	Color/Finish
PF2831BN	Brushed Nickel
PF2831CP	Chrome
PF2831ORB	Oil Rubbed Bronze

Toilet Tissue Holders



- Zinc die-cast posts
- Metal bars and rings

SKU	Color/Finish
PF6731BN	Brushed Nickel
PF6731CP	Chrome
PF6731RB	Oil Rubbed Bronze

Toilet Tissue Holders



- Concealed screw
- With white plastic rollers
- Color/Finish: Chrome

SKU
PFLLTPCP

Towel Bars



- Zinc alloy die-cast posts
- Metal bars and rings
- Mounting hardware included

SKU	Length	Color/Finish
PF2800BN	18"	Brushed Nickel
PF2800CP	18"	Chrome
PF2800ORB	18"	Oil Rubbed Bronze
PF2890BN	24"	Brushed Nickel
PF2890CP	24"	Chrome
PF2890ORB	24"	Oil Rubbed Bronze

Towel Bars



- Zinc die-cast posts
- Metal bars and rings

SKU	Length	Color/Finish
PF6700BN	18"	Brushed Nickel
PF6700CP	18"	Chrome
PF6700RB	18"	Oil Rubbed Bronze
PF6770BN	24"	Brushed Nickel
PF6770CP	24"	Chrome
PF6770RB	24"	Oil Rubbed Bronze

Towel Bars



- Concealed screw
- Aluminum bar and zinc alloy die-cast posts
- Color/Finish: Chrome

SKU	Length
PFLL18CP	18"
PFLL24CP	24"

Towel Rings



- Zinc alloy die-cast posts
- Mounting hardware included
- Metal bars and rings

SKU	Color/Finish
PF2851BN	Brushed Nickel
PF2851CP	Chrome
PF2851ORB	Oil Rubbed Bronze

Towel Rings



- Zinc die-cast posts
- Metal bars and rings

SKU	Color/Finish
PF6751BN	Brushed Nickel
PF6751CP	Chrome
PF6751RB	Oil Rubbed Bronze

Towel Rings



- Concealed screw
- Color/Finish: Chrome

SKU
PFLLTRCCP



For additional bath and kitchen faucets, fixtures and sinks,
see our Mirabelle brand products at MirabelleProducts.com.

*Mirabelle Eastland Collection

Mirabelle®



Kitchen & Bar Faucets

What can we help you find?

Pull-Down/Pull-Out Kitchen Faucets 39
Single Handle Kitchen Faucets 40
Two Handle Kitchen Faucets 41
Two Handle Bar Faucets 41-42
Kitchen & Bar Faucet Accessories. 43-44

Pull-Down/Pull-Out Kitchen Faucets



PROFLO

- Spout Height: 7 7/8"
- Spout Reach: 9 1/4"
- Faucet Installation: 1 or 3 hole
- Flow Rate: 1.8 gpm
- Handle Type: Metal Lever
- 3-function sprayer with stream, full spray & pause with 360° swivel
- Ceramic cartridge
- Non-kink nylon hose
- Optional deck plate included

SKU	Color/Finish
PFXC7011BN	Brushed Nickel
PFXC7011CP	Chrome

Pull-Down/Pull-Out Kitchen Faucets



PROFLO

- Spout Height: 5 5/16"
- Spout Reach: 8 3/4"
- Faucet Installation: 1 or 3 hole
- Flow Rate: 1.5 gpm
- Handle Type: Metal Lever
- With 2-function sprayer
- Ceramic disc cartridge
- Optional deck plate included

SKU	Color/Finish
PFXC5150BN	Brushed Nickel
PFXC5150CP	Chrome
PFXC5150ORB	Oil Rubbed Bronze

Pull-Down/Pull-Out Kitchen Faucets



PROFLO

- Spout Height: 8 5/8"
- Spout Reach: 8 1/4"
- Faucet Installation: 1 or 3 hole
- Flow Rate: 1.8 gpm
- Handle Type: Metal Lever
- 2-function spray head with pause
- Ceramic cartridge
- Optional deck plate included

SKU	Color/Finish
PFXC9011BN	Brushed Nickel
PFXC9011CP	Chrome

Pull-Down/Pull-Out Kitchen Faucets



PROFLO

- Spout Height: 4 13/16"
- Spout Reach: 9"
- Faucet Installation: 1 or 3 hole
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- With 2-function sprayer
- Ceramic disc cartridge
- Optional deck plate included

SKU	Color/Finish
PFXC6011BN	Brushed Nickel
PFXC6011CP	Chrome
PFXC6011RB	Oil Rubbed Bronze

Single Handle Kitchen Faucets



- Spout Height: 6 1/4"
- Spout Reach: 8 15/16"
- Faucet Installation: 1 or 3 hole
- Flow Rate: 1.8 gpm
- Handle Type: Lever
- Ceramic cartridge
- Deck plate included

SKU	Type	Color/Finish
PFXC1901BN	Less Spray	Brushed Nickel
PFXC1901CP	Less Spray	Chrome
PFXC1911BN	With Spray	Brushed Nickel
PFXC1911CP	With Spray	Chrome

Single Handle Kitchen Faucets



- Spout Height: 6"
- Spout Reach: 8 1/16"
- Faucet Installation: 3 hole
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- Ceramic cartridge

SKU	Color/Finish
PFXC3101CP	Chrome
PFXC4101BN	Brushed Nickel

Single Handle Kitchen Faucets



- Spout Height: 6"
- Spout Reach: 8"
- Faucet Installation: 4 hole
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- Ceramic cartridge
- Black handspray
- Color/Finish: Chrome

SKU
PFXC3111CP

Single Handle Kitchen Faucets



- Spout Height: 6"
- Spout Reach: 8"
- Faucet Installation: 4 hole
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- Ceramic cartridge
- Color matched handspray

SKU	Color/Finish
PFXC4111BN	Brushed Nickel
PFXC4111CP	Chrome

Single Handle Kitchen Faucets



- Spout Height: 6"
- Spout Reach: 8"
- Faucet Installation: 3 hole
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- Ceramic cartridge
- Black handspray on deck
- Color/Finish: Chrome

SKU
PFXC3121CP

Single Handle Kitchen Faucets



- Spout Height: 6"
- Spout Reach: 8"
- Faucet Installation: 3 hole
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- Ceramic cartridge
- Color matched handspray on deck

SKU	Color/Finish
PFXC4121BN	Brushed Nickel
PFXC4121CP	Chrome

Two Handle Kitchen Faucets



- Spout Height: 5 13/16"
- Spout Reach: 8 13/16"
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Acrylic
- Ceramic cartridge
- Color/Finish: Chrome

SKU	Type
PFXC1080CP	With Spray
PFXC1080LSCP	Less Spray

Two Handle Kitchen Faucets



- Spout Height: 10 5/8"
- Spout Reach: 10 1/16"
- Faucet Installation: 3 or 4 hole
- Flow Rate: 1.8 gpm
- Handle Type: Lever
- Stainless disc cartridges

SKU	Type	Color/Finish
PFXC6880BN	With Spray	Brushed Nickel
PFXC6880CP	With Spray	Chrome
PFXC6880LSBN	Less Spray	Brushed Nickel
PFXC6880LSCP	Less Spray	Chrome

Two Handle Kitchen Faucets



- Spout Height: 5 7/8"
- Spout Reach: 9 5/16"
- 8" centerset installation
- Flow Rate: 1.5 gpm
- Handle Type: Lever
- Ceramic cartridge
- Color/Finish: Chrome

SKU	Type
PFXC1180CP	With Spray
PFXC1180LSCP	Less Spray

Two Handle Kitchen Faucets



- Spout Height: 11 3/8"
- Spout Reach: 5 1/2"
- Spout Type: Gooseneck
- Faucet Center Size: 6"-16"
- Handle Type: Wrist Blade
- Ceramic cartridge
- Color/Finish: Chrome

SKU	Flow Rate
PFXU3085	0.5 gpm
PFXU308	1.5 gpm

Two Handle Kitchen Faucets



- Spout Height: 12 3/4"
- Spout Reach: 7 7/8"
- Flow Rate: 1.8 gpm
- 2 hole wall mount installation
- Handle Type: Lever
- Ceramic cartridges

SKU
PFXC1880CP

Two Handle Bar Faucets



- Spout Height: 9 9/16"
- Spout Reach: 5"
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Handle Type: Lever
- Ceramic cartridge
- Color/Finish: Chrome

SKU
PFWSC1190CP

Two Handle Bar Faucets



- Spout Height: 10"
- Spout Reach: 4"
- 4" centerset installation
- Handle Type: 4" Wrist Blade
- Ceramic cartridge
- Color/Finish: Chrome

SKU	Flow Rate
PFWSC13905CP	0.5 gpm
PFWSC1390CP	1.2 gpm

Two Handle Bar Faucets



- Spout Height: 11 5/8"
- Spout Reach: 5 1/8"
- Spout Type: Gooseneck
- 4" centerset installation
- Flow Rate: 1.2 gpm
- Handle Type: Lever
- Ceramic disc cartridges
- Less pop-up

SKU	Color/Finish
PFWSC6890BN	Brushed Nickel
PFWSC6890CP	Chrome

Two Handle Bar Faucets



- Spout Height: 9 7/8"
- Spout Reach: 3 1/2"
- 4" centerset installation
- Handle Type: Wrist Blade
- Ceramic disc cartridge
- Color/Finish: Chrome

SKU	Flow Rate
PFXB3045	0.5 gpm
PFXB304	1.5 gpm



Kitchen & Bar Sinks
P. 67-70



Water Dispensers



MONOGRAM BRASS™

- For use with filtration units
- Not compatible with reverse osmosis systems
- Brass construction

SKU	Color/Finish
MB111BN	Brushed Nickel
MB111CP	Chrome
MB111ORB	Oil Rubbed Bronze

Faucet Hole Covers



MONOGRAM BRASS™

- Diameter: 2"
- Stainless steel construction

SKU	Color/Finish
MB131BLK	Black
MB131BN	Brushed Nickel
MB131BS	Biscuit
MB131ORB	Oil Rubbed Bronze
MB131SS	Stainless Steel
MB131WH	White

Faucet Hole Covers



PROFLO

- Stem style

SKU	Size	Color/Finish
PFFHC	1 3/4"	Chrome
PFFHCP	2"	Chrome
PFFHCWH	2"	White

Faucet Hole Covers



PROFLO

- Diameter: 1 1/2"
- Snap-in-style
- Color/Finish: Stainless Steel

SKU
PFSHSC

Hose & Spray Kits



PROFLO

- Plastic spray head with 48" hose and universal adapter

SKU	Color/Finish
PF310400	Black
PF310400WH	White

Soap/Lotion Dispensers



MONOGRAM BRASS™

- Maximum Deck Thickness: 2"
- Capacity: 12 fl oz
- Plastic bottle and tube
- Brass head, nut and flange

SKU	Color/Finish
MB121BN	Brushed Nickel
MB121CP	Chrome
MB121ORB	Oil Rubbed Bronze
MB121PN	Polished Nickel

Spray Heads



PROFLO

- Standard replacement spray head
- Plastic construction

SKU	Color/Finish
PF310410	Black
PF310410WH	White

Spray Hose & Guides



PROFLO

- For use with kitchen faucets
- Product includes Chrome hose (not shown)

SKU
PF140330PK

Spray Hose Guides



PROFLO

- Standard replacement spray hose guide
- Plastic construction
- Color/Finish: Black

SKU
PF310440

Spray Hoses



PROFLO

- 48" reinforced hose with universal adapter

SKU
PF310430

EVERYTHING
YOU NEED,
RIGHT AT YOUR
FINGERTIPS.

FERGUSON.COM



FERGUSON®



What can we help you find?

Toilets 45-54
Urinals 55
Toilet Seats 56-58
Toilet & Tank Repair 59-61
Lavatory Sinks & Accessories 62-63
Pedestal Lavatories 64
Lavatory Drains 65-66
Kitchen & Bar Sinks 67-70
Kitchen & Bar Sink Accessories 71-74
Floor & Laundry Sinks 75-76

Complete Toilet Kits - HET



PROFLO

- Elongated Bowl
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 15"
- 12" rough-in
- Includes toilet seat, wax ring and closet bolts
- Gravity fed
- 2" glazed trapway
- Color matched trip lever
- Color/Finish: White

SKU
PFCT101HEWH

Complete Toilet Kits - HET



PROFLO

- Elongated Bowl
- Vitreous China
- Flow Rate: 1.28 gpf
- ADA Bowl Height: 17"
- 12" rough-in
- Includes toilet seat, wax ring and closet bolts
- Gravity fed
- 2" glazed trapway
- Color matched trip lever
- Color/Finish: White

SKU
PFCT103HEWH



PROFLO COMPLETE TOILET KITS

CONVENIENCE IN A BOX

Complete Toilet Kits - HET



PROFLO

- Round Front Bowl
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 15"
- 12" rough-in
- Includes toilet seat, wax ring and closet bolts
- Gravity fed
- 2" glazed trapway
- Color matched trip lever
- Color/Finish: White

SKU
PFCT100HEWH

Elongated Toilets - Low Consumption



PROFLO

- 1400T Low Consumption Series
- Vitreous China
- Flow Rate: 1.6 gpf
- Bowl Height: 15"
- Gravity fed box rim with integral jets
- 2" trapway
- 8" x 9" water surface
- Close coupled tank with cover
- Anti-siphon pilot fill valve prevents back siphoning
- Quick connect, 2 bolt tank-to-bowl installation
- Standard color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF5110BSM	Biscuit
PF5110WHM	White
12" Rough-in Tank	
PF5112BSM	Biscuit
PF5112WHM	White
14" Rough-in Tank	
PF5114WHM	White
12" Rough-in Right-Hand Tank	
PF5112RWHM	White
12" Rough-in Insulated Tank	
PF5112UWHM	White
12" Rough-in Locking Lid Tank	
PF5112LHEWH	White
Bowl Only	
PF1401TBS	Biscuit
PF1401TWH	White

Elongated Toilets - HET



PROFLO

- 1500 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 15 1/2"
- 2" glazed trapway
- Gravity fed, jetted box rim
- 8 1/2" x 7" water surface
- Close coupled tank with cover
- Chrome trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF6110WH	White
12" Rough-in Tank	
PF6112WH	White
14" Rough-in Tank	
PF6114WH	White
12" Rough-in Right-Hand Tank	
PF6112RWH	White
Bowl Only	
PF1501WH	White

Elongated Toilets - Low Consumption



PROFLO

- 1400T Low Consumption Series
- Vitreous China
- Flow Rate: 1.6 gpf
- ADA Bowl Height: 17"
- Gravity fed box rim with integral jets
- 2" trapway
- 8" x 9" water surface
- Close coupled tank with cover
- Anti-siphon pilot fill valve prevents back siphoning
- Quick connect, 2 bolt tank-to-bowl installation
- Standard color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF5110BSM	Biscuit
PF5110WHM	White
12" Rough-in Tank	
PF5112BSM	Biscuit
PF5112WHM	White
14" Rough-in Tank	
PF5114WHM	White
12" Rough-in Right-Hand Tank	
PF5112RWHM	White
12" Rough-in Insulated Tank	
PF5112UWHM	White
Bowl Only	
PF1403TBS	Biscuit
PF1403TWH	White

Elongated Toilets - HET



PROFLO

- 1400T High-Efficiency Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 15"
- 2" glazed trapway
- Gravity fed, double jetted box rim
- 8" x 9" water surface
- Close coupled tank with cover
- Uses 20% less water than standard low consumption toilets
- Standard color match trip lever

SKU	Color/Finish
10" Rough-in Tank	
PF5110HEBS	Biscuit
PF5110HEWH	White
12" Rough-in Tank	
PF5112HEBS	Biscuit
PF5112HEWH	White
14" Rough-in Tank	
PF5114WH	White
12" Rough-in Right-Hand Tank	
PF5112RHEWH	White
12" Rough-in Insulated Tank	
PF5112UHEWH	White
12" Rough-in Locking Lid Tank	
PF5112LHEWH	White
Bowl Only	
PF1401TBS	Biscuit
PF1401TWH	White

Elongated Toilets - HET



PROFLO

- 9400 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 16 1/8"
- Gravity fed jetted box rim
- 2" glazed trapway
- 8 1/2" x 7" water surface
- Close coupled tank with cover
- Chrome trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF9410WH	White
12" Rough-in Tank	
PF9412WHC	White
14" Rough-in Tank	
PF9414WH	White
12" Rough-in Right-Hand Tank	
PF9412RWH	White
12" Rough-in Insulated Tank	
PF9412UWH	White
12" Rough-in Locking Lid Tank	
PF9412LWH	White
Bowl Only	
PF9401WH	White

Elongated Toilets - HET



PROFLO

- 1400T High-Efficiency Series
- Vitreous China
- Flow Rate: 1.28 gpf
- ADA Bowl Height: 17"
- 2" glazed trapway
- Gravity fed, double jetted box rim
- 8" x 9" water surface
- Close coupled tank with cover
- Standard color match trip lever
- Uses 20% less water than standard low consumption toilets

SKU	Color/Finish
10" Rough-in Tank	
PF5110HEBS	Biscuit
PF5110HEWH	White
12" Rough-in Tank	
PF5112HEBS	Biscuit
PF5112HEWH	White
14" Rough-in Tank	
PF5114HEWH	White
12" Rough-in Right-Hand Tank	
PF5112RHEWH	White
12" Rough-in Insulated Tank	
PF5112UHEWH	White
12" Rough-in Locking Lid Tank	
PF5112LHEWH	White
Bowl Only	
PF1403TBS	Biscuit
PF1403TWH	White

Elongated Toilets - HET



PROFLO

- 1400T Dual Flush Series
- Vitreous China
- Flow Rate: 1.1/1.6 gpf
- Bowl Height: 15"
- Dual flush
- Gravity fed jetted box rim
- 2" glazed trapway
- 9" x 7" water surface
- Close coupled tank with cover
- Color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF9310WH	White
12" Rough-in Tank	
PF9312WH	White
12" Rough-in Right-Hand Tank	
PF9312RWH	White
Bowl Only	
PF1401TWH	White

Elongated Toilets - HET



PROFLO

- 1500 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- ADA Bowl Height: 17"
- 2" glazed trapway
- Gravity fed, jetted box rim
- 8 1/2" x 7" water surface
- Close coupled tank with cover
- Chrome trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF6110WH	White
12" Rough-in Tank	
PF6112WH	White
14" Rough-in Tank	
PF6114WH	White
12" Rough-in Right-Hand Tank	
PF6112RWH	White
Bowl Only	
PF1503WH	White

Elongated Toilets - HET



- 9400 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- ADA Bowl Height: 17"
- Gravity fed jetted box rim
- 2" glazed trapway
- 8 1/2" x 7" water surface
- Close coupled tank with cover
- Chrome trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF9410WH	White
12" Rough-in Tank	
PF9412WHC	White
14" Rough-in Tank	
PF9414WH	White
12" Rough-in Right-Hand Tank	
PF9412RWH	White
12" Rough-in Insulated Tank	
PF9412UWH	White
12" Rough-in Locking Lid Tank	
PF9412LWH	White
Bowl Only	
PF9403WH	White

Elongated Toilets - HET



- 1400T Dual Flush Series
- Vitreous China
- Flow Rate: 1.1/1.6 gpf
- ADA Bowl Height: 17"
- Dual flush
- Gravity fed jetted box rim
- 2" glazed trapway
- 9" x 7" water surface
- Close coupled tank with cover
- Color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF9310WH	White
12" Rough-in Tank	
PF9312WH	White
12" Rough-in Right-Hand Tank	
PF9312RWH	White
Bowl Only	
PF1403TWH	White

Elongated Toilets - UHET



- PF9800 Series
- Vitreous China
- Flow Rate: 0.8 gpf
- ADA Bowl Height: 17"
- Gravity fed box rim with integral jets
- 1 3/4" trapway
- Close coupled tank with cover
- Color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-In Tank	
PF9810WH	White
12" Rough-In Tank	
PF9812WH	White
Bowl Only	
PF9803WH	White

Round Front Toilets - Low Consumption



- 1400T Low Consumption Series
- Vitreous China
- Flow Rate: 1.6 gpf
- ADA Bowl Height: 15"
- Gravity fed box rim with integral jets
- 2" trapway
- 8" x 9" water surface
- Close coupled tank with cover
- Anti-siphon pilot fill valve prevents back siphoning
- Quick connect, 2 bolt tank-to-bowl installation
- Standard color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF5110BSM	Biscuit
PF5110WHM	White
12" Rough-in Tank	
PF5112BSM	Biscuit
PF5112WHM	White
14" Rough-in Tank	
PF5114WHM	White
12" Rough-in Right-Hand Tank	
PF5112RWHM	White
12" Rough-in Insulated Tank	
PF5112UWHM	White
Bowl Only	
PF1400TBS	Biscuit
PF1400TWH	White

Round Front Toilets - HET



PROFLO

- 1400T High-Efficiency Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 15"
- 2" glazed trapway
- Gravity fed, double jetted box rim
- 8" x 9" water surface
- Close coupled tank with cover
- Standard color match trip lever
- Uses 20% less water than standard low consumption toilets

SKU	Color/Finish
10" Rough-in Tank	
PF5110HEWH	White
12" Rough-in Tank	
PF5112HEBS	Biscuit
PF5112HEWH	White
14" Rough-in Tank	
PF5114HEWH	White
12" Rough-in Right-Hand Tank	
PF5112RHEWH	White
12" Rough-in Insulated Tank	
PF5112UHEWH	White
12" Rough-in Locking Lid Tank	
PF5112LHEWH	White
Bowl Only	
PF1400TBS	Biscuit
PF1400TWH	White

Round Front Toilets - HET



PROFLO

- 1500 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 15 1/2"
- 2" glazed trapway
- Gravity fed, jetted box rim
- 8 1/2" x 7" water surface
- Close coupled tank with cover
- Chrome trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF6110WH	White
12" Rough-in Tank	
PF6112WH	White
14" Rough-in Tank	
PF6114WH	White
12" Rough-in Right-Hand Tank	
PF6112RWH	White
Bowl Only	
PF1500WH	White

Round Front Toilets - HET



PROFLO

- 9400 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 16 1/8"
- Gravity fed jetted box rim
- 2" glazed trapway
- 8 1/2" x 7" water surface
- Close coupled tank with cover
- Chrome trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF9410WH	White
12" Rough-in Tank	
PF9412WHC	White
14" Rough-in Tank	
PF9414WH	White
12" Rough-in Right-Hand Tank	
PF9412RWH	White
12" Rough-in Insulated Tank	
PF9412UWH	White
12" Rough-in Locking Lid Tank	
PF9412LWH	White
Bowl Only	
PF9400WH	White

Round Front Toilets - HET



PROFLO

- 1400T Dual Flush Series
- Vitreous China
- Flow Rate: 1.1/1.6 gpf
- Bowl Height: 15"
- Dual flush
- Gravity fed jetted box rim
- 2" glazed trapway
- 9" x 7" water surface
- Close coupled tank with cover
- Color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF9310WH	White
12" Rough-in Tank	
PF9312WH	White
12" Rough-in Right-Hand Tank	
PF9312RWH	White
Bowl Only	
PF1400TWH	White

Round Front Toilets - UHET



- PF9800 Series
- Vitreous China
- Flow Rate: 0.8 gpf
- Gravity fed box rim with integral jets
- 1 3/4" trapway
- Close coupled tank with cover
- Bowl Height: 16 1/2"
- Color matched trip lever
- Seat and supply not included

SKU	Color/Finish
10" Rough-In Tank	
PF9810WH	White
12" Rough-In Tank	
PF9812WH	White
Bowl Only	
PF9800WH	White

Pressure Assist Elongated Toilets - HET



- 1600 Series
- Vitreous China
- Flow Rate: 1.0 gpf
- Bowl Height: 14 1/8"
- Equipped with Sloan Flushmate IV system
- 2" fully glazed trapway
- Siphon jet technology
- Large 13 1/2" x 11" water surface
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
12" Rough-in Tank	
PF1612PAWH	White
12" Rough-in Right-Hand Tank	
PF1612PARWH	White
12" Rough-in Locking Lid Tank	
PF1612PALWH	White
Bowl Only	
PF1601PAWH	White

Pressure Assist Elongated Toilets - HET



- 1600 Series
- Vitreous China
- Flow Rate: 1.0 gpf
- ADA Bowl Height: 17"
- Equipped with Sloan Flushmate IV system
- Siphon jet technology
- 2" fully glazed trapway
- 13 1/2" x 11" water surface
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
12" Rough-in Tank	
PF1612PAWH	White
12" Rough-in Right-Hand Tank	
PF1612PARWH	White
12" Rough-in Locking Lid Tank	
PF1612PALWH	White
Bowl Only	
PF1603PAWH	White

Pressure Assist Round Front - HET



- 1600 Series
- Vitreous China
- Flow Rate: 1.0 gpf
- Bowl Height: 14 1/2"
- Equipped with Sloan Flushmate IV system
- Siphon jet technology
- 2" fully glazed trapway
- 13 1/2" x 11" water surface
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
12" Rough-in Tank	
PF1612PAWH	White
12" Rough-in Right-Hand Tank	
PF1612PARWH	White
12" Rough-in Locking Lid Tank	
PF1612PALWH	White
Bowl Only	
PF1600PAWH	White

Pressure Assist Elongated Toilets - HET



- 1600 Series
- Vitreous China
- Flow Rate: 1.0 gpf
- Bowl Height: 15 1/8"
- Rear outlet
- Equipped with Sloan Flushmate IV system
- Siphon jet technology
- 2" fully glazed trapway
- 13 1/2" x 11" water surface
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
12" Rough-in Tank	
PF1612PAWH	White
12" Rough-in Right-Hand Tank	
PF1612PARWH	White
12" Rough-in Locking Lid Tank	
PF1612PALWH	White
Bowl Only	
PF1605PAWH	White

Pressure Assist Elongated Toilets - HET



- 1600 Series
- Vitreous China
- Flow Rate: 1.0 gpf
- ADA Bowl Height: 17"
- Rear outlet
- Back outlet
- Equipped with Sloan Flushmate IV system
- Siphon jet technology
- 2" fully glazed trapway
- 13 1/2" x 11" water surface
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
12" Rough-In Tank	
PF1612PAWH	White
12" Rough-in Right-Hand Tank	
PF1612PARWH	White
12" Rough-in Locking Lid Tank	
PF1612PALWH	White
Bowl Only	
PF1606PAWH	White

Pressure Assist Round Front Toilets - HET



- 1600 Series
- Vitreous China
- Flow Rate: 1.0 gpf
- Bowl Height: 15 1/8"
- Back outlet
- Equipped with Sloan Flushmate IV system
- Siphon jet technology
- 2" fully glazed trapway
- 13 1/2" x 11" water surface
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
12" Rough-in Tank	
PF1612PAWH	White
12" Rough-in Right-Hand Tank	
PF1612PARWH	White
12" Rough-in Locking Lid Tank	
PF1612PALWH	White
Bowl Only	
PF1604PAWH	White

Wall Mount Elongated Toilets - HET



- 1700 Series
- Vitreous China
- Flow Rate: 1.28 gpf
- Wall mounted with back outlet
- Siphon jet technology
- Close coupled tank with cover
- Seat and supply not included

SKU	Color/Finish
Tank Only	
PF1710HEWH	White
Bowl Only	
PF1705HEWH	White

Flush Valve Toilets - HET



- 1700 Series
- Vitreous China
- Flow Rate: 1.28/1.6 gpf
- Siphon jet flushing
- 2" fully glazed trapway
- 1 1/2" top inlet spud
- Integral rim jets for added bowl cleansing
- Seat and flush valve not included
- Color/Finish: White

SKU
PF1721WH

Flush Valve Toilets - HET



- 1700 Series
- Vitreous China
- Flow Rate: 1.28/1.6 gpf
- ADA compliant when installed according to ADA guidelines
- Wall mount installation
- Siphon jet flushing
- 2" fully glazed trapway
- 1 1/2" top inlet spud
- Integral rim jets for added bowl cleansing
- Seat and flush valve not included
- Color/Finish: White

SKU
PF1731WH

Flush Valve Toilets - HET



- 1700 Series
- Vitreous China
- Flow Rate: 1.28/1.6 gpf
- ADA Bowl Height: 17"
- Siphon jet flushing
- 2" fully glazed trapway
- 1 1/2" top inlet spud
- Integral rim jets for added bowl cleansing
- Seat and flush valve not included
- Color/Finish: White

SKU
PF1723WH

Children's Bowl Toilets - HET



- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 10 1/4"
- Siphon jet technology
- 3" flush valve
- Close coupled tank with cover
- Sanitary bar
- Seat and supply not included

SKU	Color/Finish
10" Rough-in Tank	
PF1712BBHEWH	White
12" Rough-in Insulated Tank	
PF1712BBRHEWH	White
Tank Only with Lid Lock	
PF1712BBLHEWH	White
Bowl Only	
PF1704BBHEWH	White

Children's Bowl Only Toilets



- Vitreous China
- Flow Rate: 1.28 gpf
- Bowl Height: 10"
- 10" rough-in
- Siphon jet flushing
- 8 7/8" x 7" water surface
- 1 1/2" top inlet spud
- Flush valve and seat not included
- Color/Finish: White

SKU
PF1700BBHEWH

Toilets








	1600PA STD	1600PA FMBO	PF1705HE	PF1721 PF1723 PF1731	PF1704BBHE	PF1700BBHE
Flush Volume	1.0 gpf	1.0 gpf	1.28 gpf	1.28 gpf	1.28 gpf	1.28 gpf
Flush Type	Pressure Assist	Pressure Assist	Gravity	Flushometer	Gravity	Flushometer
			Tank Options			
10" RI	-	-	-	-	PF1712BBHE	-
12" RI	PF1612PA	PF1612PA	PF1710HE	-	-	-
14" RI	-	-	-	-	-	-
RH	PF1612PAR	PF1612PAR	-	-	PF1712BBRHE	-
Lined	-	-	-	-	-	-
Locking Lid	PF1612PAL	PF1612PAL	-	-	PF1712BBHE	-
			Bowl Options			
Round	PF1600PA	PF1604PA	-	-	PF1704BBHE	PF1700BBHE
Elongated	PF1601PA	PF1605PA	-	PF1721	-	-
ADA	PF1603PA	PF1606PA	-	PF1723	-	-
Wall Mount	-	-	PF1705HE (EL)	PF1731 (EL)	-	-
			Bowl Height			
RF	14 1/2"	15 1/8"	-	-	10 1/2"	10"
EL	14 1/2"	15 1/8"	-	14 3/8"	-	-
ADA	17"	17"	-	17"	-	-
Wall	-	-	Variable	Variable	-	-
Flapper	-	-	3"	-	3"	-
WaterSense	Yes	Yes	No	Yes	No	No
Flush Lever	Chrome	Chrome	Chrome	-	Chrome	-
Color/Finish	White	White	White	White	White	White

Toilets








	PF1400T Low Consumption	PF1400T High Efficiency	PF1500	PF9400	PF1400T Dual Flush	PF9800 Ultra High Efficiency
Flush Volume	1.6 gpf	1.28 gpf	1.28 gpf	1.28 gpf	1.6 gpf/ 1.1 gpf	0.8 gpf
Flush Type	Gravity	Gravity	Gravity	Gravity	Gravity	Gravity
Tank Options						
10" RI	PF5110	PF5110HE	PF6110	PF9410	PF9310	PF9810
12" RI	PF5112	PF5112HE	PF6112	PF9412	PF9312	PF9812
14" RI	PF5114	PF5114HE	PF6114	PF9414	-	-
RH	PF5112R	PF5112RHE	-	PF9412R	PF9312R	-
Lined	PF5112U	PF5112UHE	-	PF9412U	-	-
Locking Lid	-	PF5112LHW	-	PF9412L	-	-
Bowl Options						
Round	PF1400T	PF1400T	PF1500	PF9400	PF1400T	PF9800
Elongated	PF1401T	PF1401T	PF1501	PF9401	PF1401T	-
ADA	PF1403T	PF1403T	PF1503	PF9403	PF1403T	PF9803
Wall Mount	-	-	-	-	-	-
Bowl Height						
RF	15"	15"	15 1/2"	16 1/8"	15"	16 1/2'
EL	15"	15"	15 1/2"	16 1/8"	15"	-
ADA	17"	17"	17"	17"	17"	17"
Wall	-	-	-	-	-	-
Flapper	2"	2"	3"	3"	2"	2"
WaterSense	No	Yes	Yes	Yes	Yes	Yes
Flush Lever	Color match	Color match	Chrome	Chrome	Color match	Color match
Color/Finish	White, Biscuit	White, Biscuit	White	White	White	White

Urinals



PROFLO

- 1800 Series
- Vitreous China
- Flow Rate: 0.5 gpf/1.9 lpf - 1.0 gpf/3.8 lpf
- Urinal Type: High efficiency/quarter stall
- Wash-out flushing
- 3/4" top inlet spud
- Integral flushing rim
- Hanging bracket included
- 1 1/2" outlet for exposed trap connection
- WaterSense labeled when used with a 0.5 gpf WaterSense labeled flushometer
- Color/Finish: White

SKU
PF1805WH

Urinals



PROFLO

- 1800 Series
- Vitreous China
- Urinal Type: High efficiency/half stall
- 3/4" top inlet spud
- Integral flushing rim and trap
- Hanging bracket included
- Flush valve not included
- WaterSense labeled when used with a 0.5 gpf WaterSense labeled flushometer
- Color/Finish: White

SKU	Configuration	Flow Rate
PF1825PTWH	Wash-Out	0.125 - 1.0 gpf
PF1835WH	Siphon Jet	0.5 - 1.0 gpf

Urinals



PROFLO

- 1800 Series
- Vitreous China
- Urinal Type: High efficiency/quarter stall
- 3/4" top inlet spud
- Hanging bracket included
- Flush valve not included
- WaterSense labeled when used with a 0.5 gpf WaterSense labeled flushometer
- Color/Finish: White

SKU	Configuration	Flow Rate
PF1815PTWH	Wash-Out	0.125 - 1.0 gpf
PF1815WH	Siphon Jet	0.5-1.0 gpf

Urinals

SKU	Type	Flow Rate	Strainer	Flush Type	Outlet Type	Outlet Size	Trapway Type
PF1805	Compact	0.5 - 1.0 gpf	Integral	Wash-Out	Bottom	1 1/2"	Exposed Integral
PF1815	Compact	0.5 - 1.0 gpf	Integral	Siphon Jet	Rear	2"	Integral
PF1815PT	Compact	0.125 - 1.0 gpf	Integral	Wash-Out	Rear	2"	Integral
PF1825PT	Half Stall	0.125 - 1.0 gpf	Integral	Wash-Out	Rear	2"	Integral
PF1835	Half Stall	0.5 - 1.0 gpf	Integral	Siphon Jet	Rear	2"	Integral

Elongated Plastic Seats



- Closed front with cover
- With easy-clean hinges
- Molded in color matched bumpers
- Slow close
- Corrosion proof nuts and bolts
- Slip resistant pads with variable positioning washers
- Solid plastic construction

SKU	Color/Finish
PFTSEC2000BS	Biscuit
PFTSEC2000WH	White

Elongated Plastic Seats



- Closed front with cover
- Plastic top mount hinge
- Solid plastic construction

SKU	Color/Finish
PFTSE2000BS	Biscuit
PFTSE2000WH	White

Elongated Plastic Seats



- Closed front with cover
- Top mount concealed hinge with slip resistant pads
- Large, color matched bumpers
- Slide-off hinge for easy cleaning
- Solid plastic construction
- Corrosion free hardware

SKU	Color/Finish
PFTSHEC2000BS	Biscuit
PFTSHEC2000WH	White

Elongated Wood Seats



- Closed front with cover
- Plastic top mount hinge
- Slide-off hinge for easy cleaning
- Wood construction

SKU	Color/Finish
PFTSWEC2000BO	Bone
PFTSWEC2000BS	Biscuit
PFTSWEC2000WH	White

Elongated Wood Seats



- Closed front with cover
- Plastic top mount hinge
- Wood construction
- Color/Finish: White

SKU
PFTSWE2001WH

Round Front Plastic Seats



- Closed front with cover
- With easy-clean hinges
- Molded in color matched bumpers
- Slow close
- Corrosion proof nuts and bolts
- Slip resistant pads with variable positioning washers
- Solid plastic construction
- Color/Finish: White

SKU
PFTSEC1000WH

Round Front Plastic Seats



- Closed front with cover
- Plastic top mount hinge
- Solid plastic construction

SKU	Color/Finish
PFTSE1000BS	Biscuit
PFTSE1000WH	White

Round Front Plastic Seats



- Closed front with cover
- Top mount concealed hinge with slip resistant pads
- Large, color matched bumpers
- Slide-off hinge for easy cleaning
- Solid plastic construction
- Corrosion free hardware

SKU	Color/Finish
PFTSHEC1000BS	Biscuit
PFTSHEC1000WH	White

Round Front Wood Seats



- Closed front with cover
- Plastic top mount hinge
- Slide-off hinge for easy cleaning
- Wood construction

SKU	Color/Finish
PFTSWEC1000BO	Bone
PFTSWEC1000BS	Biscuit
PFTSWEC1000WH	White

Round Front Wood Seats



- Closed front with cover
- Plastic top mount hinge
- Wood construction
- Color/Finish: White

SKU
PFTSWE1001WH

Elongated Plastic OF Seats



- Open front less cover
- External self-sustaining check hinge holds seat in any raised position up to 11° beyond vertical
- Large, molded in bumpers
- Slip resistant pads
- Solid plastic construction
- 304 series stainless steel hardware

SKU	Color/Finish
PFTSCOF2000BL	Black
PFTSCOF2000WH	White

Elongated Plastic OF Seats



- Open front less cover
- Anti-microbial
- External self-sustaining check hinge holds seat in any raised position up to 11° beyond vertical
- Large, molded in bumpers
- Slip resistant pads
- Solid plastic with anti-microbial agent
- 304 series stainless steel hardware
- Color/Finish: White

SKU
PFTSCOFA2000WH

Elongated Plastic OF Seats



- Open front less cover
- External check hinge
- Large, molded in bumpers
- Slip resistant pads
- Solid plastic construction
- 304 series stainless steel hardware
- Color/Finish: White

SKU
PFTSCOFE2000WH

Elongated Plastic OF Seats



- Open front less cover
- Extra heavy weight
- External self-sustaining check hinge holds seat in any raised position up to 11° beyond vertical
- Large, molded in bumpers
- Slip resistant pads
- Solid plastic construction
- 304 series stainless steel hardware
- Color/Finish: White

SKU
PFTSCOFH2000WH

Elongated Plastic OF Seats



- Open front with cover
- Large, molded in bumpers
- Slip resistant pads
- Solid plastic construction
- Color/Finish: White

SKU
PFTSCOFC2000WH

Children's Plastic OF Seats



- Open front less cover
- External self-sustaining check hinge holds seat in any raised position up to 11° beyond vertical
- Large, molded in bumpers
- Slip resistant pads
- Solid plastic construction with antimicrobial agent
- 304 series stainless steel hardware
- Color/Finish: White

SKU
PFTSBB1000WH

Toilet Seats

Round	Elongated		
		Slow close toilet seat with easy clean	
 PFTSEC1000	 PFTSEC2000	· Heavy weight molded solid plastic seat · Closed front with cover · Molded in color matched bumpers · Slip resistant pads with variable positioning washers	· Slow close hinge system with quick release for easy cleaning · Elongated only · Available in white (WH), and biscuit (BS)
		Heavy duty plastic seat with easy clean	
 PFTSHEC1000	 PFTSHEC2000	· Extra heavy weight molded solid plastic · Closed front with cover · Plastic top mount hinge	· Large color matched bumpers · Available in white (WH) and biscuit (BS) · Slide-off hinge for easy cleaning
		Plastic toilet seat	
 PFTSE1000	 PFTSE2000	· Impact resistant plastic construction · Closed front with cover	· Plastic top mount concealed hinge · Available in white (WH) and biscuit (BS)
		Wood toilet seat with easy clean	
 PFTSWEC1000	 PFTSWEC2000	· Molded wood construction · Closed front with cover · Plastic top mount hinge with slip resistant pads and variable positioning washers	· Large color matched bumpers · Multi-coat enamel finish · Available in white (WH), biscuit (BS) and bone (BO) · Slide-off hinge for easy cleaning
		Wood toilet seat	
 PFTSWE1001	 PFTSWE2001	· Molded wood construction · Closed front with cover · Plastic top mount hinge	· Color matched bumpers · Multi-coat enamel finish · Available in white (WH)

Commercial Open Front Seats


PFTSCOFC2000


PFTSBB1000WH


PFTSCOF2000WH

All PROFLO Commercial Toilet Seats are made from heavy-weight molded solid plastic with molded in color matched bumpers. Seats with stainless steel bolts are type 304.

PROFLO Commercial Seat Features

SKU	Bowl	Open Front	With Cover	Check Hinge	Self-Sustaining Hinge	Stainless Steel Bolts	Extra Heavy Weight	Anti-Microbial	Color/Finish
PFTSBB1000WH	Children's Seat	✓		✓	✓	✓		✓	White
PFTSCOFE2000WH	Elongated	✓		✓		✓			White
PFTSCOF2000WH	Elongated	✓		✓	✓	✓			White
PFTSCOF2000BL	Elongated	✓		✓	✓	✓			Black
PFTSCOFA2000WH	Elongated	✓		✓	✓	✓			White
PFTSCOFH2000WH	Elongated	✓		✓	✓	✓	✓		White
PFTSCOFC2000WH	Elongated	✓	✓						White

**PFTSBB1000WH for use with PROFLO elementary bowls PF1704BB and PF1700BB.*

Flush Levers



MONOGRAM BRASS™

- Fits most conventional toilet tanks
- Brass arm with zinc handle and nut
- Color/Finish: Oil Rubbed Bronze

SKU
MB401ORB

Flush Levers



MONOGRAM BRASS™

- Fits most conventional toilet tanks
- Brass arm with zinc handle and nut

SKU	Color/Finish
MB402BN	Brushed Nickel
MB402PN	Polished Nickel

Flush Levers



MONOGRAM BRASS™

- Fits PROFLO® High Efficiency Toilets PF9400 series toilet tanks
- Side mount
- Zinc handle
- Brass arm with plastic nut

SKU	Color/Finish
MB422BN	Brushed Nickel
MB422ORB	Oil Rubbed Bronze

Flush Levers



MONOGRAM BRASS™

- Fits Mirabelle® Bradenton® toilet tanks
- Fits most front mount conventional toilet tanks
- Brass arm, zinc handle and plastic nut

SKU	Color/Finish
MB423BN	Brushed Nickel
MB423CP	Chrome
MB423ORB	Oil Rubbed Bronze
MB423PN	Polished Nickel

Flush Levers



MONOGRAM BRASS™

- Fits Mirabelle® Provincetown® toilet tanks
- Fits most front mount conventional toilet tanks
- Brass arm, zinc handle and plastic nut

SKU	Color/Finish
MB424BN	Brushed Nickel
MB424CP	Chrome
MB424ORB	Oil Rubbed Bronze

Flush Levers



MONOGRAM BRASS™

- Fits most front conventional toilet tanks, including Mirabelle® Amberley®, Boca Raton® and Key West® toilets
- Brass construction

SKU	Color/Finish
MB425BN	Brushed Nickel
MB425CP	Chrome
MB425ORB	Oil Rubbed Bronze

Toilet Flappers



PROFLO

- For PF5112 series tanks
- Compatible with most 2" flush valve toilets

SKU
PF5112FRPK

Toilet Flappers



PROFLO

- Korky® style flappers fit regular Douglas® style flush valves or new style plastic flush valves with projecting arms
- Effective for areas with poor water quality
- Color/Finish: Red

SKU
PF2001BP

Toilet Flappers



- Kohler® style for Wellworth®
- Bagged/boxed

SKU
PF49114

Toilet Flappers



- For PF9400 series tanks and PF1712BB tanks
- Compatible with most 3" flush valve toilets

SKU
PF9412FRPK

Toilet Flappers



- Korky® style flappers
- Fits regular Douglas® style flush valves or new style plastic flush valves with projecting arms

SKU
PFL54X

Fill Valves



- For PF5112 series tanks
- Adjustable to fit most tanks
- Anti-siphon

SKU
PF5112FLPK

Fill Valves



- For PF9312 tanks
- Anti-siphon

SKU
PF9312FLPK

Fill Valves



- For PF9400 series tanks
- Anti-siphon system

SKU
PF9412FLPK

Flush Valves



- For PF9400 series tanks
- 3"

SKU
PF9412FVPK

Flush Valves



- Douglas® style
- With rubber flapper and stainless steel chain
- Plastic construction

SKU
PF210420

Flush Valves



- American Standard® style
- Base not included

SKU
PFAS5

Flush Valves



- Douglas® style
- With overflow tube and guide
- Brass construction

SKU
PFDFVB

Flush Valves



- Eljer Style
- Total flush unit
- Plastic construction
- Color/Finish: Chrome

SKU
PFEFU

Flush Valves



- American Standard® style

SKU
PROPFAS4

Flush Levers



- For PF5112 series left hand tanks
- Fits most conventional front mount tanks
- Color/Finish: White

SKU
PF5112TLWHPK

Flush Levers



- Briggs® style
- For left hand tanks
- Color/Finish: Chrome

SKU
PF140954PK

Flush Levers



- For PF9412 series tanks
- Color/Finish: Chrome

SKU
PF9412TLPK

Flush Levers



- Economy, die cast trip
- Includes plastic nut and brass arm
- Color/Finish: Chrome

SKU
PFETL

Flush Levers



- Die cast handle
- Includes zinc nut and brass arm
- Color/Finish: Chrome

SKU
PFTLCP

Ballcocks



- Hooverline®
- 8"
- Plastic anti-siphon

SKU
PF210200

Self-Rimming Lavatory Sinks



- Overall Size: 17 1/2" x 14 1/4"
- Bowl Depth: 7"
- Elegantly sculptured
- Template and instructions included
- Material: Vitreous China
- Color/Finish: White

SKU
PF1125WH

Self-Rimming Lavatory Sinks



- Overall Size: 19" x 16 1/2"
- Bowl Size: 15" x 10" x 7 7/8"
- Concealed front overflow
- Can be mounted for ADA installation
- Material: Vitreous China

SKU	Faucet Installation	Color/Finish
PF19164BS	4" Centers	Biscuit
PF19164WH	4" Centers	White
PF19168WH	8" Centers	White

Self-Rimming Lavatory Sinks



- Overall Size: 19"
- Bowl Size: 14 1/2" x 11 3/4" x 8"
- Concealed front overflow drain
- Can be mounted for ADA installation
- Material: Vitreous China

SKU	Faucet Installation	Color/Finish
PF191RWH	1 Hole	White
PF194RBS	4" Centers	Biscuit
PF194RWH	4" Centers	White
PF198RBS	8" Centers	Biscuit
PF198RWH	8" Centers	White

Self-Rimming Lavatory Sinks



- Overall Size: 20" x 17"
- Bowl Size: 16" x 11" x 8"
- Concealed front overflow drain
- Can be mounted for ADA installation
- Material: Vitreous China

SKU	Faucet Installation	Color/Finish
PF20171WH	1 Hole	White
PF20174BS	4" Centers	Biscuit
PF20174WH	4" Centers	White
PF20178BS	8" Centers	Biscuit
PF20178WH	8" Centers	White

Self-Rimming Lavatory Sinks



- Overall Size: 19" x 19"
- 4" centerset only
- Concealed front overflow
- Mounting bracket included
- Material: Enameled Steel
- Factory direct special order only

SKU	Color/Finish
PFS194RBS	Biscuit
PFS194RWH	White

Self-Rimming Lavatory Sinks



- Overall Size: 20" x 17"
- 4" centerset only
- Concealed front overflow
- Mounting bracket included
- Material: Enameled Steel
- Factory direct special order only

SKU	Color/Finish
PFS20174BS	Biscuit
PFS20174WH	White

Undermount Lavatory Sinks



- Overall Size: 21 1/16" x 14 9/16"
- Bowl Size: 18 11/16" x 12 3/16"
- Bowl Depth: 6 5/16"
- Concealed front overflow
- Material: Vitreous China
- Mounting clips included

SKU	Color/Finish
PF1812UBS	Biscuit
PF1812UWH	White

Undermount Lavatory Sinks



- Overall Size: 19 7/8" x 15 15/16"
- Bowl Size: 17 1/2" x 13 9/16"
- Bowl Depth: 5 9/16"
- With overflow
- Material: Vitreous China
- Mounting clips included

SKU	Color/Finish
PF1713UBS	Biscuit
PF1713UWH	White

Undermount Lavatory Sinks



- Overall Size: 19" x 16"
- Bowl Size: 17" x 14" x 5 3/4"
- Concealed front overflow
- Mounting clips included
- Material: Vitreous China

SKU	Color/Finish
PF1714UABS	Biscuit
PF1714UAWH	White

Undermount Lavatory Sinks



- Overall Size: 17" x 13 1/2"
- Bowl Size: 15" x 12" x 5 3/4"
- Concealed front overflow
- Mounting clips included
- Material: Vitreous China

SKU	Color/Finish
PF1512UBS	Biscuit
PF1512UWH	White

Wall-Mount Lavatory Sinks



- Overall Size: 19 5/8" x 17 3/8"
- Bowl Size: 14 3/4" x 10 7/8" x 5"
- Anti-splash rim
- Wall bracket included
- Concealed front overflow
- Material: Vitreous China
- Color/Finish: White

SKU	Faucet Installation
PF5411WH	1 Hole
PF5414WH	4" Centers

Wall-Mount Lavatory Sinks



- Overall Size: 20 5/8" x 18 1/2"
- Bowl Size: 14 3/4" x 11" x 6 1/8"
- High backsplash
- Punched for concealed arm carrier
- Wall bracket included
- Concealed front overflow
- Material: Vitreous China
- Color/Finish: White

SKU	Faucet Installation
PF5511WH	1 Hole
PF5514WH	4" Centers
PF5518WH	8" Centers

Wall-Mount Brackets



- Universal bracket for wall-mount lavatories and urinals
- Color/Finish: Chrome

SKU
PFBRACKET

Wall-Mount Brackets



- Bracket for PROFLO wall-mount commercial lavatories
- Color/Finish: Chrome

SKU
PFWMBKT

Pedestal Lavatories



PROFLO

- Overall Size: 19 1/2" x 17 3/8"
- Pedestal Height: 17 3/4"
- Material: Vitreous China
- Mounting brackets and instructions included
- Faucet not included

SKU	Color/Finish
4" Lavatory	
PF1131WHP	White
Pedestal Only	
PF1103WH	White

Pedestal Lavatories



PROFLO

- Overall Size: 25 1/2" x 19 5/8"
- Pedestal Height: 25"
- Material: Vitreous China
- Mounting brackets and instructions included

SKU	Color/Finish
4" Lavatory	
PF14104WH	White
8" Lavatory	
PF14108WH	White
Pedestal Only	
PF1011WH	White

Pedestal Lavatories



PROFLO

- Overall Size: 24" x 20"
- Pedestal Height: 26 1/2"
- Pedestal conceals all plumbing
- Integral self-draining faucet deck
- High gloss and stain resistant surface
- Material: Vitreous China
- Mounting bracket included

SKU	Color/Finish
4" Lavatory	
PF4004BS	Biscuit
PF4004WH	White
8" Lavatory	
PF4008BS	Biscuit
PF4008WH	White
Pedestal Only	
PF1045BS	Biscuit
PF1045WH	White

Pedestal Lavatories



PROFLO

- Overall Size: 20" x 18"
- Pedestal Height: 26 1/2"
- Integral self-draining soap dishes
- High gloss and stain resistant surface
- Material: Vitreous China
- Mounting brackets and instructions included

SKU	Color/Finish
4" Lavatory	
PF5004BS	Biscuit
PF5004WH	White
8" Lavatory	
PF5008BS	Biscuit
PF5008WH	White
Pedestal Only	
PF1045BS	Biscuit
PF1045WH	White

Pedestal Lavatories



PROFLO

- Overall Size: 22 1/2" x 19"
- Pedestal Height: 24 1/10"
- Material: Vitreous China
- Twin soap dishes
- Mounting brackets and instructions included

SKU	Color/Finish
4" Lavatory	
PF1121WHP	White
Pedestal Only	
PF1021WH	White

Lavatory Drains



MONOGRAM BRASS™

- Pop-up style
- For lavatories with overflow holes
- 1 1/4" OD x 8"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB301BN	Brushed Nickel
MB301CP	Chrome
MB301ORB	Oil Rubbed Bronze
MB301PB	Polished Brass
MB301PN	Polished Nickel

Lavatory Drains



MONOGRAM BRASS™

- Flat grid strainer
- For lavatories with no overflow holes
- 1 1/4" OD x 6"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB311BN	Brushed Nickel
MB311CP	Chrome
MB311ORB	Oil Rubbed Bronze
MB311PN	Polished Nickel

Lavatory Drains



MONOGRAM BRASS™

- Flat grid strainer with decorative dome cover
- For lavatories less overflow holes
- 1 1/4" OD x 6"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB312BN	Brushed Nickel
MB312CP	Chrome
MB312ORB	Oil Rubbed Bronze

Lavatory Drains



MONOGRAM BRASS™

- Teardrop design
- For lavatories with overflow drains
- 1 1/4" OD x 6"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB313BN	Brushed Nickel
MB313CP	Chrome
MB313ORB	Oil Rubbed Bronze
MB313PN	Polished Nickel

Lavatory Drains



MONOGRAM BRASS™

- Teardrop design
- For lavatories less overflow holes
- 1 1/4" OD x 6"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB314BN	Brushed Nickel
MB314CP	Chrome
MB314ORB	Oil Rubbed Bronze

Lavatory Drains



MONOGRAM BRASS™

- Lift & turn pull out plug
- For lavatories with no overflow holes
- 1 1/4" OD x 7"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB321BN	Brushed Nickel
MB321CP	Chrome
MB321ORB	Oil Rubbed Bronze

Lavatory Drains



MONOGRAM BRASS™

- Pop-up style
- For lavatories with no overflow holes
- 1 1/4" OD x 6 1/2"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB331BN	Brushed Nickel
MB331CP	Chrome
MB331ORB	Oil Rubbed Bronze

Lavatory Drains



MONOGRAM BRASS™

- Clic-clac style
- For lavatories with overflow holes
- 1 1/4" OD x 6"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB332BN	Brushed Nickel
MB332CP	Chrome
MB332ORB	Oil Rubbed Bronze
MB332PN	Polished Nickel

Lavatory Drains



MONOGRAM BRASS™

- Clic-clac style
- For lavatories less overflow holes
- 1 1/4" OD x 6"
- Fits 1 1/2" opening
- Brass construction

SKU	Color/Finish
MB333BN	Brushed Nickel
MB333CP	Chrome
MB333ORB	Oil Rubbed Bronze
MB333PN	Polished Nickel

Lift Rod Extensions



MONOGRAM BRASS™

- Fits pop-up lift rod or horizontal rod on pop-up assemblies
- Extends vertical depth of lift rod 6" or extends horizontal length of ball rod 6"
- Brass construction

SKU
MB351NA

Grid Drains



PROFLO

- 1 1/4" x 6"
- 17 gauge
- Cast brass body
- Brass construction
- Color/Finish: Chrome

SKU
PFGD100

Grid Drains



PROFLO

- Offset design
- 1 1/4" tailpiece
- 17 gauge
- Includes cast brass elbow
- Brass construction
- Color/Finish: Chrome

SKU
PFGD101

Offset Drains



PROFLO

- 1 1/2" x 12 3/4"
- Offset design
- 17 gauge
- Does not include basket strainer
- Brass construction
- Color/Finish: Chrome

SKU
PFOD100

PO Plug Lavatory Drains



PROFLO

- 1 1/4" x 7"
- Brass
- Includes stopper and chain
- Color/Finish: Chrome

SKU
PFPO200

Pop-Up Lavatory Drains



PROFLO

- 1 1/4" x 4"
- 20 gauge
- Dual flow diverter with lever control
- Brass construction
- Color/Finish: Chrome

SKU	CSA Certified
PFBPUCP	No
PFBPUCPC	Yes

Complete Kitchen Sink Kits



- Includes: Double bowl stainless steel sink, single handle faucet and 2 basket strainers
- Self-rimming
- Overall Size: 33" x 22"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 8 1/8"
- 20 gauge stainless steel
- Flow Rate: 1.5 gpm
- Metal lever handle with side sprayer
- Ceramic disc cartridge
- 1/2" IPS connections
- With 360° swivel spout
- 430 stainless steel basket strainer
- Zinc locknut & slipnut
- **Optional accessories:**
  Bottom basin grid: PFG1112

SKU
PFCS100

Single Bowl Bar Sinks



- Self-rimming
- Overall Size: 15" x 15"
- Bowl Size: 12 1/4" x 10 1/2"
- Bowl Depth: 6"
- Drain Opening: 3 1/2"
- 22 gauge stainless steel
- Undercoated and padded for quiet operation
- Color/Finish: Stainless Steel
- ASME A112.19.3
- CSA B45.4-08

SKU	Holes
PFSR151561A	1
PFSR151562A	2



Single Bowl Bar Sinks



- Self-rimming
- Overall Size: 17" x 19"
- Bowl Size: 14" x 14"
- Bowl Depth: 6 1/8"
- Drain Opening: 3 1/2"
- 22 gauge stainless steel
- Undercoated and padded for quiet operation
- Sink strainer sold separately
- Sink clips included
- Color/Finish: Satin Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1111

SKU	Holes
PFSR171962	2
PFSR171963	3

Single Bowl Bar Sinks



- Self-rimming
- Overall Size: 17" x 22"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 7"
- Drain Opening: 3 1/2"
- 20 gauge stainless steel
- Faucet Installation: 3 hole
- Undercoated and padded for quiet operation
- Sink strainers sold separately
- Sink clips included
- Color/Finish: Satin Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1112

SKU
PFSR172273

Single Bowl Bar Sinks



- Undermount
- Overall Size: 15 1/2" x 20"
- Bowl Size: 13 1/4" x 18"
- Bowl Depth: 9"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- Color/Finish: Stainless Steel

SKU
PFUC303

Single Bowl Bar Sinks



- Undermount
- Overall Size: 16 5/16"
- Bowl Size: 14 1/8"
- Bowl Depth: 7"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- ASME A112.19.3
- CSA B45.4-08

SKU
PFUC405A

Single Bowl Bar Sinks



- Undermount
- Overall Size: 16" x 17 3/4"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 8"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- **Optional accessories:**
  Bottom grid: PFG1112

SKU
PFUC109

Single Bowl Kitchen Sinks



- Self-rimming
- Overall Size: 25" x 21 1/4"
- Bowl Size: 21" x 15 3/4"
- Bowl Depth: 5 3/8"
- Drain Opening: 3 1/2"
- Faucet Installation: 3 hole
- 22 gauge stainless steel
- Undercoated and padded for quiet operation
- Sink strainers sold separately
- Sink clips included
- Color/Finish: Satin Stainless Steel

SKU	Drain Location
PFSR2521553C	Center
PFSR2521553L	Left
PFSR2521553R	Right

Single Bowl Kitchen Sinks



- Self-rimming
- Overall Size: 25" x 22"
- Bowl Size: 21" x 15 3/4"
- Drain Opening: 3 1/2"
- Sink clips included
- Under spray coating and pads for sound deadening and insulation
- 6 1/8" deep sinks are ADA compliant
- Color/Finish: Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1712

SKU	Bowl Depth	Gauge	Holes
PFSR252263	6 1/8"	22	3
PFSR252264	6 1/8"	22	4
PFSR252263BP	6 1/8"	23	3
PFSR252264BP	6 1/8"	23	4
PFSR2522653	6 1/2"	22	3
PFSR2522654	6 1/2"	22	4
PFSR252273	7 1/8"	20	3
PFSR252274	7 1/8"	20	4
PFSR252283A	8"	20	3
PFSR252284A	8"	20	4

Single Bowl Kitchen Sinks



- Undermount
- Overall Size: 23 5/16" x 17 5/8"
- Bowl Size: 21 5/16" x 15 5/8"
- Bowl Depth: 8"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- Undercoated and padded for quiet operation
- Sink strainer sold separately
- Color/Finish: Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1712

SKU
PFUC301A

Single Bowl Kitchen Sinks



- Undermount
- Overall Size: 23 1/4" x 21"
- Bowl Size: 21 1/4" x 19"
- Bowl Depth: 9"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- ASME A112.19.3
- CSA B45.4-08
- **Optional accessories:**
  Bottom grid: PFG1917

SKU
PFUC307A

Single Bowl Kitchen Sinks



- Undermount
- Overall Size: 30" x 18"
- Bowl Size: 28 1/8" x 16"
- Bowl Depth: 9"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- ASME A112.19.3
- CSA B45.4-08
- **Optional accessories:**
  Bottom grid: PFG2513

SKU
PFUC308A

Double Bowl Kitchen Sinks



- Self-rimming
- Overall Size: 33" x 21"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 6 1/2"
- Double equal bowls
- 22 gauge stainless steel
- Undercoated and padded for quiet operation
- Sink strainers sold separately
- Sink clips included
- Color/Finish: Satin Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1112

SKU	Holes
PFSR3321653	3
PFSR3321654	4

Double Bowl Kitchen Sinks



- Self-rimming
- Overall Size: 33" x 22"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 6 1/2"
- Double equal bowls
- Drain Opening: 3 1/2"
- Sink clips included
- Under spray coating and pads for sound deadening and insulation
- 6" deep sinks are ADA compliant
- Color/Finish: Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1112

SKU	Bowl Depth	Gauge	Holes
PFSR332263	6"	22	3
PFSR332264	6"	22	4
PFSR332263BP	6"	23	3
PFSR332264BP	6"	23	4
PFSR332273	7"	20	3
PFSR332274	7"	20	4
PFSR332283	8"	20	3
PFSR332284	8"	20	4

Double Bowl Kitchen Sinks



- Self-rimming
- Overall Size: 33" x 22"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 6 1/2"
- Double equal bowls
- Drain Opening: 3 1/2"
- 22 gauge stainless steel
- Undercoated and padded for quiet operation
- Sink strainers sold separately
- Sink clips included
- Color/Finish: Satin Stainless Steel
- **Optional accessories:**
  Bottom grid: PFG1112
  Brass disposer flange and stopper: MB132974 or MB132978

SKU	Holes
PFSR3322653	3
PFSR3322654	4

Double Bowl Kitchen Sinks



- Undermount
- Overall Size: 31 1/4" x 17 3/4"
- Bowl Size: 14" x 15 3/4"
- Bowl Depth: 9"
- Double equal bowls
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- **Optional accessories:**
  Bottom grid: PFG1112

SKU
PFUC206

Double Bowl Kitchen Sinks



- Undermount
- Overall Size: 31 3/4" x 20 1/2"
- Large Bowl Size: 13 1/2" x 18" x 10"
- Small Bowl Size: 14" x 15 3/4" x 8"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- **Optional accessories:**
  Bottom grid: PFG1315 (large bowl)
  Bottom grid: PFG912 (small bowl)

SKU
PFUC907

Double Bowl Kitchen Sinks



- Undermount
- Overall Size: 31 1/4" x 20 1/2"
- Bowl Size: 13 1/2" x 18"
- Bowl Depth: 9"
- Double equal bowls
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- **Optional accessories:**
  Bottom grid: PFG1015

SKU
PFUC208

Sink Clips



- For use with self-rimming stainless steel sinks
- Package Quantity: 10/box

SKU
PFCLIP

Double Bowl Kitchen Sinks



- Undermount
- Overall Size: 31 3/4" x 20 1/2"
- Small Bowl Size: 14" x 15 3/4" x 8"
- Large Bowl Size: 13 1/2" x 18" x 10"
- Drain Opening: 3 1/2"
- 18 gauge stainless steel
- **Optional accessories:**
  Bottom grid: PFG1315 (large bowl)
  Bottom grid: PFG912 (small bowl)

SKU
PFUC907R

Sink Clips



- For use with undermount sinks
- Package Quantity: 10/box

SKU
PFUCCLIP

Basket Strainers

SKU	Series	Drain Size	Body Material	Color/Finish	Basket Material	Mounting	Sealing	Type
PF151ACP	Premium	3 1/2"	Forged Brass	Chrome	Brass	Slip & Locknut	Adjustable Post	Brass Nuts with Tailpiece
PF151CP	Premium	3 1/2"	Forged Brass	Chrome	Brass	Slip & Locknut	Adjustable Post	Brass Nuts
PF250BRCP	Premium	3 1/2"	Brass	Chrome	Stainless	Slip & Locknut	Fixed Post	Brass Nuts
PF250PC	Premium	3 1/2"	Brass	Chrome	Stainless	Slip & Locknut	Fixed Post	Zinc Nuts
PFWTS	Premium	3 1/2"	Brass	Chrome	Brass	Slip & Locknut	Grid Strainer	Zinc Locknut & Brass Slip Nut
PF1433BRSS	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Twist and Lock	Brass Nuts
PF1433SS	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Twist and Lock	Zinc Nuts
PF646443	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Thumbscrew Flange	Fixed Post	Brass Nuts
PF647003	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Fixed Post	Zinc Nuts
PF1432SS	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Deep Cup Nut	Fixed Post	Zinc Nuts
PF1434BRSS	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Deep Cup Nut	Ball Lock	Brass Nuts
PF1434SS	Standard	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Deep Cup Nut	Ball Lock	Zinc Nuts
PF1430SS	Economy	3 1/2"	ABS Plastic	Stainless Steel	Stainless	Slip & Locknut	Fixed Post	Plastic Nuts
PF1431BRSS	Economy	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Fixed Post	Brass Nuts
PF1431SS	Economy	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Fixed Post	Zinc Nuts
PF1435SS	Economy	3 1/2"	Stainless Steel	Stainless Steel	Stainless	Shallow Cup Nut	Fixed Post	Zinc Nuts
PF73BRCP	Junior	2 1/2"	Brass	Chrome	Brass	Slip & Locknut	Grid Basket	Brass Nuts
PF73CP	Junior	2 1/2"	Brass	Chrome	Brass	Slip & Locknut	Grid Basket	Zinc Nuts
PF83BRSS	Junior	2 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Drop-In	Brass Nuts
PF83SS	Junior	2 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Drop-In	Zinc Nuts
PF93SS	Junior	2 1/2"	Stainless Steel	Stainless Steel	Stainless	Slip & Locknut	Grid Strainer with Rubber Stopper	Zinc Nuts

Replacement Parts:
PF1431SSB: Replacement basket for; PF1431SS, PF1431BRSS, PF1432SS, PF250PC, PF250BRCP & PF647003
PFBSG: 3mm replacement washer for all basket strainers, 10 pack

Air Gaps



MONOGRAM BRASS™

- Brass cap
- Plastic body

SKU	Color/Finish
MB141BN	Brushed Nickel
MB141CP	Chrome
MB141ORB	Oil Rubbed Bronze
MB141PN	Polished Nickel

Air Gaps



PROFLO

- Prevents backflow from dishwasher into water system
- Plastic body construction
- Includes chrome plated plastic cap

SKU
PFGAPCP

Basket Strainer Washers



PROFLO

- Thickness: 3mm
- Washers for basket strainer repair
- Package Quantity: 10

SKU
PFBSG

Basket Strainers



MONOGRAM BRASS™

- Drain Diameter: 3 1/2"
- Brass construction

SKU	Color/Finish
MB171BN	Brushed Nickel
MB171CP	Chrome
MB171ORB	Oil Rubbed Bronze
MB171PN	Polished Nickel
MB171SS	Stainless Steel
MB171WH	White

Basket Strainers



MONOGRAM BRASS™

- Drain Diameter: 3 1/2"
- ABS plastic construction

SKU	Color/Finish
MB172BLK	Black
MB172BS	Biscuit
MB172WH	White

Basket Strainers



MONOGRAM BRASS™

- Drain Diameter: 2"
- Fits bar and laundry sinks
- Brass construction

SKU	Color/Finish
MB173BN	Brushed Nickel
MB173ORB	Oil Rubbed Bronze

Basket Strainers



PROFLO

- Economy Series
- Fits 3 1/2" opening
- With stainless steel clad trim and basket
- Fixed post style basket
- Plastic nuts
- ABS plastic body

SKU
PF1430SS

Basket Strainers



PROFLO

- Economy Series
- Fits 3 1/2" opening
- Fixed post style basket
- Stainless steel basket and body
- **Optional accessories:**
  Replacement basket: PF1431SSB

SKU	Type
PF1431BRSS	With Brass Nuts
PF1431SS	With Die Cast Nuts

Basket Strainers



- Standard Series - Deep Cup
- Fits 3 1/2" opening
- Die cast nuts
- Fixed post style basket
- Deep cup stainless steel basket and body
- **Optional accessories:**
  Replacement basket: PF1431SSB

SKU
PF1432SS

Basket Strainers



- Premium Series
- Forged brass body
- Adjustable post basket
- Heavy duty commercial design
- Solid brass slipnut and locknut
- 8mm locknut washer
- Color/Finish: Chrome

SKU	Size
PF151ACP	3 1/2" with 1 1/2" x 4" tailpiece
PF151CP	3 1/2"

Basket Strainers



- Standard Series
- Fits 3 1/2" opening
- Twist and lock style basket with positive seal
- Stainless steel basket and body

SKU	Type
PF1433BRSS	With Brass Nut
PF1433SS	With Die Cast Nut

Basket Strainers



- Premium Series
- Fits 3 1/2" opening
- Brass body
- Fixed post basket
- 8mm locknut washer
- Color/Finish: Chrome
- **Optional accessories:**
  Replacement basket: PF1431SSB

SKU	Type
PF250BRCP	With Brass Nuts
PF250PC	With Die Cast Nuts

Basket Strainers



- Standard Series - Deep Cup
- Fits 3 1/2" opening
- Brass ball lock style basket
- Deep cup stainless steel basket and body

SKU	Type
PF1434BRSS	With Brass Nuts
PF1434SS	With Die Cast Nuts

Basket Strainers



- Standard Series
- Fits 3 1/2" opening
- Triangular threaded flange with three thumbscrews for easy installation
- Fixed post style basket
- Brass nut
- Stainless steel basket and body

SKU
PF646443

Basket Strainers



- Economy Series
- Fits 3 1/2" opening
- Die cast nuts
- Fixed post style basket
- Shallow cup stainless steel basket and body

SKU
PF1435SS

Basket Strainers



- Standard Series
- Fits 3 1/2" opening
- Die cast nuts
- Fixed post style basket
- Stainless steel basket and body
- **Optional accessories:**
  Replacement basket: PF1431SSB

SKU
PF647003

Basket Strainers



- Junior
- Fits 2 1/2" opening
- Deep drop in sediment basket
- Chrome brass basket and body

SKU	Type
PF73BRCP	With Brass Nuts
PF73CP	With Die Cast Nuts

Basket Strainers



- Junior
- Flat top grid strainer
- Fits 2 1/2" opening
- Includes optional rubber stopper
- Die cast nuts
- Stainless steel body and strainer

SKU
PF93SS

Basket Strainers



- Junior
- Fits 2 1/2" opening
- Standard drop in basket with fixed zinc post
- Stainless steel basket and body

SKU	Type
PF83BRSS	With Brass Nuts
PF83SS	With Die Cast Nuts

Basket Strainers



- Fits 3 1/2" opening
- Stainless steel grid
- Brass body
- Does not include tailpiece
- Chrome brass construction

SKU
PFWTS

Stainless Steel Basket Strainer Collection



PF1432SS
- Fits 3 1/2" diameter opening
- Extra deep cup stainless steel body with locking shell
- Long shank with deep cut threads
- Fixed post stainless steel basket
- 8mm rubber locknut washer
- Zinc locknut & slip nut



PF1433SS/PF1433BRSS
- Fits 3 1/2" diameter opening
- Stainless steel threaded deep body
- Twist & lock stainless steel basket
- 8mm rubber locknut washer
- Zinc locknut & slip nut
- PF1433BRSS includes brass locknut & slip nut



PF646443
- Fits 3 1/2" diameter opening
- Stainless steel body
- Fixed post stainless steel spring style basket
- 8mm rubber locknut washer
- Thumb screw locknut & ring with 3 screws
- Brass slip nut



PF647003
- Fits 3 1/2" diameter opening
- Stainless steel threaded deep body
- Fixed post stainless steel basket
- 8mm rubber locknut washer
- Zinc wide locknut & slip nut



PF1434SS/PF1434BRSS
- Fits 3 1/2" diameter opening
- Extra deep cup stainless steel body with locking shell
- Long shank with deep cut threads
- Ball lock stainless steel basket
- 8mm rubber locknut washer
- Zinc locknut & slip nut
- PF1434BRSS includes brass locknut & slip nut

Disposal Flanges



MONOGRAM BRASS™

- With stopper
- Push in over existing flange
- Fits InSinkErator®, Whirlpool, GE, Kenmore and KitchenAid
- ABS plastic construction

SKU	Color/Finish
MB161BLK	Black
MB161BS	Biscuit
MB161WH	White

Disposal Flanges



MONOGRAM BRASS™

- Fits InSinkErator®, Emerson, Whirlpool, GE, Kenmore and KitchenAid
- Brass construction

SKU	Color/Finish
MB162BN	Brushed Nickel
MB162BS	Biscuit
MB162CP	Chrome
MB162ORB	Oil Rubbed Bronze
MB162PN	Polished Nickel
MB162SS	Stainless Steel
MB162WH	White

Disposal Flanges



MONOGRAM BRASS™

- Fits InSinkErator®
- Extended disposal flange with stopper
- Brass construction

SKU	Color/Finish
MB163CP	Chrome
MB163ORB	Oil Rubbed Bronze
MB163SS	Stainless Steel

Premium Brass Basket Strainer Collection



PF151CP

- Fits 3 1/2" diameter opening
- Solid forged brass body
- Adjustable post brass basket
- 8mm rubber locknut washer
- Solid brass locknut & slip nut



PF151ACP

- Fits 3 1/2" diameter opening
- Solid forged brass body
- Adjustable post brass basket
- Includes 1 1/2" x 4" chrome-plated 20 gauge tailpiece
- 8mm rubber locknut washer
- Solid brass locknut & slip nut



PF250PC/PF250BRCP

- Fits 3 1/2" diameter opening
- Solid brass body with deep cut threads
- Fixed post stainless steel basket
- 8mm rubber locknut washer
- Die cast locknut & slip nut
- PF250BRCP includes solid brass locknut & slip nut

Mop Basin Guards



- Stainless steel bumper guard
- Package Quantity: 1 guard/pack

SKU	Length
PFBG24S	24"
PFBG36S	36"


Mop Basin Guards



- Vinyl bumper guard
- PFBG24V includes 2 - 24" guards
- PFBG36V includes 1 - 36" guard and 1 - 24" guard

SKU	Length
PFBG24V	24"
PFBG36V	36"

Mop Basin Wall Guards



- Stainless steel wall guard set
- PFWG24S includes 2 - 24" L x 12" H guards
- PFWG36S includes 1 - 36" L x 12" H guard and 1 - 24" L x 12" H guard

SKU	Length
PFWG24S	24"
PFWG36S	36"

Mop Basins



- Molded of high density composite
- Stainless steel strainer
- 36" model includes integrally molded, self-draining mop shelf
- Color/Finish: White
- **Optional accessories:**
  24" Bumper guard: PFBG24S or PFBG24V
  36" Bumper guard: PFBG36S or PFBG36V
  24" Wall guard set: PFWG24S
  36" Wall guard set: PFWG36S
  Pipe reducer: PFMBQD

SKU	Size	Drain Opening
PFMB2424	24" x 24" x 10"	PVC
PFMB2424S	24" x 24" x 10"	Stainless
PFMB3624S	36" x 24" x 10"	Stainless

Mop Hangers



- 3 hangers
- For use with service sinks

SKU
PF245

Laundry Sinks



- Overall Size: 24 1/2" x 22"
- Molded of super compressed composite
- Self-rimming design
- Drain Opening: 1 1/2"
- Color/Finish: White

SKU
PFLT2522D

Laundry Sinks



PROFLO

- Overall Size: 20" x 24"
- Polypropylene construction with integral strainer
- Includes white baked enamel steel angle legs
- 4" knock-out centerset faucet holes
- Color/Finish: White

SKU
PFLT2024

Laundry Sinks



PROFLO

- Overall Size: 23" x 21 1/2"
- Molded of super compressed composite
- Includes white baked enamel steel angle legs
- 4" knock-out centerset faucet holes
- Color/Finish: White

SKU	Installation
PFLT2123	Freestanding
PFLT2123W	Wall Mount

Laundry Sinks




PROFLO

- Overall Size: 40" x 24"
- Molded of super compressed composite
- Includes white baked enamel steel angle legs
- 4" knock-out centerset faucet holes
- Color/Finish: White

SKU	Installation
PFLT4024	Freestanding
PFLT4024W	Wall Mount







Laundry Sink Faucets
P. 176-177



What can we help you find?

Tubular 77-90
Testing 91-92
Specialty 93-95
Toilet Repair 96-101
Supply 102-117
Supports 118-123
Brass Fittings 124-134
Drains 135-142
Wall Faucets & Hydrants 143-147
Plumbing Valves 148-154
Pumps 155-158
Cast Iron 159-161
Repair 162-165

P-Traps



MONOGRAM BRASS™

- 1 1/2" tube outlet x 1 1/4" slip joint inlet
- 20 gauge
- With stainless steel high box flange
- Brass construction

SKU	Color/Finish
MB361BN	Brushed Nickel
MB361CP	Chrome
MB361ORB	Oil Rubbed Bronze
MB361PN	Polished Nickel

P-Traps



MONOGRAM BRASS™

- 1 1/4" tub inlet x 1 1/4" outlet
- 17 gauge
- Deep wall flange
- Brass construction

SKU	Color/Finish
MB363BN	Brushed Nickel
MB363CP	Chrome

P-Traps



MONOGRAM BRASS™

- 1 1/4" tube outlet x 1 1/4" slip joint inlet
- 20 gauge
- With stainless steel high box flange
- Brass construction

SKU	Color/Finish
MB362BN	Brushed Nickel
MB362CP	Chrome
MB362ORB	Oil Rubbed Bronze
MB362PB	Polished Brass
MB362PN	Polished Nickel

P-Traps



PROFLO

- P-Trap without cleanout
- 17 gauge
- Brass nuts
- Box flange
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFPTB100	1 1/4"
PFPTB103	1 1/4" x 1 1/2"
PFPTB107	1 1/2"

P-Traps



- P-Trap with cleanout
- 17 gauge
- Brass nuts
- Box flange
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFPTB101	1 1/4"
PFPTB104	1 1/4" x 1 1/2"
PFPTB108	1 1/2"

P-Traps



- P-Trap with cleanout
- 17 gauge
- Semi-cast design
- Cast brass body and tubular wall bend
- Zinc nuts
- Shallow flange
- Brass construction

SKU	Size
PFPTB102	1 1/4" x 1 1/4"
PFPTB106	1 1/4" x 1 1/2"
PFPTB109	1 1/2" x 1 1/2"

P-Traps



- P-Trap without cleanout
- 17 gauge
- Ground joint connection
- Brass construction

SKU	Size	Color/Finish
PFPTB105	1 1/4" x 1 1/2"	Chrome
PFPTB110	1 1/2" x 1 1/2"	Chrome
PFPTB111	1 1/2" x 1 1/2"	Unfinished

P-Traps



- P-Trap without cleanout
- 1 1/4"
- Brass nuts
- Shallow flange
- Brass construction

SKU	Gauge	Color/Finish
PFPTB112	17	Chrome
PFPTB202	20	Unfinished

P-Traps



- P-Trap without cleanout
- Zinc nuts
- Box flange
- Brass construction
- Color/Finish: Chrome

SKU	Size	Gauge
PFPTB200	1 1/4"	20
PFPTB300	1 1/4"	22
PFPTB201	1 1/2"	20
PFPTB301	1 1/2"	22

P-Traps



- 17 gauge
- Semi-cast design
- Cast brass body and tubular wall bend
- Brass nuts
- Box flange
- Brass construction
- Color/Finish: Chrome

SKU	Size	Cleanout Included
PFPTB400	1 1/4" x 1 1/4"	Yes
PFPTB401	1 1/2" x 1 1/4"	Yes
PFPTB402	1 1/2" x 1 1/4"	No
PFPTB403	1 1/2" x 1 1/2"	Yes
PFPTB404	1 1/2" x 1 1/2"	No

P-Traps



- Cast brass body and wall bend
- Threaded outlet
- Color/Finish: Chrome

SKU	Size	Cleanout Included
PFPTB500	1 1/4" x 1 1/2"	Yes
PFPTB501	1 1/4" x 1 1/2"	No
PFPTB502	1 1/2" x 1 1/2"	Yes
PFPTB503	1 1/2" x 1 1/2"	No

Sink Traps



- 1 1/2"
- 17 gauge
- Slip joint adapter
- Cast brass threaded elbow
- Brass construction
- LA Code approved

SKU	Color/Finish
PFSTB100	Chrome
PFSTB101	Unfinished

Sink Traps



- 1 1/2"
- 17 gauge
- Includes cover tube
- Brass construction
- Color/Finish: Chrome

SKU	Cleanout Included
PFSTB102	No
PFSTB103	Yes

Trap Adapters



- Brass body
- Brass slip ring
- Die cast nut

SKU	Connection
PF2000	1 1/4" MIP x 1 1/4" Slip Joint
PF2030	1 1/4" FIP x 1 1/4" Slip Joint
PF2010	1 1/2" MIP x 1 1/4" Slip Joint
PF2040	1 1/2" FIP x 1 1/4" Slip Joint
PF2020	1 1/2" MIP x 1 1/2" Slip Joint
PF2050	1 1/2" FIP x 1 1/2" Slip Joint

Branch Tailpieces



- Slip joint adapter
- Includes brass nut and washer (PFTPB305 includes Zinc nut)
- 20 gauge
- Brass construction

SKU	Size	Nuts	Color/Finish
PFTPB300	1 1/4" x 8"	Brass	Chrome
PFTPB301	1 1/4" x 8"	Brass	Unfinished
PFTPB305	1 1/2" x 8"	Zinc	Chrome
PFTPB306	1 1/2" x 8"	Brass	Chrome
PFTPB307	1 1/2" x 8"	Brass	Unfinished

Branch Tailpieces



- 1 1/4" x 8"
- 20 gauge
- Threaded top
- Brass construction
- Color/Finish: Chrome

SKU
PFTPB302

Branch Tailpieces



- Direct connect
- Captive nut and washer
- 22 gauge
- Brass construction
- Color/Finish: Unfinished

SKU	Size
PFTPB304	1 1/2" x 6"
PFTPB303	1 1/2" x 12"

Branch Tailpieces



- 1 1/2" x 8"
- Direct connect
- Captive nut and washer
- 17 gauge
- Brass construction
- Color/Finish: Chrome

SKU	Connection
PFTPB308	1/2" Sweat
PFTPB309	3/4" Sweat

Branch Tailpieces



- 1 1/2" x 6"
- 1/2" sweat or 3/4" hose thread
- 17 gauge
- Color/Finish: Rough Brass

SKU
PFTPB310

Branch Tailpieces



- 1 1/2" x 8"
- Direct connect
- Captive nut and washer
- Includes TPR washer
- Polypropylene construction

SKU	Branch Diameter	Color/Finish
PFTPP300	5/8"	White
PFTPP301	7/8"	White
PFTPP302	7/8"	Black

Branch Tailpieces



- 1 1/2" x 8"
- Slip joint adapter
- Includes nut and washer
- Polypropylene construction

SKU	Branch Diameter	Color/Finish
PFTPP400	5/8"	White
PFTPP401	7/8"	White
PFTPP402	7/8"	Black

Flanged Tailpieces



- Single flanged end
- Brass construction

SKU	Size	Gauge	Color/Finish
PFTPB100	1 1/2" x 4"	17	Chrome
PFTPB108	1 1/2" x 4"	20	Chrome
PFTPB105	1 1/2" x 4"	20	Unfinished
PFTPB101	1 1/2" x 6"	17	Chrome
PFTPB109	1 1/2" x 6"	20	Chrome
PFTPB106	1 1/2" x 6"	20	Unfinished
PFTPB113	1 1/2" x 6"	22	Chrome
PFTPB102	1 1/2" x 8"	17	Chrome
PFTPB110	1 1/2" x 8"	20	Chrome
PFTPB107	1 1/2" x 8"	20	Unfinished
PFTPB114	1 1/2" x 8"	22	Chrome
PFTPB103	1 1/2" x 12"	17	Chrome
PFTPB111	1 1/2" x 12"	20	Chrome
PFTPB104	1 1/2" x 12"	20	Unfinished
PFTPB112	1 1/2" x 12"	22	Chrome

Flanged Tailpieces



- 1 1/2" x 16"
- Double flanged ends
- Brass construction

SKU	Gauge	Color/Finish
PFTPB200	20	Chrome
PFTPB201	20	Unfinished
PFTPB202	22	Chrome

Flanged Tailpieces



- Single flanged end
- Includes TPR washer
- Polypropylene construction

SKU	Size	Color/Finish
PFTPP100	1 1/2" x 4"	White
PFTPP101	1 1/2" x 6"	White
PFTPP104	1 1/2" x 6"	Black
PFTPP102	1 1/2" x 8"	White
PFTPP105	1 1/2" x 8"	Black
PFTPP103	1 1/2" x 12"	White
PFTPP106	1 1/2" x 12"	Black

Flanged Tailpieces



PROFLO

- 1 1/2" x 16"
- Double flanged ends
- Includes TPR washer
- Polypropylene construction

SKU	Color/Finish
PFTPP200	White
PFTPP201	Black

Trap Primer Tailpieces



PROFLO

- Semi-cast branch connection
- 5/8" OD compression branch
- Brass construction
- Color/Finish: Chrome

SKU	Size
PF127033	1 1/4"
PF127044	1 1/2"

Extension Tubes



MONOGRAM BRASS™

- 1 1/4" x 8" OD
- 17 gauge
- Includes nut and washer
- Brass construction

SKU	Color/Finish
MB341BN	Brushed Nickel
MB341ORB	Oil Rubbed Bronze
MB341PN	Polished Nickel

Extension Tubes



PROFLO

- Threaded on both ends
- Brass construction

SKU	Size	Gauge	Color/Finish
PFETB406	1 1/4" x 6"	17	Chrome
PFETB400	1 1/4" x 6"	20	Chrome
PFETB407	1 1/4" x 8"	17	Chrome
PFETB402	1 1/4" x 8"	20	Chrome
PFETB408	1 1/4" x 12"	17	Chrome
PFETB403	1 1/4" x 12"	20	Chrome
PFETB401	1 1/2" x 6"	20	Chrome
PFETB404	1 1/2" x 8"	20	Chrome
PFETB409	1 1/2" x 12"	17	Chrome
PFETB405	1 1/2" x 12"	20	Chrome
PFETB410	1 1/2" x 12"	20	Unfinished

Extension Tubes



PROFLO

- Solder connection
- Brass construction
- Color/Finish: Chrome

SKU	Size	Gauge
PFETB501	1 1/4" x 6"	17
PFETB502	1 1/4" x 8"	17
PFETB503	1 1/4" x 12"	17
PFETB505	1 1/4" x 12"	20
PFETB500	1 1/2" x 12"	17
PFETB504	1 1/2" x 12"	20



Shower Arms: P. 26

Extension Tubes



- Slip joint adapter
- Includes nut and washer
- Zinc nuts (Except PFETB612- brass nuts)
- Brass construction
- Color/Finish: Chrome

SKU	Size	Gauge
PFETB608	1 1/4" x 6"	17
PFETB603	1 1/4" x 6"	20
PFETB615	1 1/4" x 6"	22
PFETB606	1 1/4" x 8"	17
PFETB604	1 1/4" x 8"	20
PFETB616	1 1/4" x 8"	22
PFETB609	1 1/4" x 12"	17
PFETB605	1 1/4" x 12"	20
PFETB614	1 1/4" x 12"	22
PFETB610	1 1/2" x 6"	17
PFETB600	1 1/2" x 6"	20
PFETB617	1 1/2" x 6"	22
PFETB607	1 1/2" x 8"	17
PFETB601	1 1/2" x 8"	20
PFETB618	1 1/2" x 8"	22
PFETB611	1 1/2" x 12"	17
PFETB602	1 1/2" x 12"	20
PFETB612	1 1/2" x 12"	20
PFETB613	1 1/2" x 12"	22

Extension Tubes



- Double slip joint
- Includes nuts and washers
- Brass construction

SKU	Size	Gauge	Color/Finish
PFETB700	1 1/4" x 16"	20	Chrome
PFETB703	1 1/4" x 16"	22	Chrome
PFETB701	1 1/2" x 16"	20	Unfinished
PFETB702	1 1/2" x 16"	20	Chrome
PFETB704	1 1/2" x 16"	22	Chrome

Extension Tubes



- 22 gauge
- Double offset slip joint
- Includes nuts and washers
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFETB800	1 1/4"
PFETB801	1 1/2"

Extension Tubes



- Slip joint adapter
- Includes nuts and washers
- Includes TPR washer
- Polypropylene construction

SKU	Size	Color/Finish
PFETP600	1 1/2" x 6"	White
PFETP601	1 1/2" x 8"	White
PFETP603	1 1/2" x 8"	Black
PFETP602	1 1/2" x 12"	White
PFETP604	1 1/2" x 12"	Black

Extension Tubes



- Slip joint adapter
- Double ended
- Includes nuts and washers
- Includes TPR washer
- Polypropylene construction

SKU	Size	Color/Finish
PFETP702	1 1/4" x 16"	White
PFETP700	1 1/2" x 16"	White
PFETP701	1 1/2" x 16"	Black

End Outlet Continuous Waste



- 1 1/2"
- Length: 16"
- Slip joint connection
- Baffle tee
- Brass construction
- Color/Finish: Chrome (except PFEWB108 - unfinished)

SKU	Gauge	Nuts
PFEWB100	17	Brass
PFEWB107	20	Zinc
PFEWB108	20	Brass

End Outlet Continuous Waste



- 1 1/2"
- Cast tee
- Zinc nuts
- Brass construction
- Color/Finish: Chrome

SKU	Length	Gauge	Connection
PFEWB105	16"	17	DC
PFEWB106	16"	17	SJ
PFEWB103	16"	20	DC
PFEWB104	16"	20	SJ
PFEWB110	16"	22	DC
PFEWB112	16"	22	SJ
PFEWB111	16 1/8"	22	DC
PFEWB102	21"	17	SJ
PFEWB101	21"	20	SJ
PFEWB109	21"	22	SJ


End Outlet Continuous Waste



- 1 1/2" x 16"
- Includes TPR washer
- Polypropylene construction

SKU	Connection	Color/Finish
PFEWP100	SJ	White
PFEWP103	SJ	Black
PFEWP101	DC	White
PFEWP102	DC	Black


End Outlet Continuous Waste Disposer Kits



- 1 1/2" x 13"
- Slip joint adapter
- 17 gauge
- Zinc nuts
- Does not include P-Trap
- Brass construction
- Color/Finish: Chrome

SKU
PFEWB200

End Outlet Continuous Waste Disposer Kits



- 1 1/2" x 13"
- Slip joint adapter
- Does not include P-Trap
- Includes TPR washer
- Polypropylene construction

SKU	Color/Finish
PFEWP200	White
PFEWP201	Black Adjacent Arm
PFEWP202	Black

J-Bends



- Connection: Slip Joint
- Includes nuts and washers
- Includes poly and TPR washers
- Brass construction
- Color/Finish: Chrome

SKU	Size	Gauge
PFJBB100	1 1/4"	17
PFJBB101	1 1/4"	20
PFJBB200	1 1/2"	17
PFJBB201	1 1/2"	20

Sink J-Bends



- Connection: Slip Joint
- Includes nuts and washers
- Includes poly and TPR washers
- Brass construction

SKU	Size	Gauge	Color/Finish
PFJBB300	1 1/4"	22	Chrome
PFJBB400	1 1/2"	17	Chrome
PFJBB401	1 1/2"	17	Rough Brass
PFJBB402	1 1/2"	20	Chrome

Sink J-Bends



- 1 1/2"
- Connection: Ground Joint
- 20 gauge
- Includes nuts and washers
- Includes poly and TPR washers
- Brass construction
- Color/Finish: Polished Chrome

SKU
PFJBB403

Tubular Repair Fittings



- 45° elbow
- 22 gauge
- Slip joint adapter
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFTRC100	1 1/4"
PFTRC101	1 1/2"

Tubular Repair Fittings



- 90° elbow
- 22 gauge
- Slip joint adapter
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFTRC102	1 1/4"
PFTRC103	1 1/2"

Tubular Repair Fittings



- Straight coupling
- 22 gauge
- Slip joint adapter
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFTRC104	1 1/4"
PFTRC105	1 1/2"

Wall Bends



- 17 gauge
- Brass construction
- Color/Finish: Chrome

SKU	Size
PFWBB102	1 1/4" x 15"
PFWBB201	1 1/2" x 9"
PFWBB204	1 1/2" x 18"

Waste Arms



- Connection: Slip Joint
- Includes nuts and washers
- Includes poly and TPR washers
- Brass construction

SKU	Size	Gauge	Color/Finish
PFWAB101	1 1/2" x 11 1/2"	17	Chrome
PFWAB112	1 1/2" x 11 1/2"	20	Chrome
PFWAB201	1 1/2" x 15"	17	Chrome
PFWAB107	1 1/2" x 15"	20	Chrome
PFWAB206	1 1/2" x 15"	22	Chrome
PFWAB113	1 1/2" x 15"	22	Rough Brass

P-Traps



- 1 1/4" x 1 1/2"
- Includes all necessary parts
- Polypropylene construction
- Includes Marvel adapter

SKU	Color/Finish
PFPTP100	White
PFPTP101	Black
PFPTP102	White/Black

P-Traps



- 1 1/2" x 1 1/2"
- Includes extension tube
- Includes 1 1/2" and 2" PVC solvent weld elbow
- Includes TPR washer
- Polypropylene construction
- Color/Finish: White

SKU
PFPTP103

P-Traps



- 1 1/4" x 1 1/4"
- Does not include Marvel connector or escutcheon
- Includes TPR washer
- Polypropylene construction
- Color/Finish: White

SKU
PFPTP104

P-Traps



- 1 1/2" x 1 1/2"
- Slip joint adapter with PVC solvent weld
- Includes TPR washer
- Polypropylene construction
- Color/Finish: White

SKU
PFPTP105

P-Traps



- 1 1/4" x 1 1/2"
- Includes 1 1/2" and 1 1/2" x 1 1/4" nuts and washers
- Includes TPR washer
- Polypropylene construction
- Color/Finish: Chrome

SKU
PFPTP200

S-Traps



- Slip joint adapter
- Includes Marvel connector
- Includes 1 1/2" nuts and washers and reducing washers
- Includes TPR washer
- Polypropylene construction

SKU	Size	Color/Finish
PFSTP100	1 1/4"	White
PFSTP101	1 1/2"	White
PFSTP102	1 1/2"	Black

Center Outlet Continuous Waste



- 1 1/2" x 16"
- Slip joint adapter
- Does not include basket strainer
- Includes TPR washer
- Polypropylene construction

SKU	Color/Finish
PFCWP100	White
PFCWP102	Black

Center Outlet Continuous Waste

- 1 1/2" x 16"
- Slip joint or direct connect adapter
- Does not include basket strainer
- Includes TPR washer
- Polypropylene construction
- Color/Finish: White

SKU
PFCWP101

Molded Trap Covers



- P-Trap Cover Only
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PF200WH

Molded Trap Covers



- P-Trap & One Supply Cover
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PF201WH

Molded Trap Covers



- P-Trap & Two Supply Covers
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PF202WH

Molded Trap Covers



- Offset Tailpiece Cover
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PF205WH

Molded Trap Covers



- P-Trap, Two Supply & Offset Tailpiece Covers
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PF203WH

Molded Trap Covers



- One Supply Cover Only
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- ADA, CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PF299WH

Trap Covers

SKU	Type	Color/Finish	P-Trap	Supplies	Offset
PF200WH	Molded	White	1	-	-
PF201WH	Molded	White	1	1	-
PF202WH	Molded	White	1	2	-
PF203WH	Molded	White	1	2	1
PF205WH	Molded	White	-	-	1
PF299WH	Molded	White	-	1	-
PFEXT200WH	Molded	White	EXT	-	-
PFSCPTWH	Soft	White	1	-	-
PFSCPTBK	Soft	Black	1	-	-
PFSCPT1SWH	Soft	White	1	1	-
PFSCPT1SBK	Soft	Black	1	1	-
PFSCPT2SWH	Soft	White	1	2	-
PFSCPT2SBK	Soft	Black	1	2	-
PFSCPT2SOFFWH	Soft	White	1	2	1
PFSCPT2SOFFBK	Soft	Black	1	2	1
PFSCOFFWH	Soft	White	TLPC	-	1
PFSC1SWH	Soft	White	-	1	-
PFSC1SBK	Soft	Black	-	1	-

Molded Trap Covers



PROFLO

- Tailpiece/Drain Waste Cover Only
- Length: 16"
- SnapClip™ fasteners
- Universal flexible design fits virtually all P-Trap assemblies
- E-Z Tear-to-fit feature
- Antimicrobial vinyl
- Color/Finish: White
- Made in USA
- CABO/ANSI, UFAS, cUPC/IAPMO ICC and Canada barrier-free compliant

SKU
PFEXT200WH

Soft Trap Covers



PROFLO

- One Supply Cover Only
- Installs quick and easy with Velcro®
- Universal flexible design fits virtually all P-Trap assemblies
- Valve and supply has a soft flexible design that allows for over 360° flexibility
- Smooth high gloss finish with UV, antimicrobial/antifungal properties
- Made in USA
- PVC insulation material is Class A fire rated and meets ASTM E84 with a 25 Flame and 450 Smoke rating
- ADA, IBC, ICC/ANSI, IPC, UPC and Canada barrier-free compliant

SKU	Color/Finish
PFSC1SBK	Black
PFSC1SWH	White

Soft Trap Covers



PROFLO

- Offset Tailpiece Cover
- Installs quick and easy with Velcro®
- Universal flexible design fits virtually all P-Trap assemblies
- Valve and supply has a soft flexible design that allow for over 360° flexibility
- Smooth high gloss finish with UV, antimicrobial/antifungal properties
- Color/Finish: White
- Made in USA
- PVC insulation material is Class A fire rated and meets ASTM E84 with a 25 Flame and 450 Smoke rating
- IBC, ICC/ANSI and Canada barrier-free compliant

SKU
PFSCOFFWH

Soft Trap Covers



PROFLO

- P-Trap & One Supply Cover
- Installs quick and easy with Velcro®
- Universal flexible design fits virtually all P-Trap assemblies
- Valve and supply has a soft flexible design that allow for over 360° flexibility
- Smooth high gloss finish with UV, antimicrobial/antifungal properties
- Made in USA
- PVC insulation material is Class A fire rated and meets ASTM E84 with a 25 Flame and 450 Smoke rating
- ADA, IBC, ICC/ANSI, IPC, UPC and Canada barrier-free compliant

SKU	Color/Finish
PFSCPT1SBK	Black
PFSCPT1SWH	White

Soft Trap Covers



PROFLO

- P-Trap & Two Supply Covers
- Installs quick and easy with Velcro®
- Universal flexible design fits virtually all P-Trap assemblies
- Valve and supply has a soft flexible design that allow for over 360° flexibility
- Smooth high gloss finish with UV, antimicrobial/antifungal properties
- Made in USA
- PVC insulation material is Class A fire rated and meets ASTM E84 with a 25 Flame and 450 Smoke rating
- ADA, IBC, ICC/ANSI, IPC, UPC and Canada barrier-free compliant

SKU	Color/Finish
PFSCPT2SBK	Black
PFSCPT2SWH	White

Soft Trap Covers



PROFLO

- P-Trap, Two Supply & Offset Tailpiece Covers
- Installs quick and easy with Velcro®
- Universal flexible design fits virtually all P-Trap assemblies
- Valve and supply has a soft flexible design that allow for over 360° flexibility
- Smooth high gloss finish with UV, antimicrobial/antifungal properties
- Made in USA
- PVC insulation material is Class A fire rated and meets ASTM E84 with a 25 Flame and 450 Smoke rating
- ADA, IBC, ICC/ANSI, IPC, UPC and Canada barrier-free compliant

SKU	Color/Finish
PFSCPT2SOFFBK	Black
PFSCPT2SOFFWH	White

Soft Trap Covers



- P-Trap Cover Only
- Installs quick and easy with Velcro®
- Universal flexible design fits virtually all P-Trap assemblies
- Valve and supply has a soft flexible design that allow for over 360° flexibility
- Smooth high gloss finish with UV, antimicrobial/antifungal properties
- Made in USA
- PVC insulation material is Class A fire rated and meets ASTM E84 with a 25 Flame and 450 Smoke rating
- ADA, IBC, ICC/ANSI, IPC, UPC and Canada barrier-free compliant

SKU	Color/Finish
PFSCPTBK	Black
PFSCPTWH	White

Escutcheons



- Sure grip
- 5/8" OD
- Steel construction

SKU	Color/Finish
MB271BN	Brushed Nickel
MB271CP	Chrome
MB271ORB	Oil Rubbed Bronze
MB271PB	Polished Brass
MB271PN	Polished Nickel

Escutcheons



- Sure grip
- 1/2" IPS
- Steel construction

SKU	Color/Finish
MB272BN	Brushed Nickel
MB272CP	Chrome
MB272ORB	Oil Rubbed Bronze
MB272PB	Polished Brass
MB272PN	Polished Nickel

Escutcheons



- Corrosion-proof
- Shallow, one-piece design
- High density polyethylene
- Material: Plastic

SKU	Size	Color/Finish
PFPE1WH	3/8" IPS	White
PFPE2CP	1/2" IPS	Chrome
PFPE2WH	1/2" IPS	White
PFPE6CP	1/2" CTS	Chrome
PFPE6WH	1/2" CTS	White
PFPE3CP	3/4" IPS	Chrome
PFPE3WH	3/4" IPS	White
PFPE7CP	3/4" CTS	Chrome
PFPE7WH	3/4" CTS	White
PFPE8CP	1" Tubular	Chrome
PFPE8WH	1" Tubular	White
PFPE9CP	1 1/4" Tubular	Chrome
PFPE9WH	1 1/4" Tubular	White
PFPE4CP	1 1/2" IPS	Chrome
PFPE4WH	1 1/2" IPS	White
PFPE5CP	2" IPS	Chrome
PFPE5WH	2" IPS	White

Escutcheons



- Fits chrome plated brass nipples or shower arms
- Set screw style
- Steel construction
- Color/Finish: Chrome

SKU	Size
PFSSE1	3/8"
PFSSE2	1/2"

Escutcheons



- For use with shower arms
- 1/2" IPS
- Steel construction
- Color/Finish: Chrome

SKU
PFS42

Escutcheons



- Fits iron pipe or copper tube
- Shallow style
- Steel construction

SKU	Size	Color/Finish
PFE1	3/8" IPS	Chrome
PFE2	1/2" IPS	Chrome
PFE2PB	1/2" IPS	Polished Brass
PFE7	1/2" CTS	Chrome
PFE7PB	1/2" CTS	Polished Brass
PFE8	3/4" IPS	Chrome
PFE9	3/4" CTS	Chrome
PFE9A	1" IPS	Chrome
PFE10	1 1/4" IPS	Chrome
PFE11	1 1/2" IPS	Chrome
PFE16A	2" IPS	Chrome

Escutcheons



- Iron pipe size
- Shallow, split design
- Material: ABS

SKU	Size	Color/Finish
PFSEDCP	1/2"	Chrome
PFSEDWH	1/2"	White
PFSEFCP	3/4"	Chrome
PFSEFWH	3/4"	White
PFSEGCP	1"	Chrome
PFSEGWH	1"	White
PFSEJCP	1 1/2"	Chrome
PFSEJWH	1 1/2"	White
PFSEKCP	2"	Chrome
PFSEKWH	2"	White

Escutcheons



- Copper tube size
- Shallow, split design
- Material: ABS

SKU	Size	Color/Finish
PFSEECP	1/2"	Chrome
PFSEEWH	1/2"	White
PFSE78ODCP	3/4"	Chrome
PFSE78ODWH	3/4"	White

Escutcheons - Bell



- Sure grip bell flange
- 5/8" OD
- Steel construction

SKU	Color/Finish
MB273BN	Brushed Nickel
MB273ORB	Oil Rubbed Bronze
MB273PN	Polished Nickel

Escutcheons - Bell



- Fits iron pipe or copper tube
- Steel construction
- Color/Finish: Chrome

SKU	Size
PFBE1	3/8" IPS
PFBE2	1/2" IPS
PFBE7	1/2" CTS
PFBE6X	5/8" CTS

Escutcheons - Box



- Fits iron pipe
- Steel construction
- Color/Finish: Chrome

SKU	Size
PFE36	1 1/4" IPS
PFE37	1 1/2" IPS

Escutcheons - Box



- Fits tubular
- Steel construction
- Color/Finish: Chrome

SKU	Size
PFE40	1 1/4" OD
PFE41	1 1/2" OD
PFE42	2" OD

Escutcheons - Deep Bell



- Fits iron pipe and tubular
- Steel construction
- Color/Finish: Chrome

SKU	Size
PFE32	1 1/4" OD
PFE34	1 1/4" IPS
PFE33	1 1/2" OD
PFE35	1 1/2" IPS

Flanged Tailpiece Washers



- 1 1/2"
- Polyethylene construction

SKU
PFT10

Floor/Ceiling Plates



- Fits iron pipe
- Steel construction
- Hinged design
- Color/Finish: Chrome

SKU	Size
PFF170	3/8" IPS
PFF171	1/2" IPS
PFF172	3/4" IPS
PFF173	1" IPS
PFF174	1 1/4" IPS
PFF175	1 1/2" IPS
PFF176	2" IPS

Floor/Ceiling Plates



- Fits copper tube
- Steel construction
- Hinged design
- Color/Finish: Chrome

SKU	Size
PFF171C	1/2" CTS
PFF172C	3/4" CTS
PFF173C	1" CTS
PFF174C	1 1/4" CTS
PFF175C	1 1/2" CTS

Slip Joint Washers



- Thermoplastic rubber (TPR)
- Flexible design provides positive seal
- Package Quantity: 10
- Color/Finish: Silver

SKU	Size
PFPWH	1 1/4"
PFPWJ	1 1/2"
PFPWJH	1 1/2" x 1 1/4"

Slip Joint Washers



- Beveled design
- Polyethylene construction

SKU	Size
PFSJP125	1 1/4"
PFSJP3	1 1/2"
PFSJP1	1 1/2" x 1 1/4"

Slip Nut Washers



- Rubber construction

SKU	Size
PFSNWH	1 1/4"
PFSNWJ	1 1/2"
PFSNWJH	1 1/2" x 1 1/4"

Slip Nuts



SKU	Size	Material	Color/Finish
PFSNH	1 1/4"	Zinc	Chrome
PFSNJ	1 1/2"	Zinc	Chrome
PFSNRBJ	1 1/2"	Solid Brass	Satin Bronze
PFSNJH	1 1/2" x 1 1/4"	Zinc	Chrome

Gas Test Gauges



- 2" face
- Complete assembly includes gauge and air valve
- Dual scale (psi/kpa)
- Brass block and valve
- **Optional accessories:**
  Gas test block: PFGTBA

SKU	Pressure Range
PFGG15K1	0-15 psi
PFGG30K	0-30 psi
PFGG60K	0-60 psi
PFGG100K	0-100 psi

Water Test Gauges



- 2 1/2" face
- Operating Pressure: 0–300 psi
- Connection: 3/4" GHT brass
- Dual scale (psi/kpa)

SKU	Type
PFWG300L	Without Indicator
PFWGI300L	With Indicator

Pressure Gauges



- Connection: 1/4" NPT brass lower mount
- Dual scale (psi/kpa)
- Steel case

SKU	Face Size	Pressure Range
PFPG15K1	2"	0-15 psi
PFPG30K	2"	0-30 psi
PFPG60K	2"	0-60 psi
PFPG100K	2"	0-100 psi
PFPG160K	2"	0-160 psi
PFPG200K	2"	0-200 psi
PFPG300K	2"	0-300 psi
PFPG5L	2 1/2"	0-5 psi
PFPG30L	2 1/2"	0-30 psi
PFPG60L	2 1/2"	0-60 psi
PFPG100L	2 1/2"	0-100 psi
PFPG160L	2 1/2"	0-160 psi
PFPG200L	2 1/2"	0-200 psi
PFPG300L	2 1/2"	0-300 psi
PFPG100N	3 1/2"	0-100 psi
PFPG200N	3 1/2"	0-200 psi
PFPG300N	3 1/2"	0-300 psi

Test Caps



- Plastic
- Solvent welds to PVC or ABS pipe
- High impact polystyrene construction

SKU	Size
PF131J	1 1/2"
PF131K	2"
PF131M	3"
PF131P	4"

Test Caps



- Plastic
- Multi-size design
- PVC construction

SKU	Size
PF34225	1 1/2" x 2"
PF34226	3" x 4"

Pressure Gauges



- Connection: 1/2" NPT brass lower mount
- Maximum Pressure: 100 psi
- Dual scale (psi/ksa)
- Bourdon tube style

SKU	Liquid Filled
PFXPG100K	No
PFXPGLF100K	Yes

Test Caps



- Heavy duty rubber cap with stainless steel clamp
- Must install with torque wrench not exceeding 60 in-lbs

SKU	Size
PFETCJ	1 1/2"
PFETCK	2"
PFETCM	3"
PFETCP	4"
PFETCS	5"
PFETCU	6"
PFETCX	8"

Test Caps



- Plastic
- Maximum Pressure: 50 psi
- Solvent weld over end of pipe
- Will not clog or go down pipe
- Heavy duty PVC
- Color/Finish: White

SKU	Size
PFTCJ	1 1/2"
PFTCK	2"
PFTCM	3"
PFTCP	4"

Test Caps with Hose Bibb



- Heavy duty rubber cap with stainless steel clamp
- Used to test cast iron or SCH 40 pipe
- Allows testing of flow and drainage of water
- Versatile one-piece unit including hose bibb

SKU	Size
PFETCHBJ	1 1/2"
PFETCHBK	2"
PFETCHBM	3"
PFETCHBP	4"
PFETCHBS	5"
PFETCHBU	6"

Test Plugs



- Cast iron top and bottom plate
- Neoprene rubber gasket
- Steel nipple
- Operating Pressure: 10 psi
- With wing nut

SKU	Size
PF39002	2"
PF39003	3"
PF39004	4"
PF39006	6"
PF39008	8"
PF39010	10"
PF39012	12"

Test Plugs



- Rubber
- Fits iron or plastic pipe
- Wing nut design

SKU	Size
PFETPJ	1 1/2"
PFETPK	2"
PFETPM	3"
PFETPP	4"

Test Plugs



- Shower arms test plug
- 1/2" NPT male connection with gasket
- Can easily be installed or removed by hand
- Reuseable
- No thread sealant required
- Polypropylene construction

SKU
PFTPD



Lavatory Drains: P. 65-66

Access Covers



- 24 gauge
- Includes 5/16" x 2 1/4" screw
- Stainless steel construction

SKU	Size
PFC51LAM	3"
PFC51LAP	4"
PFC51LAS	5"
PFC51LAU	6"
PFC51LAX	8"
PFC51LA10	10"


Access Covers



- 24 gauge
- Includes 1/4" x 2 1/4" screw
- Stainless steel construction

SKU	Size
PFC51M	3"
PFC51P	4"
PFC51S	5"
PFC51U	6"
PFC51X	8"
PFC5110	10"

Access Covers



- Dome cleanout
- Individually bagged with 2 1/2" wood screw
- ABS construction

SKU	Size	Color/Finish
PFDAC4C	4 1/4"	Chrome
PFDAC4W	4 1/4"	White
PFDAC5C	5 1/4"	Chrome
PFDAC5W	5 1/4"	White
PFDAC7C	7 1/4"	Chrome
PFDAC7W	7 1/4"	White

Access Covers



- Flat cleanout
- Individually bagged with 2 1/2" wood screw
- ABS construction

SKU	Size	Color/Finish
PFFAC4C	4 1/4"	Chrome
PFFAC4W	4 1/4"	White
PFFAC5C	5 1/4"	Chrome
PFFAC5W	5 1/4"	White
PFFAC7C	7 1/4"	Chrome
PFFAC7W	7 1/4"	White

Access Doors



- Concealed rod hinge
- Screwdriver operated latch
- 16 gauge steel construction

SKU	Size	Color/Finish
PF88AD	8" x 8"	White
PF88SSAD	8" x 8"	Stainless Steel
PF1010AD	10" x 10"	White
PF1010SSAD	10" x 10"	Stainless Steel
PF1212AD	12" x 12"	White
PF1212SSAD	12" x 12"	Stainless Steel
PF1414AD	14" x 14"	White
PF1616AD	16" x 16"	White
PF1818AD	18" x 18"	White
PF2424AD	24" x 24"	White

Access Panels



- Includes pull back tabs and locator holes for easy installation
- 1 1/2" frame around door
- Removable door
- Door and frame can be painted or wallpapered
- Plastic construction
- Color/Finish: White

SKU	Door Size
PF910710	6" x 9"
PF910708	8" x 8"
PF91071014	14" x 14"

AAV Wall Boxes



- Includes metal grille face plate and screws
- Made in USA

SKU	Type
PFAAVBX	AAV Wall Box
PFAAVG	Replacement Grille

Air Admittance Valves



- 6 DFU
- 1 1/2" SCH 40 adapter
- For venting 2" DWV and smaller
- Includes screening on air inlets to protect the seal
- Made in USA

SKU	Adapter
PFAAV6	PVC
PFAAV6A	ABS

Air Admittance Valves



- 6 DFU
- 1 1/2" polyproplyene tubular adapter
- For venting 2" DWV and smaller
- Includes screening on air inlets to protect the seal
- Made in USA

SKU	Adapter
PFAAV6T	PVC
PFAAV6TA	ABS

Air Admittance Valves



- 20 DFU
- 1 1/2" x 2" SCH 40 adapter
- For venting 2" DWV and smaller
- Includes screening on air inlets to protect the seal
- Made in USA

SKU	Adapter
PFAAV20	PVC
PFAAV20A	ABS

Air Admittance Valves



- 160 DFU
- 2" x 3" SCH 40 adapter
- For venting 4" DWV and smaller
- Includes screening on air inlets to protect the seal
- Made in USA

SKU	Adapter
PFAAV160	PVC
PFAAV160A	ABS

Air Admittance Valves



- 500 DFU
- 3" x 4" SCH 40 adapter
- For venting 4" DWV and smaller
- Includes screening on air inlets to protect the seal
- Made in USA

SKU	Adapter
PFAAV500	PVC
PFAAV500A	ABS

In-Line Vents



- For use on sinks, tubs and showers
- 1 1/2" MPT
- ABS construction

SKU
PF108202

Socket Flanges



- Van Stone style
- Two piece design
- PVC SCH 80 construction
- Solvent weld connection
- Intended for applications where operating temperatures will not exceed 140°F

SKU	Size
PFP80VSSFK	2"
PFP80VSSFL	2 1/2"
PFP80VSSFM	3"
PFP80VSSFP	4"
PFP80VSSFU	6"
PFP80VSSFX	8"

Socket Unions



- PVC construction with EPDM O-rings
- Fits SCH 40 and SCH 80 pipe
- 150 psi at 73°F
- Solvent weld connection

SKU	Size
PFP80SUD	1/2"
PFP80SUF	3/4"
PFP80SUG	1"
PFP80SUH	1 1/4"
PFP80SUJ	1 1/2"
PFP80SUK	2"
PFP80SUL	2 1/2"
PFP80SUM	3"

Plungers



- Diameter: 5 11/16"
- Super style fold-back cup design
- Handle Material: Eucalyptus Wood
- Material: Rubber

SKU
PFF6

Toilet Shims



- Polypropylene
- Ribbed for non-slip stacking
- Hard, stackable design

SKU	Pkg Qty
PFCSH4	4/pack
PFCSH75	75/jar
PFCSH300	300/bulk

Toilet Shims



- Soft and flexible
- Can be easily trimmed
- Ribbed for non-slip stacking
- PVC construction

SKU	Pkg Qty
PFCSS4	4/pack
PFCSS75	75/jar
PFCSS300	300/bulk

Toilet/Urinal Spud Washers



- 1 1/4"
- Rubber construction
- Replacement closet spud flange washer

SKU
PF40481

Toilet/Urinal Spuds



- Brass with rubber washer

SKU	Size
PF105	1" x 3/4"
PF106	1 1/4" x 3/4"
PF108	1 1/4" x 1 1/4"
PF109	1 1/2" x 3/4"
PF107	1 1/2" x 1 1/4"
PF103	1 1/2" x 1 1/2"
PF101	2" x 1 1/2"
PF100	2" x 2"

Air Admittance Valves

SKU	Size	DFU	Material
PFAAV6	1 1/2"	6	PVC
PFAAV6A	1 1/2"	6	ABS
PFAAV6T	1 1/2" w/ Tubular Adapter	6	PVC
PFAAV6TA	1 1/2" w/ Tubular Adapter	6	ABS
PFAAV20	1 1/2" x 2"	20	PVC
PFAAV20A	1 1/2" x 2"	20	ABS
PFAAV160	2" x 3"	160	PVC
PFAAV160A	2" x 3"	160	ABS
PFAAV500	3" x 4"	500	PVC
PFAAV500A	3" x 4"	500	ABS

Closet Bolts



- Brass plated steel bolts
- Nickel plated steel washers
- Acorn nuts

SKU	Size	Washer
PFC2110	1/4" x 2 1/4"	Oval
PFC2110RW	1/4" x 2 1/4"	Round
PFC3110	1/4" x 3 1/2"	Oval
PFC3110RW	1/4" x 3 1/2"	Round
PFC54A10	5/16" x 2 1/4"	Oval
PFC54A10RW	5/16" x 2 1/4"	Round

Closet Bolts



- 1/4" x 2 1/4"
- Double nickel plated steel round washers
- Double nuts

SKU	Material
PFC2110RWLA	Brass Plated Steel
PFC8110RWLA	Solid Brass

Closet Bolts



- Solid brass bolts
- Nickel plated steel washers
- Acorn nuts

SKU	Size	Washer
PFC8110	1/4" x 2 1/4"	Oval
PFC8110RW	1/4" x 2 1/4"	Round
PFC9110	1/4" x 3 1/2"	Oval
PFC44A10	5/16" x 1 3/4"	Oval
PFC114A10	5/16" x 2 1/4"	Oval
PFC114A10RW	5/16" x 2 1/4"	Round

Closet Bolts



- Snap off design
- Brass or nickel plated steel washers
- Acorn nuts

SKU	Size	Washer	Nut Type
PF90104	1/4" x 2 1/4"	Round	Nickel Plated Steel
PF90104BRSS	1/4" x 2 1/4"	Round	Nickel Plated Brass
PF90154	1/4" x 3 1/2"	Oval	Nickel Plated Steel
PF90124	5/16" x 2 1/4"	Round	Nickel Plated Steel
PF90124BRSS	5/16" x 2 1/4"	Round	Nickel Plated Brass
PF90174BRSS	5/16" x 3 1/2"	Round	Nickel Plated Brass

Closet Bolts

SKU	Bolt Material	Diameter	Length	Style	Nut Material	Nut Style	# Nuts	Washer Style	Material	# Washers
PF90104	Brass w/ Brass Plated Steel Washer	1/4"	2 1/4"	Snap Off	Steel	Open	2	Round	Steel	2
PF90104BRSS	Brass w/ Brass Plated Steel Washer	1/4"	2 1/4"	Snap Off	Brass	Open	2	Round	Steel	2
PFC8110	Brass	1/4"	2 1/4"	Standard	Steel	Open	2	Oval	Steel	2
PFC8110RW	Brass	1/4"	2 1/4"	Standard	Steel	Open	2	Round	Steel	2
PFC8110RWLA	Brass	1/4"	2 1/4"	Standard	Steel	(2) Open, (2) Square	2	Round	Steel	4
PF90154	Brass w/ Brass Plated Steel Washer	1/4"	3 1/2"	Snap Off	Steel	Open	2	Round	Steel	2
PFC9110	Brass	1/4"	3 1/2"	Standard	Steel	Open	2	Oval	Steel	2
PF90124	Brass w/ Brass Plated Steel Washer	5/16"	2 1/4"	Snap Off	Steel	Open	2	Round	Steel	2
PF90124BRSS	Brass w/ Brass Plated Steel Washer	5/16"	2 1/4"	Snap Off	Brass	Heavy Duty Open Nut	2	Round	SS304	2
PF90174BRSS	Brass w/ Brass Plated Steel Washer	5/16"	3 1/2"	Snap Off	Steel	Open	2	Round	Steel	2
PFC2110	Brass Plated Steel	1/4"	2 1/4"	Standard	Steel	Open	2	Oval	Steel	2
PFC2110RW	Brass Plated Steel	1/4"	2 1/4"	Standard	Steel	Open	2	Round	Steel	2
PFC2110RWLA	Brass Plated Steel	1/4"	2 1/4"	Standard	Steel	(2) Open, (2) Square	2	Round	Steel	4
PFC3110	Brass Plated Steel	1/4"	3 1/2"	Standard	Steel	Open	2	Oval	Steel	2
PFC3110RW	Brass Plated Steel	1/4"	3 1/2"	Standard	Steel	Open	2	Round	Steel	2
PFC44A10	Brass Plated Steel	5/16"	1 3/4"	Standard	Steel	Open	2	Oval	Steel	2
PFC114A10	Brass Plated Steel	5/16"	2 1/4"	Standard	Steel	Open	2	Oval	Steel	2
PFC114A10RW	Brass Plated Steel	5/16"	2 1/4"	Standard	Steel	Open	2	Round	Steel	2
PFC54A10	Brass Plated Steel	5/16"	2 1/4"	Standard	Steel	Open	2	Oval	Steel	2
PFC54A10RW	Brass Plated Steel	5/16"	2 1/4"	Standard	Steel	Open	2	Round	Steel	2
PFNCBL	Nylon	5/16"	2 1/2"	Standard	Nylon	Open	1	-	-	-
PFC15515	Brass Plated Steel	1/4"	2 1/2"	Screw	Steel	Closed	2	Round	Steel	2

Closet Bolts



- 5/16" x 2 1/2"
- One piece nut and washer
- Tensile strength exceeds 1100 lbs for each bolt
- Corrosion proof nylon
- Color/Finish: White

SKU
PFNCBL

Closet Bolt Caps



- Plastic construction
- Includes cap and base
- Color/Finish: White

SKU
PFBC43

Closet Screws



- 1/4" x 2 1/2"
- Brass plated steel screws with acorn nuts and round washers

SKU
PFC15515

Tank to Bowl Bolts



- Solid brass construction
- Includes rubber washers

SKU	Type
PF025	With Hex Nuts/Washers
PF035	With Wing Nuts/Washers

Tank Pal Clips



- 5/16"
- Holds closet bolts in upright position
- Steel construction
- Package Quantity: 100/bag

SKU
PFPAL516

Tank to Bowl Gaskets



- Rubber construction
- Universal design

SKU
PFTBG

Tank to Bowl Gaskets



- Tank to bowl gasket with bolts for PROFLO toilet
- Fits most toilets with 2" flush valves

SKU
PFTGFPK

Tank to Bowl Bolt & Gasket Kits



- Fits most toilets with 3" flush valve
- For PF9400 and PF1712BB series tanks

SKU
PF9412TGPK

Back Outlet Toilet Gaskets



- 4"
- For wall hung toilets
- Ethylene vinyl acetate
- Gaskets include an adhesive coating so you can just "peel and stick"

SKU
PFBOGSKT

Toilet Flange Repair



- Full ring design
- Repair damaged toilet flanges
- Corrosion-resistant
- Works with new installation
- Concrete or wood floor
- Fits over 3" or 4" pipe
- Material: Stainless Steel

SKU
PFRR

Toilet Flange Repair



- Repairs broken toilet flanges without costly replacement
- Stops leaking, wobbly toilets
- Fast and easy installation
- Suitable for cast iron, copper, brass and plastic toilet flanges

SKU
PFSF1

Brass Closet Flanges



- 4"
- Leaded connection
- For standard connection
- Brass construction

SKU
PFCF11

Brass Closet Flanges



- 4" x 1 1/8"
- Leaded connection
- For deep connection
- Brass construction

SKU
PFCF13

Brass Closet Flanges



- 4" x 4" x 1 1/2"
- 4-way offset
- For deep connection
- With clip
- Brass construction

SKU
PFCF8

Cast Iron Closet Flanges



- Offset design
- 4" inside caulk
- Cast iron construction
- cUPC certified

SKU	Size
PFCFCOPKJ	4" x 2" x 1 1/2"
PFCFCOPPK	4" x 4" x 2"

Cast Iron Closet Flanges



- Inside Caulk Series
- Notched and slotted
- Cast iron construction
- cUPC certified

SKU	Size
PFCFCPJ	4" x 1 1/2"
PFCFCPK	4" x 2"
PFCFCPL	4" x 2 1/2"
PFCFCPM	4" x 3"
PFCFCPP	4" x 4"

Cast Iron Closet Flanges



- Reducing/Offset
- 4" x 3" x 3"
- Notched and slotted
- 3" inside caulk or 4" no hub connection
- Cast iron construction
- cUPC certified

SKU
PFCFCRPMM

Cast Iron Closet Flanges



- No Hub Series
- No hub deep connection
- Notched and slotted
- Cast iron construction
- cUPC certified

SKU	Size
PFCFNHMN	3" x 3 1/2"
PFCFNHPN	4" x 3 1/2"

Cast Iron Closet Flanges



- Quick Connect Series
- Notched and slotted
- Neoprene rubber gasket
- Includes stainless steel nuts, bolts and washers
- Cast iron construction
- cUPC certified

SKU	Size
PFCFQCMK	3" x 2"
PFCFQCPK	4" x 2"
PFCFQCPM	4" x 3"
PFCFQCPP	4" x 4"

Cast Iron Closet Flanges



- Quick Connect Series
- 4" x 2" x 1"
- Offset design
- Notched and slotted
- Neoprene rubber gasket
- Includes stainless steel nuts, bolts and washers
- Cast iron construction
- cUPC certified

SKU
PFCFQCOPKG

Cast Iron Closet Flanges



- Quick Connect Series
- 4" x 2"
- With test cap
- Notched and slotted
- Neoprene rubber gasket
- Includes stainless steel nuts, bolts and washers
- Cast iron construction
- cUPC certified

SKU
PFCFQCPKT

Closet Flanges



- 4" x 3"
- One piece design
- Fits over 3" or inside 4" SCH 40 DWV pipe
- Allows for flush installation inside 4" pipe
- Provides a simple push and peel back test cap that won't fall down the drain
- No hammer required to remove test cap
- Solvent weld connection

SKU	Material
PF4034A	ABS
PF4034P	PVC

Closet Flanges



- 4" x 3"
- Two piece floating stainless steel ring design
- Fits over 3" or inside 4" SCH 40 DWV pipe
- Allows for flush installation inside 4" pipe
- Provides a simple push and peel back test cap that won't fall down the drain
- No hammer required to remove test cap
- Solvent weld connection

SKU	Material
PF4134A	ABS
PF4134P	PVC

Urinal Flange Kits



- Adjustable horizontally
- Includes stainless steel bolts, nut and washers
- Includes thick foam rubber gasket
- Plastic construction

SKU	Connection	Material
PFAHUFK	2" Hub	ABS
PFAIUFK	2" Inside Fit	ABS
PFASUFK	2" Spigot	ABS
PFPHUFK	2" Hub	PVC
PFPIUFK	2" Inside Fit	PVC
PFPSUFK	2" Spigot	PVC

Lift Wires



- For flush valve repair

SKU	Size	Type
PFLLWR	4 1/2"	Lower
PFLLWT	5 1/2"	Lower
PFULW	8 1/2"	Upper

Seat Discs



- American Standard® style

SKU	Connection
PF453A	Snap on
PF7523	Screw on

Tank Balls



- 5" x 4"
- For ballcocks
- Plastic
- Color/Finish: Black

SKU
PFTBSP

Tank Balls



- Universal style
- Less tip
- Color/Finish: Black

SKU
PFUTB

Tank Repair Kits



- For PF9300 series dual flush tanks

SKU
PF9312FVPK

Wax Rings with Bolt Kits



- 100% pure petroleum wax gasket
- Made with a plastic polyethylene flanged horn which extends the discharge opening and provides a positive seal and proper bowl alignment
- Includes pair of 1/4" x 2 1/4" solid brass bolts with double nuts and washers

SKU	Size	Type
PFWRWHWB	3" x 4"	-
PFWRWHXWWB	3" x 4"	With Extra Wax
PFWR4WHWB	4"	-

Wax Rings with Bolt Kits



- 100% pure petroleum wax gasket
- Fits all floor-type toilet bowls with 3" or 4" waste lines
- Includes pair of 1/4" x 2 1/4" solid brass bolts with double nuts and washers

SKU
PFWRWB

Wax Rings



- 100% pure petroleum wax gasket
- Fits all floor-type toilet bowls with 3" or 4" waste lines

SKU	Type
PFWR	-
PFWRXW	With Extra Wax

Wax Rings for Urinals



- 100% pure petroleum wax gasket
- Designed to fit 2" urinal outlets

SKU
PFWRU

Wax Rings



- For back outlet toilets
- Felt reinforced to avoid slippage
- Fits most 4" wall toilets

SKU
PFWRBO

Wax Rings with Horn



- 100% pure petroleum wax gasket
- Fits all floor-type toilet bowls with 3" or 4" waste lines
- Made with a plastic polyethylene flanged sleeve which extends the discharge opening and provides a positive seal and proper bowl alignment

SKU	Type
PFWRWH	-
PFWRWHXW	With Extra Wax

Toilets | P. 45-54



Cover Tubes



MONOGRAM BRASS™

- 11/16" OD x 3 1/2"
- 3/4" OD sure grip bell flange
- Cover tube fits over 5/8" OD copper pipe
- Steel construction

SKU	Color/Finish
MB261BN	Brushed Nickel
MB261CP	Chrome
MB261ORB	Oil Rubbed Bronze

Lavatory Supply Tubes



MONOGRAM BRASS™

- Connection: 3/8" OD tube x 20"
- Brass top
- Copper tube

SKU	Color/Finish
MB221BN	Brushed Nickel
MB221CP	Chrome
MB221ORB	Oil Rubbed Bronze
MB221PB	Polished Brass
MB221PN	Polished Nickel

Supply Tubes



MONOGRAM BRASS™

- Connection: 3/8" OD tube x 12"
- 12" flat head rigid toilet tube
- Plastic top
- Copper tube

SKU	Color/Finish
MB241BN	Brushed Nickel
MB241CP	Chrome
MB241ORB	Oil Rubbed Bronze
MB241PB	Polished Brass
MB241PN	Polished Nickel

Supply Tubes



MONOGRAM BRASS™

- Connection: 3/8" OD tube x 20"
- 20" flat head rigid toilet tube
- Plastic top
- Copper tube

SKU	Color/Finish
MB242BN	Brushed Nickel
MB242CP	Chrome
MB242ORB	Oil Rubbed Bronze
MB242PB	Polished Brass
MB242PN	Polished Nickel

Closet Supply Tubes



PROFLO

- PEX with plastic compression sleeve

SKU	Size
PF3812CRX	3/8" x 12"
PF3820CRX	3/8" x 20"

Lavatory Supply Tubes



PROFLO

- PEX with plastic compression sleeve

SKU	Size
PF3812LR	3/8" x 12"
PF3820LR	3/8" x 20"
PF3830LR	3/8" x 30"
PF3836LR	3/8" x 36"

Closet Connectors



PROFLO

- Connection: 3/8" Comp x 7/8" BC x 12"
- Heavy duty reinforced PVC hose
- Heavy duty sealing washers snap into place
- Plastic ballcock nuts have wings for hand tightening only
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F

SKU
PFX146172

Closet Connectors



PROFLO

- Exclusive double reinforced construction consists of a high strength stainless steel braid and reinforced thermoplastic inner core
- Heavy duty sealing washers snap into place
- Plastic ballcock nuts have wings for hand tightening only
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F

SKU	Length	Connection
PFX146471	9"	3/8" Comp x 7/8" BC
PFX146472	12"	3/8" Comp x 7/8" BC
PFX146462	12"	1/2" FIP x 7/8" BC
PFX146492	12"	1/2" Comp x 7/8" BC
PFX146473	16"	3/8" Comp x 7/8" BC
PFX146463	16"	1/2" FIP x 7/8" BC
PFX146474	20"	3/8" Comp x 7/8" BC

Toilet Connectors

SKU	Inlet	Outlet	Length	Material
PFX146172	3/8" Compression	7/8" CLST	12"	PVC
PFX146471	3/8" Compression	7/8" CLST	9"	Stainless Steel
PFX146472	3/8" Compression	7/8" CLST	12"	Stainless Steel
PFX146473	3/8" Compression	7/8" CLST	16"	Stainless Steel
PFX146474	3/8" Compression	7/8" CLST	20"	Stainless Steel
PFX146462	1/2" Compression	7/8" CLST	12"	Stainless Steel
PFX146492	1/2" FIP	7/8" CLST	12"	Stainless Steel
PFX146463	1/2" FIP	7/8" CLST	16"	Stainless Steel

Lavatory Connectors

SKU	Inlet	Outlet	Length	Material
PFX146022	3/8" Compression	1/2" FIP	12"	PVC
PFX146023	3/8" Compression	1/2" FIP	16"	PVC
PFX146024	3/8" Compression	1/2" FIP	20"	PVC
PFX146322	3/8" Compression	1/2" FIP	12"	Stainless Steel
PFX146323	3/8" Compression	1/2" FIP	16"	Stainless Steel
PFX146324	3/8" Compression	1/2" FIP	20"	Stainless Steel
PFX146326	3/8" Compression	1/2" FIP	30"	Stainless Steel
PFX146330	3/8" Compression	1/2" FIP	48"	Stainless Steel
PFX146332	3/8" Compression	1/2" FIP	60"	Stainless Steel
PFX146334	3/8" Compression	1/2" FIP	72"	Stainless Steel
PFX146342	3/8" Compression	3/8" Compression	12"	Stainless Steel
PFX146430	3/8" Compression	3/8" OD Coupling	12"	Stainless Steel
PFX146432	3/8" Compression	3/8" OD Coupling	20"	Stainless Steel
PFX146343	3/8" Compression	3/8" Compression	16"	Stainless Steel
PFX146344	3/8" Compression	3/8" Compression	20"	Stainless Steel
PFX146423	1/2" Compression	1/2" FIP	16"	Stainless Steel
PFX146424	1/2" Compression	1/2" FIP	20"	Stainless Steel
PFX146302	1/2" FIP	1/2" FIP	12"	Stainless Steel
PFX146303	1/2" FIP	1/2" FIP	16"	Stainless Steel
PFX146304	1/2" FIP	1/2" FIP	20"	Stainless Steel
PFX146306	1/2" FIP	1/2" FIP	30"	Stainless Steel

Water Heater Connectors

SKU	Type	End 1	End 2	Length
PFX146232	SS Braided	3/4" MIP	3/4" FIP	18"
PFX146222	SS Braided	3/4" FIP	3/4" FIP	18"
PFX146224	SS Braided	3/4" FIP	3/4" FIP	24"
PFXCHFW18NA	SS Corrugated	3/4" FIP	3/4" Sweat	18"
PFXCHFW24NA	SS Corrugated	3/4" FIP	3/4" Sweat	24"
PFXCHFU18N	SS Corrugated	3/4" FIP	3/4" Push	18"
PFXCHFM18N	SS Corrugated	3/4" FIP	3/4" MIP	18"
PFXCHFM24N	SS Corrugated	3/4" FIP	3/4" MIP	24"
PFXCHFT18N	SS Corrugated	3/4" FIP	3/4" FIP	18"
PFXCHFT24N	SS Corrugated	3/4" FIP	3/4" FIP	24"
PFXCHGFT24N	SS Corrugated	1" FIP	3/4" FIP	24"
PFXCHGT18	SS Corrugated	1" FIP	1" FIP	18"
PFXCHGT24	SS Corrugated	1" FIP	1" FIP	24"
PFXCHHT18	SS Corrugated	1 1/4" FIP	1 1/4" FIP	18"
PFXCHHGT24	SS Corrugated	1 1/4" FIP	1" FIP	24"
PFXCHJT18	SS Corrugated	1 1/2" FIP	1 1/2" FIP	18"

Lavatory Connectors



- Connection: 3/8" Comp x 1/2" FIP
- Heavy duty reinforced PVC hose
- Heavy duty sealing washers snap into place
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F

SKU	Length
PFX146022	12"
PFX146023	16"
PFX146024	20"

Lavatory Connectors



- Exclusive double reinforced construction consists of a high strength stainless steel braid and reinforced thermoplastic inner core
- Heavy duty sealing washers snap into place
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F

SKU	Length	Connection
PFX146342	12"	3/8" Comp x 3/8" Comp
PFX146430	12"	3/8" Comp x 3/8" Comp OD Coup
PFX146322	12"	3/8" Comp x 1/2" FIP
PFX146302	12"	1/2" FIP x 1/2" FIP
PFX146343	16"	3/8" Comp x 3/8" Comp
PFX146323	16"	3/8" Comp x 1/2" FIP
PFX146423	16"	1/2" Comp x 1/2" FIP
PFX146303	16"	1/2" FIP x 1/2" FIP
PFX146344	20"	3/8" Comp x 3/8" Comp
PFX146432	20"	3/8" Comp x 3/8" Comp OD Coup
PFX146324	20"	3/8" Comp x 1/2" FIP
PFX146424	20"	1/2" Comp x 1/2" FIP
PFX146304	20"	1/2" FIP x 1/2" FIP
PFX146326	30"	3/8" Comp x 1/2" FIP
PFX146306	30"	1/2" FIP x 1/2" FIP
PFX146330	48"	3/8" Comp x 1/2" FIP
PFX146332	60"	3/8" Comp x 1/2" FIP
PFX146334	72"	3/8" Comp x 1/2" FIP

Ice Maker Connectors



- Connection: 1/4" Comp x 1/4" Comp
- Length: 60"
- Heavy duty sealing washers snap into place
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F
- PVC construction

SKU
PFX146198

Ice Maker Connectors



- Connection: 1/4" Comp x 1/4" Comp
- Exclusive double reinforced construction consists of a high strength stainless steel braid and reinforced thermoplastic inner core
- Heavy duty sealing washers snap into place
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F

SKU	Length
PFX146202	24"
PFX146205	60"
PFX146207	84"

Ice Maker Kits



- Connection: 3/8" OD to 1" OD x 1/4" OD Comp
- Self-tapping brass valve
- Connects from water line to appliance
- Kit Includes: tubing, needle valve, saddle clamp, nuts, bolts, washers and inserts

SKU	Tubing
PFXIMK15CA	Copper
PFXIMK25PA	Polyethylene

Dishwasher Connectors



- Exclusive double reinforced construction consists of a high strength stainless steel braid and reinforced thermoplastic inner core
- Heavy duty sealing washers snap into place
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F - 160°F
- Includes 3/8" MIP x 3/8" Comp Elbow

SKU	Length	Connection
PFX146350	48"	3/8" Comp x 3/8" Comp
PFX146352	60"	3/8" Comp x 3/8" Comp
PFX146354	72"	3/8" Comp x 3/8" Comp
PFX146365	84"	1/2" Comp x 1/2" Comp

Dishwasher Connectors



- Rubber sleeve construction

SKU	Clamps
PFT250	2
PFH60	4

Dishwasher Connector Kits



- Connection: 3/8" Comp x 3/8" Comp
- Kit includes dishwasher connector and 2 elbows; PFXMCECCN and PFXDEN
- Exclusive double reinforced construction consists of a high strength stainless steel braided hose and reinforced thermoplastic inner core
- Heavy duty sealing washers
- Extra thick, specially molded, flat washers are used with brass nuts
- Max Operating Pressure: 150 psi
- Operating Temperature: 33°F - 180°F

SKU	Length
PFXSD6C60ET	60"
PFXSD6C72ET	72"

Dishwasher Elbows



- Brass construction
- NSF/ANSI 372

SKU	Connection	With Nut
PFXDEN	3/4" FHT x 3/8" Comp	Yes
PFXDEDN	3/4" FHT x 1/2" Comp	No

Dishwasher Drain Hoses



- Black reinforced rubber hose
- Length: 50'

SKU	Size
PF506N	5/8"
PF507N	7/8"

Ice Maker Connectors

SKU	Inlet	Outlet	Length	Material
PFX146198	1/4" Compression	1/4" Compression	60"	PVC
PFX146202	1/4" Compression	1/4" Compression	24"	Stainless Steel
PFX146205	1/4" Compression	1/4" Compression	60"	Stainless Steel
PFX146207	1/4" Compression	1/4" Compression	84"	Stainless Steel

Dishwasher Connectors

SKU	Inlet	Outlet	Length	Material
PFX146350	3/8" Compression	3/8" Compression	48"	Stainless Steel
PFXSD6C60ET*	3/8" Compression	3/8" Compression	60"	Stainless Steel
PFX146352	3/8" Compression	3/8" Compression	60"	Stainless Steel
PFXSD6C72ET*	3/8" Compression	3/8" Compression	72"	Stainless Steel
PFX146354	3/8" Compression	3/8" Compression	72"	Stainless Steel
PFX146365	1/2" FIP	1/2" FIP	84"	Stainless Steel

**ET models include 2 adapter elbows*

Washing Machine Connectors

SKU	Inlet	Outlet	Length	Material
PFWMH4PR	3/4" Hose	3/4" Hose	48"	Rubber (PR)
PFWMH5PR	3/4" Hose	3/4" Hose	60"	Rubber (PR)
PFWMH6PR	3/4" Hose	3/4" Hose	72"	Rubber (PR)
PF146814	3/4" Hose	3/4" Hose	48"	Stainless Steel
PF146815	3/4" Hose	3/4" Hose	60"	Stainless Steel
PF146816	3/4" Hose	3/4" Hose	72"	Stainless Steel

Washing Machine Connectors



- Connection: 3/4" FHT x 3/4" FHT
- Exclusive double reinforced construction consists of a high strength stainless steel braid and reinforced thermoplastic inner core
- Heavy duty sealing washers snap into place
- Max Operating Pressure: 125 psi
- Operating Temperature: 40°F – 160°F

SKU	Length
PF146814	48"
PF146815	60"
PF146816	72"

Washing Machine Connectors



- Connection: 3/4" FHT x 3/4" FHT
- Rubber washing machine hose with straight ends
- Sold in pairs
- Made in USA

SKU	Length
PFWMH4PR	48"
PFWMH5PR	60"
PFWMH6PR	72"

Washing Machine Tees



- Connection: 1 1/2" Slip x 3/4" MIP or 1/2" FIP
- Individually boxed
- Rough Brass

SKU
PFWTI75

Water Heater Connectors



- Exclusive double reinforced construction consists of a high strength stainless steel braid and reinforced thermoplastic inner core
- Heavy duty sealing washers snap into place
- Operating Pressure: 200 psi
- Operating Temperature: 25°F – 160°F

SKU	Length	Connection
PFX146222	18"	3/4" FIP x 3/4" FIP
PFX146232	18"	3/4" MIP x 3/4" FIP
PFX146224	24"	3/4" FIP x 3/4" FIP

Water Heater Connectors



- Stainless steel corrugated, kink resistant tubing
- Max Pressure: 125 psi
- Max Temperature: 180°F
- Working Temperature: 40°F – 160°F

SKU	Length	Connection
PFXCHFT18N	18"	3/4" FIP x 3/4" FIP
PFXCHFM18N	18"	3/4" FIP x 3/4" MIP
PFXCHFU18N	18"	3/4" FIP x 3/4" Push
PFXCHFW18NA	18"	3/4" FIP x 3/4" Sweat
PFXCHGT18	18"	1" FIP x 1" FIP
PFXCHHT18	18"	1 1/4" FIP x 1 1/4" FIP
PFXCHJT18	18"	1 1/2" FIP x 1 1/2" FIP
PFXCHFM24N	24"	3/4" FIP x 3/4" MIP
PFXCHFW24NA	24"	3/4" FIP x 3/4" Sweat
PFXCHFT24N	24"	3/4" FIP x 3/4" FIP
PFXCHGFT24N	24"	1" FIP x 3/4" FIP
PFXCHGT24	24"	1" FIP x 1" FIP
PFXCHHGT24	24"	1 1/4" FIP x 1" FIP

Stop Valves



- Multi-turn design
- Use for toilets and sinks
- Connection: 1/2" FIP x 3/8" OD Comp
- Brass construction

SKU	Color/Finish
MB201BN	Brushed Nickel
MB201ORB	Oil Rubbed Bronze
MB201PB	Polished Brass
MB201PN	Polished Nickel

Stop Valves



- Quarter-turn design
- Use for toilets and sinks
- Connection: 1/2" FIP x 3/8" OD Comp
- Cross handle
- Brass construction

SKU	Color/Finish
MB202BN	Brushed Nickel
MB202CP	Chrome
MB202ORB	Oil Rubbed Bronze
MB202PB	Polished Brass
MB202PN	Polished Nickel

Stop Valves



MONOGRAM BRASS™

- Multi-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Brass construction

LOW LEAD

SKU	Color/Finish
MB203BN	Brushed Nickel
MB203ORB	Oil Rubbed Bronze
MB203PB	Polished Brass
MB203PN	Polished Nickel

Stop Valves



MONOGRAM BRASS™

- Quarter-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Square handle
- Brass construction

LOW LEAD

SKU	Color/Finish
MB206BN	Brushed Nickel
MB206CP	Chrome

Stop Valves



MONOGRAM BRASS™

- Quarter-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Cross handle
- Brass construction

LOW LEAD

SKU	Color/Finish
MB204BN	Brushed Nickel
MB204CP	Chrome
MB204ORB	Oil Rubbed Bronze
MB204PB	Polished Brass
MB204PN	Polished Nickel

Stop Valves



MONOGRAM BRASS™

- Quarter-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Round handle
- Brass construction

LOW LEAD

SKU	Color/Finish
MB207BN	Brushed Nickel
MB207CP	Chrome

Stop Valves



MONOGRAM BRASS™

- Quarter-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Cross handle
- Brass construction

LOW LEAD

SKU	Color/Finish
MB205BN	Brushed Nickel
MB205CP	Chrome

Stop Valves



MONOGRAM BRASS™

- Angle stop
- Use for toilets and sinks
- Connection: 1/2" Sweat x 3/8" OD Comp angle stop
- 5/8" OD bell flange
- Brass construction

LOW LEAD

SKU	Color/Finish
MB208BN	Brushed Nickel
MB208CP	Chrome
MB208ORB	Oil Rubbed Bronze
MB208PN	Polished Nickel

Stop Valves



MONOGRAM BRASS™

- Multi-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Brass construction

SKU	Color/Finish
MB211BN	Brushed Nickel
MB211ORB	Oil Rubbed Bronze
MB211PN	Polished Nickel

Stop Valves



MONOGRAM BRASS™

- Quarter-turn design
- Use for toilets and sinks
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Cross handle
- Brass construction

SKU	Color/Finish
MB212BN	Brushed Nickel
MB212CP	Chrome
MB212ORB	Oil Rubbed Bronze
MB212PB	Polished Brass

3-Way Stop Valves



PROFLO

- Multi-turn design
- Connection: 5/8" OD Comp x 3/8" OD Comp x 3/8" OD Comp
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handle

SKU	Color/Finish
PFX3C322C	Chrome
PFX3C322R	Rough Brass

3-Way Stop Valves



PROFLO

- Quarter-turn design
- Connection: 5/8" OD Comp x 3/8" OD Comp x 3/8" OD Comp
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handle
- Color/Finish: Chrome

SKU
PFXQ3C322C

Angle Supply Stop Valves



PROFLO

- Multi-turn design
- Connection: 1/2" FIP x 3/8" Comp x 3/8" Comp
- Valve Body Material: Brass
- Dual outlet design

SKU	Color/Finish
PFX3T322C	Chrome
PFX3T322R	Rough Brass

Angle Supply Stop Valves



PROFLO

- Multi-turn design
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handles

SKU	Connection	Color/Finish
PFXAT22C	3/8" FIP x 3/8" OD Comp	Chrome
PFXAS31C	1/2" Sweat x 1/4" OD Comp	Chrome
PFXAS31R	1/2" Sweat x 1/4" OD Comp	Rough Brass
PFXAP32C	1/2" PEX x 3/8" OD Comp	Chrome
PFXAS32C	1/2" Sweat x 3/8" OD Comp	Chrome
PFXAS32R	1/2" Sweat x 3/8" OD Comp	Rough Brass
PFXAT32C	1/2" FIP x 3/8" OD Comp	Chrome
PFXAV32C	1/2" CPVC x 3/8" OD Comp	Chrome
PFXAV32R	1/2" CPVC x 3/8" OD	Rough Brass
PFXAC31C	5/8" OD Comp x 1/4" OD Comp	Chrome
PFXAC32C	5/8" OD Comp x 3/8" OD Comp	Chrome
PFXAC32R	5/8" OD Comp x 3/8" OD Comp	Rough Brass

Angle Supply Stop Valves



PROFLO

- Quarter-turn design
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handles
- Color/Finish: Chrome

LOW LEAD

SKU	Connection
PFXQAT22C	3/8" FIP x 3/8" OD Comp
PFXQAP32C	1/2" PEX x 3/8" OD Comp
PFXQAS32C	1/2" Sweat x 3/8" OD Comp
PFXQAT32C	1/2" FIP x 3/8" OD Comp
PFXQAV32C	1/2" CPVC x 3/8" OD Comp
PFXQAC31C	5/8" OD Comp x 1/4" OD Comp
PFXAC32CLK	5/8" Comp x 3/8" Comp (loose key)
PFXAC32CLON	5/8" Comp x 3/8" Comp (less outlet nut)
PFXQAC32C	5/8" OD Comp x 3/8" OD Comp
PFXQAJ34C	5/8" OD Comp x 7/16" & 1/2" SJ

Angle Supply Stop Valves



PROFLO

- Quarter-turn design
- Connection: 5/8" OD Comp x 3/8" OD Comp
- With loose key
- Low lead brass ball mechanism
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Color/Finish: Chrome

LOW LEAD

SKU
PFXQAC32CLK

Angle Supply Stop Valves



PROFLO

FASTFIT™

- Quarter-turn design
- Connection: 5/8" OD Push x 3/8" OD
- Push connect technology
- Removable and reusable
- Works with copper, PEX and CPVC
- Brass stem and body

LOW LEAD

SKU	Color/Finish
PFXQAQ32BN	Brushed Nickel
PFXQAQ32C	Chrome
PFXQAQ32ORB	Oil Rubbed Bronze

Commercial Angle Stops



PROFLO

- Multi-turn design
- Brass stem and body
- Round metal handle
- Color/Finish: Chrome

SKU	Connection
PFXCAT22C	3/8" IPS x 3/8" OD Comp
PFXCAS32C	1/2" Sweat x 3/8" OD Comp
PFXCAT32C	1/2" FIP x 3/8" OD Comp
PFXCAT33C	1/2" FIP x 1/2" OD Comp
PFXCAC32C	5/8" OD Comp x 3/8" OD Comp

Commercial Angle Stops



PROFLO

- Multi-turn design
- Connection: 1/2" Sweat x 3/8" OD Comp
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Includes cover tube
- Color/Finish: Chrome

SKU
PFXCAZ32C

Commercial Angle Stops with Loose Key



PROFLO

- Multi-turn design
- Brass stem and body
- Color/Finish: Chrome

SKU	Connection
PFXCAT22CLK	3/8" IPS x 3/8" OD Comp
PFXCAT32CLK	1/2" FIP x 3/8" OD Comp
PFXCAS32CLK	1/2" Sweat x 3/8" OD Comp
PFXCAC32CLK	5/8" OD x 3/8" OD Comp

Quarter-Turn Stops

SKU	Stop Type	Inlet	Outlet	Color/Finish	Type
PFXQAC31C	Angle	5/8" OD Compression	1/4" Compression	Chrome	-
PFXQAC32C	Angle	5/8" OD Compression	3/8" Compression	Chrome	-
PFXQAC32CLK	Angle	5/8" OD Compression	3/8" Compression	Chrome	Loose Key
PFXQAJ34C	Angle	5/8" OD Compression	7/16" & 1/2" Slip Joint	Chrome	-
PFXQAT22C	Angle	3/8" FIP	3/8" Compression	Chrome	-
PFXQAT32C	Angle	1/2" FIP	3/8" Compression	Chrome	-
PFXQAPP32C	Angle	1/2" Cold Expansion PEX	3/8" Compression	Chrome	-
PFXQAS32C	Angle	1/2" Sweat	3/8" Compression	Chrome	-
PFXQAP32C	Angle	1/2" Crimp PEX	3/8" Compression	Chrome	-
PFXQAV32C	Angle	1/2" CPVC	3/8" Compression	Chrome	-
PFXQSC32C	Straight	5/8" OD Compression	3/8" Compression	Chrome	-
PFXQSF22C	Straight	3/8" FEM OD Compression	3/8" Compression	Chrome	-
PFXQST22C	Straight	3/8" FIP	3/8" Compression	Chrome	-
PFXQST32C	Straight	1/2" FIP	3/8" Compression	Chrome	-
PFXQSS32C	Straight	1/2" Sweat	3/8" Compression	Chrome	-
PFXQSP32C	Straight	1/2" Crimp PEX	3/8" Compression	Chrome	-
PFXQSPP32C	Straight	1/2" Cold Expansion PEX	3/8" Compression	Chrome	-
PFXQSV32C	Straight	1/2" CPVC	3/8" Compression	Chrome	-
PFXQ3C322C	Dual Outlet	5/8" OD Compression	3/8" x 3/8" Compression	Chrome	-

Multi-Turn Stops

SKU	Stop Type	Inlet	Outlet	Color/Finish	Type
PFXAC31C	Angle	5/8" OD Compression	1/4" Compression	Chrome	-
PFXAC32C	Angle	5/8" OD Compression	3/8" Compression	Chrome	-
PFXAC32R	Angle	5/8" OD Compression	3/8" Compression	Rough Brass	-
PFXAC32CLK	Angle	5/8" OD Compression	3/8" Compression	Chrome	Loose Key
PFXAC32CLON	Angle	5/8" OD Compression	3/8" Compression	Chrome	Less Outlet Nut
PFXAT22C	Angle	3/8" FIP	3/8" Compression	Chrome	-
PFXAT32C	Angle	1/2" FIP	3/8" Compression	Chrome	-
PFXAS31C	Angle	1/2" Sweat	1/4" Compression	Chrome	-
PFXAS31R	Angle	1/2" Sweat	1/4" Compression	Rough Brass	-
PFXAS32C	Angle	1/2" Sweat	3/8" Compression	Chrome	-
PFXAS32R	Angle	1/2" Sweat	3/8" Compression	Rough Brass	-
PFXAP32C	Angle	1/2" PEX	3/8" Compression	Chrome	-
PFXAV32C	Angle	1/2" CPVC	3/8" Compression	Chrome	-
PFXAV32R	Angle	1/2" CPVC	3/8" Compression	Rough Brass	-
PFXSC32C	Straight	5/8" OD Compression	3/8" Compression	Chrome	-
PFXSC32CA	Straight	5/8" OD Compression	3/8" Compression	Chrome	Plastic Stem
PFXST22C	Straight	3/8" FIP	3/8" Compression	Chrome	-
PFXST32C	Straight	1/2" FIP	3/8" Compression	Chrome	-
PFXSS32C	Straight	1/2" Sweat	3/8" Compression	Chrome	-
PFXSP32C	Straight	1/2" PEX	3/8" Compression	Chrome	-
PFXSV32C	Straight	1/2" CPVC	3/8" Compression	Chrome	-
PFXSV32R	Straight	1/2" CPVC	3/8" Compression	Rough Brass	-
PFX3C322C	Dual Outlet	5/8" OD Compression	3/8" x 3/8" Compression	Chrome	-
PFX3C322R	Dual Outlet	5/8" OD Compression	3/8" x 3/8" Compression	Rough Brass	-
PFXDC321R	Dual Handle	5/8" OD Compression	3/8" x 1/4" Compression	Rough Brass	-
PFXDC322C	Dual Handle	5/8" OD Compression	3/8" x 3/8" Compression	Chrome	-
PFXDC322R	Dual Handle	5/8" OD Compression	3/8" x 3/8" Compression	Rough Brass	-
PFXDT322R	Dual Handle	1/2" FIP	3/8" x 3/8" Compression	Rough Brass	-

Fast Fit™ Push-On Quarter-Turn Stops

SKU	Stop Type	Inlet	Outlet	Color/Finish	Type
PFXQAQ32C	Angle	5/8" OD Push	3/8" Compression	Chrome	-
PFXQAQ32BN	Angle	5/8" OD Push	3/8" Compression	Brushed Nickel	-
PFXQAQ32ORB	Angle	5/8" OD Push	3/8" Compression	Oil Rubbed Bronze	-
PFXQSQ32C	Straight	5/8" OD Push	3/8" Compression	Chrome	-
PFXQSQ32BN	Straight	5/8" OD Push	3/8" Compression	Brushed Nickel	-
PFXQSQ32ORB	Straight	5/8" OD Push	3/8" Compression	Oil Rubbed Bronze	-

Multi-Turn Commercial Stops

SKU	Stop Type	Inlet	Outlet	Color/Finish	Type
PFXCAC32C	Angle	5/8" OD Compression	3/8" Compression	Chrome	-
PFXCAC32CLK	Angle	5/8" OD Compression	3/8" Compression	Chrome	Loose Key
PFXHAC32C	Angle	5/8" OD Compression	3/8" Compression	Chrome	Heavy Pattern
PFXHAC32CLK	Angle	5/8" OD Compression	3/8" Compression	Chrome	Heavy Pattern & Loose Key
PFXCAT22C	Angle	3/8" FIP	3/8" Compression	Chrome	-
PFXCAT22CLK	Angle	3/8" FIP	3/8" Compression	Chrome	Loose Key
PFXCAT33C	Angle	1/2" FIP	1/2" Compression	Chrome	-
PFXHATT33CLK	Angle	1/2" FIP	1/2" FIP	Chrome	Heavy Pattern & Loose Key
PFXCAT32C	Angle	1/2" FIP	3/8" Compression	Chrome	-
PFXCAT32CLK	Angle	1/2" FIP	3/8" Compression	Chrome	Loose Key
PFXHAT32CLK	Angle	1/2" FIP	3/8" Compression	Chrome	Heavy Pattern & Loose Key
PFXCAS32C	Angle	1/2" Sweat	3/8" Compression	Chrome	-
PFXCAS32CLK	Angle	1/2" Sweat	3/8" Compression	Chrome	Loose Key
PFXCAZ32C	Angle	1/2" Sweat	3/8" Compression	Chrome	With Cover Tube
PFXCAZ32CLK	Angle	1/2" Sweat	3/8" Compression	Chrome	With Cover Tube & Loose Key
PFX3T322C	Dual Outlet	1/2" FIP	3/8" x 3/8" Compression	Chrome	-
PFX3T322R	Dual Outlet	1/2" FIP	3/8" x 3/8" Compression	Rough Brass	-

Multi-Turn Commercial Kits

SKU	Supply Type	Inlet	Outlet	Color/Finish	Type
PFXCAC32CL12	Lav Kit (sold in pairs)	5/8" OD Compression	3/8" Compression	Chrome	-
PFXCAC32CLKL12	Lav Kit (sold in pairs)	5/8" OD Compression	3/8" Compression	Chrome	Loose Key
PFXCAC32CC12	Closet Kit	5/8" OD Compression	3/8" Compression	Chrome	-
PFXCAC32CLKC12	Closet Kit	5/8" OD Compression	3/8" Compression	Chrome	Loose Key
PFXCAT22CL12	Lav Kit (sold in pairs)	3/8" FIP	3/8" Compression	Chrome	-
PFXCAT22CLKL12	Lav Kit (sold in pairs)	3/8" FIP	3/8" Compression	Chrome	Loose Key
PFXHATT22CLKL12	Lav Kit (sold in pairs)	3/8" FIP	3/8" Compression	Chrome	Heavy Pattern & Loose Key
PFXCATT22CLKRL12	Lav Kit (sold in pairs)	3/8" FIP	3/8" FIP	Chrome	Loose Key w/ Nipple
PFXHAT33CLKL12	Lav Kit (sold in pairs)	1/2" FIP	1/2" Compression	Chrome	Heavy Pattern & Loose Key
PFXCAT32CL12	Lav Kit (sold in pairs)	1/2" FIP	3/8" Compression	Chrome	-
PFXCAT32CLKL12	Lav Kit (sold in pairs)	1/2" FIP	3/8" Compression	Chrome	Loose Key
PFXHAT32CL12	Lav Kit (sold in pairs)	1/2" FIP	3/8" Compression	Chrome	Heavy Pattern
PFXHAT32CLKL12	Lav Kit (sold in pairs)	1/2" FIP	3/8" Compression	Chrome	Heavy Pattern & Loose Key
PFXCAZ32CC12	Closet Kit	1/2" Sweat	3/8" Compression	Chrome	With Cover Tube
PFXCAS32CL12	Lav Kit (sold in pairs)	1/2" Sweat	3/8" Compression	Chrome	-
PFXCAS32CLKL12	Lav Kit (sold in pairs)	1/2" Sweat	3/8" Compression	Chrome	Loose Key
PFXCAZ32CL12	Lav Kit (sold in pairs)	1/2" Sweat	3/8" Compression	Chrome	With Cover Tube
PFXCAZ32CLKL12	Lav Kit (sold in pairs)	1/2" Sweat	3/8" Compression	Chrome	With Cover Tube & Loose Key
PFXCAS32CC12	Closet Kit	1/2" Sweat	3/8" Compression	Chrome	-
PFXCAS32CLKC12	Closet Kit	1/2" Sweat	3/8" Compression	Chrome	Loose Key

All kits include escutcheon(s) and riser(s) (length 12")

Commercial Angle Stops with Loose Key



- Multi-turn operation
- Connection: 1/2" Sweat x 3/8" Comp
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body construction
- Includes cover tube
- Color/Finish: Chrome

SKU
PFXCAZ32CLK

Dual Handle Stop Valves



- Multi-turn design
- Connection: 5/8" OD Comp x 3/8" OD Comp x 3/8" OD Comp
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handles
- Color/Finish: Chrome

SKU
PFXDC322C

Dual Handle Stop Valves



- Dual handle design
- Brass stem and body
- Color/Finish: Rough Brass

SKU	Connection
PFXDT322R	1/2" FIP x 3/8" Comp x 3/8" OD Comp
PFXDC321R	5/8" Comp x 3/8" Comp x 1/4" OD Comp
PFXDC322R	5/8" Comp x 3/8" Comp x 3/8" Comp

Heavy Duty Angle Stops



- Commercial or residential use
- Multi-turn design
- Connection: 5/8" OD x 3/8" OD Comp
- Heavy pattern
- Brass stem and body
- Color/Finish: Chrome

SKU
PFXHAC32C

Heavy Duty Angle Stops with Loose Key



- For commercial use
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Heavy pattern design
- Color/Finish: Chrome

SKU	Connection
PFXHAT32CLK	1/2" IPS x 3/8" OD Comp
PFXHATT33CLK	1/2" IPS x 1/2" IPS
PFXHAC32CLK	5/8" OD Comp x 3/8" OD Comp

Loose Key Replacements



- Replacement key for PROFLO loose key stops
- Color/Finish: Chrome

SKU
PFRKLK

Straight Supply Stop Valves



- Multi-turn design
- Connection: 5/8" OD Comp x 3/8" OD Comp
- Machined in one piece from extruded brass bar stock
- Brass body
- Plastic stem
- Metal handle
- Color/Finish: Chrome

SKU
PFXSC32CA

Straight Supply Stop Valves



- Quarter-turn design
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handle
- Color/Finish: Chrome

SKU	Connection
PFXQSF22C	3/8" Fem Comp x 3/8" OD Comp
PFXQST22C	3/8" FIP x 3/8" OD Comp
PFXQSP32C	1/2" PEX x 3/8" OD Comp
PFXQSS32C	1/2" Sweat x 3/8" OD Comp
PFXQST32C	1/2" FIP x 3/8" OD Comp
PFXQSV32C	1/2" CPVC x 3/8" OD Comp
PFXQSC32C	5/8" OD Comp x 3/8" OD Comp

Straight Supply Stop Valves



PROFLO FASTFIT™

- Quarter-turn design
- Connection: 5/8" OD Push x 3/8" OD
- Push connect technology
- Removable and reusable
- Works with copper, PEX and CPVC
- Brass stem and body

SKU	Color/Finish
PFXQSQ32BN	Brushed Nickel
PFXQSQ32C	Chrome
PFXQSQ32ORB	Oil Rubbed Bronze

Straight Supply Stop Valves



PROFLO

- Multi-turn design
- Brass stem and body
- Metal handles
- Machined in one piece from extruded brass bar stock

SKU	Connection	Color/Finish
PFXST22C	3/8" FIP x 3/8" OD Comp	Chrome
PFXSP32C	1/2" PEX x 3/8" OD Comp	Chrome
PFXSS32C	1/2" Sweat x 3/8" OD Comp	Chrome
PFXST32C	1/2" FIP x 3/8" OD Comp	Chrome
PFXSV32C	1/2" CPVC x 3/8" OD Comp	Chrome
PFXSV32R	1/2" CPVC x 3/8" OD Comp	Rough Brass
PFXSC32C	5/8" OD Comp x 3/8" OD Comp	Chrome

Supply Stop Valves



PROFLO

- Quarter-turn design
- Machined in one piece from extruded brass bar stock
- Brass stem and body
- Metal handle
- Cold Expansion PEX Connection: F1960
- Size: 1/2" F1960 PEX x 3/8" OD
- Color/Finish: Chrome

SKU	Stops
PFXQAPP32C	Angle
PFXQSPP32C	Straight

Supply Kits



MONOGRAM BRASS™

- For toilets and sinks
- Connection: 1/2" Sweat x 3/8" OD Comp straight stop
- 5/8" OD bell flange
- Metal construction

SKU	Color/Finish
MB213BN	Brushed Nickel
MB213ORB	Oil Rubbed Bronze

Supply Kits



MONOGRAM BRASS™

- Connection: 5/8" OD Comp x 3/8" OD Comp angle stop
- 3/8" x 20" flat head rigid toilet tube
- 5/8" OD sure grip bell flange

SKU	Color/Finish
MB251BN	Brushed Nickel
MB251CP	Chrome
MB251ORB	Oil Rubbed Bronze
MB251PN	Polished Nickel

Supply Kits



MONOGRAM BRASS™

- Connection: 5/8" OD Comp x 3/8" OD Comp angle stop
- 3/8" x 12" flexible riser
- 5/8" OD sure grip bell flange

SKU	Color/Finish
MB254BN	Brushed Nickel
MB254CP	Chrome
MB254ORB	Oil Rubbed Bronze
MB254PN	Polished Nickel

Closet Supply Kits



PROFLO

- Connection: 3/8" IPS x 3/8" OD Comp
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Flexible copper risers with plated steel deep flanges and stops
- Color/Finish: Chrome
- ASME A112.18.1
- CSA B125.1
- NSF 372

LOW LEAD

SKU
PFXCAT22CC12

Closet Supply Kits



PROFLO

- For commercial use
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Flexible copper risers with plated steel deep flanges and stops
- Color/Finish: Chrome

LOW LEAD

SKU	Connection
PFXCAS32CC12	1/2" Sweat x 3/8" OD Comp
PFXCAC32CC12	5/8" OD x 3/8" OD Comp

Closet Supply Kits



PROFLO

- For commercial use
- Multi-turn design
- Connection: 1/2" IPS x 3/8" OD Comp
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Flexible copper risers with steel deep flanges and stops
- Heavy pattern
- Color/Finish: Chrome
- ANSI A112.18.1
- CSA B125.1
- NSF 372

LOW LEAD

SKU
PFXHAT32CC12

Closet Supply Kits



PROFLO

- For commercial use
- Handle Type: Loose Key
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Flexible copper risers with plated steel deep flanges and stops
- Color/Finish: Chrome

LOW LEAD

SKU	Connection
PFXCAT22CLKC12	3/8" IPS x 3/8" OD Comp
PFXCAS32CLKC12	1/2" Sweat x 3/8" OD Comp
PFXCAC32CLKC12	5/8" OD x 3/8" OD Comp

Closet Supply Kits



PROFLO

- For commercial or residential use
- Multi-turn design
- Connection: 1/2" Sweat
- Brass stem and body
- Color/Finish: Chrome

LOW LEAD

SKU
PFXAZ32CC12

Closet Supply Kits



PROFLO

- Multi-turn design
- Connection: 1/2" NOM Sweat
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Flexible copper risers with plated steel deep flanges and stops
- Includes cover tube
- Color/Finish: Chrome

LOW LEAD

SKU
PFXCAZ32CC12

Lavatory Supply Kits



MONOGRAM BRASS™

- Connection: (2) 5/8" OD Comp x 3/8" OD Comp angle stop
- (2) 3/8" x 20" bull nose rigid lavatory tube
- (2) 5/8" OD sure grip bell flange

SKU	Color/Finish
MB231BN	Brushed Nickel
MB231CP	Chrome
MB231ORB	Oil Rubbed Bronze

Lavatory Supply Kits



- Connection: 1/2" IPS x 3/8" OD Comp
- Flexible copper risers with steel deep flanges and stops
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Heavy pattern
- Color/Finish: Chrome

SKU
PFXHAT32CL12

Lavatory Supply Kits



- For commercial use
- Flexible copper risers with plated steel deep flanges and stops
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Color/Finish: Chrome

SKU	Connection
PFXCAT22CL12	3/8" IPS x 3/8" OD Comp
PFXCAS32CL12	1/2" Sweat x 3/8" OD Comp
PFXCAT32CL12	1/2" IPS x 3/8" OD Comp
PFXCAC32CL12	5/8" OD x 3/8" OD Comp

Lavatory Supply Kits with Loose Key



- For commercial use
- Flexible copper risers with plated steel deep flanges and stops
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Color/Finish: Chrome

SKU	Connection
PFXCAT22CLKL12	3/8" IPS x 3/8" OD Comp
PFXHATT22CLKL12	3/8" IPS x 3/8" Comp
PFXCAS32CLKL12	1/2" Sweat x 3/8" OD Comp
PFXCAT32CLKL12	1/2" IPS x 3/8" OD Comp
PFXHAT32CLKL12	1/2" IPS x 3/8" OD Comp
PFXCAC32CLKL12	5/8" OD Comp x 3/8" OD Comp

Lavatory Supply Kits



- Flexible copper risers with plated steel deep flanges, stops and cover tubes
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- With cover tube
- Brass stem and body
- Color/Finish: Chrome

SKU	Connection
PFXCAZ32CL12	1/2" Sweat x 3/8" Comp
PFXCAZ32CLKL12	1/2" Sweat x 3/8" Comp w/ Loose Key

Lavatory Supply Kits with Loose Key



- Commercial or residential use
- Multi-turn design
- Connection: 3/8" IPS x 3/8" IPS
- Flexible copper risers with plated steel deep flanges and stops
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Color/Finish: Chrome
- ASME A112.18.1
- CSA B125.1
- NSF 372

SKU
PFXCATT22CLKRL12

Lavatory Supply Kits with Loose Key



PROFLO

- Commercial or residential use
- Multi-turn design
- Connection: 1/2" IPS x 1/2" Comp
- Flexible copper risers with steel deep flanges and stops
- Maximum Temperature: 160°F
- Maximum Pressure: 125 psi
- Brass stem and body
- Heavy pattern design
- Color/Finish: Chrome
- ANSI A112.18.1
- CSA B125.1
- NSF 372

LOW LEAD

SKU
PFXHAT33CLKL12

Distribution Units



PROFLO

- Connection: 1/2" MIP x 1/2" FIP
- Prime multiple floor drains using only one trap priming valve
- Level mounting required
- Water supply line must be a minimum of 1/2" OD copper tube
- Does not include adapters or tubing
- PVC construction

SKU
PFPDUU

Clear Vinyl Tubing



PROFLO

- Flexible clear tubing
- PVC construction
- Not recommended for repair/installation of dishwasher lines
- Not resistant to esters, ketones and aromatic hydro-carbons
- Maximum Operating Temperature: 150°F

SKU	Size	Inside Diameter
PF149012N	1/4" x 100'	1/8"
PF149014N	5/16" x 100'	3/16"
PF149016N	3/8" x 100'	1/4"
PF149022N	1/2" x 100'	3/8"
PF149026N	5/8" x 100'	1/2"
PF149028N	3/4" x 100'	1/2"
PF149030N	7/8" x 100'	5/8"
PF149032N	1" x 50'	3/4"
PF149034N	1 1/4" x 50'	1"

Water Hammer Arrestors



PROFLO

- Connection: 1/2" Female Sweat x 1/2" Male Sweat
- 1/2" tub/shower
- Helps to eliminate shock waves generated in piping systems by sudden on/off changes in flow
- Polypropylene piston
- Temperature Range: 33°F to 180°F
- Maximum Working Pressure: 350 psi
- AA arrestors are suitable for 1-3 fixture units per PDI standard

LOW LEAD

SKU
PFXWHATSD

Poly Tubing



PROFLO

- Flexible white tubing
- Not recommended for repair/installation of dishwasher lines
- Resistant to many acids, alkalis and most organic solutions
- Polyethylene construction

SKU	Size
PF149002N	1/4" x 100'
PF149006N	3/8" x 100'
PF149008N	1/2" x 100'

Water Hammer Arrestors



PROFLO

- Connection: 3/4" FHT x 3/4" MHT
- For laundry applications
- Helps to eliminate shock waves generated in piping systems by sudden on/off changes in flow
- Brass piston
- Temperature Range: 33°F to 180°F
- Maximum Pressure: 350 psi
- AA arrestors are suitable for 1-3 fixture units per PDI standard

SKU
PFMM500L

Water Hammer Arrestors



PROFLO

- Compression tee
- Helps to eliminate shock waves generated in piping systems by sudden on/off changes in flow
- Polypropylene piston
- Temperature Range: 33°F to 180°F
- Maximum Pressure: 350 psi
- AA arrestors are suitable for 1-3 fixture units per PDI standard
- Compression x Female Compression designed to install either between stub out and supply stop or between supply stop and supply tube for dishwashers, faucets, toilets or ice makers

LOW LEAD

SKU	Connection
PFXWHAUTB	1/4" OD Comp x 1/4" OD Comp
PFXWHACTC	3/8" OD Comp x 3/8" OD Female Comp
PFXWHAUTC	3/8" OD Comp x 3/8" OD Comp
PFXWHACTD	5/8" OD Comp x 5/8" OD Female Comp
PFXWHAUTD	5/8" OD Comp x 5/8" OD Comp

Water Hammer Arrestors



PROFLO

- In-line PEX connection
- Helps to eliminate shock waves generated in piping systems by sudden on/off changes in flow
- Polypropylene piston
- Temperature Range: 33°F to 180°F
- Maximum Working Pressure: 350 psi
- AA arrestors are suitable for 1-3 fixture units per PDI standard

LOW LEAD

SKU	Connection
PFXWHAPPTD	1/2" F1960 PEX
PFXWHAPTD	1/2" F1807 PEX

Water Hammer Arrestors



PROFLO

- 1/2" straight
- Helps to eliminate shock waves generated in piping systems by sudden on/off changes in flow
- Polypropylene piston
- Temperature Range: 33°F to 180°F
- Maximum Pressure: 350 psi
- AA arrestors are suitable for 1-3 fixture units per PDI standard

LOW LEAD

SKU	Connection
PFXWHACFD	1/2" CPVC Female Socket
PFXWHACSD	1/2" CPVC Male Spigot
PFXWHASD	1/2" Copper Male Sweat
PFXWHATD	1/2" Copper Male Threaded
PFXWHAPD	1/2" F1807 PEX
PFXWHAPPD	1/2" F1960 PEX







Washing Machine Valves
P. 151-152

Bell Hangers



- Coating: Epoxy
- CTS connection
- Assembled with #10 x 2 coarse thread drywall screw
- Includes zinc dichromate screws
- Recessed mounting screw has a pierce point to penetrate metal studs
- Provides 13/16" standoff
- Material: Carbon Steel

SKU	Pipe Size
PFBHD	1/2"
PFBHF	3/4"
PFBHG	1"
PFBHH	1 1/4"
PFBHJ	1 1/2"
PFBHK	2"

DWV Hangers



- Vinyl coated
- Galvanized steel construction

SKU	Size
PF220J	1 1/2"
PF220K	2"
PF220M	3"
PF220P	4"


Hanger Straps



- Galvanized steel construction

SKU	Length	Gauge
PF100G20F10	10'	20
PFPT22010	10'	22
PF100G24F10	10'	24
PFPT26010	10'	26
PF101G28F10	10'	28
PF100G24F50	50'	24
PF101G28F50	50'	28
PF100G24F100	100'	24
PF101G28F100	100'	28

Hanger Straps



- Copper clad construction

SKU	Length	Gauge
PFPT24010CC	10'	24
PF100C22F50	50'	22

Hanger Straps



- 24 gauge
- Steel construction

SKU	Length
PF100S24F10	10'
PF100S24F50	50'
PF100S24F100	100'

Hanger Straps



- Max Working Load: 15 lbs at -20°F to 120°F
- Breaking Strength: 100 lbs at 68°F
- Plastic construction

SKU	Length
PF102F25	25'
PF102F50	50'
PF102F100	100'

Hook-On Straps



- 14 gauge
- Galvanized steel construction

SKU	Size
PFHS18	18"
PFHS26	26"

J-Hooks



- 12 gauge

SKU	Size	Material
PF12CCJNPL	3/8" IPS / 1/2" CTS	Plastic Coated Copper
PF12CCJN	1/2"	Copper Plated
PF12GAJN	1/2"	Galvanized
PF540	1/2" & 3/4" CTS	Copper
PF34CCJNPL	1/2" IPS / 3/4" CTS	Plastic Coated Copper
PF1CCJNPL	3/4" IPS / 1" CTS	Plastic Coated Copper

J-Hooks



- For use on SCH 40 pipe
- Nail holes on all four sides for attachment at various angles and pipe runs
- Safe Load: 50 lbs
- Maximum Temperature Rating: 240°F
- Nails included
- ABS construction
- Color/Finish: White

SKU	Size
PF33845	1 1/2"
PF33846	2"
PF33847	3"
PF33848	4"

Pipe Straps



- Two hole design
- Copper clad steel construction
- With nails

SKU	Size
PF500WND	1/2"
PF500WNF	3/4"
PF500WNG	1"
PF500WNH	1 1/4"
PF500WNJ	1 1/2"
PF500WNK	2"

Pipe Straps



- Two hole design
- Copper clad steel construction

SKU	Size
PFCTSA	1/8" CTS
PF500B	1/4" IPS
PFCTSB	1/4" CTS
PF500C	3/8" IPS
PFCTSC	3/8" CTS
PF500D	1/2" IPS
PFCTSD	1/2" CTS
PF500F	3/4" IPS
PFCTSF	3/4" CTS
PF500G	1" IPS
PFCTSG	1" CTS
PF500H	1 1/4" IPS
PFCTSH	1 1/4" CTS
PF500J	1 1/2" IPS
PFCTSJ	1 1/2" CTS
PF500K	2" IPS
PFCTSK	2" CTS

Pipe Straps



- Two hole design
- Iron pipe size
- Galvanized steel construction

SKU	Size
PF600C	3/8" IPS
PF600D	1/2" IPS
PF600F	3/4" IPS
PF600G	1" IPS
PF600H	1 1/4" IPS
PF600J	1 1/2" IPS
PF600K	2" IPS
PF600L	2 1/2" IPS
PF600M	3" IPS
PF600N	3 1/2" IPS
PF600P	4" IPS
PF600U	6" IPS

Pipe Straps



- One hole design
- Iron pipe size
- Galvanized steel construction

SKU	Size
PF610C	3/8" IPS
PF610D	1/2" IPS
PF610F	3/4" IPS
PF610G	1" IPS
PF610H	1 1/4" IPS
PF610J	1 1/2" IPS
PF610K	2" IPS

Wire Pipe Hooks



- 3/4" x 6" CTS
- 10 gauge
- Copper tube size
- PVC coated copper
- Made in the USA

SKU
PF200PFU10

Wire Pipe Hooks



- Iron pipe size
- PVC coated steel
- Made in the USA

SKU	Size	Gauge
PF200PSDU12	1/2" x 6" IPS	12
PF200PSFP10	3/4" x 4" IPS	10
PF200PSFU10	3/4" x 6" IPS	10
PF200PSFU12	3/4" x 6" IPS	12

Wire Pipe Hooks



- 10 gauge
- Copper tube size
- Color/Finish: Copper Plated

SKU	Size
PF200CDP10	1/2" x 4" CTS
PF200CDU10	1/2" x 6" CTS
PF200CFP10	3/4" x 4" CTS
PF200CFU10	3/4" x 6" CTS
PF200CGU10	1" x 6" CTS


Wire Pipe Hooks



- 10 gauge
- Iron pipe size

SKU	Size	Material
PF200SDU10	1/2" x 6" IPS	Black Steel
PF200SFP10	3/4" x 4" IPS	Black Steel
PF200SFU10	3/4" x 6" IPS	Black Steel
PF200SGU10	1" x 6" IPS	Black Steel
PF200PSGU10	1" x 6" IPS	PVC Coated
PF200SGX10	1" x 8" IPS	Black Steel

Insulated Pipe Clamps



- Provides fast and easy installation and support for all types of copper tube size piping
- Impact resistant to 0°F
- Maximum Temperature: 180°F
- Eliminates contact between the pipe and framing surface
- Insulates against sound
- Can be used with hydronic heating systems
- Flexible low density polyethylene

SKU	Size
PF34256	1/2"
PF34257	3/4"
PF34258	1"

Pipe Clamps



- Half clamp including barb nail
- Provides fast and easy installation and support for all types of copper tube size piping
- Eliminates contact between the pipe and framing surface
- Insulates against sound
- Can be used with hydronic heating systems
- High impact polypropylene

SKU	Size
PF34240	1/2"
PF34241	3/4"
PF34242	1"

Pipe Clamps



- Full clamp including barb nail
- Provides fast and easy installation and support for all types of copper tube size piping
- Eliminates contact between the pipe and framing surface
- Insulates against sound
- Can be used with hydronic heating systems
- High impact polypropylene

SKU	Size
PF34243	1/2"
PF34244	3/4"
PF34245	1"

Pipe Clamps



- Suspension style
- Provides fast and easy installation and support for all types of copper tube size piping
- Can be used as an insulator when running water distribution lines through wooden framing
- Can be used with hydronic heating systems
- Polypropylene construction

SKU	Size
PF34250	1/2" CTS
PF34251	3/4" CTS
PF34252	1" CTS
PF34260	1 1/4" CTS
PF34261	1 1/2" CTS
PF34262	2" CTS

Pipe Clamps



- Provides fast and easy installation and support for all types of piping
- Permits quick pipe cooling and reduces water noise
- Design allows piping to be flush mounted to the wall and joists
- Can be used with hydronic heating systems
- Copper tube size
- Polypropylene construction

SKU	Size
PF34253	1/2" CTS
PF34254	3/4" CTS
PF34255	1" CTS
PF34263	1 1/4" CTS
PF34264	1 1/2" CTS
PF34265	2" CTS

Pipe Clamps



- Quick, one hand installation
- Snaps shut
- Pre-loaded nail
- Ribbed for low noise
- Copper safe copolymer

SKU	Size
PF513D	1/2"
PF513F	3/4"

Pipe Support Brackets



- 16 gauge, copper bonded steel
- Positions copper water supplies for sinks, water closets, and other fixtures

SKU	Length	Fits Pipe Size
PFCB20D	20"	1/2" holes
PFCB20DF	20"	1/2" & 3/4" holes
PFCB20DFG	20"	1/2", 3/4" & 1" holes
PFCB20FG	20"	3/4" & 1" holes
PFCB26D	26"	1/2" holes
PFCB26DF	26"	1/2" & 3/4" holes
PFCB26FG	26"	3/4" & 1" holes

Pipe Support Brackets



- Extruded holes
- 16 gauge, copper bonded steel
- Positions copper water supplies for sinks, water closets, and other fixtures

SKU	Length	Fits Pipe Size
PFCBE20D	20"	1/2" holes
PFCBE26DF	26"	1/2" & 3/4" holes

Pipe Support Brackets



- 1/2", 3/4" & 1" holes
- Rolled edges & extruded holes
- 24 gauge, copper bonded steel
- Positions copper water supplies for sinks, water closets, and other fixtures

SKU	Length
PFCBRE20DFG	20"
PFCBRE26DFG	26"

Pipe Support Brackets



- 16 gauge, copper bonded steel
- Horizontal or vertical support
- Clamps directly to waste/vent piping
- Positions copper water supplies for sinks, water closets, and other fixtures

SKU	Length	Fits Pipe Size
PFCVBD	9 1/3"	1/2" notches
PFCHVBDF	9 1/2"	1/2" & 3/4" notches


Pipe Support Brackets



- Length: 20"
- 1/2" & 3/4" notches
- 16 gauge, copper bonded steel
- Positions copper water supplies for sinks, water closets, and other fixtures

SKU
PFCNB20DF

Pipe Support Brackets



- 1/2" & 3/4" holes
- 16 gauge, copper bonded steel
- Positions stub-outs at various heights
- Also functions as a nail plate

SKU
PFCSB6

Pipe Support Brackets



- 1/2", 3/4" or 1" holes
- 14 gauge, galvanized steel
- Positions copper water supplies for sinks, water closets, and other fixtures

SKU	Length
PFGB20	20"
PFGB26	26"

Pipe Support Brackets



- 1/2" & 3/4" holes
- Designed exclusively to support CPVC piping
- 20 gauge, galvanized steel

SKU	Length
PFGB20DF	20"
PFGB26DF	26"

Pipe Support Brackets



- 1/2", 3/4" or 1" holes
- 20 gauge, copper bonded steel
- Positions copper, PEX or CPVC water supplies
- Hole pattern on 90° base
- Bracket can be mounted directly to flat surface or suspended from 3/8" ATR

SKU
PFGABDFG

FHA Plates



- Steel plate straps

SKU	Size	Holes (Ea. End)	Gauge
PF935NU	6" x 3 1/2"	2	16
PFSP0916	9" x 1 1/2"	4	16
PF918J9	9" x 1 1/2"	4	18
PF918J12	12" x 1 1/2"	4	18
PF916J18	18" x 1 1/2"	4	16
PF918J18	18" x 1 1/2"	4	18
PF938J18	18" x 1 1/2"	8	16
PF919M18	18" x 3"	4	18
PF949M18	18" x 3"	8	16
PF950S18	18" x 5"	8	16

Interlocking Safety Plates



- 6" x 1 1/2"
- Interlocking style

SKU	Gauge
PF92216JU	16
PF92218JU	18
PF922U	20

Plate Straps



PROFLO

- Steel construction

SKU	Size	Holes (Ea. End)	Gauge
PFPS0916	1 1/2" x 9"	4	16
PFPS09126	1 1/2" x 9"	6	12
PFPS169	1 1/2" x 9"	6	16
PFPS12164	1 1/2" x 12"	4	16
PFPS12126	1 1/2" x 12"	6	12
PFPS12166	1 1/2" x 12"	6	16
PFPS18126	1 1/2" x 18"	6	12
PFPS18166	1 1/2" x 18"	6	16
PFPS2416	1 1/2" x 24"	4	16
PFPS24126	1 1/2" x 24"	6	12
PFPS24166	1 1/2" x 24"	6	16

Stud Guards



PROFLO

- Steel construction

SKU	Size	Holes (Ea. End)	Gauge
PF906JM	3" x 1 1/2"	1	18
PF906JU	6" x 1 1/2"	1	18
PF958	8" x 5"	3	16

Safety Plates



PROFLO

- Steel self-nailing safety plates

SKU	Size	Gauge
PFSP316100	1 1/2" x 3"	16
PF530JM	1 1/2" x 3"	18
PFSP416100	1 1/2" x 4"	16
PF536JS	1 1/2" x 5"	16
PF530JS	1 1/2" x 5"	18
PF531JS	1 1/2" x 5"	20
PF536JU	1 1/2" x 6"	16
PF530JU	1 1/2" x 6"	18
PF531JU	1 1/2" x 6"	20
PF532JU	1 1/2" x 6"	22
PF531JX	1 1/2" x 8"	20
PFSP5161002	2" x 5"	16
PFSP5161003	3" x 5"	16
PF957	8" x 5"	16

Stud Shoes




PROFLO


- Not for load bearing wall

SKU	Type
PF5331	Single
PF5332	Double
PF5333	Triple

PROSELECT™



WE CARRY THE FASTENERS YOU NEED



Our vast distribution network and in-depth HVAC knowledge help you get the job done.

Shop PROSELECT at FERGUSON.COM.

CPVC Transition Fittings



- CPVC/SS transition fittings
- Molded CPVC adapter with 300 series stainless steel female adapter
- Pressure rated to 100 psi @ 180°F
- Compact design

SKU	Size
PFXCPFAD	1/2"
PFXCPFAF	3/4"
PFXCPFAG	1"
PFXCPFAH	1 1/4"
PFXCPFAJ	1 1/2"
PFXCPFAK	2"

CPVC Transition Fittings



- CPVC/SS transition union fittings
- Molded CPVC socket union with 300 series stainless steel female adapter
- Pressure rated to 100 psi @ 180°F
- Compact design

SKU	Size
PFXCPSUD	1/2"
PFXCPSUF	3/4"

CPVC Transition Fittings



- CPVC/SS transition fittings
- Size: 1/2"
- Molded CPVC drop ear elbow adapter with 300 series stainless steel female adapter
- Pressure rated to 100 psi @ 180°F
- Compact design

SKU
PFXCPFDE9DSS

CPVC Transition Fittings



- CPVC/SS transition fittings
- Size: 1/2"
- Molded CPVC drop ear elbow adapter with 300 series stainless steel female adapter
- Pressure rated to 100 psi @ 180°F
- Compact design

SKU
PFXCPFDE9D

CPVC Transition Fittings



- CPVC/SS transition fittings
- Molded CPVC adapter with 300 series stainless steel male adapter
- Pressure rated to 100 psi @ 180°F
- Compact design

SKU	Size
PFXCPMAD	1/2"
PFXCPMAF	3/4"
PFXCPMAG	1"
PFXCPMAH	1 1/4"
PFXCPMAJ	1 1/2"
PFXCPMAK	2"

Copper Adapters



- Female Sweat x MIP threaded adapter
- Full slip allows adapter to slide over copper tubing
- For use on tub spout or urinal installations
- Solid brass construction

SKU	Size	Connection
PFCSMAD	1/2"	MIP x Sweat Bushing
PFCSMAF	3/4"	MIP x Sweat Bushing
PFCSMAG	1"	MIP x Sweat Bushing
PFCMRH	1 1/4"	DWV CxM Marvel Ring
PFCMRJ	1 1/2"	DWV CxM Marvel Ring
PFCMRK	2"	DWV CxM Marvel Ring

Dielectric Nipples



PROFLO

- Metal to metal design
- Connection: Groove x Groove
- Maximum Pressure: 300 psi
- Maximum Temperature: 230°F (110°C)
- Polypropylene plastic liner
- Zinc Plated

LOW LEAD

SKU	Size
PFXDNGKP	2" x 4"
PFXDNGLU	2 1/2" x 6"
PFXDNGMU	3" x 6"
PFXDNGPU	4" x 6"
PFXDNGUU	6" x 6"

Dielectric Nipples



PROFLO

- Metal to metal design
- Connection: Groove x Thread
- Maximum Pressure: 300 psi
- Maximum Temperature: 230°F (110°C)
- Polypropylene plastic liner
- Zinc Plated

LOW LEAD

SKU	Length	Size
PFXDNGTGP	4"	1"
PFXDNGTHP	4"	1 1/4"
PFXDNGTJP	4"	1 1/2"
PFXDNGTKP	4"	2"
PFXDNGTLU	6"	2 1/2"
PFXDNGTMU	6"	3"
PFXDNGTPU	6"	4"

Dielectric Nipples



PROFLO

- Metal to metal design
- Connection: Thread x Thread
- Maximum Pressure: 300 psi
- Maximum Temperature: 230°F (110°C)
- Polypropylene plastic liner
- Zinc Plated

LOW LEAD

SKU	Length	Size
PFXDNTDM	3"	1/2"
PFXDNTFM	3"	3/4"
PFXDNTGP	4"	1"
PFXDNTHP	4"	1 1/4"
PFXDNTJP	4"	1 1/2"
PFXDNTKP	4"	2"
PFXDNTLU	6"	2 1/2"
PFXDNTMU	6"	3"
PFXDNTPU	6"	4"

Dielectric Union Gaskets



PROFLO

- Replacement dielectric union gaskets for PROFLO dielectric unions
- EPDM construction
- Package Quantity: 10

SKU	Size
PFDUGD	1/2"
PFDUGF	3/4"
PFDUGFD	3/4" x 1/2"
PFDUGG	1"
PFDUGH	1 1/4"
PFDUGJ	1 1/2"
PFDUGK	2"

Dielectric Unions



PROFLO

- Prevents electrolysis or galvanic action when connecting dissimilar materials
- Pressure rated to 250 psi @ 180°F
- Includes EPDM gasket and nylon fiber sleeve
- UPC/IAPMO listed
- NSF/ANSI 61 and NSF/ANSI 372 compliant

LOW LEAD

SKU	Connection
PFXCCMS22	1/2" Sweat x 1/2" MIP
PFXCCS22	1/2" Sweat x 1/2" FIP
PFXCCS32	3/4" Sweat x 1/2" FIP
PFXCCMS33	3/4" Sweat x 3/4" MIP
PFXCCS33	3/4" Sweat x 3/4" FIP
PFXCCS44	1" Sweat x 1" FIP
PFXCCS55	1 1/4" Sweat x 1 1/4" FIP
PFXCCS66	1 1/2" Sweat x 1 1/2" FIP
PFXCCS77	2" Sweat x 2" FIP

Lavatory Nose Pieces



PROFLO

- For tube solder application
- Brass construction
- NSF/ANSI 372

LOW LEAD

SKU
PFXLNPCN

Compression Adapters



- Converts 3/8" compression valve outlet to dual outlet
- For use with potable water, instrumentation, hydraulic and pneumatic systems
- Designed for use with aluminum, copper and plastic tubing
- Maximum Temperature: -65°F – 250°F
- Maximum Pressure: 200 psi
- Not intended for use with steel tubing
- Brass construction

SKU	Size
PFXCTFCCCN	3/8"
PFXCTFCCBN	3/8" x 3/8" x 1/4"

Compression Adapters



- Connection: 3/8" OD x 1/2" FIP
- Brass construction
- NSF/ANSI 372

SKU
PFXFCUCDCPN

Compression Adapters



- Brass construction
- Color/Finish: Chrome
- NSF/ANSI 372

SKU	Connection
PFXMCUCBCP	3/8" OD x 1/4" MIP
PFXMCUCDCPN	3/8" OD x 1/2" MIP

Compression Caps



- Maximum Temperature: 250°F
- Brass construction
- NSF/ANSI 372

SKU	Size
PFXCCBN	1/4" OD Comp
PFXCCCN	3/8" OD Comp
PFXCCDN	1/2" OD Comp
PFXCCEN	5/8" OD Comp

Compression Elbows



- Connection: 1/4" OD Comp x 3/8" MIP
- Brass construction

SKU
PFXMCEBCN

Compression Elbows



- Connection: 3/4" FHT x 3/8" OD Tube
- Maximum Pressure: 75 psi
- Maximum Temperature: 140°F
- Compression nut, sleeve and high-temp washer included
- Brass construction

SKU
PFXDEN

Compression Elbows



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXMCEBAN	1/4" OD x 1/8" MIP
PFXMCEBBN	1/4" OD x 1/4" MIP
PFXMCECAN	3/8" OD x 1/8" MIP
PFXMCECBN	3/8" OD x 1/4" MIP
PFXMCECCN	3/8" OD x 3/8" MIP
PFXMCECDN	3/8" OD x 1/2" MIP
PFXMCEDCN	1/2" OD x 3/8" MIP
PFXMCEDDN	1/2" OD x 1/2" MIP
PFXMCEEDN	5/8" OD x 1/2" MIP

Compression Elbows



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXCEBBN	1/4" Comp x 1/4" Comp
PFXCECCN	3/8" Comp x 3/8" Comp
PFXCEDDN	1/2" Comp x 1/2" Comp
PFXCEEEN	5/8" Comp x 5/8" Comp

Compression Elbows



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXFCECCN	3/8" OD Comp x 3/8" FIP
PFXFCECDN	3/8" OD x 1/2" FIP

Compression Elbows



- Brass construction
- Color/Finish: Chrome
- NSF/ANSI 372

SKU	Connection
PFXFCECPCDN	3/8" OD x 1/2" FIP Comp
PFXCEECN	5/8" x 3/8" Comp
PFXCEECCPN	5/8" x 3/8" Comp (Chrome)


Compression Elbows



- Connection: 7/8" Comp x 7/8" Comp
- Brass construction

SKU
PFXCE7878

Compression Nuts



- Brass construction
- NSF/ANSI 372

SKU	Size
PFCNAN	1/8" Comp
PFCNBN	1/4" Comp
PFCNCNN	3/8" Comp
PFCNDNN	1/2" Comp
PFCNEN	5/8" Comp
PFXCN78	7/8" Comp

Compression Plugs



- Connection: 3/8" Comp
- Brass construction

SKU
PFXCPCN

Compression Sleeves



- Plastic construction
- NSF/ANSI 372

SKU	Size
PFPCSBN	1/4" OD
PFPCSCN	3/8" OD
PFPCSDN	1/2" OD
PFPCSEN	5/8" OD

Compression Sleeves



- Brass construction
- NSF/ANSI 372

SKU	Size
PFCSAN	1/8" OD
PFCSBN	1/4" OD
PFCSCN	3/8" OD
PFCSDN	1/2" OD
PFCSEN	5/8" OD
PFCS78N	7/8" OD

Compression Tees



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXCTBN	1/4" x 1/4" x 1/4" Comp
PFXCTCN	3/8" x 3/8" x 3/8" Comp
PFXCTDN	1/2" x 1/2" x 1/2" Comp
PFXCTEN	5/8" x 5/8" x 5/8" Comp
PFXCTCCPN	3/8" x 3/8" x 3/8" Comp (Chrome)
PFXCTCCBN	3/8" x 3/8" x 1/4" Comp

Compression Union Adapters



- Brass construction
- Sweat to compression transition adapter
- NSF/ANSI 372

SKU	Connection
PFXCARBDBN	1/2" Sweat x 1/4" OD Comp
PFXARBDCN	1/2" Sweat x 3/8" Comp

Compression Unions



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXMCUAAN	1/8" OD Comp x 1/8" MIP
PFXMCUBAN	1/4" OD x 1/8" MIP Comp
PFXMCUBBN	1/4" OD x 1/4" MIP Comp
PFXMCUBCN	1/4" OD x 3/8" MIP Comp
PFXMCUBDN	1/4" OD x 1/2" MIP Comp
PFXMCUCAN	3/8" OD x 1/8" Comp
PFXMCUCBN	3/8" OD x 1/4" MIP
PFXMCUCCN	3/8" OD x 3/8" MIP Comp
PFXMCACCCPN	3/8" MIP x 3/8" Comp
PFXMCUCDN	3/8" OD x 1/2" MIP Comp
PFXMCUCFN	3/8" OD x 3/4" MIP Comp
PFXMCUDBN	1/2" OD x 1/4" MIP Comp
PFXMCRADCN	1/2" OD x 3/8" MIP
PFXMCADCCPN	1/2" MIP x 3/8" Comp
PFXMCUDDN	1/2" OD x 1/2" MIP Comp
PFXMCUDFN	1/2" OD x 3/4" MIP Comp
PFXMCUECN	5/8" OD x 3/8" MIP Comp
PFXMCUEDN	5/8" OD x 1/2" MIP Comp
PFXMCUEFN	5/8" OD x 3/4" MIP Comp
PFXMCU78FN	7/8" OD x 3/4" MIP Comp
PFXMCU78GN	7/8" OD x 1" MIP Comp

Compression Unions



- Connection: 3/8" OD Comp x 3/8" MIP
- Brass construction
- Color/Finish: Chrome
- NSF/ANSI 372

SKU
PFXMCUCPCCN

Compression Unions



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXCUBN	1/4" x 1/4" Comp
PFXCUCBN	3/8" x 1/4" Comp
PFXCUCN	3/8" x 3/8" Comp
PFXCUDCN	1/2" x 3/8" Comp
PFXCUDN	1/2" x 1/2" Comp
PFXCUECN	5/8" x 3/8" Comp
PFXCUECCPN	5/8" x 3/8" Comp
PFXCUEDN	5/8" x 1/2" Comp
PFXCCUEN	5/8" x 5/8" Comp
PFXCU78N	7/8" x 7/8" Comp



Compression Unions



- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXFCUBAN	1/4" OD x 1/8" FIP
PFXFCUBBN	1/4" OD x 1/4" FIP
PFXFCUBCN	1/4" OD x 3/8" FIP
PFXFCUBDN	1/4" OD x 1/2" FIP
PFXFCUCBN	3/8" OD x 1/4" FIP
PFXFCUCCN	3/8" OD x 3/8" FIP
PFXFCUCDN	3/8" OD x 1/2" FIP
PFXFCUDCN	1/2" OD x 3/8" FIP
PFXFCUDDN	1/2" OD x 1/2" FIP
PFXFCUECN	5/8" OD x 3/8" FIP
PFXFCUEDN	5/8" OD x 1/2" FIP
PFXFCU78FN	7/8" OD x 3/4" FIP

Compression Unions



- Connection: 3/8" Comp
- Brass construction
- Color/Finish: Chrome
- NSF/ANSI 372

SKU
PFXCUBECPCN

Compression Unions



- Connection: 3/8" FEM FLR x 3/8" OD Comp
- Flare to compression transition adapter
- Brass construction
- NSF/ANSI 372

SKU
PFXCUACCN

Swivel Nut Union Valve Connectors



- For use with copper, aluminum, brass or steel tubing that can be flared
- For use with fuel, oil, natural gas, air and liquid petroleum
- Brass construction

SKU	Connection
PFSNVCC	3/8" OD FLR x 3/8" OD FLR
PFSNVCD	1/2" OD FLR x 1/2" OD FLR

Inserts



- For use with plastic and nylon hose and compression fittings
- NSF/ANSI 372

SKU	Size	Material
PFXBRIBN	1/4" OD	Brass
PFXBRICN	3/8" OD	Brass
PFXBRIDN	1/2" OD	Brass
PFXBRIEN	5/8" OD	Brass
PFXSSIEN	5/8" OD	Stainless Steel

Brass 45° Elbows



- Connection: 1/2" Comp
- Brass construction
- Color/Finish: Chrome

SKU
PFXCH4D

Brass 90° Elbows



- Brass construction
- Color/Finish: Chrome

SKU	Connection
PFXCH9C	3/8" FIP
PFXCH9D	1/2" FIP
PFXCH9F	3/4" FIP
PFXCH9G	1" FIP

Brass 90° Street Elbows



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHS9D	1/2"
PFXCHS9F	3/4"
PFXCHS9G	1"

Brass Bushings



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHBDC	1/2" x 3/8"
PFXCHBFD	3/4" x 1/2"

Brass Caps



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHCAPD	1/2"
PFXCHCAPF	3/4"
PFXCHCAPG	1"

Brass Couplings



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHCC	3/8"
PFXCHCD	1/2"
PFXCHRCDC	1/2" x 3/8"

Brass Nipples



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHNCCL	3/8" x Close
PFXCHNCJ	3/8" x 1 1/2"
PFXCHNCK	3/8" x 2"
PFXCHNCL	3/8" x 2 1/2"
PFXCHNCM	3/8" x 3"
PFXCHNCN	3/8" x 3 1/2"
PFXCHNCP	3/8" x 4"
PFXCHNCR	3/8" x 4 1/2"
PFXCHNCS	3/8" x 5"
PFXCHNCT	3/8" x 5 1/2"
PFXCHNCU	3/8" x 6"
PFXCHNCX	3/8" x 8"
PFXCHNC12	3/8" x 12"
PFXCHNDJ	1/2" x 1 1/2"
PFXCHNDK	1/2" x 2"
PFXCHNDL	1/2" x 2 1/2"
PFXCHNDM	1/2" x 3"
PFXCHNDN	1/2" x 3 1/2"
PFXCHNDP	1/2" x 4"
PFXCHNDR	1/2" x 4 1/2"
PFXCHNDS	1/2" x 5"
PFXCHNDT	1/2" x 5 1/2"
PFXCHNDU	1/2" x 6"
PFXCHNDX	1/2" x 8"
PFXCHND10	1/2" x 10"
PFXCHND12	1/2" x 12"
PFXCHND18	1/2" x 18"
PFXCHND36	1/2" x 36"
PFXCHNDCL	1/2" x Close
PFXCHNFCL	3/4" x Close
PFXCHNFJ	3/4" x 1 1/2"
PFXCHNFK	3/4" x 2"
PFXCHNFM	3/4" x 3"
PFXCHNFP	3/4" x 4"
PFXCHNFU	3/4" x 6"
PFXCHNGCL	1" x Close
PFXCHNGK	1" x 2"
PFXCHNGM	1" x 3"
PFXCHNGP	1" x 4"
PFXCHNGS	1" x 5"
PFXCHNGU	1" x 6"







To see more pipe fittings, visit **FERGUSON.COM**

Brass Nipples



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHNFL	3/4" x 2 1/2"
PFXCHNFN	3/4" x 3 1/2"
PFXCHNFR	3/4" x 4 1/2"
PFXCHNFS	3/4" x 5"
PFXCHNFT	3/4" x 5 1/2"
PFXCHNGL	1" x 2 1/2"
PFXCHNGT	1" x 5 1/2"
PFXCHNHK	1 1/4" x 2"
PFXCHNHL	1 1/4" x 2 1/2"
PFXCHNHN	1 1/4" x 3 1/2"
PFXCHNHP	1 1/4" x 4"
PFXCHNHR	1 1/4" x 4 1/2"
PFXCHNHS	1 1/4" x 5"
PFXCHNHU	1 1/4" x 6"
PFXCHNJCL	1 1/2" x Close
PFXCHNJK	1 1/2" x 2"
PFXCHNJL	1 1/2" x 2 1/2"
PFXCHNJP	1 1/2" x 4"
PFXCHNKCL	2" x Close
PFXCHNKM	2" x 3"

Brass Tees



- Brass construction
- Color/Finish: Chrome

SKU	Size
PFXCHTC	3/8"
PFXCHTD	1/2"

Brass Unions



- Connection: 1/2"
- Brass construction
- Color/Finish: Chrome

SKU
PFXCHUD

Faucet Drain Nipples



- Size: 1 1/2" x 6"
- For use on brass threaded drains
- Brass construction
- Color/Finish: Chrome

SKU
PF250

Flare Caps



- Brass construction

SKU	Size
PFFCB	1/4" OD
PFFCC	3/8" OD
PFFCD	1/2" OD
PFFCE	5/8" OD
PFFCEFT	5/8" OD (15/16-16 Thread)

Flare Elbows



- For use with copper, aluminum, brass or steel tubing that can be flared
- For use with fuel, oil, natural gas, air and liquid petroleum
- Brass construction

SKU	Connection
PFMFECC	3/8" OD FLR x 3/8" MIP
PFMFECD	3/8" OD FLR x 1/2" MIP
PFMFEDC	1/2" OD FLR x 3/8" MIP
PFMBRFEDD	1/2" OD FLR x 1/2" MIP

Flare Elbows



- Designed for use with aluminum, copper, brass and welded steel tubing that can be flared
- Brass construction

SKU	Connection
PFMFEBB	1/4" OD x 1/4" MIP
PFMFECB	3/8" OD x 1/4" MIP
PFMFEED	5/8" OD x 1/2" MIP
PFMFEFF	3/4" OD x 3/4" MIP

Flare Nuts



- Short style
- Designed for use with aluminum, copper, brass and welded steel tubing that can be flared
- Brass construction

SKU	Size
PFSFNB	1/4" OD
PFSFNC	3/8" OD
PFSFND	1/2" OD
PFSFNE	5/8" OD
PFSFNF	3/4" OD
PFSFN78	7/8" OD

Flare Nuts



- Short style
- Forged brass construction

SKU	Size
PFFSRFNB	1/4"
PFSRFNFC	3/8"
PFSRFNFD	1/2"
PFSRFNFE	5/8"

Flare Nuts



- Long style
- Size: 1/4"
- Brass construction

SKU
PFLFNB

Flare Plugs



- Brass construction

SKU	Size
PFFPC	3/8" OD
PFFPD	1/2" OD

Flare Tees



- Designed for use with aluminum, copper, brass and welded steel tubing that can be flared
- Brass construction

SKU	Size
PFFTC	3/8" OD
PFFTD	1/2" OD

Flare Unions



- Brass construction

SKU	Connection
PFFFUCB	3/8" OD x 1/4" FIP
PFFFUCC	3/8" OD x 3/8" FIP
PFFFUCD	3/8" OD x 1/2" FIP
PFFFUDD	1/2" OD x 1/2" FIP
PFFFUDF	1/2" OD x 3/4" FIP
PFFFU516B	5/16" OD x 1/4" FIP
PFOFFUED	5/8" OD x 1/2" FIP

Flare Unions



- Brass construction

SKU	Size
PFFUB	1/4" OD
PFFUC	3/8" OD
PFFUCD	3/8" OD x 1/2" OD
PFFUD	1/2" OD
PFFUE	5/8" OD
PFFUED	5/8" OD x 1/2" OD

Flare Unions



- Brass construction

SKU	Connection
PFMFUBA	1/4" OD x 1/8" MIP
PFMFUBB	1/4" OD x 1/4" MIP
PFMFUBC	1/4" OD x 3/8" MIP
PFMFUBD	1/4" OD x 1/2" MIP
PFMFUCA	3/8" OD x 1/8" MIP
PFMFUCB	3/8" OD x 1/4" MIP
PFMFUCC	3/8" OD x 3/8" MIP
PFMFUCD	3/8" OD x 1/2" MIP
PFMFUCF	3/8" OD x 3/4" MIP
PFMFUDB	1/2" OD x 1/4" MIP
PFMFUDC	1/2" OD x 3/8" MIP
PFMFUDD	1/2" OD x 1/2" MIP
PFMFUDF	1/2" OD x 3/4" MIP
PFMFUFF	3/4" OD x 3/4" MIP
PFOMFUED	5/8" OD x 1/2" MIP
PFOMFUEF	5/8" OD x 3/4" MIP
PFMFU78F	7/8" OD x 3/4" MIP

Flare Unions



- Connection: 1/2" OD x 1/2" MIP
- Steel adapter

SKU
PFMUSTLD

Garden Hose Caps



- 3/4"
- Female hose thread
- Includes 12" chain and solid rubber washer
- Brass construction

SKU
PFXGHCC12W

Garden Hose Caps



- 3/4"
- Female hose thread connections require a rubber washer (not included)
- Brass construction
- NSF/ANSI 372

SKU
PFXGHCFN

Garden Hose Washers



- Fits standard 3/4" garden hose connections

SKU
PFRGHWN

Garden Hose Wyes



- Wye design
- Connection: 3/4" FHT x 3/4" MHT
- Female hose thread connections require a rubber washer (not included)
- Brass construction
- NSF/ANSI 372

SKU
PFXHWFFN

Hose Adapters



- Includes rubber washer
- Brass construction
- PFXFFHSFFN is a swivel adapter
- NSF/ANSI 372

SKU	Connection
PFXFFHDFN	1/2" FIP x 3/4" FHT
PFXFMHDFN	1/2" FIP x 3/4" MHT
PFXMFHDFN	1/2" MIP x 3/4" FHT
PFXMMHDFN	1/2" MIP x 3/4" MHT
PFXMFMHFDFN	3/4" MHT x 1/2" FIP (3/4" MIP)
PFXMFHFFN	3/4" MIP x 3/4" FHT
PFXMMHFFN	3/4" MIP x 3/4" MHT
PFXFFHSFFN	3/4" FIP x 3/4" FHT
PFXFMHFFN	3/4" FIP x 3/4" MHT
PFXFFHFFN	3/4" FIP x 3/4" FHT
PFXMHFFN	3/4" MHT x 3/4" MHT

Hose Barb Adapters



- For use with plastic or rubber tubing
- Female hose thread connections require a rubber washer (not included)
- Hose clamp required for installation (not included)
- Brass construction
- NSF/ANSI 372

SKU	Connection
PFXBFHDFN	1/2" BARB x 3/4" FHT
PFXBFHEFN	5/8" BARB x 3/4" FHT
PFXBMHEFN	5/8" BARB x 3/4" MHT
PFXBFHFFN	3/4" BARB x 3/4" FHT

Hose Barb Adapters



PROFLO

- Brass construction
- NSF/ANSI 372

LOW LEAD

SKU	Connection
PFXMHAAN	1/8" ID x 1/8" MPT
PFXMHBABN	1/8" ID x 1/4" MIP
PFXMHBBAN	1/4" ID x 1/8" MIP
PFXFHBBBN	1/4" ID x 1/4" FIP
PFXMHBBBN	1/4" ID x 1/4" MIP
PFXMHBBCN	1/4" ID x 3/8" MIP
PFXMHBBDN	1/4" ID x 1/2" MIP
PFXMHBCBN	3/8" ID x 1/4" MIP
PFXFHBCCN	3/8" ID x 3/8" FIP
PFXMHBCCN	3/8" ID x 3/8" MIP
PFXMHBCDN	3/8" ID x 1/2" MIP
PFXMHBDCN	1/2" ID x 3/8" MIP
PFXMHBDDN	1/2" ID x 1/2" MIP
PFXMHBDFN	1/2" ID x 3/4" MIP
PFXMBRHBEF	5/8" ID x 3/4" MIP
PFXMHBEFN	5/8" x 3/4" MIP
PFXMHBGGN	1" ID x 1" MIP

Hose Swivel Adapters



PROFLO

- Female hose thread connections require a rubber washer (not included)
- Brass construction
- NSF/ANSI 372

LOW LEAD

SKU	Connection
PFXFFHSDFN	1/2" FIP x 3/4" FHT
PFXFHFHSFFN	3/4" FHT x 3/4" FHT



Area Drains



- Full water way design
- Includes cast iron strainer
- Inside caulk outlet
- Cast iron construction
- Color/Finish: Black
- **Optional accessories:**
  Replacement grate: PFFW93BG

SKU	Size
PFFW92B	2"
PFFW93B	3"

Sewer Boxes



- Round
- Stamped sewer
- Red anti-rust finish
- Cast iron construction
- ASTM A48 Class 20

SKU	Size
PFRB12X	8"
PFRB1310	10"

Bell Trap Drains



- Fits SCH 40 pipe

SKU	Size	OD Size	Material
PF42863	1 1/2" or 2"	6" x 6"	PVC
PF42920	1 1/2" or 2"	6" x 6"	ABS
PF42862	3" or 4"	9" x 9"	PVC
PF42919	3" or 4"	9" x 9"	ABS

Cleanout Assemblies



- 3 1/2" MIP barrel threads
- Anti-skid scoriated surface
- Barrel assembly adjusts to meet the finished floor height
- Surrounding ring allows cover removal without disturbing finished floor
- Includes internal thread that accepts 3" cleanout plug
- Medium Duty: safe live load between 2,000 lbs and 4,999 lbs

SKU	Cover	Material
PF42807	5 3/4"	PVC
PF42927	6"	ABS

Cleanout Assemblies



- 3 1/2" MIP barrel threads
- Anti-skid scoriated surface
- Barrel assembly adjusts to meet the finished floor height
- Includes internal thread that accepts 3" cleanout plug
- Medium Duty: safe live load between 2,000 lbs and 4,999 lbs
- 6" brass cover

SKU	Size	Material
PF42813	3" – 4"	PVC
PF42929	3" – 4"	ABS
PF42809	4"	PVC
PF42928	4"	ABS

Cleanouts



- Snap-in style
- Fits over or inside of SCH 40 pipe
- Color/Finish: White

SKU	Size	Material
PF42804	2" or 3"	PVC
PF42934	2" or 3"	ABS
PF42805	3"	PVC
PF42935	3"	ABS
PF42868	3" or 4"	PVC
PF42926	3" or 4"	ABS
PF42806	4"	PVC
PF42936	4"	ABS

Cleanouts



- 3 1/2" MIP barrel threads
- Barrel length allows for 1 3/4" height adjustment
- 6" brass cover and PVC barrel
- Does not include base

SKU	Type
PF42816	Without Trim Ring
PF42817	With Trim Ring

Drain Barrels



- 3 1/2" MIP barrel threads
- Barrel length allows for 1 3/4" height adjustment
- 6" round strainer
- Plastic body
- **Optional accessories:**
  6" strainer: PF42842

SKU	Color/Finish
PF42845	Chrome
PF42846	Brass
PF42847	Stainless Steel
PF42889	Nickel


Drain Barrels



- 3 1/2" MIP barrel threads
- Barrel length allows for 1 3/4" height adjustment
- 5" round strainer with 6" trim ring
- Plastic body

SKU	Color/Finish
PF42848	Brass
PF42890	Nickel

Drain Barrels



- 3 1/2" MIP barrel threads
- Barrel length allows for 1 3/4" height adjustment
- 6" square strainer and ring
- Cast brass construction
- Color/Finish: Nickel

SKU
PF42891

Drain Bases



- 4"
- Hub fit

SKU	Material
PF42838	PVC
PF42876	ABS

Drain Bases



- 4"
- Pipe fit
- PVC construction

SKU
PF42839

Drain Bases



- Size: 3" or 4"
- Multi-size pipe fit

SKU	Material
PF42840	PVC
PF42879	ABS

Drain Bases



- Floor drain base only
- With 1/2" primer tap

SKU	Size	Material
PF42882	2"	PVC
PF42883	2"	ABS
PF42884	3" or 4"	PVC
PF42885	3"	ABS
PF42924	4"	ABS

Floor Drains with Integral Trap



- Polypro strainer
- 3 3/4" deep sump bowl and a full 3" trap seal
- One piece drain body
- Fits 2" SCH 40 pipe
- Backwater device installed to prevent backflow through the floor drain

SKU	Material
PF800A	ABS
PF800P	PVC

Service Sink P-Traps



- Kohler® style strainer
- FIP connection
- Cast iron construction
- Color/Finish: Epoxy Coated White/Chrome
- **Optional accessories:**
  Replacement strainer: PF003S

SKU	Size
PF002	2"
PF003	3"

Floor Sinks



- 12" x 12" flange dimension
- 5 3/4" deep
- Withstands water temperature up to 160°F
- Floor mounted
- For light traffic areas
- Fits PVC couplings or fitting hubs
- Grate sold separately
- PVC construction

SKU	Drain Opening
PF42855	2"
PF42856	3"
PF42857	4"

Floor Sink Grates



- 9" x 9"
- For PVC floor sinks
- Provides easy access to sump for debris removal and cleaning
- Handles large amounts of water
- Light duty grate with large open area
- Plastic construction
- Color/Finish: White

SKU	Type
PF42858	Full Top
PF42895	1/2 Top
PF42896	3/4 Top

Floor Sinks



- 12" x 12" flange dimension
- 6 1/4" deep
- Floor mounted
- Cast iron construction
- Aluminum dome strainer included
- Acid resistant, porcelain finish
- No hub connection
- Grate sold separately
- **Optional accessories:**
  Sink basket: PF906B
  Aluminum dome strainer: PFADS

SKU	Drain Opening
PF906K	2"
PF906M	3"
PF906P	4"

Floor Sink Grates



- 9 1/2"
- For cast iron floor sinks
- Acid resistant, porcelain finish
- Cast iron construction
- Color/Finish: White

SKU	Type
PF910	Full Top
PF912	1/2 Top
PF912S	Split 1/2 Top
PF934	3/4 Top

Floor Sink Hoses



- 5/8" x 30"

SKU
PFSSHE

Hose Brackets



- For use with service sinks

SKU
PF296

Roof Drains



- Designed to drain water from a flat roof
- Provides flow area exceeding 200 sq in
- Contoured design allows for free flow and resists material build-up
- PVC drain body

SKU	Size	Dome
PF42850	3"	Cast Iron
PF42870	3"	Plastic
PF42851	4"	Cast Iron
PF42871	4"	Plastic

Underdeck Clamp Kits



PROFLO

- Provides additional strength in securing the roof drain
- Includes five 6" threaded rods, washers and nuts
- PVC construction

SKU
PF42859

General Purpose Drains



PROFLO

- Size: 2" or 3"
- Strainer: 4"
- Fits over or inside of SCH 40 pipe
- Removeable strainer
- Standard height

SKU	Material	Color/Finish
PF42820	PVC	Stainless Steel
PF42874	PVC	Nickel
PF42918	ABS	Nickel
PF42930	ABS	Stainless Steel

General Purpose Drains



PROFLO

- Size: 3" or 4"
- Strainer: 5"
- Fits over or inside of SCH 40 pipe
- Removeable strainer
- Standard height

SKU	Material	Color/Finish
PF42821	PVC	Nickel
PF42873	PVC	Stainless Steel
PF42931	ABS	Stainless Steel
PF42932	ABS	Nickel

General Purpose Drains



PROFLO

- Snap-in style
- Fits inside pipe
- Molded one-piece plastic construction
- Color/Finish: White

SKU	Size	Material
PF42869	2"	PVC
PF42937	2"	ABS
PF42834	3"	PVC
PF42938	3"	ABS
PF42835	4"	PVC
PF42939	4"	ABS

Drain Grids



MONOGRAM BRASS™

- Fits PROFLO® drains PF42800 & PF42801
- Fits Plastic Oddities, Prier Brass, Richmond Foundry, CP Industries and Rapid Fit™ drains
- 4" OD
- Center to Center Screw Holes: 3 3/8"
- 304 stainless steel

SKU	Color/Finish
MB601BN	Brushed Nickel
MB601CP	Chrome
MB601ORB	Oil Rubbed Bronze
MB601PB	Polished Brass
MB601PN	Polished Nickel

Drain Grids



MONOGRAM BRASS™

- Fits PROFLO® drains PF42867, PF42872, PF140NC, PF101PNC, PF42933, PF42942, PF42940 & PF42941
- Fits Casper style drains
- Snap-in style
- 4 1/4" OD
- Prong to Prong: 2 7/8"
- 304 stainless steel

SKU	Color/Finish
MB602BN	Brushed Nickel
MB602CP	Chrome
MB602ORB	Oil Rubbed Bronze
MB602PN	Polished Nickel

Drain Grids



MONOGRAM BRASS™

- Fits PROFLO® drains PFA600, PFP600 & PF42925
- Fits Plastic Oddities drains
- 4 1/4" OD
- Center to Center Screw Holes: 2 5/8"
- 304 stainless steel

SKU	Color/Finish
MB603BN	Brushed Nickel
MB603ORB	Oil Rubbed Bronze
MB603PN	Polished Nickel

Drain Grids



MONOGRAM BRASS™

- Fits PROFLO® drains PF42945, PF42946, PF42943 & PF42944
- 3 5/8" OD
- Center to Center Screw Holes: 2 7/8"
- 304 stainless steel

SKU	Color/Finish
MB604BN	Brushed Nickel
MB604CP	Chrome
MB604ORB	Oil Rubbed Bronze
MB604PN	Polished Nickel

Drain Grids



MONOGRAM BRASS™

- Fits PROFLO® drains PF42945, PF42946, PF42943 & PF42944
- 4 1/4" OD
- Center to Center Screw Holes: 2 7/8"
- 304 stainless steel

SKU	Color/Finish
MB605BN	Brushed Nickel
MB605CP	Chrome
MB605ORB	Oil Rubbed Bronze
MB605PN	Polished Nickel

Drain Grids



MONOGRAM BRASS™

- Fits PROFLO® PFSB series shower floors
- Snap-in style
- 4 1/2" OD
- Prong to Prong: 3"
- 304 stainless steel

SKU	Color/Finish
MB606BN	Brushed Nickel
MB606CP	Chrome
MB606ORB	Oil Rubbed Bronze

Shower Drains



MONOGRAM BRASS™

- Adjustable strainer height
- 2" to 3" PVC connection
- Square solid brass strainer
- PVC shower drain

SKU	Color/Finish
MB607BN	Brushed Nickel
MB607CP	Chrome
MB607ORB	Oil Rubbed Bronze

Shower Drains



PROFLO®

- Designed for use on tile or marble shower bases where a shower pan liner is used
- Adjustable strainer height
- Fits Pipe Size: 2"
- 4.44" square top
- Material: ABS
- Color/Finish: Brushed Nickel

SKU
PF821ANBQ

Shower Drains



PROFLO®

- Designed for use on preformed shower bases: fiberglass, acrylic or metal
- 2" no caulk connection
- 4 1/4" snap-in strainer
- Fiber and rubber gaskets provide a tight seal to the base
- **Optional accessories:**
  Replacement strainer: MB132935

SKU	Strainer Type	Material
PF42941	Plastic	ABS
PF101PNC	Plastic	Plastic
PF42940	Stainless Steel	ABS

Shower Drains



- Designed for use on preformed shower bases: fiberglass, acrylic or metal
- 2" no caulk connection
- 4 1/4" snap-in stainless steel strainer
- Fiber and rubber gaskets provide a tight seal to the base
- Brass construction
- **Optional accessories:**
  Replacement strainer: MB602BN
  Replacement gasket: PF140NCGPL, PF140NCGCI or PF140NCGCO

SKU
PF140NC

Shower Drains



- Designed for use on tile or marble shower bases where a shower pan liner is used
- Size: 2" or 3"
- Machine screws and threaded brass inserts in drain body and top housing
- Weep holes in drain assembly allow drainage
- Beveled flashing body for easy subfloor installation
- 4" stainless steel strainer
- Adjustable strainer height

SKU	Material
PF42800	ABS
PF42801	PVC

Shower Drains



- Designed for use on preformed shower bases: fiberglass, acrylic or metal
- 2" solvent weld connection
- 4 1/4" snap-in strainer
- Fiber and rubber gaskets provide a tight seal to the base
- **Optional accessories:**
  Replacement strainer: MB602BN

SKU	Strainer Type	Material
PF42867	Stainless Steel	PVC
PF42933	Stainless Steel	ABS
PF42942	Plastic	ABS

Shower Drains



- Offset design
- Fits 2" SCH 40 DWV pipe
- 4 1/4" stainless steel strainer
- PVC construction

SKU
PF42872

Shower Drains



- Sub-drain for composition pan application
- Non-adjustable drain
- Complete with 3 1/4" stainless steel screw-on strainer, ring and screws
- **Optional accessories:**
  Replacement strainer: MB604BN

SKU	Connection	Material
PF42943	Solvent Weld	ABS
PF42944	Solvent Weld	ABS Bottom/Cast Iron Top
PF42945	Threaded	Cast Iron
PF42946	No Caulk	Cast Iron

Shower Drains



- Designed for use on tile or marble shower bases where a shower pan liner is used
- Size: 2"
- Adjustable strainer height
- Cast iron construction
- Strainer is brass construction and chrome finish

SKU	Type	Connection
PF42947SQ	Square	IPS
PF42957RD	Round	IPS
PF42958RD	Round	No Hub
PF42959RD	Round	Inside Caulk

Shower Drains



- Designed for use on tile or marble shower bases where a shower pan liner is used
- Fits Pipe Size: 2"
- Machine screws and threaded brass inserts in drain body and top housing
- Weep holes in drain assembly
- Beveled flashing body for easy subfloor installation
- Heavy duty round nickel ring and strainer
- Adjustable strainer height

SKU	Material
PF821200ANR	ABS
PF821200PNR	PVC

Shower Drains



- Designed for use on tile or marble shower bases where a shower pan liner is used
- Adjustable strainer height
- Fits Pipe Size: 2"
- Material: PVC

SKU	Color/Finish
PF821PCPQ	Chrome
PF821PNBQ	Brushed Nickel
PF821PORBQ	Oil Rubbed Bronze

Shower Drains



- Designed for use on preformed shower bases: fiberglass, acrylic or metal
- Fits Pipe Size: 2"
- Stainless steel strainer
- Fiber and rubber gaskets provides a tight seal to the base
- **Optional accessories:**
  Strainer: MB603BN

SKU	Material
PFA600	ABS
PFP600	PVC

Strainers



- 6" round replacement strainer
- Includes screws
- Brass

SKU
PF42842

Strainers



- 4 1/4" snap-in strainer

SKU	Material	Color/Finish
PF42899	Stainless Steel	Stainless Steel
PF42947	Plastic	White

Strainers



- Fits inside SCH 40 DWV pipe
- Snap-in strainer only
- Stainless steel construction

SKU	Size
PF42950	2"
PF42951	3"
PF42952	4"

Strainers



- Strainer for PFSB series shower bases
- Color/Finish: White

SKU
PFSBSTR

Strainers



- Diameter: 3 1/2"
- Chrome zinc body
- Color/Finish: Stainless Steel

SKU
PFSSCPK

Trap Primer Valves



- Connection: 1/2" MIP x 1/2" FIP
- PFP1500 primes 3 or 4 floor drains
- PFP2500 primes 1 or 2 floor drains
- Pressure drop of 5 to 10 psig (35 to 70 Kpa) required to activate the priming valve
- Operating Range: 35 to 75 psig (245 to 525 Kpa)
- Piston operated
- Brass construction
- Made in the USA

SKU	Max # of Drains
PFP2500	2
PFP1500	4

Trap Primer Valves



- Connection: 1/2" MIP x 1/2" FIP
- Primes 1 or 2 floor drains
- Pressure drop of 10 psig (70 Kpa) required to activate the priming valve
- Operating Range: 20 to 80 psig (138 to 552 Kpa)
- Piston operated
- Brass construction
- Made in the USA

SKU
PFPR500

Trap Primer Valves



- Flow activated
- Includes automatic vacuum breaker
- Designed to maintain a water seal in trap
- Bronze construction


SKU	Connection
PFTRAPID	1/2" FIP x 1/2" FIP
PFTRAPSD	1/2" Sweat x 1/2" Sweat

Shower Pan Liners



- Constructed of PVC sheet
- Primarily used for lining ceramic, marble or terrazzo tile shower floors
- Sold by linear foot
- UPC/IAPMO listed
- Meets ANSI Standard D4551

SKU	Size	Thickness	Color/Finish
PF30S40	40' x 5'	30 mil	Blue
PF40S40	40' x 5'	40 mil	Black
PF30P50	50' x 4'	30 mil	Blue
PF40P50	50' x 4'	40 mil	Black
PF30U50	50' x 6'	30 mil	Blue
PF40U50	50' x 6'	40 mil	Black
PF40P100	100' x 4'	40 mil	Black
PF30S100	100' x 5'	30 mil	Blue
PF40S100	100' x 5'	40 mil	Black



YOUR SUPPLIES ARE JUST A FEW MOUSE CLICKS AWAY.

VISIT FERGUSON.COM TO VIEW OUR FULL SELECTION OF PRODUCTS AND SERVICES.

Hose Bibb Ball Valves



- 1/4 turn operation
- Brass construction

SKU	Connection
PFBVHBD	1/2" MIP x 3/4" GHT
PFBVHBF	3/4" MIP x 3/4" GHT

Hose Bibb Ball Valves



- MIP connections
- 1/4 turn operation
- Brass construction

SKU	Size
PFXBVHBD	1/2"
PFXBVHBF	3/4"

Hose Bibbs



- Operating Pressure: 125 psi
- No kink hose bibb
- Includes backflow preventer
- Bronze construction

SKU	Size	Connection
PF103DBFPC	1/2"	MIP
PF104DBFPC	1/2"	Sweat
PF105DBFPC	1/2"	FIP
PF106DBFPC	1/2"	Comp
PF109FBFPC	3/4"	MIP
PF110FBFPC	3/4"	FIP

Hose Bibbs



- Operating Pressure: 25 – 125 psi
- No kink hose bibb
- Bronze construction

SKU	Size	Connection
PF103DC	1/2"	MIP
PF104DC	1/2"	Sweat
PF105DC	1/2"	FIP
PF106DC	1/2"	Comp
PF109FC	3/4" or 1/2"	MIP or Sweat
PF110FC	3/4"	FIP

Hose Bibbs



- Operating Pressure: 125 psi
- No kink hose bibb
- Includes loose key
- Bronze construction

SKU	Size	Connection
PF103DLKC	1/2"	MIP
PF105DLKC	1/2"	FIP
PF109FLKC	3/4"	MIP
PF110FLKC	3/4"	FIP

Hose Bibbs



- MIP connection
- Operating Pressure: 125 psi

SKU	Size	Material
PF108DC	1/2"	Bronze
PF71DC	1/2"	Brass
PF116FC	3/4"	Bronze
PF71FC	3/4"	Brass

Hose Bibbs



- MIP connection
- Operating Pressure: 200 psi WOG
- Lever handle
- 1/4 turn operation
- Brass construction

SKU	Size
PF71QTD	1/2"
PF71QTF	3/4"

Hose Bibbs



- End Connection: 3/4" FIP
- Operating Pressure: 125 psi
- Inverted outlet
- Round wheel handle
- Bronze construction

SKU
PF115FC

Hose Bibbs



PROFLO

- Garden valve
- FIP connection
- Operating Pressure: 125 psi
- Bent nose design
- Handwheel operation
- Bronze construction

SKU	Size
PF117DC	1/2"
PF113FC	3/4"
PF118GC	1"

Hose Bibbs



PROFLO

- Garden valve
- End Connection: 3/4" FIP
- Operating Pressure: 125 psi
- Bent nose design
- Loose key operation
- Bronze construction

SKU
PF113FLKC

Sillcocks



PROFLO

- FIP connection
- Operating Pressure: 125 psi
- Handwheel operation
- Bronze construction

SKU	Size
PF119DC	1/2"
PF111FC	3/4"

Sillcocks



PROFLO

- End Connection: 1/2" FIP
- Operating Pressure: 125 psi
- Handwheel operation
- Includes vacuum breaker
- Bronze construction

SKU
PF120DC

Sillcocks



PROFLO

- Economy
- Operating Pressure: 125 psi
- Brass construction

SKU	Size	Connection
PF7009DC	1/2"	FIP
PF7010DC	1/2"	Sweat
PF7009FC	3/4"	FIP

Sillcocks



PROFLO

- Heavy pattern with stuffing box
- Operating Pressure: 125 psi
- Handwheel operation
- Brass construction

SKU	Size	Connection
PF74DC	1/2"	FIP
PF74SDC	1/2"	Sweat
PF74FC	3/4"	FIP
PF74SFC	3/4"	Sweat

Sillcocks



PROFLO

- FIP connection
- Operating Pressure: 125 psi
- Loose key operation
- Bronze construction

SKU	Size
PF107DLKC	1/2"
PF111FLKC	3/4"

Sillcock Keys



RAPTOR®

- Fits many sillcocks and valves
- Fits sizes 1/4", 9/32", 5/16" and 11/32"
- Heat treated steel
- Carded

SKU
RAP50105

Wall Hydrants



- Multi-turn handwheel operation
- Frost-proof design
- Anti-siphon
- Chrome brass tube
- **Optional accessories:**
  Replacement handle: PF73ASHDL
  Repair kit: PF73ASRK1

SKU	Length	Connection
PF73ASDP	4"	1/2" MPT and 1/2" Sweat
PF73ASFP	4"	3/4" MPT and 1/2" FPT
PF73ASDU	6"	1/2" MPT and 1/2" Sweat
PF73ASFU	6"	3/4" MPT and 1/2" FPT
PF73ASDX	8"	1/2" MPT and 1/2" Sweat
PF73ASFX	8"	3/4" MPT and 1/2" FPT
PF73ASD10	10"	1/2" MPT and 1/2" Sweat
PF73ASF10	10"	3/4" MPT and 1/2" FPT
PF73ASD12	12"	1/2" MPT and 1/2" Sweat
PF73ASF12	12"	3/4" MPT and 1/2" FPT
PF73ASFF12	12"	3/4" MPT and 3/4" FPT
PF73ASD14	14"	1/2" MPT and 1/2" Sweat
PF73ASDCC	CC	1/2" MPT and 1/2" Sweat

Wall Hydrants



- End Connection: 1/2" PEX
- Multi-turn handwheel operation
- Frost-proof design
- Anti-siphon
- Chrome brass tube
- **Optional accessories:**
  Replacement handle: PF73ASHDL
  Repair kit: PF73ASRK1

SKU	Length
PF73ASPXP	4"
PF73ASPXU	6"
PF73ASPXX	8"
PF73ASPX10	10"
PF73ASPX12	12"

Wall Hydrants



- Frost-proof design
- 1/2" MPT and 1/2" Sweat
- Multi-turn handwheel operation
- Chrome brass tube
- **Optional accessories:**
  Replacement handle: PF73ASHDL
  Repair kit: PF73ASRK1

SKU	Length
PF73DP	4"
PF73DU	6"
PF73DX	8"
PF73D10	10"
PF73D12	12"
PF73D14	14"

Wall Hydrant Repair Kits



- Replacement cartridge for PF74 series hydrants only
- Color/Finish: Brass

SKU
PF74CART

Wall Hydrant Repair Kits



- Replacement handle for PF73AS and PF74 series hydrants
- Metal construction
- Color/Finish: Beige

SKU
PF73ASHDL

Wall Hydrant Repair Kits



- For use with PF73AS series hydrants only
- Includes handle, anti-siphon, rubber packing and plunger assembly

SKU
PF73ASRK1

Wall Hydrant Repair Kits



- Replacement vacuum breaker kit
- For use with PF73AS and PF74 series hydrants

SKU
PF74VBKIT

Wall Hydrant Repair Kits



- Any Flow® Series Hydrants
- Replacement handle for PROFLO AF Series yard hydrants
- Cast iron construction

SKU
PFXAFHDL

Wall Hydrant Repair Kits



- EM Series Hydrants
- Replacement handle for PROFLO EM Series yard hydrants
- Cast iron construction

SKU
PFXEMHDL

Vacuum Breakers



- Connection: 3/4" FHT x 3/4" MHT
- 3/4" cast brass
- Includes set screw
- Brass construction

SKU
PFVB

Manual Drain Vacuum Breakers



- Connection: 3/4" FHT x 3/4" MHT
- 3/4" cast brass
- Includes set screw

SKU
PFVBMD

Yard Hydrant Repair Kits



- PFAF7500RK Includes: draw straps (pair), pivot connector & nuts, valve stem packing and plunger assembly
- PFEM7500RK Includes: valve stem packing, plunger and container of silicone lube
- Made in the USA

SKU	Type
PFAF7500RK	For PFXAF7500
PFEM7500RK	For PFXEM7500

Yard Hydrants



- Premium Series
- Connection: 3/4" FIP inlet x 3/4" FHT outlet
- Length: 34" plus bury depth
- Lever control with variable flow
- 1" galvanized rustproof pipe
- Solid brass hose adapter
- Stainless steel operating rod
- Can be padlocked to prevent unauthorized use
- Drains below the frost line once hydrant is shut off
- Frostproof
- Made in USA
- **Optional accessories:**
  Repair kit: PFAF7500RK
  Repair handle: PFXAFHDL

SKU	Bury Depth
PFXAF7501	1'
PFXAF7502	2'
PFXAF7503	3'
PFXAF7504	4'
PFXAF7505	5'
PFXAF7506	6'
PFXAF7507	7'

Yard Hydrants



PROFLO

- Connection: 3/4" FIP inlet x 3/4" FHT outlet
- Length: 28" plus bury depth
- Lever control with variable flow
- Solid brass hose adapter
- 1" galvanized rustproof pipe
- Can be padlocked to prevent unauthorized use
- Drains below the frost line once hydrant is shut off
- Frostproof
- Made in USA
- **Optional accessories:**
  Repair kit: PFEM7500RK
  Repair handle: PFXEMHDL

SKU	Bury Depth
PFXEM7501	1'
PFXEM75015	1 1/2'
PFXEM7502	2'
PFXEM7503	3'
PFXEM7504	4'
PFXEM7505	5'
PFXEM7506	6'
PFXEM7508	8'
PFXEM7510	10'

Stop Valves



PROFLO

- Operating Pressure: 125 psi
- Handwheel operation
- Brass construction

SKU	Size	Connection
PF50DC	1/2"	FIP
PF50SDC	1/2"	Sweat
PF80DC	1/2"	Comp
PF50SFC	3/4"	Sweat
PF80FC	3/4"	Comp

Stop Valves



PROFLO

- Economy
- Connection: Sweat
- Brass construction
- Operating Pressure: 125 psi

SKU	Size
PF7002DC	1/2"
PF7002FC	3/4"

Stop & Waste Valves



PROFLO

- Operating Pressure: 125 psi
- Handwheel operation
- Brass construction
- **Optional accessories:**
  Replacement cap: PFXRCAP

SKU	Size	Connection
PF60DC	1/2"	FIP
PF60SDC	1/2"	Sweat
PF60FC	3/4"	FIP
PF60SFC	3/4"	Sweat

Stop & Waste Valves



PROFLO

- Connection: Sweat
- Brass construction

SKU	Size
PFX60SDC	1/2"
PFX60SFC	3/4"

Stop & Waste Valves



PROFLO

- Economy
- Connection: Sweat
- Brass construction
- Operating Pressure: 125 psi
- **Optional accessories:**
  Replacement cap: PFXRCAP

SKU	Size
PF7004DC	1/2"
PF7004FC	3/4"

Ball & Waste Valves



- Valve Port Opening: Full
- 150 WSP, 600 WOG includes waste cap
- Pressure Class: 600#
- PTFE seats
- Lever handle
- Forged brass construction
- Not for use at or below ground level
- **Optional accessories:**
  Replacement cap: PFXRCAP

SKU	Size	Connection
PFR850PD	1/2"	FIP
PFR858PD	1/2"	Sweat
PFR850PF	3/4"	FIP
PFR858PF	3/4"	Sweat
PFR850PG	1"	FIP
PFR858PG	1"	Sweat

Repair Parts



- Waste cap for ball & waste valve
- Brass construction

SKU
PFXRCAP

Ball Valves



- Two-piece design
- Reduced port valve opening
- 400 WOG
- PTFE ball and stem seats
- Lever handle
- Brass body and chrome brass ball

SKU	Size	Connection
PF200D	1/2"	FIP
PF200SD	1/2"	Sweat
PF200F	3/4"	FIP
PF200SF	3/4"	Sweat
PF200G	1"	FIP
PF200SG	1"	Sweat
PF200H	1 1/4"	FIP
PF200SH	1 1/4"	Sweat
PF200J	1 1/2"	FIP
PF200SJ	1 1/2"	Sweat
PF200K	2"	FIP
PF200SK	2"	Sweat

Ball & Waste Valves



- Drain with cap
- Valve Port Opening: Full
- Maximum Pressure: 600 WOG
- Valve Body Material: Brass

SKU	Size	Connection
PFXR850PD	1/2"	FIP
PFXR858PD	1/2"	Sweat
PFXR850PF	3/4"	FIP
PFXR858PF	3/4"	Sweat
PFXR850PG	1"	FIP
PFXR858PG	1"	Sweat

CPVC Ball Valves



- Connection: Solvent Weld
- Reduced port valve opening
- For use with hot or cold water
- Low flow loss
- Copper tube size
- PTFE seats
- EPDM O-rings
- CPVC construction
- Operating Temperature: 150 psi @ 73.2°F
- Maximum Temperature: 180°F

SKU	Size
PFCBVD	1/2"
PFCBVF	3/4"
PFCBVG	1"
PFCBVH	1 1/4"
PFCBVJ	1 1/2"
PFCBVK	2"

PEX Ball Valves



- Connection: F1807 Crimp PEX
- 2 piece brass ball valve
- Full port design
- Maximum Pressure: 400 WOG

SKU	Size
PFX462D	1/2"
PFX462F	3/4"
PFX462G	1"

PEX Ball Valves



- Full port design
- End Connection: F1960 Cold Expansion PEX
- Two piece brass ball valve
- 400 WOG
- Not for use at or below ground level

SKU	Size
PFX472D	1/2"
PFX472F	3/4"
PFX472G	1"

PVC Ball Valves



- Compact one piece design
- Reduced port valve opening
- Low flow loss
- EPDM seats and O-rings
- PVC construction
- Operating Temperature: 150 psi @ 73.4°F

SKU	Size	Connection
PFPSBVD	1/2"	Solvent Weld
PFPTBVD	1/2"	FIP
PFPSBVF	3/4"	Solvent Weld
PFPTBVF	3/4"	FIP
PFPSBVG	1"	Solvent Weld
PFPTBVG	1"	FIP
PFPSBVH	1 1/4"	Solvent Weld
PFPSBVJ	1 1/2"	Solvent Weld
PFPTBVJ	1 1/2"	FIP
PFPSBVK	2"	Solvent Weld
PFPTBVK	2"	FIP
PFPSBVL	2 1/2"	Solvent Weld
PFPSBVM	3"	Solvent Weld
PFPTBVM	3"	FIP
PFPSBVP	4"	Solvent Weld

Gas Ball Valves



- Connection: FIP
- Two piece design
- Suitable for natural, manufactured, mixed liquefied petroleum, L.P. gas/air mixtures
- Brass construction

SKU	Size	Handle
PF87CD	1/2"	Tee
PF88CD	1/2"	Lever
PF87CF	3/4"	Tee
PF88CF	3/4"	Lever
PF87CG	1"	Tee
PF88CG	1"	Lever

Gas Ball Valves



- Connection: FIP
- One piece design
- Suitable for natural, manufactured, mixed liquefied petroleum, L.P. gas/air mixtures
- Lever handle
- Brass construction

SKU	Size
PF9280C	3/8"
PF9280D	1/2"
PF9280F	3/4"

Gas Ball Valves



- One piece design
- Suitable for natural, manufactured, mixed liquefied petroleum, L.P. gauges/air mixtures
- Lever handle
- Brass construction

SKU	Connection
PF9281FDC	1/2" FIP x 3/8" OD FLR
PF9281FDD	1/2" FIP x 1/2" OD FLR

Gas Ball Valves



- Coated aluminum handle
- Heavy forged brass construction
- UL Listed

SKU	Connection
PFR602MDC	1/2" MIP x 3/8" OD FLR
PFR602FLD	1/2" OD FLR x 1/2" OD FLR
PFR602MDD	1/2" MIP x 1/2" OD FLR

Log Lighter Keys



- Replacement key for PROFLO log lighter valves
- Zinc construction
- Fits 1/4" hex nut

SKU	Length	Color/Finish
PFP56ACP	3"	Chrome
PFP56APB	3"	Polished Brass
PFP57ACP	10"	Chrome
PFP57APB	10"	Polished Brass

Log Lighter Valves with Key



- Connection: 1/2" FIP
- 1/4 turn operation
- Includes valve, escutcheon and key
- For use with natural gas or propane gas systems
- Brass construction
- **Optional accessories:**
  3" Log lighter key: PFP56ACP
  10" Log lighter key: PFP57ACP

SKU	Valve Body Style
PFBVL2LCP	Angle
PFBVL2SCP	Straight

Log Lighter Valves with Key



- Connection: 1/2" FIP
- Multi-turn operation
- Kit includes valve, escutcheon and key
- For use with natural gas or propane gas systems
- Brass construction
- **Optional accessories:**
  Log lighter key: PFP56APB, PFP56ACP, PFP57APB or PFP57ACP

SKU	Valve Body Style	Color/Finish
PFSVL2CP	Angle	Chrome
PFSVL2PB	Angle	Polished Brass
PFSVS2CP	Straight	Chrome
PFSVS2PB	Straight	Polished Brass

Swing Check Valves - In-Line



- Swing type brass disc and integral seat
- Operating Pressure: 125 psi WSP, 200 psi WOG
- Cast brass construction

LOW LEAD

SKU	Size	Connection
PFX31D	1/2"	FIP
PFX31SD	1/2"	Sweat
PFX31F	3/4"	FIP
PFX31SF	3/4"	Sweat
PFX31G	1"	FIP
PFX31SG	1"	Sweat
PFX31H	1 1/4"	FIP
PFX31SH	1 1/4"	Sweat
PFX31J	1 1/2"	FIP
PFX31SJ	1 1/2"	Sweat
PFX31K	2"	FIP
PFX31SK	2"	Sweat
PFX31L	2 1/2"	FIP
PFX31M	3"	FIP
PFX31P	4"	FIP

Swing Check Valves - In-Line



- Swing type brass disc and integral seat
- Operating Pressure: 125 psi WSP, 200 psi WOG
- Cast brass construction
- Not for use at or below ground level

SKU	Size	Connection
PF31D	1/2"	FIP
PF31SD	1/2"	Sweat
PF31F	3/4"	FIP
PF31SF	3/4"	Sweat
PF31G	1"	FIP
PF31SG	1"	Sweat
PF31H	1 1/4"	FIP
PF31SH	1 1/4"	Sweat
PF31J	1 1/2"	FIP
PF31SJ	1 1/2"	Sweat
PF31K	2"	FIP
PF31SK	2"	Sweat
PF31L	2 1/2"	FIP
PF31M	3"	FIP
PF31P	4"	FIP

Check Valves



- Connection: Solvent Weld
- Spring loaded
- PVC with EPDM seals and stainless steel spring
- Operating Pressure: 100 psi
- Minimum Flow: 2 psi
- PVC construction

SKU	Size
PFPCVF	3/4"
PFPCVG	1"
PFPCVH	1 1/4"
PFPCVJ	1 1/2"
PFPCVK	2"

Spring Check Valves - In-Line



- Connection: FIP
- Bronze spring check
- Low Cracking Pressure: 1/2 psi
- Operating Pressure: 400 WOG
- Soft NBR seat for bubble tight shut off
- Stainless steel springs with neoprene O-ring seal
- Spring loaded
- Brass construction

LOW LEAD

SKU	Size
PFXSCVD	1/2"
PFXSCVF	3/4"
PFXSCVG	1"
PFXSCVH	1 1/4"
PFXSCVJ	1 1/2"
PFXSCVK	2"

Spring Check Valves - In-Line



PROFLO

- Spring loaded
- Connection: FIP
- Low Cracking Pressure: 1/2 psi
- Maximum Pressure: 400 psi
- Stainless steel springs with neoprene O-ring seal
- Not for use at or below ground level
- Brass construction

SKU	Size
PFSCVD	1/2"
PFSCVF	3/4"
PFSCVG	1"
PFSCVH	1 1/4"
PFSCVJ	1 1/2"
PFSCVK	2"

Gate Valves



PROFLO

- Connection: FIP
- Operating Pressure: 200 psi WOG
- Solid wedge disc
- Non-rising stem
- Brass construction

SKU	Size	Connection
PFT300B	1/4"	FIP
PFT300C	3/8"	FIP
PFT300D	1/2"	FIP
PFT300SD	1/2"	Sweat
PFT300F	3/4"	FIP
PFT300SF	3/4"	Sweat
PFT300G	1"	FIP
PFT300SG	1"	Sweat
PFT300H	1 1/4"	FIP
PFT300SH	1 1/4"	Sweat
PFT300J	1 1/2"	FIP
PFT300SJ	1 1/2"	Sweat
PFT300K	2"	FIP
PFT300SK	2"	Sweat
PFT300L	2 1/2"	FIP
PFT300M	3"	FIP
PFT300P	4"	FIP

Gate Valves



PROFLO

- Operating Pressure: 200 psi WOG
- Solid wedge disc
- Non-rising stem
- Not for use at or below ground level
- Brass construction
- NSF/ANSI 372

LOW LEAD

SKU	Size	Connection
PFXT300D	1/2"	FIP
PFXT300SD	1/2"	Sweat
PFXT300F	3/4"	FIP
PFXT300SF	3/4"	Sweat
PFXT300G	1"	FIP
PFXT300SG	1"	Sweat
PFXT300H	1 1/4"	FIP
PFXT300SH	1 1/4"	Sweat
PFXT300J	1 1/2"	FIP
PFXT300SJ	1 1/2"	Sweat
PFXT300K	2"	FIP
PFXT300SK	2"	Sweat
PFXT300L	2 1/2"	IPS
PFXT300SL	2 1/2"	Sweat
PFXT300M	3"	IPS
PFXT300SM	3"	Sweat
PFXT300P	4"	IPS

Washing Machine Valves



PROFLO

- Tee handle operation
- Bronze construction
- Color/Finish: Nickel Plated

SKU	Connection
PF100DCC	1/2" Comp
PF102DC	1/2" FIP

Washing Machine Valves



PROFLO

- Connection: 1/2" Sweat x 3/4" MHT
- Single lever controls both hot and cold supply
- Brass construction

SKU
PFS11D

Washing Machine Valves



- Connection: 1/2" MPT x 3/4" MHT
- Single lever controls both hot and cold supply
- Brass construction

SKU
PFT11D

Backwater Valves



- Fits SCH 40 pipe
- Easy maintenance and inspection
- For gravity flow applications only
- Do not install vertically
- **Optional accessories:**
  3" Replacement flapper: PFBWVFM
  4" Replacement flapper: PFBWVFP

SKU	Size	Material
PF42849	2"	PVC
PF42914	2"	ABS
PF42852	3"	PVC
PF42915	3"	ABS
PF42853	4"	PVC
PF42916	4"	ABS
PF42854	6"	PVC
PF42917	6"	ABS

Backwater Valves with Sleeve



- Fits SCH 40 pipe
- Easy maintenance and inspection
- For gravity flow applications only
- Do not install vertically
- **Optional accessories:**
  3" Replacement flapper: PFBWVFM
  4" Replacement flapper: PFBWVFP

SKU	Size	Material
PF42849WS	2"	PVC
PF42852WS	3"	PVC
PF42915WS	3"	ABS
PF42853WS	4"	PVC
PF42916WS	4"	ABS

Backwater Valve Sleeve Kits



- Includes ring for valve and lid for SDR pipe (by others)

SKU	Size	Material
PF42852SKO	3"	PVC
PF42915SKO	3"	ABS
PF42853SKO	4"	PVC
PF42916SKO	4"	ABS

Boiler Drains



- Connection: MIP
- Operating Pressure: 125 psi
- Stuffing box not included
- Round handle
- Brass construction

SKU	Size
PF7013DC	1/2"
PF7013FC	3/4"

Boiler Drains



- Multi-purpose supply or drain valve
- For use in low pressure domestic water systems
- 125 lbs cold water pressure to 100°F

SKU	Size	Connection	Material
PF100DC	1/2"	MIP or Sweat	Bronze
PF101DC	1/2"	FIP	Bronze
PF75DC	1/2"	MIP or Sweat	Brass
PF76DC	1/2"	FIP	Brass
PF101MFC	3/4"	MIP	Bronze
PF75FC	3/4"	MIP	Brass
PF76FC	3/4"	FIP	Bronze

Boiler Drains



- 125 lbs cold water pressure to 100°F
- No kink full pattern with stuffing box
- Brass construction

SKU	Size	Connection
PFX75DC	1/2"	MIP x Sweat
PFX76DC	1/2"	FIP
PFX75FC	3/4"	MIP
PFX76FC	3/4"	FIP

Hot Water Union Elbows



- Connection: FIP x MIP
- For use on heating applications
- Forged brass tailpiece
- Includes bronze nut and elbow
- Male union

SKU	Size
PF438D	1/2"
PF438F	3/4"
PF438G	1"
PF438H	1 1/4"

Hot Water Union Elbows



- Connection: Sweat x MIP
- For use on heating applications
- Forged brass tailpiece
- Includes bronze nut and elbow
- Male union

SKU	Size
PF439D	1/2"
PF439F	3/4"

Hydronic Valves



- Connection: FIP x MIP
- For use on heating applications
- Operating Pressure: 15 psi WSP
- 60 psi non-shock, hot water angle valve
- Includes nut and tailpiece
- Steam angle valve
- Phenolic bronze construction

SKU	Size
PF431D	1/2"
PF431F	3/4"
PF431G	1"
PF431H	1 1/4"
PF431J	1 1/2"

Hydronic Valves



- Connection: 3/4" FIP x 3/4" MIP
- For use on heating applications
- Operating Pressure: 15 psi WSP
- 60 psi non-shock, hot water straight valve
- Includes nut and tailpiece
- Steam straight valve
- Phenolic bronze construction

SKU
PF435F

Hydronic Valves



- Connection: Sweat x MIP
- For use on heating applications
- Operating Pressure: 15 psi WSP
- 60 psi non-shock, hot water angle valve
- Includes nut and tailpiece
- Phenolic bronze construction

SKU	Size
PF436D	1/2"
PF436F	3/4"

Hydronic Valves



- Connection: FIP x MIP
- For use on heating applications
- Operating Pressure: 15 psi WSP
- 60 psi non-shock, hot water angle valve
- Includes nut and tailpiece
- Phenolic bronze construction

SKU	Size
PF437D	1/2"
PF437F	3/4"
PF437G	1"
PF437H	1 1/4"

Oil Tank Valves



- Connection: 1/2" x 3/8" MIP
- Metal to metal seat
- Rising stem
- Brass construction

SKU
PF061DC

Needle Valve Kits



- Connection: 3/8" OD to 1" OD range x 1/4" OD Comp
- Self-tapping brass valve
- Does not include tubing
- Kit Includes: needle valve, saddle clamp, nuts, bolts, washers and inserts

LOW LEAD

SKU
PFXNV200A

Needle Valves



- Connection: 1/4" OD Comp x 1/8" MIP
- Angle design
- Brass construction

SKU
PFXNV104A

Needle Valves



- Connection: Comp
- Straight design
- Brass construction

SKU	Size
PFXNV105A	1/4" OD
PFXNV106A	3/8" OD



Sump Pumps



- Cast iron construction
- For typical residential and commercial applications
- Maximum head of 25'
- 1/3 hp permanent split capacitor motor
- Side Discharge Size: 1 1/2" FNPT
- Tethered float switch
- Cord Length: 10"
- Glass reinforced nylon impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU
PF92331

Sump Pumps



- Thermoplastic construction
- For typical residential applications
- Handles 1/8" solids
- Maximum head of 25'
- Permanent split capacitor motor
- Top Discharge Size: 1 1/4" MNPT and 1 1/4" FNPT
- Vertical automatic float switch
- Cord Length: 10'
- Glass reinforced nylon housing and impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU	Horsepower
PF92260	1/4 hp
PF92342	1/3 hp

Sump Pumps



- Thermoplastic construction
- For typical residential and commercial applications
- Maximum head of 25'
- 1/3 hp permanent split capacitor motor
- Side Discharge Size: 1 1/2" FNPT
- Tethered float switch
- Cord Length: 10"
- Glass reinforced nylon impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU
PF92370

Sump Pumps



- Cast iron construction
- For typical residential and commercial applications
- Maximum head of 25'
- Permanent split capacitor motor
- Side Discharge Size: 1 1/2" FNPT
- Vertical automatic float switch
- Cord Length: 10'
- General water transfer, fountains and ponds, farm use, basement drainage

SKU	Impeller	Horsepower
PF92341	Stainless Steel	3/10 hp
PF92352	Nylon	1/3 hp
PF92511	Nylon	1/2 hp

Sump Pumps



- Cast iron construction
- For typical residential and commercial applications
- Includes installed plastic pump base, check valve and discharge pipe
- Maximum head of 25'
- 1/3 hp permanent split capacitor motor
- Side Discharge Size: 1 1/2" FNPT
- Vertical automatic float switch
- Cord Length: 10"
- Glass reinforced nylon impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU	Discharge Pipe
PFTG92352	ABS
PFTG92352P	PVC

Sump Pumps - Pedestal



- Thermoplastic construction
- For typical residential applications
- Handles 3/16" solids
- Maximum Flow Rate: 50 gpm
- Maximum head of 20'
- 1/3 hp permanent split capacitor, air-cooled motor
- Side Discharge Size: 1 1/4" FNPT
- Fully adjustable, auto switch with polypropylene float
- Glass reinforced nylon housing, stainless steel impeller
- General water transfer and basement drainage

SKU
PF92333

Effluent Pumps



- Cast iron construction
- For typical residential and commercial applications
- Handles 5/8" solids
- Maximum Flow Rate: 60 gpm
- Maximum head of 25'
- 1/3 hp permanent split capacitor motor
- Side Discharge Size: 1 1/2" FNPT
- Tethered mechanical float switch
- Cord Length: 10'
- Cast aluminum, non-clogging vortex impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU
PF92305

Drain/Utility Pumps



- Thermoplastic construction
- For typical residential and commercial applications
- Handles 1/8" solids
- Maximum Flow Rate: 26 gpm
- Maximum head of 25'
- Top Discharge Size: 1 1/4" MNPT and 3/4" GHT
- Glass reinforced nylon housing and impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU	Horsepower	Cord Length
PF91025	1/5 hp	10'
PF91335	1/3 hp	25'

Sewage Pumps



- Cast iron construction
- Submersible sewage pump for typical residential and commercial applications
- Handles 2" solids
- Maximum Flow Rate: 80 gpm
- Maximum head of 25'
- 1/2 hp permanent split capacitor motor
- Side Discharge Size: 2" FNPT
- Cord Length: 10'
- Cast aluminum, non-clogging vortex impeller
- For movement from a basin to sewer or septic lines or to drainage fields

SKU	Switch
PF93501	Tethered
PF93511	Vertical

Packaged Drain/Utility Systems



- Pre-assembled system includes cast iron sump pump, 15" x 13 1/2" structural foam basin with cover, 1 1/2" x 8" PVC pipe and 1 1/2" check valve (PFCVJH)
- For typical residential and commercial applications
- Maximum Flow Rate: 46 gpm
- Maximum head of 25'
- 1/3 hp permanent split capacitor motor
- Side Discharge Size: 1 1/2" FNPT
- Vertical automatic float switch
- Cord Length: 10'
- Stainless steel impeller
- General water transfer, fountains and ponds, farm use, basement drainage

SKU
PF92017

Sewage Pumps



- Cast Iron volute
- Stainless Steel motor housing
- Submersible sewage pump for typical residential and commercial applications
- Handles 2" solids
- Maximum Flow Rate: 140 gpm
- Maximum head of 30'
- 1/2 hp stainless steel motor
- Discharge Size: 2" FNPT
- Cord Length: 15'
- Solid stainless steel, non-clogging vortex impeller
- For moving materials upward from a basin to sewer or septic lines or to drainage fields

SKU	Switch
PF93781	Tethered
PF93782	Vertical

Packaged Sewage Systems



- Simplex pre-assembled system includes cast iron sewage pump, 18" x 30" structural foam basin with cover and 2" x 30" PVC pipe
- For typical residential and commercial applications
- Handles 2" solids
- Maximum Flow Rate: 80 gpm
- Maximum head of 25'
- 1/2 hp permanent split capacitor motor
- Side Discharge Size: 2" FNPT
- Cord Length: 10'
- Cast aluminum, non-clogging vortex impeller
- For movement from a basin to sewer or septic lines or to drainage fields

SKU	Type
PF93015	With PF93501 Pump
PF93020	With PF93511 Pump

Packaged Sump Systems



- Pre-assembled system includes primary cast iron sump pump
- 2 Amp AC battery charger with 10' cord
- 12V DC back up pump with vertical float switch
- Includes alarm/control panel with fuse
- Includes thermoplastic battery box
- Battery sold separately

SKU	Horsepower
PF92941	3/10 hp
PF92952	1/3 hp

Battery Back Up Pump Kits



- 12V DC back up pump with vertical float switch
- Includes alarm/control panel with fuse
- Includes thermoplastic battery box
- 2 Amp AC battery charger with 10' cord
- Battery sold separately

SKU
PF92910

Float Switches



- Replacement float switch
- Piggy back style plug
- 115V
- Cord Length: 10'

SKU	Style
PF92000SJE	Tethered
PF92010	Vertical

Check Valves



- Sump pump check valve
- Full port valve design
- Maximum Temperature: 140°F (60°C)
- Zero obstruction valve
- Can be threaded directly into pump discharge
- PVC construction

SKU	Connection
PF99547	1 1/4" MIP x 1 1/4" BARB
PF99549	1 1/2" MIP x 1 1/4" BARB
PF99509	1 1/2" MPT x 1 1/2" SLIP or 1 1/4" BARB

Check Valves



- Checks backflow of water and sewer gauges
- Length: 8.15"
- Flexible rubber slip x slip unions
- Unions slip over PVC, ABS, copper or steel pipe
- PVC body and stainless steel clamps
- Vertical or horizontal installation

SKU	Connection
PFCVJH	1 1/4" or 1 1/2" x 1 1/4" or 1 1/2"
PFCVK	2" x 2"

Foot Valves



- Connection: FIP
- Maximum Pressure: 200 psi
- Soft seat for bubble tight shutoff, spring loaded for fast seating action
- Flow profile designed to minimize head loss
- Perfect sealing both at high and low pressure
- High technology materials to ensure best resistance in any condition
- Valve Body Material: Brass

SKU	Size
PFXBFVF	3/4"
PFXBFVG	1"
PFXBFVH	1 1/4"
PFXBFVJ	1 1/2"
PFXBFVK	2"
PFXBFVM	3"

Foot Valves



- Connection: FIP
- Temperature Range: 10°F to 210°F
- Stainless steel strainer and spring
- Size: 3"
- Bronze construction

SKU
PFBFVM

Pump Tanks



- Steel construction
- Pre-pressurized water system tanks
- Butyl/EPDM diaphragm
- Polypropylene liner
- Malleable iron elbow connection
- Made in the USA

SKU	Size	Capacity
PFX20	15 3/8" x 31 5/8"	20 gal
PFX26	15 3/8" x 38 1/4"	26 gal
PFX32	15 3/8" x 46 1/2"	32 gal
PFX34	22" x 29 5/8"	34 gal
PFX44	22" x 36"	44 gal
PFX62	22" x 46 3/4"	62 gal
PFX81	22" x 56"	81 gal
PFX86	26" x 47 1/4"	86 gal
PFX119	26" x 61 7/8"	119 gal

Pumps

SKU	Type	Material	HP	Switch	Max Flow	Cord	Warranty
PF91025	Utility	Thermoplastic	1/5	-	26 gpm	10'	3 year
PF91335	Utility	Thermoplastic	1/3	-	40 gpm	25'	3 year
PF92260	Sump	Thermoplastic	1/4	Vertical	30 gpm	10'	3 year
PF92342	Sump	Thermoplastic	1/3	Vertical	40 gpm	10'	3 year
PF92370	Sump	Thermoplastic	1/3	Tethered	48 gpm	10'	3 year
PF92331	Sump	Cast Iron	3/10	Tethered	46 gpm	10'	5 year
PF92341	Sump	Cast Iron	3/10	Vertical	46 gpm	10'	5 year
PF92352	Sump	Cast Iron	1/3	Vertical	60 gpm	10'	5 year
PFTG92352	Sump	Cast Iron	1/3	Vertical	60 gpm	10'	5 year
PFTG92352P	Sump	Cast Iron	1/3	Vertical	60 gpm	10'	5 year
PF92511	Sump	Cast Iron	1/2	Vertical	70 gpm	10'	5 year
PF92333	Pedestal	Thermoplastic	1/3	Vertical	50 gpm	10'	3 year
PF92305	Effluent	Cast Iron	1/3	Tethered	60 gpm	10'	3 year
PF93501	Sewage	Cast Iron	1/2	Tethered	80 gpm	10'	3 year
PF93511	Sewage	Cast Iron	1/2	Vertical	80 gpm	10'	3 year
PF93015	Sewage Kit	Cast Iron	1/2	Tethered	80 gpm	10'	3 year
PF93020	Sewage Kit	Cast Iron	1/2	Vertical	80 gpm	10'	3 year
PF92017	Remote Drain	Cast Iron	3/10	Vertical	46 gpm	10'	5 year
PF92941	Battery Backup	Cast Iron	1/3	Vertical	46 gpm	10'	3 year
PF92952	Battery Backup	Cast Iron	1/3	Vertical	60 gpm	10'	3 year
PF92910	Battery Backup	Thermoplastic	12V	Vertical	22 gpm	10'	3 year


Cleanout Plugs



- Countersunk slotted design
- MIP connection
- For residential and light commercial use
- Not for pressure applications
- Tapped 5/16" all the way through
- Brass construction

SKU	Size
PFEP53LAK	2"
PFEP53LAL	2 1/2"
PFEP53LAM	3"
PFEP53LAN	3 1/2"
PFEP53LAP	4"

Cleanout Plugs



- Countersunk design
- MIP connection
- For residential and light commercial use
- Not for pressure applications
- Southern code
- Brass construction

SKU	Size
PFBP5CSKJ	1 1/2"
PFBP5CSKK	2"
PFBP5CSKL	2 1/2"
PFBP5CSKM	3"
PFBP5CSKN	3 1/2"
PFBP5CSKP	4"
PFBP5CSKS	5"
PFBP5CSKU	6"
PFBP5CSKX	8"

Cleanout Plugs



- Raised square head design
- MIP connection
- For residential and light commercial use
- Not for pressure applications
- Southern code
- Brass construction

SKU	Size
PFBP5RHH	1 1/4"
PFBP5RHJ	1 1/2"
PFBP5RHK	2"
PFBP5RHL	2 1/2"
PFBP5RHM	3"
PFBP5RHN	3 1/2"
PFBP5RHP	4"
PFBP5RHS	5"
PFBP5RHU	6"
PFBP5RHX	8"
PFBP5RH10	10"

Cleanout Plugs



- Countersunk design
- MIP connection
- For residential and light commercial use
- Not for pressure applications
- Tapped 1/4" all the way through
- Brass construction

SKU	Size
PFEP53J	1 1/2"
PFEP53K	2"
PFEP53L	2 1/2"
PFEP53M	3"
PFEP53N	3 1/2"
PFEP53P	4"
PFEP53S	5"
PFEP53U	6"

Hose Clamps



- Micro Series
- 1/4" high nickel grade stainless steel screw
- Band and housing are 5/16" high nickel grade stainless steel
- Constructed for small hose applications
- Easy to install in confined areas
- Made in the USA

SKU	Range
PFSSHC62602	1/4" – 5/8"
PFSSHC62606	5/16" – 7/8"

Hose Clamps



- Standard duty 5/16" hex-head 410 stainless steel screws
- Band and housing are 1/2" design 201-301 stainless steel
- Made in USA

SKU	Range
PFSSHC6706	3/8" – 7/8"
PFSSHC6708	7/16" – 1"
PFSSHC6710	1/2" – 1 1/16"
PFSSHC6712	1/2" – 1 1/4"
PFSSHC6716	3/4" – 1 1/2"
PFSSHC6720	3/4" – 1 3/4"
PFSSHC6736	7/8" – 2 3/8"
PFSSHC6724	1" – 2"
PFSSHC6740	1 1/8" – 3"
PFSSHC6728	1 5/16" – 2 1/4"
PFSSHC6744	1 5/16" – 3 1/4"
PFSSHC6732	1 9/16" – 2 1/2"
PFSSHC6748	1 5/8" – 3 1/2"
PFSSHC6752	1 7/8" – 3 3/4"
PFSSHC6756	2 1/8" – 4"
PFSSHC6764	2 5/8" – 4 1/2"
PFSSHC6772	3 1/8" – 5"
PFSSHC6780	3 5/8" – 5 1/2"
PFSSHC6799	4" – 7"
PFSSHC6788	4 1/4" – 6"
PFSSHC6796	4 3/4" – 6 1/2"

Hose Clamps



- Adjustable stainless steel hose clamp
- Band and housing are 9/16" design 201-301 stainless steel
- 5/16" hex-head 410 stainless steel screw
- Made in USA

SKU	Range
PFSSHC6806	3/8" – 7/8"
PFSSHC6808	7/16" – 1"
PFSSHC6810	1/2" – 1 1/16"
PFSSHC6812	1/2" – 1 1/4"
PFSSHC6816	3/4" – 1 1/2"
PFSSHC6820	3/4" – 1 3/4"
PFSSHC6836	7/8" – 2 3/8"
PFSSHC6824	1" – 2"
PFSSHC6840	1 1/8" – 3"
PFSSHC6828	1 5/16" – 2 1/4"
PFSSHC6844	1 5/16" – 3 1/4"
PFSSHC6832	1 9/16" – 2 1/2"
PFSSHC6848	1 5/8" – 3 1/2"
PFSSHC6852	1 7/8" – 3 3/4"
PFSSHC6856	2 1/8" – 4"
PFSSHC63152	2 1/2" – 10"
PFSSHC63248	2 1/2" – 16"
PFSSHC6864	2 5/8" – 4 1/2"
PFSSHC6872	3 1/8" – 5"
PFSSHC6880	3 5/8" – 5 1/2"
PFSSHC68104	4" – 7"
PFSSHC6888	4 1/4" – 6"
PFSSHC6896	4 3/4" – 6 1/2"

Iron Body Cleanouts



- Push-on style
- SV connection
- Includes countersunk brass plug
- Cast iron construction

SKU	Size
PFPA4SVCSK	4"
PFPA6SVCSK	6"

Iron Body Cleanouts



- SV connection
- Includes raised head brass plug
- Cast iron construction

SKU	Size
PFT382RH	2"
PFT383RH	3"
PFT384RH	4"
PFT386RH	6"

Iron Body Cleanouts



- 4" SV connection
- Includes countersunk brass plug
- Cast iron construction

SKU
PFT384CS

Iron Body Cleanouts



- No hub connection
- Includes raised head brass plug
- Cast iron construction

SKU	Size
PFT523RH	3"
PFT524RH	4"

No Hub Couplings



- Standard
- 300 series stainless steel shield with neoprene gasket
- 5/16" hex-head screw designed for 60 lbs of installation torque
- Used to connect no hub cast iron pipe
- Includes 2 or 4 clamps per coupling
- **Optional accessories:**
  No hub torque wrench: RAP18550

SKU	Size
PFNHCJ	1 1/2"
PFNHCK	2"
PFNHRCKJ	2" x 1 1/2"
PFNHCM	3"
PFNHRCMK	3" x 2"
PFNHCP	4"
PFNHRCPM	4" x 3"
PFNHCS	5"
PFNHCU	6"
PFNHCX	8"
PFNHC10	10"

No Hub Couplings



- Heavy Duty
- 304 stainless steel shield with neoprene gasket
- 3/8" hex-head screw designed for 80 lbs of installation torque
- 9/16" wide clamps
- Used to connect no hub cast iron pipe
- Distinctive green shield
- Made in USA
- **Optional accessories:**
  No hub torque wrench: RAP18552

SKU	Size
PFNHHHDCJ	1 1/2"
PFNHHHDCK	2"
PFNHHHDCM	3"
PFNHHHDCP	4"
PFNHHHDCS	5"
PFNHHHDCU	6"
PFNHHHDCX	8"
PFNHHHDC10	10"

No Hub Couplings



- Heavy Duty
- 304 stainless steel shield with neoprene gasket
- 5/16" hex-head screw designed for 80 lbs of installation torque
- 9/16" wide bands
- Used to connect no hub cast iron pipe
- Distinctive yellow shield
- Made in USA
- **Optional accessories:**
  No hub torque wrench: RAP18551

SKU	Size
PFNHHMDCJ	1 1/2"
PFNHHMDCK	2"
PFNHHMDCM	3"
PFNHHMDCP	4"
PFNHHMDCS	5"
PFNHHMDCU	6"
PFNHHMDCX	8"
PFNHHMDC10	10"

No Hub Couplings



- Heavy Duty
- 304 stainless steel shield with neoprene gasket
- 3/8" hex-head screw designed for 120 lbs of installation torque
- Used to connect no hub cast iron pipe
- Includes 6 clamps per coupling
- Made in USA

SKU	Size
PFNHWBC12	12"
PFNHWBC15	15"

Compression Gaskets



- Compression type gasket joint
- Use with extra heavy hub and spigot cast iron pipe and fittings
- Made in USA

SKU	Size
PFXHGK	2"
PFXHGM	3"
PFXHGP	4"
PFXHGS	5"
PFXHGU	6"
PFXHGX	8"
PFXHG10	10"
PFXHG12	12"

Service Weight (SV) Gaskets



- One-piece compression gasket
- For use with hub and spigot cast iron pipe and fittings
- Multi-tite design
- Neoprene construction
- Made in USA
- Conforms to ASTM C564

SKU	Size
PFSVQTGK	2"
PFSVQTGM	3"
PFSVQTGP	4"
PFSVQTGS	5"
PFSVQTGU	6"
PFSVQTGX	8"
PFSVQTG10	10"
PFSVQTG12	12"
PFSVQTG15	15"

Thermal Expansion Tanks



- Connection: 3/4" SS MIP
- Diaphragm-type
- Designed for potable hot water systems
- Eliminates relief valve spills and hot water waste
- Controls pressure build up
- Extends water heater life
- Factory precharged expansion tank
- Steel construction

SKU	Capacity
PFXT5	2 gal
PFXT5I	2.10 gal
PFXT12	4.4 gal
PFXT12I	4.8 gal

Anode Rods



- Provides additional protection for water heaters against rust and corrosion for a longer tank life
- Use KA-90 rods for smelly water applications

SKU	Size	Material
PSW12103	16"	Zinc KA-90
PSW12104	29"	Magnesium
PSW12102	32"	Magnesium
PSW12101	45"	Zinc KA-90

Dip Tubes



- Universal dip tube

SKU	Size
PSW12503	45"
PSW12501	52"


Electric Water Heater Thermostats



- 240 VAC
- Fits most major OEM water heaters
- UL listed

SKU	Style
PSW12701	Upper With High Limit
PSW12702	Lower Thermostat
PSW12704	Lower Package
PSW12705	Single Element With ECO
PSW12708	Upper With ECO

Electric Water Heater Tune-Up Kits



- 240 VAC/4500W
- Includes both upper and lower thermostats, 2 elements with gaskets
- Available in APCOM style
- APCOM thermostats included

SKU
PSW12901

Gas Water Heater Thermocouples



- For residential and light commercial applications
- 30 mV
- Comes with adapters for most standard configurations
- Primarily used in water heaters, forced air heating systems, floor and wall furnaces

SKU	Size
PMTC18	18"
PMTC24	24"
PSTC30	30"
PSTC36	36"

T&P Discharge Pipes



PROSELECT

- 3/4"
- Cross-linked polypropylene construction

SKU
PSW12507

T&P Relief Valves



PROSELECT

- Fits most residential and light commercial heaters
- Setting: 150 psi @ 210°F
- 3/4" threads
- 150#
- With stainless steel spring
- Brass construction

SKU
PSW12601

Water Heater Drain Valves



PROSELECT

- 3/4" threads
- Fits most residential heaters

SKU	Length
PSW12504	5/8"
PSW12509	2"

Water Heater Element Adapter Kits



PROSELECT

- Universal element adapter kit
- Used to adapt a screw in element to a square flange
- 4 bolt pattern with 2 1/2" bolt circle, 1 3/4" bolt centers
- Includes gasket, screws & thermostat brackets

SKU
PSW12317

Water Heater Elements



PROSELECT

- For residential and light commercial use
- Watts: 4.5 kW
- Volts: 240 VAC
- End Connection: 1" NPSM
- Nickel-alloy sheathing for long life
- Fold-back design for efficiency
- **Optional accessories:**
  Adapter kit: PSW12317

SKU	Watt Density
PSW12301	High
PSW12303	Low

Water Heater Elements – Flanged



PROSELECT

- High Watt Density
- For residential and light commercial use
- Connection Type: Universal flange
- Includes gasket
- Zinc-plated for corrosion protection

SKU	Volts	Watts
PSW12313	120 VAC	1500
PSW12314	240 VAC	3800
PSW12302	240 VAC	4500

Water Heater Elements – Flanged



PROSELECT

- Low Watt Density
- For residential and light commercial use
- 240 VAC/4500W
- Connection Type: Universal flange
- Fold-back design for efficiency
- Includes gasket
- Nickel-alloy sheathing for long life

SKU
PSW12304

Water Heater Elements – Screw In



PROSELECT

- Low Watt Density
- For residential and light commercial use
- 240 VAC
- Nickel-alloy sheathing for long life
- Fold-back design for efficiency
- Optional adapter kit used for installing screw in flanged elements to four bolt flanged element openings
- **Optional accessories:**
  Adapter kit: PSW12317

SKU	Connection	Watts
PMEL4500LO	1" NPSM	4500
PSW12312	1" NPSM	5500
PSW12325	1 3/8" NPSM	4500

Water Heater Elements – Screw In



PROSELECT

- Low Watt Density
- For residential and light commercial use
- Connection: 1" NPSM
- Watts: 1650W
- 120 VAC
- Nickel-alloy sheathing for long life
- Fold-back design for efficiency
- Optional adapter kit used for installing screw in flanged elements to four bolt flanged element openings
- **Optional accessories:**
  Adapter kit: PSW12317

SKU
PSW12320

Water Heater Elements – Screw In



PROSELECT

- High Watt Density
- For residential and light commercial use
- Connection: 1" NPSM
- Zinc-plated for corrosion protection
- Includes gasket
- 1" optional adapter kit used for installing screw in flanged elements to four bolt flanged element openings
- **Optional accessories:**
  Adapter kit: PSW12317

SKU	Volts	Watts
PSW12305	120 VAC	1440
PSW12306	120 VAC	2000
PSW12307	240 VAC	1500
PSW12308	240 VAC	2000
PSW12309	240 VAC	2500
PSW12310	240 VAC	3000
PSW12311	240 VAC	3800
PMEL4500HI	240 VAC	4500
PSW12321	240 VAC	5500

Water Heater Elements – Screw In



PROSELECT

- Ultra Low Watt Density
- 240 VAC
- Best when water has high mineral content
- 15" minimum tank diameter
- Includes gasket
- Genuine armalloy ripple fold-back design
- **Optional accessories:**
  Adapter kit: PSW12317

SKU	Connection	Watts
PSW12323	1" NPSM	4500
PSW12322	1" NPSM	5500
PSW12324	1 3/8" NPSM	5500

Water Heater Nipples



PROSELECT

- PEX lined
- Package Quantity: 2

SKU	Size
PSW12505	3/4" x 2"
PSW12508	3/4" x 3"

Water Heater Nipples



PROSELECT

- 3/4" x 3"
- Heat trap
- Package Quantity: 2

SKU
PSW12506

Compression Couplings



PROFLO

- Brass body and nuts with rubber gaskets
- For cold water use only
- For repairing galvanized or copper pipe
- Pipe ends must be restrained
- Operating Pressure: 125 psi
- Maximum Temperature: 120°F
- Not for use at or below ground level

SKU	Connection
PFXBCCCM	3/8" IPS x 3" Comp
PFXBCCCS	3/8" IPS x 5" Comp
PFXBCCDM	1/2" IPS x 3" Comp
PFXBCCDS	1/2" IPS x 5" Comp
PFXBCCFM	3/4" IPS x 3" Comp
PFXBCCFS	3/4" IPS x 5" Comp
PFXBCCGM	1" IPS x 3" Comp
PFXBCCGS	1" IPS x 5" Comp
PFXBCCHM	1 1/4" IPS x 3" Comp
PFXBCCHS	1 1/4" IPS x 5" Comp
PFXBCCJM	1 1/2" IPS x 3" Comp
PFXBCCJS	1 1/2" IPS x 5" Comp
PFXIBCCKS	2" IPS x 5" Comp

Compression Couplings



PROFLO

- CPVC body and nuts with rubber gaskets
- For cold water use only
- Pipe ends must be restrained
- Copper tube size
- Operating Pressure: 100 psi

SKU	Size
PFCCCD	1/2"
PFCCCF	3/4"

Compression Couplings



- PVC body and nuts with rubber gaskets
- For cold water use only
- Pipe ends must be restrained
- Iron pipe size
- Operating Pressure: 125 psi

SKU	Size
PFPCCD	1/2"
PFPCCF	3/4"
PFPCCG	1"
PFPCCH	1 1/4"
PFPCCJ	1 1/2"
PFPCCK	2"
PFPCCL	2 1/2"
PFPCCM	3"
PFPCCP	4"
PFPCCU	6"

Compression Couplings



- Connection: 2" CTS x 5" Comp
- Brass construction
- Not for use at or below ground level

SKU
PFXCBCCKS

Compression Couplings



- Galvanized malleable body and nuts with rubber gaskets
- For cold water use only
- For repairing galvanized or black steel pipe
- Pipe ends must be restrained
- Iron pipe size
- Operating Pressure: 125 psi
- Maximum Temperature: 120°F

SKU	Size
PFXGCCDL	1/2"
PFXGCCFL	3/4"
PFXGCCGL	1"
PFXGCCHL	1 1/4"
PFXGCCJL	1 1/2"
PFXGCCKL	2"
PFXGCCLL	2 1/2"
PFXGCCML	3"
PFXGCCPL	4"


Repair Clamps



- Stainless steel clamp with neoprene gasket
- Single long plated carriage bolt

SKU	Size
PFRCDM	1/2" x 3"
PFRCFM	3/4" x 3"
PFRCGM	1" x 3"
PFRCHM	1 1/4" x 3"
PFRCJM	1 1/2" x 3"
PFRCKM	2" x 3"

Repair Clamps



- Stainless steel clamp with neoprene gasket
- Two long plated carriage bolts

SKU	Size
PFRCDU	1/2" x 6"
PFRCFU	3/4" x 6"
PFRCGU	1" x 6"
PFRCHU	1 1/4" x 6"
PFRCJU	1 1/2" x 6"
PFRCKU	2" x 6"

Slip Fix Couplings



- For cold water use only
- For use when repairing broken lines or adding additional lines or fittings
- Pipe ends must be restrained
- PVC SCH 40
- IPS spigot/socket
- Self-lubricating internal EPDM O-ring for long life and smooth movement
- Operating Pressure: 150 psi

SKU	Size
PF40SFCD	1/2"
PF40SFCF	3/4"
PF40SFCG	1"
PF40SFCH	1 1/4"
PF40SFCJ	1 1/2"
PF40SFCK	2"


Did you know we carry Aquatherm piping systems?
BENEFITS OF AQUATHERM:
- Resistant to most chemicals
- Increased flow rate
- Fast, welded connections
- Light, impact-resistant material
- Corrosion-free pipe and fittings
- Natural sound and heat insulation
- Long lasting
- Fully recyclable
- High-heat stabilized
Visit FERGUSON.COM to learn more!
aquatherm



What can we help you find?

- Low Lead Products 168-169
- Ball Valves, Brass 169
- Ball Valves, Steel. 169-171
- Thermoplastic Valves 171
- Knife Gate Valves 171
- Y-Strainers. 171-172
- Gate, Globe & Check Valves, Brass & Bronze 172
- Gate, Globe & Check Valves, Cast Steel 172
- Gate, Globe & Check Valves, Cast Iron 172-173
- Butterfly Valves 173
- Piping Products 173-174
- Fire & Fabrication Products 174
- Actuation & Accessories 174
- Flexible Connectors 174
- Gauges, Thermometers & Accessories 174
- Hangers, Clamps & Strut Accessories. 174-175
- Service Faucets 176-177
- Commercial Grab Bars. 177

FNW™ / YOUR PIPING PRODUCTS SOURCE

Since its inception in 1979, FNW™ has been dedicated to providing a vast product offering of quality products for Industrial and Commercial applications suited to meet the needs of the end user.

For updates and additional product offerings not seen in this catalog, go to FNW.com



Phone: (757) 969-4974 | **Email:** PVF.Quotations@ferguson.com



Figure X410C / X411C
LOW LEAD 2 PC FULL PORT 600 WOG BRASS BALL VALVE
- NPT (X410C), SWEAT (X411C)
- 600 WOG
- CSA RATED (X410C ONLY)
- NSF 61 ANNEX G CERTIFIED
- ADJUSTABLE PACKING
- X410C SIZES 1/4" - 4"
- X411C SIZES 3/8" - 3"



Figure X415 / X416
LOW LEAD 2 PC FULL PORT 600 WOG BRASS BALL VALVE
- NPT (X415), SWEAT (X416)
- RATED 150 WSP
- CSA RATED (X415 ONLY)
- FM RATED TO 400 PSI (X415 ONLY)
- NSF 61 ANNEX G CERTIFIED
- DUAL O-RING PACKING
- SIZES 1/4" - 4"



Figure X420A / X421
LOW LEAD 2 PC FULL PORT 600 WOG BRASS BALL VALVE
- NPT (X420A), SWEAT (X421)
- RATED 150 WSP
- NSF 372 CERTIFIED
- OPTIONAL LOCKING DEVICE, T-HANDLE, STEM EXTENSION, & MORE
- SIZES 1/2" - 2" NPT



Figure X430
LOW LEAD 200 PSI PRESS CONNECTION BRASS BALL VALVE FOR WATER SERVICE
- FULL PORT DESIGN
- NSF 61 ANNEX G CERTIFIED
- FORGED BODY & END CAP
- BLOW-OUT PROOF STEM
- ADJUSTABLE PACKING
- SIZES 1/2" - 2"



Figure X431
LOW LEAD 200 PSI PRESS CONNECTION BRASS IN-LINE CHECK VALVE FOR WATER
- HIGH CAPACITY DESIGN
- LOW 1/2 PSI CRACKING PRESSURE
- SOFT SEAT FOR TIGHT SHUTOFF
- NSF 61 ANNEX G CERTIFIED
- FORGED BODY & END CAP
- SIZES 1/2" - 2"



Figure X432
LOW LEAD 200 PSI PRESS CONNECTION BRASS BALL VALVE FOR WATER SERVICE
- ECONOMICAL DESIGN
- FULL PORT
- NSF 61 ANNEX G CERTIFIED
- BLOW-OUT PROOF STEM
- DUAL O-RING PACKING
- SIZES 1/2"-2"



Figure X432AXLC
LOW LEAD 200 PSI PRESS CONNECTION BRASS BALL VALVE FOR WATER SERVICE
- ECONOMICAL DESIGN
- FULL PORT (4" IS STANDARD PORT)
- NSF 61 ANNEX G CERTIFIED
- BLOW-OUT PROOF STEM
- DUAL O-RING PACKING
- SIZES 2 1/2", 3", 4"



Figure X440
LOW LEAD2 PC FULL PORT 600 WOG ISO MOUNT BRASS BALL VALVE
- ISO 5211 MOUNTING PAD
- RATED 150 WSP
- O-RING BACKED SEATS
- NSF 61 ANNEX G CERTIFIED
- DOUBLE O-RING VITON® PACKING
- SIZES 1/2" - 2"



Figure X480A
LOW LEAD 2 PC STANDARD PORT 400 WOG VALVE w/ COMPRESSION ENDS
- DRAIN & CAP
- NSF 372 CERTIFIED
- ADJUSTABLE PACKING
- SIZES 1/2", 3/4" & 1"



Figure X485A
LOW LEAD FULL PORT 200 PSI PUSH FIT VALVE FOR WATER OR AIR
- FOR COPPER, CPVC, & PEX PIPE
- INCLUDES REMOVAL TOOL
- NSF 372 CERTIFIED
- SIZES 1/2", 3/4" & 1"



Figure X509 / X510
LOW LEAD BRONZE Y-STRAINER
- FNPT (X509), SWEAT (X510)
- 400 WOG
- 150 PSI SWP
- NSF 61 ANNEX G CERTIFIED
- CAST BRONZE BODY
- 20 MESH STAINLESS STEEL SCREEN
- BLOW-OFF PLUG INCLUDED
- SIZES 1/2" - 2"



Figure X10P / X11P
LOW LEAD WATER HAMMER ARRESTOR
- MALE NPT (X10P), COPPER SWEAT (X11P)
- 150 PSI MAX STATIC WORKING PRESSURE
- 350 PSI MAX SPIKE PRESSURE
- LEAD FREE CERTIFIED
- SIZES 1/2" - 2" NPT, 1/2" - 1 1/4" SWEAT
- PDI CERTIFIED



Gauges
LOW LEAD COMPLIANT LIQUID FILLED & MECHANICAL CONTRACTOR'S PRESSURE GAUGES
- COMPLIES WITH FEDERAL LEAD FREE LAWS
- 2 1/2" LIQUID FILLED (GLYCERIN)
- 4 1/2" MECHANICAL CONTRACTOR'S
- RANGES FROM 0-30 PSI TO 0-300 PSI



Gauges
LOW LEAD COMPLIANT BRASS GAUGE ACCESSORIES
- COMPLIES WITH FEDERAL LEAD FREE LAWS
- NEEDLE VALVES
- PRESSURE SNUBBER/FILTERS
- P/T TEST PLUGS
- THERMOWELLS



Figure 410A / 411A
2 PC FULL PORT 600 WOG BRASS BALL VALVE
- NPT (410A), SWEAT (411A)
- RATED 150 WSP
- FM, UL, CSA RATED (410A ONLY)
- OPTIONAL LOCKING DEVICE, T-HANDLE, STEM EXTENSION, & MORE
- SIZES 1/4" - 4" NPT, 1/2" - 3" SWEAT



Figure 415
2 PC FULL PORT 600 WOG BRASS BALL VALVE
- ECONOMICAL DESIGN
- NPT CONNECTIONS
- RATED 150 WSP
- CSA RATED (1/2" - 2")
- FM RATED TO 400 PSI (1/2" - 2")
- DUAL O-RING PACKING
- SIZES 1/4" - 4"



Figure 420 / 421
2 PC FULL PORT 600 WOG BRASS BALL VALVE
- NPT (420), SWEAT (421), RATED 150 WSP
- FM, UL, CSA & GAS RATED (420)
- OPTIONAL SS TRIM (420)
- OPTIONAL LOCKING DEVICE, T-HANDLE, STEM EXTENSION, & MORE
- SIZES 1/4" - 4" NPT, 1/2" - 4" SWEAT



Figure 426A / 427A / 428A
2 PC FULL PORT 600 WOG 3/4" HOSE CONNECTION BRASS BV
- 3/4" HOSE CONNECTION
- FULL PORT
- WITH FNPT END (426A), SWEAT END (427A), MNPT (428A)
- INCLUDES CAP, CAP GASKET, & CHAIN
- FORGED BRASS BODY & END CAP
- SIZES 1/2" & 3/4"



Figure 435
125 PSI PRESS CONNECTION BRASS BALL VALVE FOR GAS SERVICE
- FULL PORT DESIGN
- CSA RATED
- FORGED BODY & END CAP
- BLOW-OUT PROOF STEM
- ADJUSTABLE PACKING
- SIZES 1/2" - 2"



Figure 430
200 PSI PRESS CONNECTION BRASS BALL VALVE FOR WATER SERVICE
- FULL PORT DESIGN
- FM & UL RATED
- FORGED BODY & END CAP
- BLOW-OUT PROOF STEM
- ADJUSTABLE PACKING
- SIZES 1/2" - 4", 2 1/2" - 4" XLC ENDS



Figure 440
2 PC FULL PORT 600 WOG ISO MOUNT BRASS BALL VALVE
- ISO 5211 MOUNTING PAD
- RATED 150 WSP
- O-RING BACKED SEATS
- DOUBLE O-RING VITON® PACKING
- FOR DIRECT MOUNT ACTUATION
- SIZES 2 1/2" - 4"



Figure 455 / 465
3-WAY 400 WOG ISO MOUNT BRASS BALL VALVE
- T-PORT (455) & L-PORT (465)
- ISO 5211 MOUNTING PAD (WITH HANDLE)
- RATED 100 WSP
- O-RING BACKED SEATS
- DOUBLE O-RING VITON® PACKING
- FOR DIRECT MOUNT ACTUATION
- SIZES 1/4" - 2"



Figure 470 / 475
2 PC FULL PORT 400 WOG PUMP ISOLATION BALL VALVE
- INTEGRAL PUMP FLANGE CONNECTION
- FULL PORT DESIGN
- FNPT END (470), SWEAT END (475)
- INCLUDES T-HANDLE, GASKET & BOLTS
- EASES PUMP INSTALL & REMOVAL
- SIZES 3/4" - 1 1/2"



Figure 480A
2 PC STANDARD PORT 400 WOG VALVE w/ COMPRESSION ENDS
- DRAIN & CAP
- FORGED BRASS BODY & END CAP
- BLOW-OUT PROOF STEM
- ADJUSTABLE PACKING
- SIZES 1/2", 3/4" & 1"



Figure 485
FULL PORT 200 PSI PUSH FIT VALVE FOR WATER OR AIR
- FOR COPPER, CPVC, & PEX PIPE
- EASY INSTALL AND REMOVAL
- INCLUDES REMOVAL TOOL
- BLOW-OUT PROOF STEM
- ADJUSTABLE PACKING
- SIZES 1/2", 3/4" & 1"



Figure 490 / 495
2 PC FULL PORT 600 WOG PUMP ISOLATION BALL VALVE w/ ROTATING FLANGE
- INTEGRAL ROTATING PUMP FLANGE CONNECTION
- FNPT END (490), SWEAT END (495)
- INCLUDES T-HANDLE (EXCEPT 1 1/2"), GASKET & BOLTS
- SIZES 3/4" - 1 1/2"



Figure 490D / 495D
2 PC FULL PORT 600 WOG PUMP ISOLATION BALL VALVE w/ ROTATING FLANGE & DRAIN
- INTEGRAL ROTATING PUMP FLANGE CONNECTION & ON/OFF DRAIN
- FNPT END (490D), SWEAT END (495D)
- INCLUDES T-HANDLE, GASKET & BOLTS
- SIZES 3/4" - 1 1/4"



Figure 100A
1 PC STANDARD PORT 1000 CWP STAINLESS STEEL BALL VALVE
- INVESTMENT CAST BODY
- 150 PSI WSP
- SS LOCKING HANDLE
- RTFE SEATS
- BLOW-OUT PROOF STEM
- SIZES 1/4" - 2"



Figure 200A
2 PC FULL PORT 1000 CWP STAINLESS STEEL BALL VALVE
- INVESTMENT CAST BODY & END CAP
- 150 PSI WSP
- SS LOCKING HANDLE
- RTFE SEATS
- BLOW-OUT PROOF STEM
- SIZES 1/4" - 2"



Figure 220A / 220AC - SSxSS
Figure 221A / 221AC - CSxSS
2 PC FULL PORT 2000 CWP BALL VALVE
- INVESTMENT CAST BODY & END CAP
- 150 PSI WSP (220A/221A)
- 250 PSI WSP (220AC/221AC)
- SS LOCKING HANDLE
- TFM SEATS
- SIZES 1/4" - 3"



Figure 220AM
2 PC FULL PORT 2000 CWP ISO MOUNT SS BALL VALVE
- ISO 5211 MOUNTING PAD
- 150 PSI WSP
- LIVE LOADED PACKING
- INVESTMENT CAST BODY & END CAP
- TFM SEATS
- FOR DIRECT MOUNT ACTUATION
- SIZES 1/4" - 3"



Figure 220SE
2 PC FULL PORT 150 PSI SAFETY EXHAUST BALL VALVE
- VENTS DOWNSTREAM PRESSURE IN CLOSED POSITION
- INVESTMENT CAST BODY & END CAP
- 150 PSI MAXIMUM PRESSURE
- NON-VENTED BALL
- SS LOCKING HANDLE
- RTFE SEATS
- SIZES 3/4" - 1 1/2"



Figure 233A
3-WAY DIVERTER 1000 CWP STAINLESS STEEL BALL VALVE
- STANDARD PORT
- 150 PSI WSP
- RTFE SEATS
- SS LOCKING HANDLE
- BLOW-OUT PROOF STEM
- ISO 5211 MOUNTING PAD
- SIZES 1/2" - 2"



Figure 260A
2 PC FULL PORT STAINLESS STEEL BALL VALVE 1000 WOG
- 150 PSI/WSP
- WORKING TEMP: -4°F - 392°F
- INVESTMENT CAST BODY
- BLOW-OUT PROOF STEM
- STAINLESS HANDLE
- LOCKING LEVER
- SIZES 1/4"-2"



Figure 360A
3 PC FULL PORT STAINLESS STEEL BALL VALVE 1000 WOG
- 150 PSI/WSP
- WORKING TEMP: -4°F - 392°F
- INVESTMENT CAST BODY
- BLOW-OUT PROOF STEM
- ISO 5211 MOUNTING PAD
- STAINLESS STEEL HANDLE
- LOCKING LEVER
- SIZES 1/4" - 3"



Figure 310A - SSxSS
Figure 311A - CSxSS
3 PC FULL PORT 1000 CWP BALL VALVE
- INVESTMENT CAST BODY & END CAPS
- 150 PSI WSP
- NPT ENDS (OPTIONAL SOCKET WELD)
- SS LOCKING HANDLE
- RTFE SEAT
- SIZES 1/4" - 3"



Figure 310AM - SSxSS
Figure 311AM - CSxSS
3 PC FULL PORT 1000 CWP ISO MOUNT SS BALL VALVE
- ISO 5211 MOUNTING PAD
- 150 PSI WSP
- LIVE LOADED PACKING
- INVESTMENT CAST BODY & END CAPS
- NPT ENDS (OPTIONAL SOCKET WELD)
- SIZES 1/4" - 4" (4" INCLUDES HANDLE)



Figure 320A / 320AC - SSxSS
Figure 321A / 321AC - CSxSS
3 PC FULL PORT 2000 CWP BALL VALVE
- 150 PSI WSP (320A/321A)
- 250 PSI WSP (320AC/321AC)
- NPT END (OPTIONAL SOCKET WELD)
- SS LOCKING HANDLE
- TFM SEATS
- SIZES 1/4" - 2"



Figure 330A
SANITARY 3 PC FULL PORT 400 CWP SS BALL VALVE
- CLAMP ENDS
- 150 PSI WSP
- CAVITY FILLED SEATS
- ISO 5211 MOUNTING PAD
- SS LOCKING HANDLE
- TFM SEATS
- SIZES 1/2" - 4"



Figure 500B - SSxSS
Figure 501B - CSxSS
1 PC STANDARD PORT 150# FLANGED BALL VALVE
- INVESTMENT CAST BODY
- ANTI-STATIC DESIGN
- RTFE SEATS
- ISO MOUNTING PAD
- SIZES 2" - 6"



Figure 600B - SSxSS
Figure 601B - CSxSS
2 PC FULL PORT 150# FLANGED BALL VALVE
- INVESTMENT CAST BODY
- ANTI-STATIC DESIGN
- RTFE SEATS
- ISO MOUNTING PAD
- SIZES 1/2" - 8"



Figure 633 / 634
3-WAY 150# FLANGED STAINLESS STEEL BALL VALVE
- L-PORT (633) & T-PORT (634)
- FULL PORT SPLIT BODY
- RTFE SEATS
- TOP ENTRY, TRUNNION MOUNTED
- ACTUATOR MOUNTING PAD
- SIZES 2" - 8"



Figure 660A
2 PC FULL PORT 150# FLANGED ECONOMY BALL VALVE
- INVESTMENT CAST BODY
- ANTI-STATIC DESIGN
- RTFE SEATS
- ISO MOUNTING PAD
- SIZES 2" - 6"



Figure 340N / 340NF / 350N
THERMOPLASTIC FULL PORT TRUE UNION BALL VALVE
- PVC (340N/340NF) & CPVC (350N)
- BOTH NPT & SW ENDS (UP TO 2")
- ABOVE 2" IN SW (NPT ON REQUEST)
- NSF 61 ANNEX G CERTIFIED
- FULL PORT BI-DIRECTIONAL DESIGN
- PTFE SEATS, EPDM OR VITON® SEALS
- SIZES 1/2" - 4"



Figure 721
THERMOPLASTIC WAFER BUTTERFLY VALVE
- 150 PSI TO 10", 100 PSI TO 12"
- COMPACT DESIGN
- BUBBLE-TIGHT SHUTOFF
- EPDM OR VITON® SEAT/SEALS
- CAN BE EASILY ACTUATED
- SIZES 2" - 12"



Figure 345 - PVC
Figure 355 - CPVC
THERMOPLASTIC DOUBLE UNION BALL CHECK VALVE
- BOTH NPT & SW ENDS
- 150 PSI MAX WORKING PRESSURE
- 5 PSI MINIMUM SHUTOFF
- FOR VERTICAL INSTALLATION
- EASY MAINTENANCE
- SIZES 1/2" - 2"



Figure 61B
LINED KNIFE GATE VALVE, METAL SEATED
- CAST DI BODY/SS LINED
- METAL SEAT
- SS WETTED PARTS
- UNI-DIRECTIONAL SHUTOFF
- ECONOMY VALVE FOR MANY APPLICATIONS
- SIZES 3" – 24"



Figure 62B
LINED KNIFE GATE VALVE, RESILIENT SEATED
- CAST DI BODY/SS LINED
- POSITIVE SHUTOFF RESILIENT SEAT
- SS WETTED PARTS
- UNI-DIRECTIONAL SHUTOFF
- ECONOMY VALVE FOR MANY APPLICATIONS
- SIZES 3" – 24"



Figure 6500
CAST SS KNIFE GATE VALVE, METAL SEATED
- CAST SS BODY/YOKE/FOLLOWER
- INTEGRAL METAL SEAT
- UNI-DIRECTIONAL SHUTOFF
- DESIGNED FOR HEAVY MEDIA
- GATE EDGE RADIUS
- ANTI-EXTRUSION RING IN PACKING
- ELASTOMER QUAD SEAL IN PACKING
- SIZES 2" – 24"



Figure 6701
CAST SS KNIFE GATE VALVE, METAL SEATED
- CAST SS BODY AND FOLLOWER
- INTEGRAL METAL SEAT
- CARBON STEEL & IRON TOPWORKS
- UNI-DIRECTIONAL SHUTOFF
- DESIGNED FOR HEAVY MEDIA
- NON-CLOGGING STEP SEAT DESIGN
- SIZES 3" – 30"



Figure 6800
CAST SS KNIFE GATE VALVE, RESILIENT SEAT
- CAST SS BODY/YOKE/FOLLOWER
- POSITIVE SHUTOFF RESILIENT SEAT EVEN AT LOW MEDIA PRESSURES
- BI-DIRECTIONAL SHUTOFF
- STAINLESS NEEDLE BEARING FOR REDUCED HW TORQUE
- ANTI-EXTRUSION STRIPS IN PACKING
- SIZES 3" – 30"



Figure 2020
HIGH PERFORMANCE KNIFE GATE VALVE
- CAST SS BODY/YOKE/FOLLOWER
- O-RING ENERGIZED REINFORCED TEFLON RESILIENT SEATS
- BI-DIRECTIONAL SHUTOFF
- STAINLESS NEEDLE BEARING FOR REDUCED HW TORQUE
- ELASTOMER QUAD SEAL IN PACKING
- SIZES 2" – 24"




Figure 60R
KNIFE GATE VALVE FOR ABRASIVE APPLICATIONS
- CAST CS BODY/YOKE/FOLLOWER
- RESILIENT SEAT
- POP-OUT SLEEVE-LINED
- BI-DIRECTIONAL SHUTOFF
- UP TO 100 PSI CWP
- SIZES 3" – 30"



Figure 2000BTIV
TRANSMITTER ISOLATION VALVE
- CAST SS BODY/YOKE/FOLLOWER
- FLEX TEFLON RESILIENT SEATS
- BI-DIRECTIONAL SHUTOFF
- RATCHET OPERATOR
- TANK SIDE FLANGE ACCESS
- SIZE 3"



F-Series
FABRICATED SLIDE & KNIFE GATE VALVES
FABRICATION CAPABILITIES FOR:
- CUSTOM MATERIALS
- CUSTOM PRESSURE RATINGS
- CUSTOM SIZES
- F150 SLIDE GATE OPTION
- F65 AND F68 KNIFE GATE OPTION
- CUSTOM CONFIGURATIONS



Figure 509 / 510
BRONZE Y-STRAINER
- FNPT ENDS (509) & SWEAT ENDS (510)
- 250 WOG, 150 PSI STEAM (509)
- 400 WOG, 250 PSI STEAM (510)
- CAST BRONZE BODY
- 20 MESH STAINLESS STEEL SCREEN
- BLOW-OFF PLUG INCLUDED
- SIZES 3/8" - 2" (509); SIZES 1/2" - 2" (510)



Figure 558A / 559
CAST IRON Y-STRAINER
- 125# FLANGED ENDS (558A) & FNPT ENDS (559)
- 200 WOG, 125 PSI STEAM (558A)
- 400 WOG, 250 PSI STEAM (559)
- STAINLESS STEEL SCREEN
- SIZES 2" - 12" (558A); SIZES 1/2" - 2 1/2" (559) (2 1/2" IS BOLTED END BONNET)



Figure 14B-YSS
THREADED SS 800 PSI CWP Y-STRAINER
- SS 20 MESH SCREEN
- VITON® O-RING SEAL
- SIZES 1/2" - 2"



Figure 1211 / 1212
NRS 125# BRONZE GATE VALVE
- 200 CWP
- 125 PSI STEAM RATED (1211 ONLY)
- SOLID WEDGE DISC
- FNPT (1211) & SWEAT (1212) ENDS
- BACK SEAT DESIGN
- CONFORMS TO MSS SP-80
- SIZES 1/4" - 3" (1211); SIZES 1/2" - 3" (1212)



Figure 1221 / 1222
RS 125# BRONZE GATE VALVE
- 200 CWP
- 125 PSI STEAM RATED (1221 ONLY)
- SOLID WEDGE DISC
- FNPT (1221) & SWEAT (1222) ENDS
- BACK SEAT DESIGN
- CONFORMS TO MSS SP-80
- SIZES 1/2" - 3"



Figure 1231 / 1232
125# BRONZE GLOBE VALVE
- 200 WOG
- 125 PSI STEAM RATED (1231 ONLY)
- RESILIENT SEAT DISC
- FNPT (1231) & SWEAT (1232) ENDS
- CONFORMS TO MSS SP-80
- SIZES 1/4" - 3" (1231); SIZES 1/2" - 2" (1232)



Figure 1241 / 1242
150# Y-PATTERN BRONZE SWING CHECK VALVE
- 300 WOG
- 150 PSI SATURATED STEAM RATED
- RESILIENT SEAT DISC
- FNPT (1241) & SWEAT (1242) ENDS
- CONFORMS TO MSS SP-80
- SIZES 1/2" - 3"



Figure 431
200 PSI PRESS CONNECTION BRASS IN-LINE CHECK VALVE FOR WATER
- HIGH CAPACITY DESIGN
- LOW 1/2 PSI CRACKING PRESSURE
- SOFT SEAT FOR TIGHT SHUTOFF
- NSF-61 APPROVED
- FORGED BODY & END CAP
- SIZES 1/2" - 2"



Figure 15B-200
THREADED SS 200 WOG NON-RISING STEM GATE VALVE
- STAINLESS STEEL TRIM
- ADJUSTABLE PACKING
- SIZES 1/2" - 2"



Figure 16B-200
THREADED SS 200 WOG SWING CHECK VALVE
- STAINLESS STEEL TRIM
- PTFE SEALS
- SIZES 1/4" - 2"



Figure 17B-200
THREADED SS 200 WOG GLOBE VALVE
- STAINLESS STEEL TRIM
- ADJUSTABLE PACKING
- SIZES 1/2" - 2"



Figure 451A / 452A - SS
Figure 551 / 552 - CS
FLANGED OS&Y WEDGE GATE VALVE
- 150# FLANGES (451A/551)
- 300# FLANGES (452A/552)
- API 600 (CS), API 603 (SS)
- INVESTMENT CAST TO 8" (SS ONLY)
- FLEX WEDGE DESIGN FOR POSITIVE SHUTOFF



Figure 461A / 462A - SS
Figure 561 / 562 - CS
FLANGED GLOBE VALVE
- 150# FLANGES (461A/561)
- 300# FLANGES (462A/562)
- API 600 (CS), API 603 (SS)
- INVESTMENT CAST TO 8" (SS ONLY)
- MODIFIED PLUG TYPE DISC FOR HAND OPERATED THROTTLING



Figure 471A / 472A - SS
Figure 571 / 572 - CS
FLANGED SWING CHECK VALVE
- 150# FLANGES (471A/571)
- 300# FLANGES (472A/572)
- API 600 (CS), API 603 (SS)
- MACHINED DISC & SEAT FOR TIGHT SHUTOFF




Figure 681
200 PSI CAST IRON WAFER SILENT CHECK VALVE
- 200 PSI NON-SHOCK
- RESILIENT SEAT
- NON-SLAM STAINLESS STEEL SPRING ACTUATED
- ALUMINUM-BRONZE DISC
- SIZES 2" - 10"



Figure 682
200 PSI CAST IRON WAFER DOUBLE DOOR CHECK VALVE
- 200 PSI NON-SHOCK
- RESILIENT SEAT
- NON-SLAM STAINLESS STEEL SPRING ACTUATED
- STAINLESS STEEL DISCS
- SIZES 2" - 10"



Figure 651A / 661 / 671A
125# IRON BODY, BRONZE MOUNTED VALVE
- IBBM GATE (651A), GLOBE (661), & CHECK (671A) VALVES
- 125 PSI SWP (SATURATED TO 353°F)
- DESIGN AND TESTED TO:
  - GATES: MSS SP-70
  - GLOBES: MSS SP-85
  - CHECKS: MSS SP-71



Figure 711 / 712
RESILIENT SEATED BUTTERFLY VALVES
- WAFER (711) & LUGGED (712)
- RATED TO 200 PSI (14" & UP - 150 PSI)
- ALUMINUM BRONZE DISC
- 416SS STEM
- ISO 5211 MOUNTING PAD
- 2 PC PINLESS STEM
- CARTRIDGE STYLE SEAT
- SIZES 2" - 24"



Figure 731 / 732
RESILIENT SEATED BUTTERFLY VALVES
- WAFER (731) & LUGGED (732)
- RATED TO 255 PSI (14" & UP - 188 PSI)
- 316SS DISC & STEM STANDARD
- ISO 5211 MOUNTING PAD
- 2 PC PINLESS STEM
- CARTRIDGE STYLE SEAT
- SIZES 2" - 24"



Figure 752
LARGE DIAMETER U-BODY RESILIENT SEATED BUTTERFLY VALVES
- RATED TO 150 PSI
- CARTRIDGE SEAT DESIGN
- DUCTILE IRON OR STAINLESS STEEL DISC
- EPDM OR NBR (BUNA) SEAT
- SIZES 28" - 48"



Figure 761 / 762
PTFE SEATED BUTTERFLY VALVES
- WAFER (761) & LUGGED (762)
- RATED TO 150 PSI
- 316SS DISC & STEM STANDARD
- ISO 5211 MOUNTING PAD
- 1 PC DISC/STEM ASSEMBLY
- BOOT STYLE SEAT
- GEAR-OP STANDARD ON 8" - 12"
- SIZES 2" - 12"



Figure HP
HIGH PERFORMANCE RESILIENT SEATED BUTTERFLY VALVES
- BI-DIRECTIONAL BUBBLE-TIGHT SHUTOFF
- DOUBLE OFF-SET DESIGN
- WAFER OR LUGGED CONNECTIONS
- SS OR CS BODY
- ISO TOPWORKS
- GEAR STANDARD (6" - 24")
- SIZES 3" - 24"



Figure 10P / 11P
WATER HAMMER ARRESTOR
- MALE NPT (10P)
- COPPER SWEAT (11P)
- 150 PSI MAX STATIC WORKING PRESSURE
- 350 PSI MAX SPIKE PRESSURE
- FOR NON-POTABLE WATER APPLICATIONS
- PDI Certified
- SIZES 1/2" - 2" NPT, 1/2" - 1 1/4" SWEAT



Figure 72 / 73
IPS DUCTILE IRON BACK-UP FLANGES
- STUB END (72)
- ANGLE FACE RING (73)
- 150# DRILLING
- IPS SIZES
- RED PRIMER OR HOT DIPPED GALVANIZED
- SIZES 1" - 24"




Figure NA / R / NE
FLANGE GASKETS
- NON-ASBESTOS (NA), RED RUBBER (R), & NEOPRENE (NE)
- 150# & 300#
- RING & FULL FACE (NE FF ONLY)
- 1/16" & 1/8" THICK (NE 1/8" ONLY)
- SIZES 1/2" - 24"



Figure NBG
NUT / BOLT / GASKET KITS
- NON-ASBESTOS, RED RUBBER, & NEOPRENE KITS
- RING & FULL FACE
- CARBON & STAINLESS STEEL NUT & BOLT MATERIALS
- SIZES VARY PER CONFIGURATION



Figure LBB / WBB / NBS
PRE-PACKAGED NUT & BOLT SETS
- LUGGED BUTTERFLY (LBB), WAFER BUTTERFLY (WBB), & FLANGE NUT/BOLT SETS (NBS)
- HARDWARE FOR 1 VALVE OR FLANGE CONNECTION
- MATERIAL & CLASSES VARY PER CONFIGURATION
- SIZES VARY PER CONFIGURATION



Figure B7
B7/2H STUD & NUT SETS
- CARBON STEEL
- ASTM A193 GRADE B7 STUDS
- ASTM A194 GRADE 2H NUTS (2/STUD)
- DIMENSIONS PER
  - ASME B1.1 UNC (UNC8) CLASS 2A
  - ASME B18.2.2
- DIAMETERS 1/2" - 1 1/2"
- LENGTHS 2 1/2" - 9"



Figure B7K
B7/2H PRE-PACKAGED FLANGE KITS
- ASTM A193 GRADE B7 STUDS
- ASTM A194 GRADE 2H NUTS (2/STUD)
- DIMENSIONS PER
  - ASME B1.1 UNC (UNC8) CLASS 2A
  - ASME B18.2.2
- 150# & 300# FLANGES
- SIZES 1/2" - 12"



Figure ABFBK
AQUATHERM BUTTERFLY FLANGE BOLT KIT
- BOLTS: ASTM A307A GRADE A
- NUTS: SAE J995 GRADE 2
- WASHERS: ASME B18.22.1
- SIZES 2"-24"



Figure ABKFAFA
AQUATHERM FLANGE ADAPTER TO FLANGE ADAPTER BOLT KIT
- BOLTS:ASTM A307A GRADE A
- NUTS: SAE J995 GRADE 2
- WASHERS: ASME B18.22.1
- SIZES 1"-24" (EXCLUDING 3 1/2" & 22")



Figure ABKFAFLG
AQUATHERM BUTTERFLY FLANGE BOLT KIT
- BOLTS: ASTM A307A GRADE A
- NUTS: SAE J995 GRADE 2
- WASHERS: ASME B18.22.1
- SIZES 1"- 24" (EXCLUDING 3 1/2" & 22")



Piping Products
BOLT INSULATORS
- REINFORCED NYLON 66 RESIN
- WHITE
- SOLD INDIVIDUALLY
- SIZES 1/2", 5/8", & 3/4"



Figure 9101
RISER GAUGE KITS
- COMPONENTS FOR INSTALLING A SPRINKLER GAUGE
- CONTRACTOR'S GAUGE, NIPPLE, DUAL OUTLET 400 WOG BRASS VALVE, REDUCER, & PIPE PLUG
- PLAIN (9101P) OR GALVANIZED (9101G) PIPE NIPPLE
- 1/4" CONNECTIONS



Actuation & Accessories
MANUAL GEAR OPERATORS
- WORM GEARS FOR QUARTER-TURN
- BEVEL GEARS FOR LINEAR MOVEMENT
- VARIOUS SIZES
- AVAILABLE WITH ISO 5211 MOUNTING FOR DIRECT MOUNT VALVES
- MACHINED MOUNTING ADAPTATION ALSO AVAILABLE



Actuation & Accessories
PNEUMATIC ACTUATORS
- CYLINDER (PNEUMATIC & HYDRAULIC)
- RACK & PINION
- SCOTCH YOKE
- DOUBLE-ACTING
- SPRING-RETURN



Actuation & Accessories
ELECTRIC VALVE ACTUATORS
- QUARTER-TURN DESIGN
- VARIOUS NEMA CLASSES
- MULTIPLE VOLTAGES AVAILABLE
- DOUBLE-ACTING (STAY IN LAST POSITION) & SPRING-RETURN DESIGNS
- MULTI-TURN & LARGE BODY ELECTRIC ACTUATORS AVAILABLE ON REQUEST




Actuation & Accessories
ACTUATOR CONTROLS
- SOLENOIDS
  - 3-WAY & 4-WAY CONFIGURATIONS
  - VARIOUS CLASSES & VOLTAGES
- POSITION / LIMIT SWITCHES
  - MECHANICAL
  - PROXIMITY
- POSITIONERS
  - 3-15 PSI & 4-20 mA SIGNAL
  - DIGITAL, SMART, HART®



Figure 30F / 30T / 35S/ 40
FLEXIBLE CONNECTORS
- METAL BRAIDED ANNULAR
  - STAINLESS INNER HOSE (30F, 30T)
  - BRONZE INNER HOSE (35S)
  - SIZES 1/2" - 10" (30F), 1/2" - 2" (30T), 3/4" - 2" (35S)
- SINGLE SPHERE
  - 150# CARBON STEEL FLANGES
  - WIRE AND FABRIC REINFORCED
  - SIZES 2 1/2" - 10"



Gauges
LIQUID FILLED & MECHANICAL CONTRACTOR'S PRESSURE GAUGES
- 2 1/2" LIQUID FILLED (GLYCERIN)
- 4 1/2" MECHANICAL CONTRACTOR'S
- PRESSURE RANGES FROM 0-30 PSI TO 0-300 PSI



Gauges
ADJUSTABLE ANGLE THERMOMETERS
- LIQUID FILLED THERMOMETER
  - RANGES 0-120, 0-160 OR 30-240°F
  - ADJUSTABLE TO 20 POSITIONS
  - GREEN KEROSENE FILLED
- DIGITAL SOLAR THERMOMETER
  - -50 TO 320°F RANGE
  - FIELD SELECTABLE °F OR °C DISPLAY



Gauges
BRASS GAUGE ACCESSORIES
- NEEDLE VALVES
- PRESSURE SNUBBER/FILTERS
- P/T TEST PLUGS
- THERMOWELLS




Piping Products
PIPE HANGERS
- MALLEABLE IRON & STEEL
- CLEVIS, LOOP, ROLLER, & "J" HANGERS
- RISER, PIPE & BEAM CLAMPS
- ATTACHMENT BRACKETS
- PLAIN, ZINC & COPPER FINISH (MI)
- EPOXY PLATED (STEEL)
- U-BOLTS IN PLAIN, ZINC, & STAINLESS STEEL




Piping Products
STRUT ACCESSORIES
- STRUT, TUBE & CONDUIT CLAMPS
- ANGLE FITTINGS
- CHANNEL NUTS
- POST BASES
- VARIOUS FINISHES



Piping Products
SANITARY STAINLESS
- CLAMP FITTINGS
- WELD FITTINGS
- HANGERS
- TUBING



Piping Products
INSULATION PROTECTION SHIELDS
- MSS COMPLIANT - IMPORT
- MSS COMPLIANT - DOMESTIC
- LIGHT DUTY



Piping Products
PIPE SUPPORT SYSTEMS
- 50# SUPPORTS
- 150# SUPPORTS
- 300# SUPPORTS
- ADJUSTABLE ELEVATION KITS
- COMPATIBLE WITH FNW HANGER AND STRUT PRODUCTS


FNW™

For product SKU, precede each Figure number with "FNW"



Figure X410C / X411C
LOW LEAD 2 PC FULL PORT
600 WOG BRASS BALL VALVE
- NPT (X410C), SWEAT (X411C)
- 600 WOG
- CSA RATED (X410C ONLY)
- NSF 61 ANNEX G CERTIFIED
- ADJUSTABLE PACKING
- X410C SIZES: 1/4" - 4"
- X411C SIZES: 3/8" - 3"

Figure X410C = SKU FNWX410C



For all products, visit FNW.com

Basin Faucets



- Faucet Installation: 1 hole
- Handle Type: Tee
- 1/2" FIP connection
- Brass construction
- Color/Finish: Chrome

SKU
PF760HECP

Basin Faucets



- Faucet Installation: 1 hole
- Handle Type: Cross
- Brass waterways
- 1/2" MIP connection
- Renewable seats and stems
- Includes hot and cold index buttons
- Color/Finish: Chrome

SKU
PFX300

Basin Faucets



- Spout Reach: 4 7/8"
- Flow Rate: 1.2 gpm
- Self closing handle
- Handle Type: Cross
- Brass construction
- Color/Finish: Chrome

SKU
PFX750C

Exposed Shower Faucets



- 3" centerset installation
- 1/2" threaded union inlet
- Handle Type: Blade
- Brass waterways
- Renewable seats and stems
- Color/Finish: Chrome

SKU
PF418

Faucet Blocks



- Mounts to laundry tubs or utility sinks for use with clamp-on faucets and overhead supply lines
- Constructed from durable impact resistant plastic
- Comes with 2 sets of screws and 2 washers for easy installation
- Works with PF244 service faucet

SKU
PFLTBLK

Service Sink Faucets



- Spout Reach: 9 1/8"
- 8" wall mount installation
- Handle Type: Lever
- Brass waterways
- 3/4" hose thread
- Vacuum breaker
- Integral stops
- Ceramic disc cartridges
- Color/Finish: Chrome

SKU
PF1119

Two Handle Laundry Faucets



- 3" centerset installation
- Handle Type: Lever
- Brass waterways
- Wall mount installation
- Renewable seats and stems
- Chrome/Rough Brass construction

SKU
PF244

Two Handle Laundry Faucets



- 3 3/8" centerset installation
- 3/4" - 14 NPSM connection ends
- Handle Type: Lever
- O-pattern bathcock
- Brass waterways
- Renewable seats and stems
- Color/Finish: Polished Chrome

SKU
PF301

Two Handle Laundry Faucets



- 3 3/8" centerset installation
- Handle Type: Lever
- Brass waterways
- Renewable seats and stems
- Gooseneck spout
- Color/Finish: Chrome

SKU
PF302

Two Handle Laundry Faucets



- 8" centerset installation
- Flow Rate: 1.8 gpm
- Handle Type: Lever
- Spout swivels
- 1/2" FIP inlets
- Soap dish included
- Color/Finish: Chrome

SKU	Spout Reach
PFXC800U	6"
PFXC80012	12"

Two Handle Laundry Faucets



- Spout Reach: 8"
- Flow Rate (with hose thread adapter): Min. 4.0 gpm
- Flow Rate (with optional aerator): Max. 1.2 gpm
- Handle Type: Lever
- Spout swivels
- 4" centerset installation
- Ceramic cartridge
- Includes optional hose thread
- Color/Finish: Chrome

SKU
PFWSC1120CP

Two Handle Laundry Faucets



- Spout Reach: 8 1/2"
- Flow Rate: 1.8 gpm
- 7"/9" wall mount installation
- Handle Type: Lever
- 1/2" FIP inlets
- Color/Finish: Chrome

SKU
PFXC800

Grab Bars




- 1 1/2" grab bar with concealed flange
- Bar: 18 gauge 304 stainless steel
- Flange: 14 gauge 304 stainless steel
- Screws: #10 x 2" self tapping stainless steel

SKU	Length	Color/Finish
PFGB12SF2	12"	Satin
PFGB16PF2	16"	Peened
PFGB16SF2	16"	Satin
PFGB18PF2	18"	Peened
PFGB18SF2	18"	Satin
PFGB24PF2	24"	Peened
PFGB24SF2	24"	Satin
PFGB30PF2	30"	Peened
PFGB30SF2	30"	Satin
PFGB32PF2	32"	Peened
PFGB32SF2	32"	Satin
PFGB36PF2	36"	Peened
PFGB36SF2	36"	Satin
PFGB42PF2	42"	Peened
PFGB42SF2	42"	Satin
PFGB48SF2	48"	Satin



Laundry Sinks
P. 75-76



Explore FNW's wide range of valves, pneumatic actuators and more to see how they are THE source for commercial and industrial piping products.

Learn more at FNW.com and Ferguson.com.

FNW™



What can we help you find?

Pipe Fitting Gaskets 179-180
Pipe Lubricants. 181
Bolts 181
Utility Tools 181-183
Valve Boxes 184-187

HDPE Transition Accessory Packs



PROSELECT

- With gland
- Includes ductile iron gland, SBR mechanical joint gasket and extra long T-head bolts
- Gland manufactured as per ANSI / AWWA C153/A21.53
- Gasket and bolts manufactured as per AWWA C111/A21.11

SKU	Size
IMJAPHDIM	3"
IMJAPHDIP	4"
IMJAPHDIU	6"
IMJAPHDIX	8"
IMJAPHDI10	10"
IMJAPHDI12	12"

Mechanical Joint Bolt & Gasket Packs



PROSELECT

- Less gland
- Includes SBR mechanical joint gasket, T-head bolts and nuts
- Gasket and bolts manufactured as per AWWA C111/A21.11

SKU	Size
IMJBGPM	3"
IMJBGPP	4"
IMJBGPU	6"
IMJBGPX	8"
IMJBGP10	10"
IMJBGP12	12"
IMJBGP14	14"
IMJBGP16	16"

Mechanical Joint Accessory Packs



PROSELECT

- With gland
- Includes mechanical joint gland, SBR gasket and T-head bolts and nuts
- Gland manufactured as per AWWA C153/A21.53
- Gasket and bolts manufactured as per AWWA C111/A21.11

SKU	Size
IMJAPM	3"
IMJAPP	4"
IMJAPU	6"
IMJAPX	8"
IMJAP10	10"
IMJAP12	12"
IMJAP14	14"
IMJAP16	16"

Mechanical Joint Gaskets



PROSELECT

- Includes SBR mechanical joint gasket only
- Manufactured as per AWWA C111/A21.11

SKU	Size
IMJGAM	3"
IMJGAP	4"
IMJGAU	6"
IMJGAX	8"
IMJGA10	10"
IMJGA12	12"
IMJGA14	14"
IMJGA16	16"

Mechanical Joint IPS Transition Accessory Packs




PROSELECT

- Includes mechanical joint gland, SBR IPS transition gasket and T-head bolts and nuts
- Gland manufactured as per AWWA C153/A21.53
- Gasket and bolts manufactured as per AWWA C111/A21.11

SKU	Size
IMJTGAPM	3"
IMJTGAPP	4"
IMJTGAPU	6"
IMJTGAPX	8"
IMJTGAP10	10"
IMJTGAP12	12"

Mechanical Joint IPS Transition Gaskets



PROSELECT

- Includes SBR mechanical joint transition gasket
- Manufactured as per AWWA C111/A21.11

SKU	Size
IMJTGM	3"
IMJTGP	4"
IMJTGU	6"
IMJTGX	8"
IMJTG10	10"
IMJTG12	12"

Mechanical Joint Gland Only



PROSELECT

- Manufactured as per AWWA C153/A21.53

SKU	Size
IMJGM	3"
IMJGP	4"
IMJGU	6"
IMJGX	8"
IMJG10	10"
IMJG12	12"
IMJG14	14"
IMJG16	16"

Mechanical Joint Transition Bolt & Gasket Packs



PROSELECT

- Less gland
- Includes SBR transition gasket and standard T-head bolts and nuts
- Gasket and bolts manufactured as per AWWA C111/A21.11

SKU	Size
IMJTBGPM	3"
IMJTBGPP	4"
IMJTBGPU	6"
IMJTBGPX	8"
IMJTBGP10	10"
IMJTBGP12	12"



PROSELECT™

PROSELECT features products such as:

- Brushes
- Cable Ties
- Condensate Pumps
- Condenser Pads
- Gloves
- GRDs
- Overflow Switches
- Tapes
- Thermostats

To view all PROSELECT products, visit FERGUSON.COM.

Pipe Joint Lubricants



PROSELECT

- All purpose, biodegradable pipe lubricant
- Can be used to assemble pipes made of cast iron, concrete, plastic and clay pipe
- Can be applied in temperatures from -10°F to 150°F
- Contains no petroleum, phosphate or silicone and will not support bacteria growth
- Water dispersible and can be washed or rinsed from surfaces easily
- Less odor
- Minimal to no separation
- Clings well to almost any surface

SKU	Carton Weight
PSLUBXL1Q	1 qt or 2 lbs
PSLUBXL1G	1 gal or 8 lbs
PSLUBXL5G	5 gal or 40 lbs

Round Cotton Swabs



PROSELECT

- 1" x 6"
- Heavy duty wire handle
- 100% cotton

SKU
PSCPLS

Duc Lugs



PROSELECT

- Manufactured from ductile iron
- Conforms to ASTM A536, Grade 64-45-12
- Package Quantity: 65

SKU
PSDLUG

Plain Eye Bolts



PROSELECT

- Low alloy steel construction
- Manufactured as per ASTM AWWA C111/A21.11

SKU	Size
PSPLEBE	5/8"
PSPLEBF	3/4"

T-Head Bolts



PROSELECT

- Anti-rotational
- Low alloy steel construction
- Manufactured as per AWWA C111/A21.53

SKU	Size
PSMJARTBFN	3/4" x 3 1/2"
PSMJARTBFP	3/4" x 4"
PSMJARTBFR	3/4" x 4 1/2"

T-Head Bolts



PROSELECT

- Low alloy steel construction
- Manufactured as per AWWA C111/A21.53

SKU	Size
PSMJTHBNEM	5/8" x 3"
PSMJTHBNFN	3/4" x 3 1/2"
PSMJTHBNFP	3/4" x 4"
PSMJTHBNFR	3/4" x 4 1/2"
PSMJTHBNFS	3/4" x 5"
PSMJTHBNFU	3/4" x 6"
PSMJTHBNFW	3/4" x 7"
PSMJTHBNGU	1" x 6"

Ratchet Wrenches



RAPTOR®

- 3 piece double socket
- Case Includes 1 of Each: 7/8" x 3/4", 1 1/8" x 15/16", 1 1/4" x 11/16"
- For use on bolts, mechanical joints, hex nuts, clamps, couplings and saddles

SKU
RAP41003

Ratchet Wrenches



RAPTOR®

- Double socket
- For tightening nuts on long bolts or all-thread rod without bottoming out
- For use on bolts, mechanical joints, hex nuts, clamps, couplings and saddles

SKU	Size	Color/Finish
RAP41007	1 1/8" x 1 5/16"	Green
RAP41008	1 1/4" x 1 1/16"	Blue

Ratchet Wrenches



RAPTOR®

- Adjustable pivot
- 1 1/4" x 1 1/16"
- Pivot handle for difficult access to nuts and bolts
- For tightening nuts on long bolts or all-thread rod without bottoming out
- For use on bolts, mechanical joints, hex nuts, clamps, couplings and saddles

SKU
RAP42009

Ratchet Wrenches



RAPTOR®

- 1 1/4" x 1 1/16"
- Open box end design allows tightening without bottoming out
- For use on 5/8" and 3/4" bolts, as well as most clamps, couplings and saddles
- Fully enclosed rugged construction keeps dirt and debris from jamming gears

SKU
RAP42040

Gate Valve Stem Extensions



PROSELECT

- No centering ring
- Rock guard
- Square socket on one end, 2" heavy square nut on the other
- Two locking screws on valve nut
- Carbon steel tube

SKU	Size
PS41101	1'
PS41102	2'
PS41103	3'
PS41104	4'
PS41105	5'
PS41106	6'
PS41115	7'
PS41116	8'

Gate Valve Stem Extensions




PROSELECT

- Centering ring
- Rock guard
- Square socket on one end, 2" heavy square nut on the other
- Two locking screws on valve nut
- Carbon steel tube

SKU	Size
PS41107	1'
PS41108	2'
PS41109	3'
PS41110	4'
PS41111	5'
PS41112	6'
PS41114	8'

Curb Stop Keys




RAPTOR®

- T-handle
- Designed to shut off 3/4" – 1" curb stops
- 5/8" round carbon steel for center stem
- 18" long T-handle
- 1/4" plate for wrench end

SKU	Length
RAP41030	3'
RAP41031	4'
RAP41032	5'
RAP41033	6'
RAP41034	8'

Curb Stop Keys




RAPTOR®

- T-handle
- Telescoping Length: 4' – 7'
- Designed to shut off 3/4" – 1" curb stops
- 5/8" round carbon steel for center stem
- 18" long T-handle
- 1/4" plate for wrench end

SKU
RAP41035

Gate Valve Keys




RAPTOR®

- T-handle
- Rugged construction
- 2 1/8" ID square socket end
- Socket designed with an opening to allow soil, rock and debris to exit tool end

SKU	Length
RAP41023	4'
RAP41024	5'
RAP41025	6'
RAP41026	8'

Gate Valve Keys



RAPTOR®

- T-handle
- Telescoping
- Rugged construction
- Square socket end
- Socket designed with an opening to allow soil, rock and debris to exit tool end

SKU	Length
RAP41027	5' - 10'
RAP41028	6' - 11'

Hydrant Setters



RAPTOR®

- 1,000 lb capacity
- Carbon steel tube
- Heavy duty chain
- Fits most hydrant designs
- Spreader bars to help with stability when maneuvering and setting fire hydrants into place

SKU
RAP41039

Hydrant Wrenches



RAPTOR®

- Adjustable
- Fits most hydrant operating nuts
- Forged steel handle
- Textured end to provide surface for gripping
- Nut is cast component, deburred for smooth seating
- For use on pentagon nuts and pumper or steamer caps

SKU
RAP41002

Manhole Cover Hooks



RAPTOR®

- Head designed for extra leverage to pry loose conventional manhole covers
- Rocker design and pointed chisel help with the toughest lids
- Rotated handle providing firm grip

SKU	Length
RAP42014	28"
RAP42015	36"

Meter Box Lid Lifters



RAPTOR®

- Length: 36"
- Simple tool used to hook and lift the lid of a meter box
- Stainless steel construction
- Cushioned handle with attached wrist strap
- Hooked end

SKU
RAP41017

Street Keys




PROFLO

- T-handle
- 5/8" diameter rod
- Steel construction

SKU	Size
PFSK36	36"
PFSK60	60"

Valve Keys



RAPTOR®

- Length: 5'
- Designed to operate a 2" or smaller valve with hand wheel
- 5/8" round carbon steel for center stem
- 18" long T-handle

SKU
RAP41037

Valve Setters



RAPTOR®

- 1,000 lb capacity
- 4"-12"
- One size; fits up to a 12" gate
- Holds gate valve straight and steady during installation

SKU
RAP41038

910 Valve Boxes



PROSELECT

- Tops
- 18"
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  910 valve box lids: IVB910SWR, IVB910WTR

SKU
IVB910TOP

910 Valve Boxes



PROSELECT

- Lids
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  910 valve box tops: IVB910TOP

SKU	Marking
IVB910SWR	Sewer
IVB910WTR	Water

940 Valve Boxes



PROSELECT

- Tops
- 18"
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  940 valve box lids: IVB940DSLID

SKU
IVB940TOP18

940 Valve Boxes



PROSELECT

- Deep skirt lids
- Marking: Water
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU
IVB940DSLID

Cast Iron Frame & Covers - Detail 198



PROSELECT

- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Type	Marking
IVBD198FRM	Frame	-
IVBD198S	Lid	Sewer
IVBD198W	Lid	Water

Cast Iron Screw Valve Box Extensions



PROSELECT

- Screw style valve box extension
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Height Increase
IVBEXT58	14"
IVBEXT59	18"
IVBEXT60	24"

Cast Iron Screw Valve Boxes



PROSELECT

- Bottoms
- For 4" - 12" valves
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  Slip valve box tops: IVBSTS10, IVBSTS16, IVBSTS26

SKU	Size
IVBSBS15	15"
IVBSBS24	24"
IVBSBS36	36"

Cast Iron Screw Valve Boxes



PROSELECT

- Tops
- For 4" - 12" valves
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  Valve box bottoms: IVBSBS15, IVBSBS24, IVBSBS36

SKU	Size
IVBSTS10	10"
IVBSTS16	16"
IVBSTS26	26"

Cast Iron Screw Valve Boxes



PROSELECT

- 3 piece cast iron valve box
- Includes 5 1/4" lid, IVBLID
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Size Top	Size Bottom	Range	Marking
PSVB461SS	10"	15"	19" – 22"	Sewer
PSVB461SW	10"	15"	19" – 22"	Water
PSVB562SW	16"	24"	27" – 37"	Water
PSVB564SW	16"	36"	39" – 50"	Water
PSVB664SW	26"	36"	39" – 60"	Water

Cast Iron Slip Valve Boxes



PROSELECT

- Tops
- For 4" - 12" valves
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  Slip valve box bottoms: IVBABS15, IVBABS24, IVBABS30, IVBABS36, IVBABS48, IVBABS60

SKU	Size
IVBATS10	10"
IVBATS16	16"
IVBATS26	26"

Cast Iron Screw Valve Boxes



PROSELECT

- 3 piece cast iron valve box
- Range: 45" – 54"
- Includes 5 1/4" lid, IVBLIDW
- Can be used with valve box base IVB6BSE or IVB160BSE
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU
PSVBC

Cast Iron Slip Valve Boxes



PROSELECT

- 3 piece cast iron valve box
- Includes 5 1/4" lid, IVBLIDW
- Marking: Water
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Size Top	Size Bottom	Range
PSVB461AW	10"	15"	20" – 24"
PSVB562AW	16"	24"	28" – 38"

Cast Iron Slip Valve Boxes



PROSELECT

- Top with top flange
- 26"
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  Slip valve box bottoms: IVBABS15, IVBABS24, IVBABS30, IVBABS36, IVBABS48, IVBABS60

SKU
IVBATS26TF

Cast Iron Slip Valve Boxes



PROSELECT

- Bottoms
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-106

SKU	Size
IVB24BOTONLY	24"
IVB36BOTONLY	36"

Cast Iron Slip Valve Boxes



PROSELECT

- Bottoms
- For 4" - 12" valves
- 5 1/4" shaft
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  Slip valve box tops: IVBATS10, IVBATS16, IVBATS26

SKU	Size
IVBABS15	15"
IVBABS24	24"
IVBABS30	30"
IVBABS36	36"
IVBABS48	48"
IVBABS60	60"

Cast Iron Valve Boxes



PROSELECT

- Lids
- With 2" skirt
- 5 1/4" lid x 4" deep
- Marking: Water
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU
IVBLID40W

Cast Iron Valve Boxes



PROSELECT

- Lids
- 5 1/4" lid x 3 1/2" deep
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Marking
IVBLIDF	Fire
IVBLIDG	Gas
IVBLIDI	Irrigation
IVBLIDR	Reuse
IVBLIDS	Sewer
IVBLIDW	Water

Cast Iron Valve Boxes



PROSELECT

- Base only
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  3 piece cast iron valve box: PSVBC

SKU
IVB160BSE

Cast Iron Valve Boxes



PROSELECT

- Lids
- 5 1/4" lid x 6" deep
- With ribbed skirt
- Marking: Water
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU
IVBLID6RIBSKT

Cast Iron Valve Boxes



PROSELECT

- Base only
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104
- **Optional accessories:**
  3 piece cast iron valve box: PSVBC

SKU
IVB6BSE

Cast Iron Valve Boxes



PROSELECT

- Risers
- Double hub
- 5" x 5'
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU
IVBSV0088

Cast Iron Valve Boxes - Corpus Christi



PROSELECT

- 2 piece cast iron valve box
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU
PSVB8450

Cast Iron Valve Boxes



PROSELECT

- Risers
- For 5 1/4" lid
- For 4" - 12" valves
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Size
IVBR514G	1"
IVBR514J	1 1/2"
IVBR514K	2"
IVBR514M	3"
IVBR514P	4"
IVBR514U	6"

Cast Iron Valve Boxes - Shorty



PROSELECT

- 3 piece cast iron valve box
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Marking
PSVB165S	Sewer
PSVB165W	Water

Cast Iron Valve Boxes - Tucson



PROSELECT

- 3 piece cast iron valve box
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Marking
PSVBTUCSONPS	Sewer
PSVBTUCSONWV	Water Valve

Monument Clean Out Body & Cover




PROSELECT

- 8" x 4" clean out ring & cover
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Marking
PSVBM1007CO	Clean Out
PSVBM1007SWR	Sewer

Monument Clean Out Body & Cover



PROSELECT

- 8" x 4" clean out locking ring & cover
- Drilled and tapped
- Stainless steel allen head bolt
- All parts other than stainless steel bolts shall be coated on all surfaces with an asphaltic varnish
- Cast iron conforms to ASTM A-48, Grade 30B
- Asphaltic varnish conforms to AWWA C-104

SKU	Marking
PSVBM1007SC	Clean Out
PSVBM1007SCSWR	Sewer





SAFETY »



HYDRANTS »



LOCATING, TESTING & LEAK DETECTION »



POWER TOOLS »



HAND TOOLS »



MEASURING SUPPLIES »



BUILDING MATERIALS & TOOLS »



JOBSITE SUPPLIES »

FERGUSON® WATERWORKS

For our full selection of waterworks products, visit FERGUSON.COM/waterworks



What can we help you find?

Registers 189-195
Diffusers 196-200
Dampers & Accessories 201
Grilles 202-208
Condenser Pads 208
Condensate Pumps 209-210
Thermostats & Accessories 211

Baseboard Registers



PROSELECT

- 1/3" spaced fins set at 20°
- 7/8" margin turnback
- 1 5/8" depth when fully opened
- Ideal for shallow duct installations
- Multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PSBBR783W10U	10" L x 6" W
PSBBR783W14U	14" L x 6" W

Curved Blade Registers



PROSELECT

- 1-way air pattern
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS1CWXP	8" L x 4" W
PS1CW10P	10" L x 4" W
PS1CW10U	10" L x 6" W
PS1CW10X	10" L x 8" W
PS1CW12P	12" L x 4" W
PS1CW12U	12" L x 6" W
PS1CW12X	12" L x 8" W
PS1CW1212	12" L x 12" W
PS1CW14U	14" L x 6" W
PS1CW14X	14" L x 8" W

Baseboard Registers



PROSELECT

- 1/3" spaced fins set at 20°
- Positive volume-control damper
- Steel construction
- Color/Finish: White

SKU	Size
PSBBRD10U	10" L x 6" W
PSBBRD14U	14" L x 6" W

Curved Blade Registers



PROSELECT

- 2-way air pattern
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS2CW10U	10" L x 6" W
PS2CW1010	10" L x 10" W
PS2CW12U	12" L x 6" W
PS2CW12X	12" L x 8" W
PS2CW1212	12" L x 12" W

Curved Blade Registers



PROSELECT

- 3-way air pattern
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS3CWUU	6" L x 6" W
PS3CWXP	8" L x 4" W
PS3CWXU	8" L x 6" W
PS3CWXX	8" L x 8" W
PS3CW10P	10" L x 4" W
PS3CW10U	10" L x 6" W
PS3CW10X	10" L x 8" W
PS3CW1010	10" L x 10" W
PS3CW12P	12" L x 4" W
PS3CW12U	12" L x 6" W
PS3CW12X	12" L x 8" W
PS3CW1212	12" L x 12" W
PS3CW14P	14" L x 4" W
PS3CW14U	14" L x 6" W
PS3CW14X	14" L x 8" W

Curved Blade Registers



PROSELECT

- 1-way air pattern
- For both sidewall and ceiling applications
- Adjustable curved blades
- Multi-shutter damper
- Aluminum construction
- Color/Finish: White

SKU	Size
PSA1CWUU	6" L x 6" W
PSA1CWXP	8" L x 4" W
PSA1CWXX	8" L x 8" W
PSA1CW10P	10" L x 4" W
PSA1CW10U	10" L x 6" W
PSA1CW10X	10" L x 8" W
PSA1CW1010	10" L x 10" W
PSA1CW12P	12" L x 4" W
PSA1CW12U	12" L x 6" W
PSA1CW12X	12" L x 8" W
PSA1CW1212	12" L x 12" W
PSA1CW14U	14" L x 6" W
PSA1CW14X	14" L x 8" W

Curved Blade Registers



PROSELECT

- 4-way air pattern
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Heights of 10" and larger require double valves
- Steel construction
- Color/Finish: White

SKU	Size
PS4CWUU	6" L x 6" W
PS4CWXX	8" L x 8" W
PS4CW1010	10" L x 10" W
PS4CW1212	12" L x 12" W
PS4CW1414	14" L x 14" W

Curved Blade Registers



PROSELECT

- 2-way air pattern
- For both sidewall and ceiling applications
- Adjustable curved blades
- Multi-shutter damper
- Aluminum construction
- Color/Finish: White

SKU	Size
PSA2CWXX	8" L x 8" W
PSA2CW10U	10" L x 6" W
PSA2CW10X	10" L x 8" W
PSA2CW1010	10" L x 10" W
PSA2CW12U	12" L x 6" W
PSA2CW12X	12" L x 8" W
PSA2CW1212	12" L x 12" W
PSA2CW14X	14" L x 8" W

For all your HVAC needs,
visit FERGUSON.COM

FERGUSON



Curved Blade Registers



PROSELECT

- 3-way air pattern
- For both sidewall and ceiling applications
- Adjustable curved blades
- Multi-shutter damper
- Aluminum construction
- Color/Finish: White

SKU	Size
PSA3CWUU	6" L x 6" W
PSA3CWXP	8" L x 4" W
PSA3CWXU	8" L x 6" W
PSA3CWXX	8" L x 8" W
PSA3CW10P	10" L x 4" W
PSA3CW10U	10" L x 6" W
PSA3CW1010	10" L x 10" W
PSA3CW12U	12" L x 6" W
PSA3CW12X	12" L x 8" W
PSA3CW1212	12" L x 12" W
PSA3CW14P	14" L x 4" W
PSA3CW14U	14" L x 6" W
PSA3CW14X	14" L x 8" W
PSA3CW1414	14" L x 14" W

Curved Blade Registers



PROSELECT

- 4-way air pattern
- Individual adjustable curved blades pivot on 0.9" centers
- Opposed blade damper
- Roll formed aluminum blades
- Color/Finish: White

SKU	Size
PSA4COBWUU	6" L x 6" W
PSA4COBWXX	8" L x 8" W
PSA4COBW1010	10" L x 10" W
PSA4COBW1212	12" L x 12" W
PSA4COBW1414	14" L x 14" W

Curved Blade Registers



PROSELECT

- 4-way air pattern
- For both sidewall and ceiling applications
- Adjustable curved blades
- Multi-shutter damper
- Aluminum construction
- Color/Finish: White

SKU	Size
PSA4CWUU	6" L x 6" W
PSA4CWXX	8" L x 8" W
PSA4CW1010	10" L x 10" W
PSA4CW1212	12" L x 12" W
PSA4CW1414	14" L x 14" W
PSA4CW1616	16" L x 16" W

Floor Registers



PROSELECT

- Average 75% for free area
- Toe operated valve control
- Steel construction

SKU	Size	Color/Finish
PSFRDBPX	4" L x 8" W	Brown
PSFRDWP10	4" L x 10" W	White
PSFRDBP12	4" L x 12" W	Brown
PSFRDBP14	4" L x 14" W	Brown
PSFRDBUX	6" L x 8" W	Brown
PSFRDWU10	6" L x 10" W	White
PSFRDBU12	6" L x 12" W	Brown
PSFRDBU14	6" L x 14" W	Brown
PSFRDBXX	8" L x 8" W	Brown
PSFRDBX12	8" L x 12" W	Brown
PSFRDBX14	8" L x 14" W	Brown
PSFRDB10P	10" L x 4" W	Brown
PSFRDB10U	10" L x 6" W	Brown

Non-Metallic Registers



PROSELECT

- 2-way air pattern
- Multi-shutter damper
- For heating or cooling applications
- Engineered polymer construction
- Color/Finish: White

SKU	Size
PSP2WWUU	6" L x 6" W
PSP2WWXP	8" L x 4" W
PSP2WW10X	10" L x 8" W
PSP2WW12U	12" L x 6" W
PSP2WW14U	14" L x 6" W
PSP2WW14X	14" L x 8" W

Non-Metallic Registers



PROSELECT

- 3-way air pattern
- Multi-shutter damper
- For heating or cooling applications
- Engineered polymer construction
- Color/Finish: White

SKU	Size
PSP3WWXP	8" L x 4" W
PSP3WW10U	10" L x 6" W
PSP3WW10X	10" L x 8" W
PSP3WW12U	12" L x 6" W
PSP3WW14X	14" L x 8" W

Non-Metallic Registers



PROSELECT

- 4-way air pattern
- Multi-shutter damper
- For heating or cooling applications
- Engineered polymer construction
- Color/Finish: White

SKU	Size
PSP4WWUU	6" L x 6" W
PSP4WWXX	8" L x 8" W
PSP4WW1010	10" L x 10" W
PSP4WW1212	12" L x 12" W

Sidewall Registers



PROSELECT

- Adjustable straight fins
- Stamped face margins
- Multi-shutter damper
- Aluminum construction
- Color/Finish: White

SKU	Size
PSAASWUU	6" L x 6" W
PSAASWXP	8" L x 4" W
PSAASWXU	8" L x 6" W
PSAASWXX	8" L x 8" W
PSAASW10P	10" L x 4" W
PSAASW10U	10" L x 6" W
PSAASW10X	10" L x 8" W
PSAASW1010	10" L x 10" W
PSAASW12P	12" L x 4" W
PSAASW12U	12" L x 6" W
PSAASW12X	12" L x 8" W
PSAASW1212	12" L x 12" W
PSAASW14P	14" L x 4" W
PSAASW14U	14" L x 6" W
PSAASW14X	14" L x 8" W
PSAASW1410	14" L x 10" W
PSAASW1414	14" L x 14" W
PSAASW16P	16" L x 4" W
PSAASW16U	16" L x 6" W
PSAASW16X	16" L x 8" W
PSAASW1610	16" L x 10" W
PSAASW1616	16" L x 16" W
PSAASW18U	18" L x 6" W
PSAASW18X	18" L x 8" W
PSAASW1810	18" L x 10" W
PSAASW1812	18" L x 12" W
PSAASW1818	18" L x 18" W
PSAASW20P	20" L x 4" W
PSAASW20U	20" L x 6" W
PSAASW20X	20" L x 8" W
PSAASW2020	20" L x 20" W
PSAASW24P	24" L x 4" W
PSAASW24U	24" L x 6" W
PSAASW24X	24" L x 8" W
PSAASW2412	24" L x 12" W
PSAASW2414	24" L x 14" W
PSAASW28U	28" L x 6" W
PSAASW28X	28" L x 8" W
PSAASW30U	30" L x 6" W
PSAASW30X	30" L x 8" W

Sidewall Registers



PROSELECT

- Steel vertical blades
- Extruded airfoil deflection blades
- Opposed blade damper
- Constructed with steel border
- Color/Finish: White

SKU	Size
PSVOBWUU	6" L x 6" W
PSVOBWXU	8" L x 6" W
PSVOBWXX	8" L x 8" W
PSVOBW10U	10" L x 6" W
PSVOBW1010	10" L x 10" W
PSVOBW12U	12" L x 6" W
PSVOBW12X	12" L x 8" W
PSVOBW1212	12" L x 12" W
PSVOBW14U	14" L x 6" W
PSVOBW14X	14" L x 8" W
PSVOBW1414	14" L x 14" W
PSVOBW16U	16" L x 6" W
PSVOBW16X	16" L x 8" W
PSVOBW18U	18" L x 6" W
PSVOBW18X	18" L x 8" W
PSVOBW20U	20" L x 6" W
PSVOBW20X	20" L x 8" W
PSVOBW24U	24" L x 6" W
PSVOBW24X	24" L x 8" W

Sidewall Registers



PROSELECT

- Airfoil deflection blades
- Aluminum construction
- With opposed blade damper
- PSAVHW1010, PSAVHW1212 and PSAVHW14X: without opposed blade damper
- Color/Finish: White

SKU	Size
PSAVHOBWUU	6" L x 6" W
PSAVHOBWXU	8" L x 6" W
PSAVHOBWXX	8" L x 8" W
PSAVHOBW10U	10" L x 6" W
PSAVHOBW10X	10" L x 8" W
PSAVHW1010	10" L x 10" W
PSAVHOBW1010	10" L x 10" W
PSAVHOBW12U	12" L x 6" W
PSAVHOBW12X	12" L x 8" W
PSAVHW1212	12" L x 12" W
PSAVHOBW1212	12" L x 12" W
PSAVHOBW14U	14" L x 6" W
PSAVHW14X	14" L x 8" W
PSAVHOBW14X	14" L x 8" W
PSAVHOBW16U	16" L x 6" W
PSAVHOBW16X	16" L x 8" W
PSAVHOBW18U	18" L x 6" W
PSAVHOBW18X	18" L x 8" W
PSAVHOBW20U	20" L x 6" W
PSAVHOBW24U	24" L x 6" W
PSAVHOBW24X	24" L x 8" W

Sidewall Registers



PROSELECT

- Vertical adjustable face bars
- Horizontal multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PSVAFWUU	6" L x 6" W
PSVAFWXP	8" L x 4" W
PSVAFWXU	8" L x 6" W
PSVAFWXX	8" L x 8" W
PSVAFW10P	10" L x 4" W
PSVAFW10U	10" L x 6" W
PSVAFW10X	10" L x 8" W
PSVAFW1010	10" L x 10" W
PSVAFW12P	12" L x 4" W
PSVAFW12U	12" L x 6" W
PSVAFW12X	12" L x 8" W
PSVAFW1210	12" L x 10" W
PSVAFW1212	12" L x 12" W
PSVAFW14P	14" L x 4" W
PSVAFW14U	14" L x 6" W
PSVAFW14X	14" L x 8" W
PSVAFW1410	14" L x 10" W
PSVAFW1414	14" L x 14" W
PSVAFW16P	16" L x 4" W
PSVAFW16U	16" L x 6" W
PSVAFW16X	16" L x 8" W
PSVAFW1612	16" L x 12" W
PSVAFW1616	16" L x 16" W
PSVAFW18U	18" L x 6" W
PSVAFW18X	18" L x 8" W
PSVAFW1810	18" L x 10" W
PSVAFW1818	18" L x 18" W
PSVAFW20U	20" L x 6" W
PSVAFW20X	20" L x 8" W
PSVAFW2010	20" L x 10" W
PSVAFW2012	20" L x 12" W
PSVAFW2014	20" L x 14" W
PSVAFW2020	20" L x 20" W
PSVAFW24U	24" L x 6" W
PSVAFW24X	24" L x 8" W
PSVAFW2424	24" L x 24" W
PSVAFW30U	30" L x 6" W
PSVAFW3010	30" L x 10" W
PSVAFW3012	30" L x 12" W
PSVAFW3018	30" L x 18" W

Sidewall/Ceiling Registers



PROSELECT

- 1-way curved blade
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS1CWMLXP	8" L x 4" W
PS1CWML10U	10" L x 6" W
PS1CWML12U	12" L x 6" W
PS1CWML12X	12" L x 8" W
PS1CWML1212	12" L x 12" W
PS1CWML14X	14" L x 8" W

Sidewall/Ceiling Registers



PROSELECT

- 1-way air pattern
- Steel construction
- Color/Finish: White

SKU	Size
PS1WWXP	8" L x 4" W
PS1WW10U	10" L x 6" W
PS1WW12U	12" L x 6" W
PS1WW14U	14" L x 6" W
PS1WW16U	16" L x 6" W

Sidewall/Ceiling Registers



PROSELECT

- 2-way air pattern
- 1/3" spaced fins at 20°
- For both sidewall and ceiling applications
- Ideal for shallow duct installation
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS2W3WUP	6" L x 4" W
PS2W3WUU	6" L x 6" W
PS2W3WXP	8" L x 4" W
PS2W3WXU	8" L x 6" W
PS2W3WXX	8" L x 8" W
PS2W3W10P	10" L x 4" W
PS2W3W10U	10" L x 6" W
PS2W3W10X	10" L x 8" W
PS2W3W12P	12" L x 4" W
PS2W3W12U	12" L x 6" W
PS2W3W12X	12" L x 8" W
PS2W3W1210	12" L x 10" W
PS2W3W1212	12" L x 12" W
PS2W3W14P	14" L x 4" W
PS2W3W14U	14" L x 6" W
PS2W3W14X	14" L x 8" W
PS2W3W16U	16" L x 6" W
PS2W3W16X	16" L x 8" W
PS2W3W24U	24" L x 6" W
PS2W3W30U	30" L x 6" W

Sidewall/Ceiling Registers



PROSELECT

- 2-way air pattern
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- 1/2" spaced fins at 40°
- Metal lever damper operator
- Steel construction
- Color/Finish: White

SKU	Size
PS2WWMLXP	8" L x 4" W
PS2WWMLXU	8" L x 6" W
PS2WWML10P	10" L x 4" W
PS2WWML10U	10" L x 6" W
PS2WWML10X	10" L x 8" W
PS2WWML12P	12" L x 4" W
PS2WWML12U	12" L x 6" W
PS2WWML12X	12" L x 8" W
PS2WWML14P	14" L x 4" W
PS2WWML14U	14" L x 6" W
PS2WWML14X	14" L x 8" W
PS2WWML16U	16" L x 6" W

Sidewall/Ceiling Registers



PROSELECT

- 3-way air pattern
- 1/3" spaced fins at 20°
- For both sidewall and ceiling applications
- Ideal for shallow duct installations
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS3W3WXP	8" L x 4" W
PS3W3W10U	10" L x 6" W
PS3W3W12P	12" L x 4" W

Sidewall/Ceiling Registers



PROSELECT

- 1/2" spaced fins at 40°
- For both sidewall and ceiling applications
- Ideal for shallow duct installation
- 2-way air pattern
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS2WWUP	6" L x 4" W
PS2WWUU	6" L x 6" W
PS2WWXP	8" L x 4" W
PS2WWXU	8" L x 6" W
PS2WWXX	8" L x 8" W
PS2WW10P	10" L x 4" W
PS2WW10S	10" L x 5" W
PS2WW10U	10" L x 6" W
PS2WW10X	10" L x 8" W
PS2WW1010	10" L x 10" W
PS2WW12P	12" L x 4" W
PS2WW12S	12" L x 5" W
PS2WW12U	12" L x 6" W
PS2WW12X	12" L x 8" W
PS2WW1210	12" L x 10" W
PS2WW1212	12" L x 12" W
PS2WW14P	14" L x 4" W
PS2WW14U	14" L x 6" W
PS2WW14X	14" L x 8" W
PS2WW1410	14" L x 10" W
PS2WW16P	16" L x 4" W
PS2WW16U	16" L x 6" W
PS2WW16X	16" L x 8" W
PS2WW18U	18" L x 6" W
PS2WW18X	18" L x 8" W
PS2WW20U	20" L x 6" W
PS2WW20X	20" L x 8" W
PS2WW24U	24" L x 6" W
PS2WW24X	24" L x 8" W

Sidewall/Ceiling Registers



PROSELECT

- 1/2" spaced fins at 40°
- For both sidewall and ceiling applications
- Ideal for shallow duct installation
- 3-way air pattern
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS3WWUU	6" L x 6" W
PS3WWXP	8" L x 4" W
PS3WWXU	8" L x 6" W
PS3WWXX	8" L x 8" W
PS3WW10P	10" L x 4" W
PS3WW10U	10" L x 6" W
PS3WW10X	10" L x 8" W
PS3WW1010	10" L x 10" W
PS3WW12P	12" L x 4" W
PS3WW12U	12" L x 6" W
PS3WW12X	12" L x 8" W
PS3WW1212	12" L x 12" W
PS3WW14P	14" L x 4" W
PS3WW14U	14" L x 6" W
PS3WW14X	14" L x 8" W
PS3WW1410	14" L x 10" W
PS3WW1414	14" L x 14" W
PS3WW16X	16" L x 8" W

Sidewall/Ceiling Registers



PROSELECT

- 3-way air pattern
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- 1/2" spaced fins at 40°
- Metal lever damper operator
- Steel construction
- Color/Finish: White

SKU	Size
PS3WWMLXP	8" L x 4" W
PS3WWMLXX	8" L x 8" W
PS3WWML10P	10" L x 4" W
PS3WWML10U	10" L x 6" W
PS3WWML12U	12" L x 6" W
PS3WWML12X	12" L x 8" W
PS3WWML14U	14" L x 6" W
PS3WWML14X	14" L x 8" W
PS3WWML1410	14" L x 10" W

Sidewall/Ceiling Registers



PROSELECT

- 4-way curved blade
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Metal lever damper operator
- Steel welded curved blade construction
- Steel construction
- Color/Finish: White

SKU	Size
PS4CWMLXX	8" L x 8" W
PS4CWML1010	10" L x 10" W
PS4CWML1212	12" L x 12" W

Sidewall/Ceiling Registers



PROSELECT

- 4-way air pattern
- 1/2" spaced fins at 40°
- For both sidewall and ceiling applications
- Integral multi-shutter damper
- Metal lever damper operator
- All-steel welded construction
- Steel construction
- Color/Finish: White

SKU	Size
PS4WWMLUU	6" L x 6" W
PS4WWMLXX	8" L x 8" W
PS4WWML1010	10" L x 10" W
PS4WWML1212	12" L x 12" W
PS4WWML1414	14" L x 14" W

Sidewall/Ceiling Registers



PROSELECT

- 4-way air pattern
- 1/2" spaced fins at 40°
- For both sidewall and ceiling applications
- Ideal for shallow duct installation
- Integral multi-shutter damper
- Steel construction
- Color/Finish: White

SKU	Size
PS4WWUU	6" L x 6" W
PS4WWXX	8" L x 8" W
PS4WW1010	10" L x 10" W
PS4WW1212	12" L x 12" W
PS4WW1414	14" L x 14" W
PS4WW1616	16" L x 16" W
PS4WW1818	18" L x 18" W

Visit our Private Label brand websites:

FNW™ FNW.COM

MONOGRAM BRASS® MONOGRAMBRASS.COM

PROFLO® PROFLO.COM

PROSELECT™ PROSELECTPRODUCTS.COM

RAPTOR® RAPTORTOOL.COM

Baseboard Diffusers



PROSELECT

- Lever operated multi-shutter damper
- All steel welded construction
- **Optional accessories:**
  Baseboard return grille: PSBBRW18

SKU	Length	Color/Finish
PSBBDW15	15"	White
PSBBDW18	18"	White
PSBBDB18	18"	Brown

Ceiling Diffusers



PROSELECT

- 3-way air diffusion
- Face mount
- For sidewall or ceiling application
- Cores flush with margin
- Built-in opposed blade damper
- Inconspicuous fingertip lever for air volume control
- Aluminum construction
- Color/Finish: White

SKU	Size
PSA3WUU	6" L x 6" W
PSA3WXX	8" L x 8" W
PSA3W1010	10" L x 10" W
PSA3W1212	12" L x 12" W

Ceiling Diffusers



PROSELECT

- 4-way air diffusion
- Face mount
- For sidewall or ceiling application
- Cores flush with margin
- Built-in opposed blade damper
- Inconspicuous fingertip lever for air volume control
- Aluminum construction
- Color/Finish: White

SKU	Size
PSA4WUU	6" L x 6" W
PSA4WXX	8" L x 8" W
PSA4W1010	10" L x 10" W
PSA4W1212	12" L x 12" W
PSA4W1414	14" L x 14" W

Ceiling Diffusers



PROSELECT

- Highly flexible directional mounting applications ceiling diffuser
- 1 or 2 way opposite, 2 way corner, 3 or 4 way air patterns
- Cores have spring loaded latches
- Color/Finish: White

SKU	Size
PSAMODOBXX	8" L x 8" W
PSAMODOB1010	10" L x 10" W
PSAMODOB1212	12" L x 12" W
PSAMODOB1414	14" L x 14" W
PSAMODOB1616	16" L x 16" W
PSAMODOB2020	20" L x 20" W

Ceiling Diffusers



PROSELECT

- 4-way air pattern
- 12" L x 12" W
- Removable core for concealed mounting
- Built-in opposed blade damper
- Surface mount
- Aluminum construction
- Color/Finish: White

SKU
PSSQCDW12

Ceiling Diffusers for T-Bar



PROSELECT

- 8" L x 8" W
- Highly flexible directional mounting applications ceiling diffuser
- 1 or 2 way opposite, 2 way corner, 3 or 4 way air patterns
- Cores have spring loaded latches
- Square to round back
- Aluminum construction
- Color/Finish: White

SKU
PSAMCTBXX

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Three cone design
- Quick-release inner assembly
- Includes a foil insulated backpan and accepts 6" – 14" field supplied inlet collars
- Steel construction
- Color/Finish: White

SKU
PSHVD32424

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Removable air diffusion panel
- 360° air diffusion pattern
- Steel construction
- Color/Finish: White

SKU	Neck Size
PSSPDU	6"
PSSPDX	8"
PSSPD10	10"
PSSPD12	12"
PSSPD14	14"

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Insulated
- 2" standard inlet collar
- 360° uniform air pattern
- Steel construction
- Color/Finish: White

SKU	Neck Size
PSHVD3IU	6"
PSHVD3IX	8"
PSHVD3I10	10"
PSHVD3I12	12"

Ceiling Diffusers for T-Bar



PROSELECT

- 4-way pattern
- 24" L x 24" W
- Core has spring loaded latches
- Includes a foil insulated backpan and accepts 6" – 12" field supplied inlet collars
- Steel construction
- Color/Finish: White

SKU
PSLFSI2424

Ceiling Diffusers for T-Bar




PROSELECT

- 24" L x 24" W
- Insulated
- Removable air diffusion panel
- Uniform 360° radiant air diffusion pattern
- Steel construction
- Color/Finish: White

SKU
PSSPDI2424

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Perforated supply
- Non insulated
- Curved blade pattern controllers mounted in the neck of the diffuser
- Pattern controllers are adjustable from a horizontal to vertical discharge pattern
- Face is hinged for quick access to the pattern controllers
- Steel construction, with seismic/earthquake tabs
- Color/Finish: White

SKU	Neck Size
PSPCBSSTU	6"
PSPCBSSTX	8"
PSPCBSST10	10"
PSPCBSST12	12"
PSPCBSST14	14"
PSPCBSST16	16"

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Fiberglass plenum designed to allow field installation of the inlet collar
- 360° air diffusion pattern
- Color/Finish: White with black interior

SKU	Type
PSPFBR	Return
PSPFBS	Supply

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Shallow back
- Perforated supply
- 1, 2, 3, or 4 way air flow
- Face is hinged for quick access to pattern controllers
- Steel construction
- Color/Finish: White

SKU	Neck Size
PSPSBSSTU	6"
PSPSBSSTX	8"
PSPSBSST10	10"
PSPSBSST12	12"

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Insulated
- 1, 2, 3, or 4 way air flow
- Face is hinged for quick access to pattern controllers
- 1" R6 ductboard fiberglass backpan accepts inlet tab collars by others
- Steel construction
- Color/Finish: White

SKU
PSPSI

Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Insulated
- Fiberglass plenum designed to allow field installation of the inlet collar
- 360° air diffusion pattern
- Diffuser face is non-removable with pattern controls
- Color/Finish: White with black interior

SKU	Type
PSPRDI2424	Return
PSPSDI2424	Supply

Ceiling Return Diffusers for T-Bar




PROSELECT

- 24" L x 24" W
- Face is hinged
- Steel construction, with seismic/earthquake tabs
- Perforated return
- Non insulated
- Color/Finish: White

SKU	Neck Size
PSPCBRSTU	6"
PSPCBRSTX	8"
PSPCBRST10	10"
PSPCBRST12	12"
PSPCBRST14	14"
PSPCBRST16	16"
PSPCBRST18	18"

Fiberglass Backpans



PROSELECT

- Formed backpan with foil backing
- R6 insulation

SKU
PSFGBP

Floor Diffusers



PROSELECT

- Multi-angled fin setting
- Foot-operated damper
- Steel construction

SKU	Size	Color/Finish
PSFDBU14	6" L x 14" W	Brown
PSFDWU14	6" L x 14" W	White
PSFDBPX	8" L x 4" W	Brown
PSFDWPX	8" L x 4" W	White
PSFDBX14	8" L x 14" W	Brown
PSFDWX14	8" L x 14" W	White
PSFDBK10	10" L x 2" W	Brown
PSFDWK10	10" L x 2" W	White
PSFDBP10	10" L x 4" W	Brown
PSFDWP10	10" L x 4" W	White
PSFDBU10	10" L x 6" W	Brown
PSFDWU10	10" L x 6" W	White
PSFDBK12	12" L x 2" W	Brown
PSFDWK12	12" L x 2" W	White
PSFDBP12	12" L x 4" W	Brown
PSFDWP12	12" L x 4" W	White
PSFDBU12	12" L x 6" W	Brown
PSFDWU12	12" L x 6" W	White
PSFDBK14	14" L x 2" W	Brown
PSFDWK14	14" L x 2" W	White
PSFDBP14	14" L x 4" W	Brown
PSFDWP14	14" L x 4" W	White

Floor Diffusers



PROSELECT

- Made for high traffic areas
- Foot-operated damper
- Multi-angle fin settings
- Steel construction

SKU	Size	Color/Finish
PSDFDBK10	10" L x 2" W	Brown
PSDFDBP10	10" L x 4" W	Brown
PSDFDBU10	10" L x 6" W	Brown
PSDFDWU10	10" L x 6" W	White
PSDFDBK12	12" L x 2" W	Brown
PSDFDBP12	12" L x 4" W	Brown
PSDFDBU12	12" L x 6" W	Brown
PSDFDBK14	14" L x 2" W	Brown
PSDFDBP14	14" L x 4" W	Brown
PSDFDBU14	14" L x 6" W	Brown
PSDFDWU14	14" L x 6" W	White

High Volume Ceiling Diffusers



PROSELECT

- Adjustable dampers provide directional airflow or closure capabilities
- Mounting holes provided for easy installation
- Steel construction
- Color/Finish: White

SKU	Size
PSCDBXW1414	14" L x 14" W
PSCDBXW1616	16" L x 16" W
PSCDBXW1818	18" L x 18" W
PSCDBXW2020	20" L x 20" W
PSCDBXW2222	22" L x 22" W
PSCDBXW2424	24" L x 24" W

High Volume Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- 2" standard inlet collar
- 360° uniform air pattern
- Steel construction, non insulated
- Package Quantity: 2
- Color/Finish: White

SKU	Neck Size
PSHVDU	6"
PSHVDX	8"
PSHVD10	10"
PSHVD12	12"
PSHVD14	14"

High Volume Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- 2" standard inlet collar
- 360° uniform air pattern
- Steel construction
- Color/Finish: White

SKU	Neck Size
PSHVD3U	6"
PSHVD3X	8"
PSHVD310	10"
PSHVD312	12"
PSHVD314	14"

High Volume Ceiling Diffusers for T-Bar



PROSELECT

- 24" L x 24" W
- Insulated foil back with butterfly damper
- Steel construction
- Color/Finish: White

SKU	Neck Size
PSHVD3IBDU	6"
PSHVD3IBDX	8"
PSHVD3IBD10	10"
PSHVD3IBD12	12"

Inlet Collars for T-Bar Diffusers



PROSELECT

- 1 1/4" high collar
- Steel construction
- **Required accessories:**
  Push pins: PSSIPP

SKU	Size
PSSICRU	6"
PSSICRW	7"
PSSICRX	8"
PSSICR10	10"
PSSICR12	12"
PSSICR14	14"

Push Pins for Inlet Collars



PROSELECT

- Attaches PSSICR collar
- Package Quantity: 100

SKU
PSSIPP

Lock Slide Sets



PROSELECT

- Includes: Washer, handle, wing nut and 5/16" bearings
- Easily mounts onto bearing edge of existing dampers
- Acceptable for use on dampers up to 22 gauge

SKU	Bearings
PSLSRS1B	1
PSLSRS2B	2

Register Sets



PROSELECT

- Washer Only
- Easily mounts onto bearing edge of existing dampers
- Acceptable for use on dampers up to 22 gauge

SKU
PSLSWSHR

Round Ceiling Diffusers



PROSELECT

- High induction/capacity 2 cone diffuser
- Low profile flush face
- Color/Finish: White

SKU	Size
PSRADWX	8"
PSRADW10	10"
PSRADW12	12"
PSRADW14	14"
PSRADW16	16"

Round Ceiling Diffusers



PROSELECT

- Concentric rings deflect air stream 360°
- Steel construction
- Color/Finish: White

SKU	Size
PSRCDWU	6"
PSRCDWX	8"
PSRCDW10	10"
PSRCDW12	12"
PSRCDW14	14"

Spiral Duct Diffusers




PROSELECT

- Front blades are vertical
- Units can be easily installed in round duct diameters 10" – 48"
- Integral gasket seals grille tightly to duct
- Includes built-in extractor for accurate balancing and uniform air flow
- Galvanized steel double deflection

SKU	Size
PSGDDSD14P	14" L x 4" W
PSGDDSD14U	14" L x 6" W
PSGDDSD18P	18" L x 4" W
PSGDDSD18U	18" L x 6" W
PSGDDSD26U	26" L x 6" W

T-Bar Plaster Frames



PROSELECT

- 24" L x 24" W
- Includes 8 screws and angle brackets
- Aluminum construction
- Color/Finish: White

SKU
PSSMF2424

Dampers



PROSELECT

- Adjustable butterfly damper
- Removable handle
- Color/Finish: Brown

SKU	Size
PSDBU	6"
PSDBW	7"
PSDBX	8"
PSDB10	10"
PSDB12	12"
PSDB14	14"

Dampers



PROSELECT

- Size: 6"
- For use in round duct
- Kit Includes: damper blade with two bearings, handle, washer and wing nut
- Ships assembled

SKU
PSIDU

Dampers



PROSELECT

- Steel vertical blades
- Regulates the flow of air inside air handling equipment
- Opposed blade damper

SKU	Size
PSOBDUU	6" L x 6" W
PSOBDXX	8" L x 8" W
PSOBD1010	10" L x 10" W
PSOBD1212	12" L x 12" W
PSOBD1414	14" L x 14" W

Dampers



PROSELECT

- 5 radial style blades
- Blades are adjusted through diffuser face
- Mounting tabs permit attachment to ceiling diffusers
- Coated steel construction

SKU	Size
PSRADU	6"
PSRADX	8"
PSRAD10	10"
PSRAD12	12"

Dampers



PROSELECT

- Controls air volume evenly
- Removable knob operator for adjustment from closed to fully open
- Steel construction
- Color/Finish: Brown

SKU	Size
PSRDRU	6"
PSRDRX	8"
PSRDR10	10"
PSRDR12	12"
PSRDR14	14"

Duct Rings



PROSELECT

- For use with round ceiling diffusers series PSRCD
- Provides for easy attachment of round duct work
- Steel construction
- Color/Finish: Brown

SKU	Size
PSDRU	6"
PSDRX	8"
PSDR10	10"
PSDR12	12"
PSDR14	14"

Baseboard Return Grilles



PROSELECT

- 1/2" spaced fins set at 40°
- 7/8" margin turnback
- Steel construction
- Color/Finish: White

SKU	Size
PSRG78W14X	14" L x 8" W
PSRG78W30X	30" L x 8" W

Baseboard Return Grilles



PROSELECT

- 1/3" spaced fins set at 20°
- Steel construction
- Color/Finish: White

SKU	Size
PSBRG3W14U	14" L x 6" W
PSBRG3W30U	30" L x 6" W

Baseboard Return Grilles



PROSELECT

- 1-way air pattern
- 7/8" margin turnback
- 1/3" spaced fins at 20°
- Steel construction
- Color/Finish: White

SKU	Size
PSRG783W12U	12" L x 6" W
PSRG783W12X	12" L x 8" W
PSRG783W14U	14" L x 6" W
PSRG783W14X	14" L x 8" W
PSRG783W16X	16" L x 8" W
PSRG783W20X	20" L x 8" W
PSRG783W24U	24" L x 6" W
PSRG783W24X	24" L x 8" W
PSRG783W2412	24" L x 12" W
PSRG783W30U	30" L x 6" W
PSRG783W30X	30" L x 8" W
PSRG783W3010	30" L x 10" W
PSRG783W3012	30" L x 12" W
PSRG783W36U	36" L x 6" W
PSRG783W36X	36" L x 8" W

Baseboard Return Grilles



PROSELECT

- 18" L x 4.47" W
- Return air grille for baseboard diffuser series PSBBD
- Steel construction
- Color/Finish: White

SKU
PSBBRW18

Fixed Bar Filter Grilles



PROSELECT

- 3/4" spaced fins set at 35°
- Flush, removable face, concealed latches and hinges
- Steel construction
- Color/Finish: White

SKU	Size
PSFBFG2W1010	10" L x 10" W
PSFBFG2W1212	12" L x 12" W
PSFBFG2W1414	14" L x 14" W
PSFBFG2W1420	14" L x 20" W
PSFBFG2W1424	14" L x 24" W
PSFBFG2W1425	14" L x 25" W
PSFBFG2W1430	14" L x 30" W
PSFBFG2W1616	16" L x 16" W
PSFBFG2W1625	16" L x 25" W
PSFBFG2W1816	18" L x 16" W
PSFBFG2W1818	18" L x 18" W
PSFBFG2W2010	20" L x 10" W
PSFBFG2W2012	20" L x 12" W
PSFBFG2W2014	20" L x 14" W
PSFBFG2W2016	20" L x 16" W
PSFBFG2W2020	20" L x 20" W
PSFBFG2W2025	20" L x 25" W
PSFBFG2W2030	20" L x 30" W
PSFBFG2W2410	24" L x 10" W
PSFBFG2W2412	24" L x 12" W
PSFBFG2W2414	24" L x 14" W
PSFBFG2W2416	24" L x 16" W
PSFBFG2W2420	24" L x 20" W
PSFBFG2W2424	24" L x 24" W
PSFBFG2W2512	25" L x 12" W
PSFBFG2W2514	25" L x 14" W
PSFBFG2W2516	25" L x 16" W
PSFBFG2W2520	25" L x 20" W
PSFBFG2W3010	30" L x 10" W
PSFBFG2W3012	30" L x 12" W
PSFBFG2W3014	30" L x 14" W
PSFBFG2W3016	30" L x 16" W
PSFBFG2W3018	30" L x 18" W
PSFBFG2W3020	30" L x 20" W
PSFBFG2W3024	30" L x 24" W
PSFBFG2W3614	36" L x 14" W
PSFBFG2W4020	40" L x 20" W

Floor Return Air Grilles




PROSELECT

- Average 75% for free area
- Steel construction
- Color/Finish: Brown

SKU	Size
PSFRGBP10	4" L x 10" W
PSFRGBP12	4" L x 12" W
PSFRGBP14	4" L x 14" W
PSFRGBP30	4" L x 30" W
PSFRGBU10	6" L x 10" W
PSFRGBU12	6" L x 12" W
PSFRGBU14	6" L x 14" W
PSFRGBU18	6" L x 18" W
PSFRGBU20	6" L x 20" W
PSFRGBU24	6" L x 24" W
PSFRGBU30	6" L x 30" W
PSFRGBX10	8" L x 10" W
PSFRGBX12	8" L x 12" W
PSFRGBX14	8" L x 14" W
PSFRGBX16	8" L x 16" W
PSFRGBX20	8" L x 20" W
PSFRGBX24	8" L x 24" W
PSFRGBX30	8" L x 30" W
PSFRGB1010	10" L x 10" W
PSFRGB1012	10" L x 12" W
PSFRGB1014	10" L x 14" W
PSFRGB1016	10" L x 16" W
PSFRGB1020	10" L x 20" W
PSFRGB1024	10" L x 24" W
PSFRGB1030	10" L x 30" W
PSFRGB1212	12" L x 12" W
PSFRGB1214	12" L x 14" W
PSFRGB1220	12" L x 20" W
PSFRGB1224	12" L x 24" W
PSFRGB1230	12" L x 30" W
PSFRGB14P	14" L x 4" W
PSFRGB1414	14" L x 14" W
PSFRGB1420	14" L x 20" W
PSFRGB1424	14" L x 24" W
PSFRGB1430	14" L x 30" W
PSFRGB1616	16" L x 16" W
PSFRGB1620	16" L x 20" W
PSFRGB1624	16" L x 24" W
PSFRGB2020	20" L x 20" W
PSFRGB36U	36" L x 6" W

Return Air Filter Grilles



PROSELECT

- 1/2" x 1/2" x 1/2" cube core
- Concealed mounting
- 90% maximum free area
- Hinged face with 1/4 turn latches for quick filter changes
- Aluminum construction
- Color/Finish: White

SKU	Size
PSAEC5FG2014	20" L x 14" W
PSAEC5FG2412	24" L x 12" W
PSAEC5FG2414	24" L x 14" W
PSAEC5FG2420	24" L x 20" W
PSAEC5FG3014	30" L x 14" W
PSAEC5FG3020	30" L x 20" W
PSAEC5FG3024	30" L x 24" W

Return Air Filter Grilles



PROSELECT

- 0.666" spaced fins at 45°
- Concealed mounting
- Hinged face with 1/4 turn latches for quick filter changes
- Aluminum construction
- Color/Finish: White

SKU	Size
PSAH45FGW1010	10" L x 10" W
PSAH45FGW1212	12" L x 12" W
PSAH45FGW1224	12" L x 24" W
PSAH45FGW14X	14" L x 8" W
PSAH45FGW1414	14" L x 14" W
PSAH45FGW1818	18" L x 18" W
PSAH45FGW1824	18" L x 24" W
PSAH45FGW2020	20" L x 20" W
PSAH45FGW2025	20" L x 25" W
PSAH45FGW2412	24" L x 12" W
PSAH45FGW2418	24" L x 18" W
PSAH45FGW2430	24" L x 30" W
PSAH45FGW3018	30" L x 18" W

Return Air Filter Grilles



PROSELECT

- 1/3" spaced fins set at 20°
- Removable face
- Equipped with adjustable filter retainers
- Steel construction
- Color/Finish: White

SKU	Size
PSFG3W1212	12" L x 12" W
PSFG3W14U	14" L x 6" W
PSFG3W1414	14" L x 14" W
PSFG3W1420	14" L x 20" W
PSFG3W1424	14" L x 24" W
PSFG3W1425	14" L x 25" W
PSFG3W1616	16" L x 16" W
PSFG3W1620	16" L x 20" W
PSFG3W1625	16" L x 25" W
PSFG3W1818	18" L x 18" W
PSFG3W2012	20" L x 12" W
PSFG3W2014	20" L x 14" W
PSFG3W2016	20" L x 16" W
PSFG3W2020	20" L x 20" W
PSFG3W2025	20" L x 25" W
PSFG3W2412	24" L x 12" W
PSFG3W2424	24" L x 24" W
PSFG3W2520	25" L x 20" W
PSFG3W3014	30" L x 14" W

Return Air Filter Grilles



PROSELECT

- 1/2" spaced fins at 40°
- Removable face with concealed latches and hinges
- Steel construction
- Color/Finish: White

SKU	Size
PSFGW10U	10" L x 6" W
PSFGW1010	10" L x 10" W
PSFGW1020	10" L x 20" W
PSFGW12U	12" L x 6" W
PSFGW1212	12" L x 12" W
PSFGW1220	12" L x 20" W
PSFGW1224	12" L x 24" W
PSFGW1230	12" L x 30" W
PSFGW1236	12" L x 36" W
PSFGW14X	14" L x 8" W
PSFGW1410	14" L x 10" W
PSFGW1412	14" L x 12" W
PSFGW1414	14" L x 14" W
PSFGW1420	14" L x 20" W
PSFGW1424	14" L x 24" W
PSFGW1425	14" L x 25" W
PSFGW1430	14" L x 30" W
PSFGW1612	16" L x 12" W
PSFGW1616	16" L x 16" W
PSFGW1620	16" L x 20" W
PSFGW1624	16" L x 24" W
PSFGW1625	16" L x 25" W
PSFGW1630	16" L x 30" W
PSFGW18X	18" L x 8" W
PSFGW1812	18" L x 12" W
PSFGW1818	18" L x 18" W
PSFGW1824	18" L x 24" W
PSFGW1830	18" L x 30" W
PSFGW20X	20" L x 8" W
PSFGW2010	20" L x 10" W
PSFGW2012	20" L x 12" W
PSFGW2014	20" L x 14" W
PSFGW2016	20" L x 16" W

SKU	Size
PSFGW2020	20" L x 20" W
PSFGW2024	20" L x 24" W
PSFGW2025	20" L x 25" W
PSFGW2030	20" L x 30" W
PSFGW2040	20" L x 40" W
PSFGW2222	22" L x 22" W
PSFGW24X	24" L x 8" W
PSFGW2410	24" L x 10" W
PSFGW2412	24" L x 12" W
PSFGW2414	24" L x 14" W
PSFGW2416	24" L x 16" W
PSFGW2418	24" L x 18" W
PSFGW2420	24" L x 20" W
PSFGW2424	24" L x 24" W
PSFGW2430	24" L x 30" W
PSFGW2436	24" L x 36" W
PSFGW2514	25" L x 14" W
PSFGW2516	25" L x 16" W
PSFGW2520	25" L x 20" W
PSFGW2525	25" L x 25" W
PSFGW2532	25" L x 32" W
PSFGW30X	30" L x 8" W
PSFGW3010	30" L x 10" W
PSFGW3012	30" L x 12" W
PSFGW3014	30" L x 14" W
PSFGW3016	30" L x 16" W
PSFGW3018	30" L x 18" W
PSFGW3020	30" L x 20" W
PSFGW3024	30" L x 24" W
PSFGW3025	30" L x 25" W
PSFGW3030	30" L x 30" W
PSFGW3225	32" L x 25" W
PSFGW4020	40" L x 20" W

Return Air Filter Grilles for T-Bar



PROSELECT

- 24" L x 24" W
- 0.666" spaced fins at 45°
- Concealed hinges
- For use with R6 insulated 1" fiberglass plenum to accept 6" – 18" round collars
- Steel construction
- Color/Finish: White

SKU
PSFGFHBW2020

Return Air Filter Grilles for T-Bar



PROSELECT

- 24" L x 24" W
- Insulated
- Stamped face has fins on 1/2" centers
- Concealed hinges and latches
- For use with R6 insulated 1" fiberglass plenum to accept 6" – 18" round collars
- Aluminum foil vapor barrier
- Steel construction
- Color/Finish: White

SKU
PSFGTBIW2020

Return Air Filter Grilles for T-Bar



PROSELECT

- 24" L x 24" W
- Stamped face has fins on 1/2" centers
- Concealed hinges and latches
- Steel construction
- Color/Finish: White

SKU
PSFGTBW2020

Return Air Filter Grilles for T-Bar



PROSELECT

- 24" L x 24" W
- Insulated
- 3/4" spaced fins at 45°
- Hinged face with 1/4 turn latches
- Steel construction
- Color/Finish: White

SKU
PSFGFHBIW2020

Return Air Filter Grilles for T-Bar



PROSELECT

- 24" L x 24" W
- Concealed hinges
- For use with R6 insulated 1" fiberglass plenum to accept 6" – 18" round collars
- Steel construction
- Color/Finish: White

SKU
PSPFGFBR

Return Air Grilles

PROSELECT



- Horizontal space bars set at 35°
- Steel construction
- Color/Finish: White

SKU	Size
PSHFSWUU	6" L x 6" W
PSHFSWXX	8" L x 8" W
PSHFSW10U	10" L x 6" W
PSHFSW1010	10" L x 10" W
PSHFSW12U	12" L x 6" W
PSHFSW12X	12" L x 8" W
PSHFSW1212	12" L x 12" W
PSHFSW14U	14" L x 6" W
PSHFSW14X	14" L x 8" W
PSHFSW1410	14" L x 10" W
PSHFSW1414	14" L x 14" W
PSHFSW16X	16" L x 8" W
PSHFSW1616	16" L x 16" W
PSHFSW1818	18" L x 18" W
PSHFSW20U	20" L x 6" W
PSHFSW20X	20" L x 8" W
PSHFSW2010	20" L x 10" W
PSHFSW2012	20" L x 12" W
PSHFSW2014	20" L x 14" W
PSHFSW2016	20" L x 16" W
PSHFSW2020	20" L x 20" W
PSHFSW2025	20" L x 25" W
PSHFSW24X	24" L x 8" W
PSHFSW2410	24" L x 10" W
PSHFSW2412	24" L x 12" W
PSHFSW2414	24" L x 14" W
PSHFSW2416	24" L x 16" W
PSHFSW2420	24" L x 20" W
PSHFSW2424	24" L x 24" W
PSHFSW2520	25" L x 20" W
PSHFSW30U	30" L x 6" W
PSHFSW30X	30" L x 8" W
PSHFSW3010	30" L x 10" W
PSHFSW3012	30" L x 12" W
PSHFSW3014	30" L x 14" W
PSHFSW3016	30" L x 16" W
PSHFSW3020	30" L x 20" W
PSHFSW3612	36" L x 12" W
PSHFSW3614	36" L x 14" W

Return Air Grilles

PROSELECT



- 1/3" spaced fins at 20°
- 5/16" margin turnback
- Steel construction
- Color/Finish: White

SKU	Size
PSRG3WUU	6" L x 6" W
PSRG3WXX	8" L x 8" W
PSRG3W10P	10" L x 4" W
PSRG3W10U	10" L x 6" W
PSRG3W1010	10" L x 10" W
PSRG3W1020	10" L x 20" W
PSRG3W1024	10" L x 24" W
PSRG3W12P	12" L x 4" W
PSRG3W12U	12" L x 6" W
PSRG3W12X	12" L x 8" W
PSRG3W1210	12" L x 10" W
PSRG3W1212	12" L x 12" W
PSRG3W1224	12" L x 24" W
PSRG3W14U	14" L x 6" W
PSRG3W14X	14" L x 8" W
PSRG3W1410	14" L x 10" W
PSRG3W1414	14" L x 14" W
PSRG3W1420	14" L x 20" W
PSRG3W1424	14" L x 24" W
PSRG3W16X	16" L x 8" W
PSRG3W1610	16" L x 10" W
PSRG3W1616	16" L x 16" W
PSRG3W1620	16" L x 20" W
PSRG3W1624	16" L x 24" W
PSRG3W18X	18" L x 8" W
PSRG3W1812	18" L x 12" W

SKU	Size
PSRG3W1818	18" L x 18" W
PSRG3W20U	20" L x 6" W
PSRG3W20X	20" L x 8" W
PSRG3W2010	20" L x 10" W
PSRG3W2012	20" L x 12" W
PSRG3W2014	20" L x 14" W
PSRG3W2016	20" L x 16" W
PSRG3W2018	20" L x 18" W
PSRG3W2020	20" L x 20" W
PSRG3W2024	20" L x 24" W
PSRG3W24U	24" L x 6" W
PSRG3W24X	24" L x 8" W
PSRG3W2410	24" L x 10" W
PSRG3W2412	24" L x 12" W
PSRG3W2414	24" L x 14" W
PSRG3W2416	24" L x 16" W
PSRG3W2420	24" L x 20" W
PSRG3W2424	24" L x 24" W
PSRG3W2430	24" L x 30" W
PSRG3W30U	30" L x 6" W
PSRG3W30X	30" L x 8" W
PSRG3W3010	30" L x 10" W
PSRG3W3012	30" L x 12" W
PSRG3W3014	30" L x 14" W
PSRG3W36X	36" L x 8" W

Return Air Grilles

PROSELECT




- 1/2" spaced fins at 40°
- 5/16" margin turnback
- Steel construction
- Color/Finish: White

SKU	Size
PSRGWUU	6" L x 6" W
PSRGWXP	8" L x 4" W
PSRGWXU	8" L x 6" W
PSRGWXX	8" L x 8" W
PSRGWX14	8" L x 14" W
PSRGW10P	10" L x 4" W
PSRGW10U	10" L x 6" W
PSRGW10X	10" L x 8" W
PSRGW1010	10" L x 10" W
PSRGW1014	10" L x 14" W
PSRGW1020	10" L x 20" W
PSRGW1024	10" L x 24" W
PSRGW12P	12" L x 4" W
PSRGW12U	12" L x 6" W
PSRGW12X	12" L x 8" W
PSRGW1210	12" L x 10" W
PSRGW1212	12" L x 12" W
PSRGW1216	12" L x 16" W
PSRGW1218	12" L x 18" W
PSRGW1220	12" L x 20" W
PSRGW1224	12" L x 24" W
PSRGW1230	12" L x 30" W
PSRGW14P	14" L x 4" W
PSRGW14U	14" L x 6" W

SKU	Size
PSRGW14X	14" L x 8" W
PSRGW1410	14" L x 10" W
PSRGW1412	14" L x 12" W
PSRGW1414	14" L x 14" W
PSRGW1416	14" L x 16" W
PSRGW1420	14" L x 20" W
PSRGW1424	14" L x 24" W
PSRGW1425	14" L x 25" W
PSRGW1430	14" L x 30" W
PSRGW16U	16" L x 6" W
PSRGW16X	16" L x 8" W
PSRGW1610	16" L x 10" W
PSRGW1612	16" L x 12" W
PSRGW1616	16" L x 16" W
PSRGW1620	16" L x 20" W
PSRGW1624	16" L x 24" W
PSRGW1625	16" L x 25" W
PSRGW18P	18" L x 4" W
PSRGW18U	18" L x 6" W
PSRGW18X	18" L x 8" W
PSRGW1812	18" L x 12" W
PSRGW1818	18" L x 18" W
PSRGW1824	18" L x 24" W
PSRGW1830	18" L x 30" W
PSRGW20U	20" L x 6" W
PSRGW20X	20" L x 8" W
PSRGW2010	20" L x 10" W
PSRGW2012	20" L x 12" W
PSRGW2014	20" L x 14" W
PSRGW2016	20" L x 16" W

SKU	Size
PSRGW2020	20" L x 20" W
PSRGW2024	20" L x 24" W
PSRGW2025	20" L x 25" W
PSRGW2030	20" L x 30" W
PSRGW24U	24" L x 6" W
PSRGW24X	24" L x 8" W
PSRGW2410	24" L x 10" W
PSRGW2412	24" L x 12" W
PSRGW2414	24" L x 14" W
PSRGW2416	24" L x 16" W
PSRGW2418	24" L x 18" W
PSRGW2420	24" L x 20" W
PSRGW2424	24" L x 24" W
PSRGW2430	24" L x 30" W
PSRGW2516	25" L x 16" W
PSRGW2520	25" L x 20" W
PSRGW30U	30" L x 6" W
PSRGW30X	30" L x 8" W
PSRGW3010	30" L x 10" W
PSRGW3012	30" L x 12" W
PSRGW3014	30" L x 14" W
PSRGW3016	30" L x 16" W
PSRGW3018	30" L x 18" W
PSRGW3020	30" L x 20" W
PSRGW3024	30" L x 24" W
PSRGW3030	30" L x 30" W
PSRGW3610	36" L x 10" W
PSRGW3612	36" L x 12" W
PSRGW3614	36" L x 14" W
PSRGW3624	36" L x 24" W

Return Air Grilles



PROSELECT

- 1/2" x 1/2" x 1/2" core
- 90% maximum free area
- For surface mounting
- Aluminum construction
- Color/Finish: White

SKU	Size
PSAEC51212	12" L x 12" W
PSAEC51414	14" L x 14" W
PSAEC52210	22" L x 10" W
PSAEC52414	24" L x 14" W

Return Air Grilles



PROSELECT

- 1/2" spaced fins at 40°
- Screws included
- Aluminum construction
- Color/Finish: White

SKU	Size
PSARGWUU	6" L x 6" W
PSARGWXX	8" L x 8" W
PSARGW1010	10" L x 10" W
PSARGW1212	12" L x 12" W
PSARGW1410	14" L x 10" W

Return Air Grilles




PROSELECT

- 0.666" spaced fins at 45° angle
- Aluminum construction
- Color/Finish: White

SKU	Size
PSAH45WUU	6" L x 6" W
PSAH45WXP	8" L x 4" W
PSAH45WXX	8" L x 8" W
PSAH45W10U	10" L x 6" W
PSAH45W1010	10" L x 10" W
PSAH45W12U	12" L x 6" W
PSAH45W12X	12" L x 8" W
PSAH45W1212	12" L x 12" W
PSAH45W1224	12" L x 24" W
PSAH45W14X	14" L x 8" W
PSAH45W1410	14" L x 10" W
PSAH45W1414	14" L x 14" W
PSAH45W1420	14" L x 20" W
PSAH45W1616	16" L x 16" W
PSAH45W1818	18" L x 18" W
PSAH45W1824	18" L x 24" W
PSAH45W20X	20" L x 8" W
PSAH45W2010	20" L x 10" W
PSAH45W2012	20" L x 12" W
PSAH45W2014	20" L x 14" W
PSAH45W2016	20" L x 16" W
PSAH45W2020	20" L x 20" W
PSAH45W24U	24" L x 6" W
PSAH45W24X	24" L x 8" W
PSAH45W2410	24" L x 10" W
PSAH45W2412	24" L x 12" W
PSAH45W2414	24" L x 14" W
PSAH45W2416	24" L x 16" W
PSAH45W2418	24" L x 18" W
PSAH45W2420	24" L x 20" W
PSAH45W2424	24" L x 24" W
PSAH45W2814	28" L x 14" W
PSAH45W30X	30" L x 8" W
PSAH45W3010	30" L x 10" W
PSAH45W3012	30" L x 12" W
PSAH45W3014	30" L x 14" W
PSAH45W3016	30" L x 16" W
PSAH45W3018	30" L x 18" W
PSAH45W3020	30" L x 20" W
PSAH45W36X	36" L x 8" W
PSAH45W3610	36" L x 10" W
PSAH45W3612	36" L x 12" W
PSAH45W3614	36" L x 14" W
PSAH45W4824	48" L x 24" W

Return Air Grilles for T-Bar




PROSELECT

- 24" L x 24" W
- 1/2" x 1/2" x 1/2" cube core
- Insulated
- 90% maximum free area
- Includes a foil insulated backpan and accepts 6" – 12" field supplied inlet collars
- Extruded aluminum frame
- Color/Finish: White

SKU
PSAEC5ITB2222

Return Air Grilles for T-Bar



PROSELECT

- 1/2" x 1/2" x 1/2" core
- 90% maximum free area
- Extruded aluminum frame
- Color/Finish: White

SKU	Size
PSAEC5TB2210	22" L x 10" W
PSAEC5TB2222	22" L x 22" W

Return Air Grilles for T-Bar



PROSELECT

- 24" L x 24" W
- 0.666" spaced fins at 45° angle
- Extruded aluminum frame and blades
- Color/Finish: White

SKU
PSAH45TB

Return Air Grilles for T-Bar




PROSELECT

- Extruded aluminum frame and blades
- Horizontal fins are permanently fixed at 45° angle
- Aluminum construction
- Color/Finish: White

SKU	Size
PSAH45TBXX	8" L x 8" W
PSAH45TB1010	10" L x 10" W
PSAH45TB1212	12" L x 12" W
PSAH45TB1414	14" L x 14" W

Return Air Grilles for T-Bar



PROSELECT

- Designed as a non-ducted return
- Perforated face has 3/16" diameter holes on 1/4" centers
- Steel construction
- Color/Finish: White

SKU	Size
PSPRF2412	24" L x 12" W
PSPRF	24" L x 24" W

Return Filter Grilles for T-Bar



PROSELECT

- Horizontal fins are permanently fixed at 45° angle
- Accepts standard 1" or 2" filters (not included)
- Hinged face with 1/4 turn latches for quick filter changes
- Extruded aluminum construction
- Color/Finish: White

SKU	Size
PSAH45FTB2020	20" L x 20" W
PSAH45FTB2424	22" L x 22" W
PSAH45FTB2448	24" L x 48" W

Toe Space Grilles



PROSELECT

- Heavy gauge steel construction for floor use
- Multi-angled fin setting
- All-steel construction

SKU	Size	Color/Finish
PSTSBK10	2" L x 10" W	Brown
PSTSWK10	2" L x 10" W	White
PSTSBK12	2" L x 12" W	Brown
PSTSWK12	2" L x 12" W	White
PSTSBK14	2" L x 14" W	Brown
PSTSWK14	2" L x 14" W	White
PSTSBP10	4" L x 10" W	Brown

Condenser Pads



PROSELECT

- For indoor and outdoor use
- Injection molded polypropylene
- Color/Finish: Gray

SKU	Size
PSCPE24242	24" L x 24" W x 2" H
PSCPE24243	24" L x 24" W x 3" H
PSCPE24302	24" L x 30" W x 2" H
PSCPE24362	24" L x 36" W x 2" H
PSCPE24363	24" L x 36" W x 3" H
PSCPE30302	30" L x 30" W x 2" H
PSCPE30303	30" L x 30" W x 3" H
PSCPE30362	30" L x 36" W x 2" H
PSCPE32322	32" L x 32" W x 2" H
PSCPE32323	32" L x 32" W x 3" H
PSCPE32442	32" L x 44" W x 2" H
PSCPE36362	36" L x 36" W x 2" H
PSCPE36363	36" L x 36" W x 3" H
PSCPE36402	36" L x 40" W x 2" H
PSCPE36483	36" L x 48" W x 3" H
PSCPE38422	38" L x 42" W x 2" H
PSCPE52523	52" L x 52" W x 3" H

Condensate P-Traps



PROFLO

- 3/4" PVC
- For condensate lines

SKU
PF42860

Condensate Running Traps



PROFLO

- 3/4" PVC
- For condensate lines

SKU
PF42861

Condensate Pump Safety Switches



PROSELECT

- Can install switch to activate audible and/or visual alarm
- Low voltage
- 72" leads
- ABS housing, polyethylene float and lead wires

SKU
PSCP72OFSS

Condensate Pumps



PROSELECT

- 115V, 60W
- Head Capacity: 15'
- 1/2 gallon tank capacity
- Removable 3/8" (9.5mm) barbed check valve
- Reversible tank cover with 3 inlet drain holes for flexible installation
- Rated for water temperature up to 140°F
- Thermal overload protection
- 6' power cord with 3 prong molded plug
- ABS tank, motor cover and volute with stainless steel shaft
- UL Listed

SKU
PSCP15

Condensate Pumps



PROSELECT

- 115V
- 1/2 gallon tank capacity
- Automatic snap-action switch
- Removable 3/8" (9.5mm) barbed check valve
- Reversible tank cover with 3 inlet drain holes for flexible installation
- Rated for water temperature up to 140°F
- Thermal overload protection
- Safety switch
- ABS tank, motor cover and volute with stainless steel shaft
- UL Listed

SKU	Head Capacity	Watts
PSCP15WS	15'	60W
PSCP20WS	20'	73W

Condensate Pumps



PROSELECT

- 115V
- 1/2 gallon tank capacity
- Automatic snap-action switch
- Removable 3/8" (9.5mm) barbed check valve
- Reversible tank cover with 3 inlet drain holes for flexible installation
- Rated for water temperature up to 140°F
- Thermal overload protection
- Includes 20' (6.1 m) of 3/8" ID (9.5mm) clear tubing
- ABS tank, motor cover and volute with stainless steel shaft
- UL Listed

SKU	Head Capacity	Watts
PSCP15WS20T	15'	60W
PSCP20WS20T	20'	73W

Condensate Pumps



PROSELECT

- 115V, 93W
- Head Capacity: 20'
- 3/10 gallon tank capacity
- Removable 3/8" (9.5mm) barbed check valve
- Thermal overload protection
- Safety switch
- 6' power cord with 3 prong molded plug
- ABS tank with stainless steel shaft

SKU
PSCP20LPWS

Condensate Pumps



PROSELECT

- 230V, 75W
- 1/2 gallon tank capacity
- Automatic snap-action switch
- Removable 3/8" (9.5mm) barbed check valve
- Reversible tank cover with 3 inlet drain holes for flexible installation
- Rated for water temperature up to 140°F
- Thermal overload protection
- Safety switch
- ABS tank, motor cover and volute with stainless steel shaft
- UL Listed

SKU
PSCP20WS230

Condensate Pumps



PROSELECT

- 115V, 148W
- 24' head capacity
- 1 gallon tank capacity
- Snap-action safety switch
- Thermal overload protection
- 6' power cord with 3 prong molded plug
- ABS tank, volute and switch cover with galvanized steel tank cover and stainless steel shaft

SKU
PSCP24WS

Condensate Pumps



PROSELECT

- 115V, 185W
- 45' head capacity
- 1 gallon tank capacity
- Snap-action safety switch
- Thermal overload protection
- 3/8" (9.5mm) discharge copper tube
- 6' power cord with 3 prong molded plug
- ABS tank, volute and switch cover with galvanized steel tank cover and stainless steel shaft

SKU
PSCP45WS

Condensate Pumps



PROSELECT

- Mini-Split
- Ductless
- For intermittent operation, maximum 50% duty cycle
- Condensate produced in application must be no more than half the pump's flow rate for any given head
- Use with most mini-split air conditioning units up to 25,000 BTU/hr
- Self-priming pump can be placed up to 3' (0.9 m) above reservoir
- Kit Includes: Suction tubing, vent tubing, drain tubing, tubing adaptor and safety switch

SKU	Volts	Watts
PSCPMS115	115V	19W
PSCPMS230	230V	20W

Condensate Pumps



PROSELECT

- Removes condensate from wall mount air conditioners up to 34,000 BTU
- Amps: 0.1A
- Volts: 230V
- Maximum Pressure: 15.2 psi
- Mounts on wall underneath air handler
- Clear, extra large reservoir for easy, visual inspection
- Safety alarm ready
- Easy to remove cover hides pump
- Requires no tools to service

SKU
PSCPMSOP230

Non-Programmable Thermostats



PROSELECT

- Conventional/Heat Pump
- Dual-Powered: Hardwired or battery
- Large display with bright blue backlight
- Adjustable temperature set point limits
- Non-volatile memory retains user settings
- Easy access front battery door
- Separate O and B terminals
- Compressor short cycle protection
- Separate heating and cooling

SKU	Size	Stages
PSTS11NP	3 18/25" x 4 3/4" x 1 3/25"	1 Heat/1 Cool
PSTS21NP	3 18/25" x 4 3/4" x 1 3/25"	2 Heat/1 Cool
PSTSL11NP	3 31/50" x 4 18/25" x 1 19/50"	1 Heat/1 Cool
PSTSL21NP	3 31/50" x 4 18/25" x 1 19/50"	2 Heat/1 Cool

Programmable Thermostats



PROSELECT

- Conventional/Heat Pump
- 5-2 day weekday/weekend programming
- Dual-Powered: Hardwired or battery
- Large display with bright blue backlight
- Adjustable temperature set point limits
- Non-volatile memory retains user settings
- Filter check monitor
- Adaptive recovery mode
- Adjustable temperature differentials
- Meets California Title 24 Guidelines

SKU	Size	Stages
PSTS11P52	3 18/25" x 4 3/4" x 1 3/25"	1 Heat/1 Cool
PSTS21P52	3 18/25" x 4 3/4" x 1 3/25"	2 Heat/1 Cool
PSTSL11P52	3 31/50" x 4 18/25" x 1 19/50"	1 Heat/1 Cool
PSTSL21P52	3 31/50" x 4 18/25" x 1 19/50"	2 Heat/1 Cool

Wall Plates



PROSELECT

- 6 1/2" L x 6 1/2" W
- Color/Finish: White

SKU
PSWALLPLT

MERCURY THERMOSTAT
RECYCLING PROGRAM

WE WANT YOUR MERCURY THERMOSTATS

Bring in all the mercury thermostats you remove from service or have sitting around your shop, and we will recycle them for you for free.

IT'S THAT EASY.



Thermostat Recycling Corporation

FERGUSON.COM



CREATING THE GLOW THAT LEADS YOU HOME

PARK HARBOR®

*Park Harbor McBryde Collection



What can we help you find?

Bits & Saws . . . 213
Blades . . . 214
Extension Cords . . . 214-215
Worklights . . . 215
Cement & Concrete Tools . . . 216
Hammers . . . 217
Hex Keys . . . 218
Nut Drivers . . . 218
Wrenches . . . 219-221
Pliers . . . 221-222
Cutting Tools . . . 222
Saws . . . 222
Snips . . . 223-224
Screwdrivers . . . 224- 225
Pipe/Tubing Tools . . . 225
Measuring Tools . . . 225-226
Knives & Blades . . . 226
Material Handling . . . 226

Bi-Metal Hole Saws



- Cuts through various types of steel sheets and pipes and other materials such as steel sheets, pipes, hardwood, plywood and plastics
- Bi-metal for long life
- GSA approved

SKU	Size
RAWHS78	7/8"
RAWHS1	1"
RAWHS1316	1 3/16"
RAWHS114	1 1/4"
RAWHS138	1 3/8"
RAWHS112	1 1/2"
RAWHS134	1 3/4"
RAWHS2	2"
RAWHS214	2 1/4"
RAWHS212	2 1/2"
RAWHS2916	2 9/16"
RAWHS258	2 5/8"
RAWHS234	2 3/4"
RAWHS3	3"
RAWHS312	3 1/2"
RAWHS4	4"
RAWHS412	4 1/2"
RAWHS5	5"
RAWHS512	5 1/2"
RAWHS6	6"

Hole Saw Arbors



- Fits hole saws 7/8" (22mm) to 1 3/16" (30mm) diameter
- Fits most bi-metal hole saws
- 7/16" hex shank
- GSA approved
- **Optional accessories:**
  Replacement pilot drill bit: RAWPD14

SKU
RAW1L

Hole Saw Arbors



- Fits hole saws 1 1/4" (32mm) to 6" (152mm) diameter
- Fits most bi-metal hole saws
- 7/16" hex shank
- GSA approved
- **Optional accessories:**
  Replacement pilot drill bit: RAWPD14

SKU
RAW2L

Reciprocating Saw Blades



- Heavy duty
- Long lasting, high performance, bi-metal construction
- Various blades available for different needs: 6 TPI (wood with nails and general roughing in); 14 TPI (metal 3/16" through 1/4"); 18 TPI (metal 1/8" through 3/16")

SKU	Length	TPI	Pkg Qty
RAWRB606HD	6"	6	3
RAWRB614HD	6"	14	5
RAWRB906HD	9"	6	3
RAWRB914HD	9"	14	5
RAWRB918HD	9"	18	5

Reciprocating Saw Blades



- Long lasting, high performance, bi-metal construction
- Various blades available for different needs: 10 TPI (wood, plastic and steel); 14 TPI (metal 3/16" through 1/4"); 18 TPI (metal 1/8" through 3/16"); 24 TPI (metal thinner than 1/8")
- Package Quantity: 5

SKU	Length	TPI
RAWRB610	6"	10
RAWRB614	6"	14
RAWRB618	6"	18
RAWRB624	6"	24
RAWRB814	8"	14
RAWRB818	8"	18
RAWRB910	9"	10

Extension Cords



- Heavy Duty
- All weather
- 12/3 gauge
- Yellow
- Water resistant and flame retardant jacket will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- Superior flexibility and resists cracking in temperatures down to -40°F and up to 140°F (-40°C up to 60°C)
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31203	25'
RAP31202	50'
RAP31201	100'

Extension Cords



- Extreme weather
- 12/3 gauge
- Blue/Orange
- SJEOW Heavy duty outdoor extension cord
- Oil resistant, water resistant and flame retardant
- Superior flexibility and resists cracking to -58°F (-50°C)
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31206	50'
RAP31207	100'

Extension Cords



- Medium Duty
- All weather
- 14/3 gauge
- Blue/Yellow
- Water resistant and flame retardant jacket will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- Superior flexibility and resists cracking in temperatures down to -40°F and up to 140°F (-40°C up to 60°C)
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31402	50'
RAP31401	100'

Extension Cords



- Medium Duty
- All weather
- 16/3 gauge
- Orange
- Water resistant and flame retardant will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- Superior flexibility and resists cracking in temperatures down to -40°F and up to 140°F (-40°C up to 60°C)
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31602	25'
RAP31601	50'

Extension Cords



- Twist-Lock
- Cord Length: 100'
- 12/3 gauge
- Oil resistant, water resistant and flame retardant
- Superior flexibility and resists cracking in temperatures down to -40°F (-40°C)
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU
RAP41201

Ground Fault Current Interrupters



- Cord Length: 3' in-line
- 12/3 gauge
- Water resistant and flame retardant jacket on cord
- Working temperature range is -31°F to +140°F
- Converts one outlet into additional GFCI protected outlets
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for ground fault circuit interrupters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU
RAP32001

Power Block Adapters



- Triple Tap
- Cord Length: 2'
- 12/3 gauge
- Triple tap U-ground power block
- Water resistant, oil resistant, and flame retardant
- Superior flexibility at sub-freezing temperatures
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU
RAP31204

Utility Worklights



- 16/3 gauge
- Working temperature range is -31°F to +140°F
- Utilizes standard 75W bulbs
- Anodized aluminum reflector
- Metal hook for hands-free applications
- Ergonomic handle is easy to hold
- On/Off switch and convenience outlet in handle
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP30501	25'
RAP30502	50'

Power Supply Cords



- 16/3-wire grounded cord
- Tinned and stripped ends for easier connection
- For RAP33003 and RAP33002, accessories may include 3 wire nuts and Romex connectors
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length	Plug
RAP33003	3'	Angle
RAP33001	6'	Angle
RAP33002	6'	Straight



GLOVES
P. 233-234

Cement Tools



RAPTOR®

- Brick trowel
- 10" L x 5" W
- Slightly rounded, diamond-shaped blade
- Designed for laying brick, laying block, tamping and cutting bricks

SKU
RAP44026

Cement Tools



RAPTOR®

- Concrete edger
- 6" L x 3" W
- 1/2" lip with 3/8" radius

SKU
RAP44034

Cement Tools



RAPTOR®

- Concrete groover
- 6" L x 3" W
- Shaped bit and leading edge cuts proper and sharp groove
- 1/2" depth, 1/2" width with 1/4" radius

SKU
RAP44032

Cement Tools



RAPTOR®

- Finish trowel
- 16" L x 4" W
- Large, flat rectangular blade
- Used to smooth a surface after concrete has begun to set

SKU
RAP44036

Cement Tools



RAPTOR®

- Gauging trowel
- 7" L x 3" W
- V-shaped back, rounded tip
- Designed for gauging, or mixing in specified proportions, small amounts of quick set plaster

SKU
RAP44024

Cement Tools



RAPTOR®

- Magnesium masonry float
- 16" L x 3" W
- Floating helps remove imperfections and produces a flatter surface
- Compacts the slab and the mortar at the surface in preparation for later finishing operations

SKU
RAP44028

Cement Tools



RAPTOR®

- Margin trowel
- 5" L x 2" W
- V-shaped back, rectangular front
- Used to mix thinset and other material and scooping/spreading material such as adhesives in tight spots

SKU
RAP44022

Cement Tools



RAPTOR®

- Pointing trowel
- Smaller version of brick trowel
- Used to separate concrete from forms, finishing brick wall joints and filling small cavities

SKU	Size
RAP44020	5 1/2"
RAP44030	7" x 3"

Hammers



RAPTOR®

- Ball Pein
- 32 oz
- Computer designed for better balance
- Slip resistant grip
- High density fiberglass handle

SKU
RAP12518

Hammers



RAPTOR®

- Fiberglass Claw
- 16 oz
- Computer designed for better balance
- High density fiberglass shock absorbtion handle with hollow core
- Slip resistant grip

SKU
RAP12501

Hammers



RAPTOR®

- Brick hammer
- 16 oz
- Head Length: 7 1/4"
- Blade Size: 2" L x 7/8" W
- Wood handle

SKU
RAP12530

Hammers



RAPTOR®

- HVAC setting
- 24 oz
- Single piece forged construction
- Balanced design
- Square beveled face
- Textured non-slip, vinyl handle
- GSA approved

SKU
RAP12525

Hammers



RAPTOR®

- Dead Blow
- 3 lbs
- Will not damage wood, tile, chrome, or soft metals like steel hammers
- Non-rebounding, non-sparking, shock-absorbant
- Rugged, uni-body heavy-duty construction

SKU
RAP12507

Hammers



RAPTOR®

- Steel Claw
- 24 oz
- Computer designed for better balance
- Patented shock absorbing hickory plug
- Slip resistant grip

SKU
RAP12504

Hammers



RAPTOR®

- Engineer
- 4 lbs
- Extra large striking face
- Slip resistant grip
- High density fiberglass handle with overstrike shield

SKU
RAP12509



For Waterworks specific tools, see P. 181-183

Hex Key Sets



RAPTOR®

- 12 Piece SAE Set
- Includes Key Sizes: 1/16", 5/64", 5/32", 3/16", 3/32", 7/32", 7/64", 1/4", 1/8", 5/16", 9/64" and 3/8"
- Snap set holder for secure storage
- Durable black finish
- GSA approved

SKU
RAP13002

Hex Key Sets



RAPTOR®

- 9 Piece Folding Set
- Includes Key Sizes: 3/16", 1/8", 7/32", 7/64", 1/4", 3/32", 5/32", 5/64" and 9/64"
- Durable black finish
- GSA approved

SKU
RAP13003

Hex Key Sets



RAPTOR®

- 9 Piece Metric Set
- Includes Key Sizes: 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm and 10mm
- Snap set holder for secure storage
- Durable black finish
- GSA approved

SKU
RAP13004

Magnetic Nut Drivers



RAPTOR®

- Hardened steel construction
- Permanent magnet
- 1/4" hex shaft fits most drills and won't strip
- GSA approved

SKU	Size	Length
RAP75001	1/4"	1 3/4"
RAP75003	1/4"	4"
RAP75004	1/4"	6"
RAP75005	3/8"	1 3/4"
RAP75006	3/8"	4"
RAP75007	5/16"	1 3/4"
RAP75009	5/16"	4"
RAP75010	5/16"	6"

Nut Driver Sets



RAPTOR®

- 7 Piece Set - Hollow Shaft
- Includes: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16" and 1/2" nut drivers
- Comfortable, color coded rubber vinyl grips
- GSA approved

SKU
RAP14509

Nut Driver Sets



RAPTOR®

- 3 Piece Set - Magnetic Tip
- Includes: 1/4", 5/16" and 3/8" tips
- Comfortable, rubber vinyl grip
- GSA approved

SKU
RAP14560PK

Nut Drivers



RAPTOR®

- Hollow Shaft
- Comfortable, color coded rubber vinyl grips
- Shaft Length: Standard
- GSA approved

SKU	Size
RAP14503	1/4"
RAP14504	5/16"
RAP14506	3/8"
RAP14507	7/16"
RAP14508	1/2"

Nut Drivers



RAPTOR®

- Magnetic Tip
- Comfortable, color coded rubber vinyl grips are easy on the hands
- GSA approved

SKU	Size	Shaft Length
RAP14550	1/4"	Stubby
RAP14551	1/4"	Standard
RAP14552	5/16"	Stubby
RAP14553	5/16"	Standard

Adjustable Wrenches



RAPTOR®

- Superwide 8" wrench opens to a full 1 1/2" jaw capacity
- Unique jaw design precisely grips the flat sides of fasteners, avoiding the rounding of fastener corners
- Specially designed handle reduces overall weight by 10%
- Laser-etched SAE and metric rule on wrench head for easy fastener size identification
- Non-protruding moveable jaw end allows easier access to fastener in tight spaces
- 18 to 25% wider jaw opening increases useful range of fastener sizes and gives the advantages of economy, convenience and lighter weight

SKU
RAP18006

Adjustable Wrenches



RAPTOR®

- Unique jaw design precisely grips the flat sides of fasteners, avoiding the rounding of fastener corners
- Specially designed handle reduces overall weight by 10%
- Non-protruding moveable jaw end allows easier access to fastener in tight spaces
- 18 to 25% wider jaw opening increases useful range of fastener sizes and gives the advantages of economy, convenience and lighter weight
- GSA approved

SKU	Length	Jaw Capacity
RAP18008	4"	5/8"
RAP18007	6"	1"
RAP18011	10"	1 1/4"
RAP18010	12"	1 1/2"
RAP18009	15"	1 7/8"

Basin Wrenches



RAPTOR®

- Length: 11"
- Self-tightening spring-loaded jaws
- T-handle

SKU
RAP50115

Basin Wrenches



RAPTOR®

- Telescoping and adjusts from 9"–15"
- Self tightening spring loaded jaws
- T-handle

SKU
RAP50230

Drain Wrenches



RAPTOR®

- Accommodates most tub drains and closet spuds
- Universal
- Smart dumbell
- Use adjustable wrench or screwdriver to turn the tool
- Double ended

SKU
RAP50205

Handle Pullers



RAPTOR®

- Standard
- T-handle
- Two jaws
- Forged Steel

SKU
RAP50175

Handle Pullers



RAPTOR®

- Two large jaws fit under handle
- Deluxe model that removes even the most stubborn handles
- Extra wide opening

SKU
RAP50210

Nut Wrenches



RAPTOR®

- Adjustable thumb screw wrench
- Locking wing nut
- Wide mouth jaw opening, 7/8" to 3"
- Malleable iron, bright finish

SKU
RAP50125

Pipe Wrenches



RAPTOR®

- Length: 14"
- Aluminum
- Scale marked on hook
- Adjusting nut spins easily

SKU
RAP11514

Plug Wrenches



RAPTOR®

- Necessary for tub/drain installation with pop-up drain plugs
- Ensures proper tightness without ruining the finish of the strainer

SKU
RAP50220

Pipe Wrenches




RAPTOR®

- Forged and heat-treated, high-grade cast iron
- Guaranteed to withstand jobsite abuse
- Scale marked on hook
- Adjusting nut spins easily

SKU	Length
RAP11214	14"
RAP11218	18"
RAP11224	24"

Seat Wrenches



RAPTOR®

- Angled and tapered
- Universal fit
- Hardened Steel

SKU
RAP50150

Pipe Wrenches



RAPTOR®

- Aluminum
- Guaranteed to withstand jobsite abuse
- Scale marked on hook
- Adjusting nut spins easily

SKU	Length
RAP11414	14"
RAP11418	18"
RAP11424	24"

Seat Wrenches



RAPTOR®

- Straight and tapered
- Universal fit
- Hardened Steel

SKU
RAP50505

Spud Wrenches



- Length: 9"
- 4-in-1 design works on many closet spuds, urinal spuds, kitchen basket strainers, urinal flush valves and more
- Compact design

SKU
RAP50130

Strainer Wrenches



- Double ended design fits most tub drains
- Install and remove bath tub drains with or without cross bars
- Use adjustable wrench or screwdriver to turn the tool

SKU
RAP50215

Torque Wrenches



- For standard duty no-hub couplings
- Measures torque on no-hub couplings to 60 in-lbs
- Ratchets when correct torque is achieved

SKU
RAP50145

Torque Wrenches



- No-hub
- T-handle style tools color coded to match the correct no-hub coupling
- Torque setting designed to slip when coupling nut has reached proper setting
- Locking collar lets user tighten nut to specified torque setting in one direction or use as non-torqueing tool in both directions
- GSA approved

SKU	Size	Maximum Torque	Color/Finish
RAP18550	5/16"	60 in-lbs	Black
RAP18551	5/16"	80 in-lbs	Yellow
RAP18552	3/8"	80 in-lbs	Green

Strap Wrenches



- Length: 12"
- Provides gripping power without scratching or deforming plastic and polished metal pipe
- Use on plastic pipe, filters, or any slick or smooth surface
- Woven nylon, polyurethane-coated strap
- Material: Aluminum

SKU
RAP11312

Locking Pliers



- Length: 10"
- Jaw Capacity: 1 3/4"
- Curved jaw for increased pressure point
- Guarded release trigger
- Durable turn screw for increased pressure
- GSA approved

SKU
RAP11502

Pliers



- Tongue & Groove
- Right angle teeth grip in all directions
- Self locking jaw opening adjustment
- Long, cushioned handles for extra leverage
- GSA approved

SKU	Length	Jaw Capacity
RAP18001	10"	2"
RAP18002	12"	2 1/2"
RAP18003	16"	4"

Pliers



- Water Plier
- Length: 6"
- Jaw Capacity: 1 1/4"
- Right angle teeth grip in all directions
- Self locking jaw opening adjustment
- Long, cushioned handles for extra leverage
- GSA approved

SKU
RAP18004

Side Cut Pliers



- Length: 8"
- Ideal for cutting copper, brass, iron and steel wire
- Not for use on live wires
- Forged steel
- GSA approved

SKU
RAP18024

Wire Strippers



- 6-in-1
- Cuts, crimps, strips and measures
- All steel tool with shear type edge that cuts both stranded and solid copper wire
- Wire stripper capacity 10-22 AWG
- Gages solid and stranded wire sizes

SKU
RAP18541

Deburring Tools



- Precision tempered blades
- Includes extra cutting blade
- Blade storage in handle
- **Optional accessories:**
  Replacement blade: RAP50250

SKU
RAP50245

Inside Pipe Cutters



- Use for closet flanges, sink waste, overflows, shower drains and sink rims
- For hard-to-reach applications
- Use with power drill
- Heat treated steel blade
- **Optional accessories:**
  Replacement blade: RAP15512

SKU
RAP15510

Pipe & Tubing Cutters



- Scissor
- Heavy duty cast aluminum scissor style cutter
- Single hand operation
- Cuts PVC and CPVC up to 3/4"
- Cuts PEX polyethylene and most types of hose up to 1"
- Reversible replaceable blade
- GSA approved
- **Optional accessories:**
  Replacement blade: RAP60021

SKU
RAP60001

Pipe & Tubing Cutters



- Ratchet
- Heavy duty cast aluminum
- Ratchet mechanism reduces force needed to make cut
- Single hand operation
- Cuts PVC and CPVC up to 1 1/4"
- Cuts PEX polyethylene and most types of hose up to 1 1/2"
- Easily replaceable blade
- GSA approved
- **Optional accessories:**
  Replacement blade: RAP60022

SKU
RAP60002

Pipe Reamers



- Reams all sizes from 3/16" to 1 1/2" OD capacity
- Inside and outside
- Works on steel, iron, copper, PVC and ABS pipe

SKU
RAP50330

Cable Saws



- Cuts PVC, CPVC and ABS
- Stainless steel cable with heavy duty handles
- Great in tight spaces

SKU	Length
RAP15610	24"
RAP15615	36"

Hacksaws



- High-tension design
- Quick-change blade
- 90° and 45° cutting angles
- Comfort grip handles front and back

SKU
RAP15507

Jab Saws



- Demolition teeth cut on both push and pull strokes
- Sharpened tip punches through drywall easily
- Ideal for wood, plastic or drywall
- Comfort slip resistant handle

SKU
RAP15502

Mini Hacksaws



- Blade Length: 10"
- Cuts wood, plaster, steel and brass
- Ideal for tight places

SKU
RAP15508

Mini Hacksaws



- Cuts wood, plaster, steel, brass and other materials
- Vinyl grip handle
- Works well in tight places
- **Optional accessories:**
  Replacement blade: RAP50320 (10 pack)

SKU
RAP50200

Saws



- For cutting PVC pipe
- Aluminum handle
- Rubberized handles allow for confident handling
- Handle converts for flush cut applications
- **Optional accessories:**
  12" Replacement blade: RAP15521
  18" Replacement blade: RAP15516

SKU	Length
RAP15520	12"
RAP15515	18"

Saws



- Plumber
- Blade Length: 22"
- Aluminum handle
- Rubberized handles allow for confident handling
- 9 TPI/10 point blade made of hardened steel

SKU
RAP15525

Snips



- One-piece drop forged high carbon steel construction
- Cuts up to 20 gauge cold rolled steel or 24 gauge stainless steel
- Designed for cutting straight and wide curves to the left or right
- Cushion handle with smooth, comfortable bows for ease in use and safety
- GSA approved

SKU
RAP16512

Snips



- Long straight
- Professional quality
- Cuts up to 18 gauge cold rolled steel
- Also cuts aluminum and vinyl siding, screening and copper wire to 10 gauge
- Serrated cutting edges prevent materials from slipping during use
- Comfort, contoured grip
- GSA approved

SKU
RAP16501

Snips



- Professional quality
- Cuts up to 16 gauge cold rolled steel or 20 gauge stainless steel
- Also cuts aluminum, vinyl siding, screening and other materials
- Serrated blade design for easy cutting
- Comfort grip handle
- Solid steel

SKU	Type
RAP16504	Straight
RAP16505	Right
RAP16506	Left

Snips



- Cuts up to 16 gauge cold rolled steel or 20 gauge stainless steel
- Ideal for straight cuts as well as tight curves, angles and circles
- Ergonomic bowed handles

SKU	Type
RAP16507	Offset Left
RAP16508	Offset Right

Robertson Head Screwdrivers



- Durable square alloy steel, precision formed tips to ensure a more secure fit
- Chrome-plated shaft for corrosion resistance
- GSA approved

SKU	Tip Size
RAP16030	#0
RAP16031	#1
RAP16032	#2
RAP16033	#3

Robertson Head Screwdrivers



- 4-piece set
- Includes: 1 each of sizes 0, 1, 2 and 3
- Durable square alloy steel tips precision formed to ensure a more secure fit
- Chrome-plated for corrosion resistance
- GSA approved

SKU
RAP16034

Screwdriver Sets



- 6-piece set
- Flat tips included: 3/16" x 3", 3/16" x 6", 1/4" x 4", 5/16" x 6"
- Phillips tips included: #1 x 3", #2 x 4"
- Vinyl grip
- Durable alloy steel, precision formed tips to ensure a more secure fit
- Chrome-plated shaft for corrosion resistance
- GSA approved

SKU
RAP16014

Screwdrivers



- Flat Head
- Shaft runs length of tool
- Contoured, comfort grip handle with ribs for added grasp
- GSA approved

SKU	Length	Tip Size
RAP16001	3"	1/8"
RAP16002	4"	3/16"
RAP16004	6"	1/4"
RAP16003	8"	5/16"

Screwdrivers



- Phillips Head
- Shaft runs length of tool
- Contoured, comfort grip handle with ribs for added grasp
- GSA approved

SKU	Length	Tip Size
RAP16009	4"	#2
RAP16007	6"	#1

Screwdrivers



- 6-in-1
- Includes: 2 flat tips, 2 Phillips tips, 1/4" and 5/16" nut drivers
- Contoured, comfort grip handle with ribs for added grasp
- GSA approved

SKU
RAP16012

Screwdrivers



RAPTOR®

- 19-in-1
- Pivoting ratchet drive
- Includes: 3 flat, 3 star, 5 Phillips, 3 hex tips and 4 nut drivers
- Screw top cap with bit storage
- Contoured comfort grip handle
- GSA approved

SKU
RAP16013

Undermount Sink Screwdrivers



RAPTOR®

- Sink Socket
- Extra long screwdriver
- Designed specifically for installing sinks that require clips

SKU
RAP50325

Flaring Tools



RAPTOR®

- 3/16", 1/4", 5/16", 3/8", 7/16", 1/2" and 5/8" O.D. tubing
- Self-centering yoke
- Ductile iron with hardened cone
- Individually carded

SKU
RAP50315

Nipple Extractors



RAPTOR®

- 3-piece set includes 3/8", 1/2" and 3/4"
- Cam type
- Provides non-slipping grip on the inside of nipples, pipes and fittings
- Can be turned either way

SKU
RAP50190

Socket Savers



RAPTOR®

- Removes plastic pipe from plastic fittings
- The rate of cut will depend on the rpm and power of the drill along with the amount of pressure applied to the drill while reboring
- To be used with schedule 40 applications only

SKU	Size
RAP13515	1/2", 3/4" & 1"
RAP13511	1 1/2"
RAP13512	2"
RAP13513	3"
RAP13514	4"

Socket Wrench Sets



PROFLO

- 5-piece socket wrench set for removing tub and shower valves
- Includes one turning bar, one retaining pin, and five sockets
- Includes: 2 1/32", 2 7/32", 2 9/32", 3 1/32", 1 1/32", 1 3/32", 1 5/32", 1 9/32", 1 11/32", 1 7/16"
- Individually carded

SKU
PF600

Tape Measures



RAPTOR®

- Length: 25'
- 8' tape standout
- 1" wide blade with large numbers for easy readability
- High impact rubber palm grip
- Top-forward blade lock for quick locking and unlocking
- Triple riveted hook grabs on side or top
- Bottom stopper for controlled tape recoil
- Shock-absorbing blade return bumper
- Belt-clip for quick accessibility
- GSA approved

SKU
RAP17002

Tape Measures



RAPTOR®

- Rubber case
- 9' tape standout
- 1 1/4" wide blade with large numbers for easy readability
- High impact case
- Large top-forward blade lock for quick locking and unlocking
- Shock-absorbing blade return bumper
- Belt-clip for quick accessibility
- GSA approved

SKU	Length
RAP17007	25'
RAP17004	30'

Tape Measures



- Stainless steel case for durability
- Length: 25'
- 8' tape standout
- 1" wide blade with large numbers for easy readability
- Top-forward blade snap lock
- Nylon coated blade
- Triple rieted end hook
- Belt-clip for quick accessibility

SKU
RAP17006

Torpedo Levels



- Length: 8"
- Protective anodized corrosion resistant finish
- 4 large Earth magnets offer superior holding power
- Vials can be viewed from all sides and are replaceable
- Features a 4-vial system that reads 90°, 45°, 30°, 0°
- Includes: Level, 2 replacement vials, bungee style cord to hold level in place on pipes and uneven surfaces

SKU
RAP14500

Utility Knife Blades



- Fits most standard utility knives
- Extra sharp treated blade
- 10 piece set

SKU
RAP10501

Utility Knife Blades



- Fits most standard utility knives
- Extra sharp treated blade
- 100 piece set

SKU
RAP10502

Utility Knives



- Steel
- Patent pending locking/folding mechanism
- Quick change blade design
- Precision machined anodized
- Aluminum handle

SKU
RAP10520

Utility Knives



- Quick change
- Easy turn dial for quick blade change
- Rubberized textured grip
- **Optional accessories:**
  Replacement blade, 10 pack: RAP10501
  Replacement blade, 100 pack: RAP10543

SKU
RAP10543

Masonry Lines



- #18 gauge braided nylon
- Used for brick and block laying, staking out sites, concrete and landscape layout

SKU	Length	Color/Finish
RAP44040	250'	Orange
RAP44042	750'	Yellow

Flame Guards



- 12" L x 16" W
- Flame and heat resistant up to 2200°F
- Asbestos free
- Smoke and odor free
- Aluminum backer can be molded around an object and helps keep guard in place

SKU
RAP64010



What can we help you find?

Fasteners 227-230
Brushes 230-231
Tapes 232
Gloves 233-234
Sand & Mesh Cloths 234
Caulking 235-236
Cements 236

Hex Head Cap Screws

PROSELECT




- Grade 2
- Color/Finish: Zinc Plated

SKU	Size	Pkg Qty
PS000412	1/4" - 20 x 1"	50
PS000414	1/4" - 20 x 1 1/2"	50
PS000427	5/16" - 18 x 1"	100
PS000431	5/16" - 18 x 2"	100
PS000439	3/8" - 16 x 3/4"	25
PS000440	3/8" - 16 x 1"	25
PS000441	3/8" - 16 x 1 1/4"	25
PS000442	3/8" - 16 x 1 1/2"	25
PS000443	3/8" - 16 x 1 3/4"	25
PS000446	3/8" - 16 x 2 1/2"	25
PS000448	3/8" - 16 x 3"	25
PS000453	1/2" - 13 x 3/4"	10
PS000454	1/2" - 13 x 1"	10
PS000456	1/2" - 13 x 1 1/2"	10
PS000461	1/2" - 13 x 2 3/4"	10
PS000462	1/2" - 13 x 3"	10
PS000470	5/8" - 11 x 1 1/4"	8
PS000471	5/8" - 11 x 1 1/2"	8
PS000472	5/8" - 11 x 1 3/4"	8
PS000473	5/8" - 11 x 2"	8
PS000474	5/8" - 11 x 2 1/4"	8
PS000475	5/8" - 11 x 2 1/2"	4

SKU	Size	Pkg Qty
PS000476	5/8" - 11 x 2 3/4"	8
PS000477	5/8" - 11 x 3"	4
PS000478	5/8" - 11 x 3 1/2"	4
PS000479	5/8" - 11 x 4"	4
PS000484	3/4" - 10 x 1 3/4"	4
PS000485	3/4" - 10 x 2"	4
PS000486	3/4" - 10 x 2 1/4"	4
PS000487	3/4" - 10 x 2 1/2"	4
PS000488	3/4" - 10 x 2 3/4"	4
PS000489	3/4" - 10 x 3"	4
PS000490	3/4" - 10 x 3 1/2"	2
PS000491	3/4" - 10 x 4"	2
PS000492	3/4" - 10 x 4 1/2"	2
PS000494	7/8" - 9 x 2 1/2"	2
PS000496	7/8" - 9 x 3 1/2"	2
PS000497	7/8" - 9 x 4"	2
PS000498	7/8" - 9 x 4 1/2"	2
PS000503	1" - 8 x 3"	2
PS000504	1" - 8 x 3 1/2"	2
PS000505	1" - 8 x 4"	2
PS000506	1" - 8 x 4 1/2"	2

Hex Nuts - Zinc Plated



PROSELECT

- Grade 2
- Low carbon steel
- Sold in packs only

SKU	Size	Pkg Qty
PS000312	1/4"- 20	100
PS000313	5/16"- 18	100
PS000314	3/8"- 16	100
PS000315	1/2"- 13	25
PS000316	5/8"- 11	10
PS000317	3/4"- 10	10
PS000318	7/8"- 9	4
PS000319	1"- 8	4

Heavy Hex Nuts - Plain



PROSELECT

- Grade 2
- Low carbon steel
- Sold in packs only

SKU	Size	Pkg Qty
PS000324	3/8"-16	50
PS000325	1/2"-13	25
PS000326	5/8"- 11	12
PS000327	3/4"-10	4
PS000328	7/8"- 9	4
PS000329	1"- 8	4

Heavy Hex Nuts - Zinc Plated



PROSELECT

- Grade 2
- Low carbon steel
- Sold in packs only

SKU	Size	Pkg Qty
PS000335	1/4"- 20	100
PS000336	5/16"- 18	100
PS000337	3/8"- 16	50
PS000338	1/2"- 13	25
PS000339	5/8"- 11	12
PS000340	3/4"-10	4
PS000341	7/8"- 9	4
PS000342	1"- 8	4
PS000343	1 1/8"- 7	2
PS000344	1 1/4"- 7	2
PS000345	1 1/2"- 6	2

Rod Couplings



PROSELECT

- Color/Finish: Zinc Plated

SKU	Size	Pkg Qty
PS000202	1/4"	12
PS000203	3/8"	12
PS000204	1/2"	12
PS000205	5/8"	4
PS000206	3/4"	4

Wood Screws



PROSELECT

- Countersunk head
- Use with Phillips #3
- Zinc plated
- Carbon steel
- Package Quantity: 50

SKU	Size
PS000909	12 -11 x 1 1/2"
PS000910	12 -11 x 2"
PS000911	12 -11 x 2 1/2"
PS000913	14 -10 x 1 1/2"
PS000915	14 -10 x 2"
PS000916	14 -10 x 2 1/2"
PS000918	14 -10 x 3"

Toggle Bolts



PROSELECT

- Package Quantity: 10

SKU	Size
PS000731	1/4"- 20 x 3"
PS000732	1/4"- 20 x 4"
PS000733	1/4"- 20 x 6"
PS000734	3/8"- 16 x 3"
PS000735	3/8"- 16 x 4"
PS000736	3/8"- 16 x 6"

Stove Bolts



PROSELECT

- Package Quantity: 25

SKU	Size
PS000702	1/4"- 20 x 3/4"
PS000703	1/4"- 20 x 1"
PS000704	1/4"- 20 x 1 1/4"

Flat Washers - Plain



PROSELECT

- Size: 3/4"
- Low carbon steel
- Sold in packs only
- Package Quantity: 12

SKU
PS000814

Flat Washers - Zinc Plated



PROSELECT

- Low carbon steel
- Sold in packs only

SKU	Size	Pkg Qty
PS000854	1/4"	100
PS000855	5/16"	100
PS000856	3/8"	100
PS000857	1/2"	25
PS000858	5/8"	25
PS000859	3/4"	12
PS000860	7/8"	12
PS000861	1"	12

Fender Washers - Zinc Plated



PROSELECT

- Low carbon steel
- Sold in packs only

SKU	Size	Pkg Qty
PS000824	1/4" x 1"	50
PS000825	1/4" x 1 1/4"	50
PS000826	3/8" x 1 1/4"	50
PS000827	3/8" x 1 1/2"	50
PS000828	3/8" x 2"	25
PS000829	1/2" x 1 1/2"	25
PS000830	1/2" x 2"	25

Self Piercing Screws



PROSELECT

- Hex head
- IHWH slot
- Driving Speed: 2,500 rpm
- Axial Load: 13.6kg
- Zinc plated

SKU	Size	Hex Head	Pkg Qty
PSZIP7D100	7 x 1/2	1/4	100
PSZIP7D1000	7 x 1/2	1/4	1,000
PSZIP7D5000	7 x 1/2	1/4	5,000
PSZIP7D15000	7 x 1/2	1/4	15,000
PSZIP8D100	8 x 1/2	1/4	100
PSZIP8D1000	8 x 1/2	1/4	1,000
PSZIP8D12000	8 x 1/2	1/4	12,000
PSZIP8F100	8 x 3/4	1/4	100
PSZIP8F1000	8 x 3/4	1/4	1,000
PSZIP8F5000	8 x 3/4	1/4	5,000
PSZIP8F10000	8 x 3/4	1/4	10,000
PSZIP8G500	8 x 1	1/4	500
PSZIP8G1000	8 x 1	1/4	1,000
PSZIP8G5000	8 x 1	1/4	5,000
PSZIP8J250	8 x 1 1/2	1/4	250
PSZIP8J1000	8 x 1 1/2	1/4	1,000
PSZIP8J5000	8 x 1 1/2	1/4	5,000
PSZIP8K100	8 x 2	1/4	100
PSZIP8K250	8 x 2	1/4	250
PSZIP8K1000	8 x 2	1/4	1,000
PSZIP10D1000	10 x 1/2	5/16	1,000
PSZIP10F100	10 x 3/4	5/16	100
PSZIP10F1000	10 x 3/4	5/16	1,000
PSZIP10F5000	10 x 3/4	5/16	5,000

Self Piercing Screws



PROSELECT

- White hex head
- IHWH slot
- Driving Speed: 2,500 rpm
- Axial Load: 13.6kg
- Zinc plated

SKU	Size	Pkg Qty
PSZIP8JW250	8 x 1 1/2	250
PSZIP8KW50	8 x 2	50
PSZIP8KW250	8 x 2	250

Self Piercing Screws



PROSELECT

- White finished head
- Size: 8" x 2"
- Zinc plated
- Package Quantity: 250

SKU
PSZIP8KWFH250

Self Tapping Screws



PROSELECT

- Hex head
- SAE C1018/C1022
- Self drilling screws, #2 point
- IHWH undercut
- Driving Speed: 2,500 rpm
- Axial Load: 30 lbs
- Test Plate Thickness: 1.6mm
- 3.0 sec max
- De-hydrogen embrittlement
- Zinc plated

SKU	Size	Pkg Qty
PSBIT8D100	8 x 1/2	100
PSBIT8D500	8 x 1/2	500
PSBIT8D1000	8 x 1/2	1,000
PSBIT8F100	8 x 3/4	100
PSBIT8F500	8 x 3/4	500
PSBIT8F1000	8 x 3/4	1,000
PSBIT10D100	10 x 1/2	100
PSBIT10D500	10 x 1/2	500
PSBIT10F100	10 x 3/4	100
PSBIT10F500	10 x 3/4	500
PSBIT10F1000	10 x 3/4	1,000
PSBIT10F5000	10 x 3/4	5,000
PSBIT10G100	10 x 1	100
PSBIT10G500	10 x 1	500

Cable Ties



- High tensile strength
- Manufactured from type 6/6 nylon
- UL181B approved on 36" and 48" ties for HVAC industry

SKU	Size	Color/Finish	Pkg Qty
PSCTBV	7 1/2"	Black	100
PSCTBV1000	7 1/2"	Black	1,000
PSCTB11	11"	Black	100
PSCTB14	14 1/2"	Black	100
PSCTB24	24"	Black	50
PSCTB36	36"	Black	50
PSCTN36	36"	Natural	50
PSCTB48	48"	Black	50
PSCTN48	48"	Natural	50

Anchor Kits



- Use to anchor concrete, block, stucco, wood, stone, drywall and more

SKU	Size
PSAK10H	#10 x 1 1/4"
PSAK14J	#14 x 1 1/2"

Acid Brushes



- 3/8"
- For use on flux, pastes and other chemicals
- Hollow tin handle
- 100% horse hair bristle

SKU
PS10001

Chip Brushes



- Wood handle chip brush
- Natural bristle

SKU	Size
PS67191	1/2"
PS67192	1"
PS67193	1 1/2"
PS67194	2"
PS67195	2 1/2"
PS67196	3"
PS67198	4"

Fitting Brushes



- Concave surface plastic handle
- Tempered high carbon kinked steel bristles
- Galvanized 2-ply wire stem

SKU	Size
PS0644	1/4"
PS0645	3/8"
PS0646	1/2"
PS0648	3/4"
PS0649	1"
PS0650	1 1/4"
PS0651	1 1/2"
PS0652	2"
PS0653	2 1/2"

Fitting Brushes



- T-Handle
- Tempered high carbon kinked steel bristles
- Galvanized 2-ply wire stem

SKU	Size
PS0654	3"
PS0655	4"

Fitting Brushes



- 2-ply wire loop handle
- Tempered high carbon kinked steel bristles
- Galvanized 2-ply wire stem

SKU	Size	Pkg Qty
PS546	1/2"	1
PS546BP	1/2"	100
PS548	3/4"	1
PS548BP	3/4"	100
PS549	1"	1
PS550	1 1/4"	1
PS551	1 1/2"	1
PS552	2"	1

Fitting Brushes



- Hex shaft
- Tempered high carbon kinked steel bristles
- Galvanized 2-ply wire stem

SKU	Size
PS9546	1/2"
PS9548	3/4"

Fitting Brushes



PROSELECT

- Heavy duty
- Flat surface plastic handle is easy to hold
- Tempered high carbon straight steel bristles
- Galvanized 4-ply wire stem

SKU	Size
PSHDFBD	1/2"
PSHDFBF	3/4"
PSHDFBG	1"
PSHDFBH	1 1/4"
PSHDFBJ	1 1/2"
PSHDFBK	2"

Pipe Dope Brushes



PROSELECT

- 3/4"
- For use on flux or other pastes
- Round tapered wooden handle
- 100% horse hair bristle

SKU
PS10007


Cleaning Tools



RAPTOR®

- 4-in-1 tool
- Cleans inside and outside of both 1/2" and 3/4" copper tube
- Cleans pipe and fittings

SKU
RAP50185



NEED FERGUSON.COM ON THE GO?

NO PROBLEM.

The FERGUSON.COM mobile website makes it easy for you to get the products and services you need no matter what device you use or where your work takes you. Discover more at FERGUSON.COM.

Duct Tapes



PROSELECT

- Size: 2" x 60 yds
- Tears evenly and shreds minimally
- Adheres well to irregular surfaces
- Won't twist or curl during application
- Made from high quality polyester (PET) cloth, polyethylene (PE) film, and a natural rubber, pressure-sensitive adhesive
- Tested in accordance with UL-723, HUD and BOCA rated

SKU	Grade	Color/Finish
PSDTC260B	Premium	Black
PSDTC260S	Premium	Silver
PSDTU260S	Utility	Silver

Electrical Tapes



PROSELECT

- Size: 3/4" x 60' x 7 mil
- For installation purposes and professional use
- Low voltage, Phase A
- Pressure-sensitive adhesive used to insulate electrical wires
- UL Listed E50292

SKU
PSXET

PTFE Pipe Thread Tapes



PROSELECT

- Yellow gas
- 1.2 g/cm^3 density
- Intended for application to male threads of metal pipe not exceeding 1 1/2"
- Used primarily in assemblies handling gasoline, naphtha, benzene, kerosene and petroleum oils to make joints tight against leakage
- Adaptable in some cases for application on pipe used with devices handling propane, butane or natural gas at a pressure not over 300 psi (2070kPa)
- 100% PTFE
- Color/Finish: Yellow

SKU	Size
PSGTTD260	260" L x 1/2" W
PSGTTD520	520" L x 1/2" W

PTFE Pipe Thread Tapes




PROSELECT

- High density
- 1.2 g/cm^3 density
- Can be used on all types of threaded fittings for passage of potable and non-potable water, most chemicals, oxygen, liquid and natural gas, hydraulic lines and high-pressure lines not exceeding 1 1/2" in diameter
- 100% PTFE
- Color/Finish: White
- Meets MIL-spec T-27730A

SKU	Size
PSMTTD260	260" L x 1/2" W
PSMTTD520	520" L x 1/2" W
PSMTTF520	520" L x 3/4" W

PTFE Pipe Thread Tapes



PROSELECT

- Standard density
- 0.35 g/cm^3 density
- Can be used on all types of threaded fittings for passage of water potable and non-potable, most chemicals, oxygen, gas, hydraulic and high-pressure lines to 1 1/2" in diameter
- Not for use on liquid fuels such as gasoline or diesel
- 100% PTFE
- Teflon
- Color/Finish: White
- Meets MIL-spec T-27730A

SKU	Size
PSTTD260	260" L x 1/2" W
PSTTF260	260" L x 3/4" W
PSTTD520	520" L x 1/2" W
PSTTF520	520" L x 3/4" W
PSTTG520	520" L x 1" W

Pipe Wraps



PROSELECT

- Non-corrosive, pressure-sensitive adhesive tape
- For use above or below ground as a rust preventer and UV inhibitor
- Moisture resistant
- Approved for use on all types of pipe including gas and oil pipe
- UPC Certified

SKU	Size	Thickness	Color/Finish
PSPWT110	1" x 100'	10 mil	Black
PSPWT210	2" x 100'	10 mil	Black
PSPWT210Y	2" x 100'	10 mil	Yellow
PSPWT220	2" x 100'	20 mil	Black
PSPWT410	4" x 100'	10 mil	Black
PSPWT410Y	4" x 100'	10 mil	Yellow

Knit Gloves



PROSELECT

- Industrial grade
- Seamless
- Textured latex palm for superior grip and chemical resistance
- Cotton/poly blend

SKU	Size
PSG17552	M
PSG17553	L
PSG17554	XL

PVC Gloves



PROSELECT

- Gauntlet style
- Extra Long Length: 14"
- Provides basic protection from oils, greases, acids and petrochemicals
- One size fits all
- PVC

SKU
PSG18156

Welder's Gloves



PROSELECT

- 1 piece back Gunn pattern glove made from select cowhide with wing thumb
- One size fits all
- Cotton/poly blend lining

SKU
PSG21106

Work Gloves



PROSELECT

- 2 1/2" rubberized cuff
- Cow leather palms, fingertips and knuckle with cotton back
- Cotton/poly blend lining

SKU	Size
PSG20452	M
PSG20453	L
PSG20454	XL

Disposable Gloves



PROSELECT

- Non-sterile
- Beaded cuff
- Textured finish
- Latex free
- Powder free
- Material: Rubber/Nitrile
- Package Quantity: 50 pairs/box

SKU	Size
PSG14102PK	M
PSG14103PK	L
PSG14104PK	XL

Disposable Gloves



PROSELECT

- Non-sterile
- For industrial use only
- Powder free
- Material: Natural Rubber Latex
- Package Quantity: 50 pairs/box

SKU	Size
PSG14302PK	M
PSG14303PK	L
PSG14304PK	XL

Driver Gloves



PROSELECT

- Driver made in Gunn pattern with straight thumb
- C Grade cow grain leather with shirred elastic back

SKU	Size
PSG20152	M
PSG20153	L
PSG20154	XL

Driver Gloves



PROSELECT

- Driver made in Gunn pattern with keystone thumb with shirred elastic back
- All cow leather

SKU	Size
PSG20352	M
PSG20353	L
PSG20354	XL

Jersey Gloves



PROSELECT

- Size: L
- 100% Cotton

SKU
PSG16323

Cut Resistant Gloves



PROSELECT

- Seamless knit Kevlar® shell protects against abrasion and cuts
- Cut resistant rubber palm
- EN Cut Level 4, ANSI Cut Level 2 Protection

SKU	Size
PSG12152	M
PSG12153	L
PSG12154	XL

Cut Resistant Gloves



PROSELECT

- High performance synthetic
- Technical synthetic performance fabric protects against abrasions and cuts
- High performance polyethylene
- EN Cut Level 3, ANSI Cut Level 2 Protection

SKU	Size
PSG12252	M
PSG12253	L
PSG12254	XL

Nitrile Coated Gloves



PROSELECT

- 100% nitrile foam coating

SKU	Size
PSG14452	M
PSG14453	L
PSG14454	XL

Open Mesh Abrasive Cloths



PROSELECT

- Mesh Size: 18
- 180 grit aluminum oxide
- Waterproof
- Open mesh cloths last longer than sand cloth
- To clean, rinse with running water or tap on a hard surface

SKU	Size
PS0602	1 1/2" x 5 yd
PS0603	1 1/2" x 10 yd
PS0604	1 1/2" x 25 yd

Open Mesh Abrasive Cloths



PROSELECT

- Mesh Size: 24
- 180 grit aluminum oxide
- Waterproof
- Super flexible
- Open mesh cloths last longer than sand cloth
- FLEX Mesh has a tough and ultra flexible small hole backing
- To clean, rinse with running water or tap on a hard surface

SKU	Size
PS0605	1 1/2" x 5 yd
PS0606	1 1/2" x 10 yd

Sand Cloths



PROSELECT

- 120 grit aluminum oxide grain
- Use for cleaning, polishing, and deburring copper tubing, copper pipe, fitting, plastic pipe and other soft metal products
- Color/Finish: Brown

SKU	Size
PS0402	1 1/2" x 5 yd
PS0403	1 1/2" x 10 yd
PS0404	1 1/2" x 25 yd

Sand Cloths



PROSELECT

- 120 grit aluminum oxide grain
- Waterproof
- Use for cleaning, polishing, and deburring copper tubing, copper pipe, fittings, plastic pipe and other soft metal products
- Color/Finish: Blue

SKU	Size
PS0503	1 1/2" x 10 yd
PS0504	1 1/2" x 25 yd

100% Silicone Caulk



- For interior/exterior use
- Excellent adhesion with lasting flexibility
- Cured sealant is mildew resistant
- VOC CARB non-chem curing (n.a) < 3.0%
- Size: 10.1 oz

SKU	Color/Finish
PFC500ALU	Aluminum
PFC500CLR	Clear
PFC500WHT	White

Latex Tub & Tile Caulk



- Fast curing, durable, mildew resistant
- Can also be used for kitchen and bath applications
- VOC CARB non-chem curing (n.a) < 1.5%
- Color/Finish: White

SKU	Size
PFC301WHT	5.5 oz
PFC300WHT	10.1 oz

Acrylic Latex Caulk



- For interior/exterior use
- 15-year life expectancy
- Paintable with latex or oil based paints
- Soap and water clean up
- Cured sealant is mildew resistant
- Do not use for structural repairs
- Do not use below grade or underwater
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 10.1 oz
- Color/Finish: White

SKU
PFC100WHT

RTV High Temperature Silicone Caulk



- Single component room temperature cure
- Continuous Operating Temperature Range: 75°F to 500°F (-60°C to 260°C)
- Excellent electrical insulation properties
- Excellent resistance to weather, ozone, UV and chemicals
- VOC CARB non-chem curing (n.a) < 3.0%
- Size: 10.1 oz
- Color/Finish: Red

SKU
PFC700RED

Expanding Polyfoam



- Fills large or small holes, cracks, gaps and pipe penetrations
- Paintable
- Can be cut and sanded prior to painting
- CFC free
- Size: 12 oz

SKU
PFM90037

Siliconized Acrylic Caulk



- For kitchen/bath use
- Dries bright white
- Cured caulk is mildew resistant
- Soap and water clean up
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 5.5 oz

SKU	Color/Finish
PFC401ALM	Almond
PFC401BIS	Biscuit
PFC401CLR	Clear
PFC401WHT	White

Siliconized Acrylic Caulk



- Non-flammable
- Neutral odor
- UV stabilized to guard against premature yellowing
- Can be painted over if desired
- Soap and water clean up
- Goes on white, dries to translucent clear in approximately 10 to 14 days
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 10.1 oz

SKU
PFC600CLR

Siliconized Acrylic Latex Caulk



- For interior/exterior use
- 35-year life expectancy
- Paintable with latex or oil based paints
- Soap and water clean up
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 10.1 oz
- Color/Finish: White

SKU
PFC200WHT

Caulk Guns



- Accepts industry standard 10.1 oz cartridge

SKU
PFCG

Caulk Guns



- Drip free
- Capacity: 12 oz
- Integrated plunger
- GSA approved

SKU
RAP11002

Caulk Guns



- Professional grade
- Capacity: 12 oz
- Steel frame
- Integrated plunger
- Smooth design for accurate application
- Ladder hook
- GSA approved

SKU
RAP11003

Hydraulic Cements



- For repair in masonry surfaces including ruptured concrete water pipes
- Compounded to withstand continual exposure to water even under pressure
- Sets rapidly for emergency repairs with minimal downtime
- For industrial, commercial and residential applications above or below grade
- Repairs leaks in sewer pipes, basements and manholes

SKU	Size	Type
PSHYD1GALREG	1 gal	Regular Set
PSHYD5GALFAS	5 gal	Fast Set
PSHYD5GALREG	5 gal	Regular Set

Patching Cements



- Ready to use in approximately 60 mins, fast initial setting (9-11 mins)
- Each bag covers approximately 10 square feet at 1/2" depth
- Size: 50 lb

SKU
PSPC50LB

For Installation Tools see P. 213-226





FNW™

FNW.COM



Mirabelle®

MIRABELLEPRODUCTS.COM



MONOGRAM BRASS®

MONOGRAMBRASS.COM




PARK HARBOR®

PARKHARBORLIGHTING.COM



PROFLO®

PROFLO.COM



PROSELECT™

PROSELECTPRODUCTS.COM



RAPTOR®

RAPTORTOOL.COM

Index

Product Category

A

Access Covers, Doors & Panels **93**
Adapters,
Compression 126
Copper 124
CPVC Transition Fittings 124
Dielectic Nipples 125
Trap 79
Aerators **34**
Air Admittance Valves **94-95**
Air Gaps **71**
Air Vents **94-95**
Anchor Kits **230**
Anode Rods **162**

B

Backwater Valves **152**
Ball Valves,
Brass 148
CPVC 148
PEX 148-149
PVC 149
Repair Kits 148
Ballcocks **61**
Bar Faucets **41-42**
Bar Sinks **67-68**
Baseboard Diffusers **196**
Baseboard Registers **189**
Baseboard Return Grilles **202**
Basin Faucets **176**
Basket Strainer Washers **71**
Basket Strainers **71-73**
Bath Faucet Accessories,
Aerators 34
Cartridges 34
Diverter Stems 35
Faucet Balls 35
Handles 35
Plug Buttons 35
Shower Arms 26
Stems 35
Bath Faucets,
Handshower Kits 30
Handshower Mounting Accessories 31
Handshowers & Hoses 29-31
Roman Tub 33
Rough-in Valves 29
Shower Arm Diverters 32
Shower Controls 32
Shower Valves 28
Showerheads 24-26
Single Handle Lavatory 17-18
Single Handle Shower Faucets Trim 21-22
Single Handle Tub/Shower Faucets 23
Slide Bars 32
Three Handle Tub/Shower Faucets 24
Tub Spouts 27-28
Two Handle Lavatory 18-20, 177
Two Handle Shower Faucets Trim 22
Two Handle Tub/Shower Faucets 24
Vacuum Breakers 32
Widespread Lavatory 20
Bath Hardware,
Grab Bars 177
Knob Handles 35
Robe Hooks 35
Shower Rods & Accessories 36
Soap Dishes 36
Toilet Tissue Holders 36-37
Towel Bars 37
Towel Rings 37
Bathing Accessories,
Cable Drains 12
Cover Plates 14-15
Drains 15-16
Shower Elbows 16
Stoppers 15
Waste Kits 12-14
Bathing,
Shower Bases 12
Soakers 8-10
Steel Tubs 10-11
Whirlpools 5-8
Blades, Reciprocating Saw **214**
Boiler Drains **152**
Bolts,
Eye 181
Stove 228
T-Bolts 181
Toggle 228
Brackets,
Hose 137
Pipe Support 121-122
Brass Fittings,
Adapters 124
Chrome 129-131
Compression Adapters 126
Compression Caps 126
Compression Elbows 105, 126-127
Compression Nuts 127
Compression Plugs 127
Compression Sleeves 127
Compression Tees 128
Compression Unions & Adapters 128-129
CPVC Transition 124
Dielectric Nipples & Unions 125
Flare 131-133
Hose 133-134
Nose Pieces 125
Union Valve Connectors 129
Brushes,
Acid 230
Chip 230
Fitting 230-231
Pipe Dope 231

C

Cable Drains **12**
Cable Ties **230**
Caulking,
Acrylic Latex 235
Guns 236
Latex Tub & Tile 235
Silicone 235
Siliconized Acrylic 235-236
Siliconized Acrylic Latex 236
Ceiling Diffusers **196, 198-199**
Ceiling Diffusers for T-Bar **196-200**
Cement Tools **216**
Cements,
Hydraulic 236
Patching 236
Center Outlet Continuous Waste **85**
Check Valves **150-151, 157**
Chrome Fittings,
Brushings 130
Caps 130
Couplings 130
Elbows 129
Nipples 130-131
Tees 131
Unions 131
Clamps,
Hose 159-160
Pipe 120-121
Repair 165
Cleaning Tools **231**
Cleanouts & Components **159-160**
Closet Bolts **96-97**
Closet Connectors **102-103**
Closet Flanges **98-99**
Closet Screws **96-97**
Closet Supply Kits **111, 114**
Closet Supply Tubes **102**
Compression,
Adapters 126
Caps 126
Couplings 164-165
Elbows 105, 126-127, 129, 131
Inserts 129
Nuts 127
Plugs 127
Sleeves 127
Tees 128
Union Valve Connectors 129
Unions & Adapters 128-129
Condensate,
P-Traps 209
Pump Safety Switches 209
Pumps 209-210
Running Traps 209
Condenser Pads **208**
Connectors,
Closet 102
Closet Supply Tubes 102
Dishwasher 104-105, 126
Ice Maker 104-105
Lavatory 103-104
Washing Machine 105-106
Water Heater 103, 106
Couplings,
Compression 164-165
Compression Gaskets 161
No Hub 160-161
Slip Fix 165
Cover Plates **14-15**
Curved Blade Registers **189-191**
Cutters,
Deburring Tools 222
Inside Pipe 222
Pipe & Tubing 222
Pipe Reamers 222

D

Dampers **201**
Dielectric Unions **125**
Diffusers,
Backpans 198
Baseboard 196
Ceiling 196, 198-200
Ceiling for T-bar 196-198
Dampers 201
Duct Rings 201
Floor 199
Inlet Collars 200
Lock Slide Sets 200
Push Pins 200
Register Sets 200
Round Ceiling 200
Spiral Duct 200
T-Bar Plaster Frames 201
Dishwasher,
Connectors 104-105
Drain Hoses 105
Elbows 105
Disposer Flanges **74**
Distribution Units **116**
Diverter Stems **35**
Drain Grids **138-139**
Drains,
Area 135
Barrels 135-136
Bases 136
Bell Trap 135
Boiler 152
Branch Tailpieces 79-80
Cable 12

Cleanouts & Assemblies....135
Commercial....135-138
Flanged Tailpieces....80-81
Floor....136
General Purpose....138
Grids....66, 138-139
Lavatory....65-66
Offset....66
P-Traps....77-79, 84-85, 136
Roof....137
S-Traps....85
Sewer Boxes....135
Shower....139-141
Sink Traps....79
Strainers....141
Trap Adapters....79
Trap Primer Tailpieces....81
Underdeck Clamp Kits....138
Waste & Overflow Components & Kits....12-16
Drinking Water Faucets....43
Duct Rings....201

E

End Outlet Continuous Waste....82-83
Escutcheons....88-90
Extension Cords,
Extreme Weather....214
Ground Fault Current Interrupters....215
Heavy Duty....214
Medium Duty....214
Power Block Adapters....215
Power Supply....215
Twist-Lock....215
Extension Tubes....81-82

F

Fasteners & Installation Supplies,
Brushes....230-231
Caulking....235-236
Fasteners....227-230
Gloves....233-234
Sand & Mesh Cloths....234
Screws....229
Tapes....232
Fasteners,
Anchor Kits....230
Bolts & Screws....227-228
Cable Ties....230
Hex Nuts....228
Rod Couplings....228
Washers....228-229
Faucet Balls....35
Faucet Cartridges....34
Faucet Hole Covers....43
Faucets,
Bar....41-42
Basin....176
Blocks....176
Exposed Shower....176
Kitchen....39-41
Laundry....176-177
Lavatory....17-20, 177
Roman Tub....33
Service Sink....176
Shower Only....21-22
Tub/Shower....23-24
Fill Valves....60
Fixed Bar Filter Grilles....202
Fixtures,
Air Gaps....71
Bar Sinks....67-68
Basket Strainers & Washers....71-73
Disposer Flanges....74
Floor & Laundry Sinks....75-76
Kitchen Sinks....67-70
Lavatory Drains....65-66
Lavatory Sinks & Accessories....62-64
Pedestal Lavatories....64
Toilet Seats....56-58
Toilet Tank & Repair....59-61
Toilets....45-54
Urinals....55
Flame Guards....226
Flanges,
Brass Closet....98
Cast Iron Closet....98-99
Plastic Closet....99
Socket....94
Urinal Kits....100
Flare,
Caps....131
Elbows....131
Nuts....132
Plugs....132
Tees....132
Unions....132-133
Float Switches....157
Floor & Laundry Sinks,
Mop Basins & Guards....75
Mop Hangers....75
Laundry & Utility Sinks....75-76
Floor Ceiling Plates....90
Floor Diffusers....199
Floor Registers....191
Floor Return Air Grilles....203
Floor Sinks....137
Flush Levers....59, 61
Flush Valves....60-61
FNW Products....167-175

G

Garden Hose,
Caps....133
Fittings & Valves....133-134
Washers....133
Wyes....133
Gaskets,
Service Weight (SV)....161
Tank to Bowl....97-98
Gate Valve Stem Extensions....182
Gate Valves....151
Gauges,
Gas....91
Pressure....91
Water....91
Gloves,
Cut Resistant....234
Disposable....233
Driver....233
Jersey....234
Knit....233
Nitrile Coated....234
PVC....233
Welder's....233
Work....233
Grab Bars....177
Grid Drains....66
Grilles,
Baseboard Return....202
Fixed Bar Filter....202
Floor Return Air....203
Return Air....203-208
Return Air Filter....203-205, 207-208
Toe Space....208

H

Hammers,
Ball Pein....217
Brick....217
Dead Blow....217
Engineer....217
Fiberglass Claw....217
HVAC Setting....217
Steel Claw....217
Handles....35
Handshowers,
Five Function....29-30
Mounting Accessories & Kits....30-31
Shower Arm Diverters....32
Shower Controls....32
Shower Hoses....31
Single Function....29
Slide Bars....32
Three Function....29
Vacuum Breakers....32
Hanger/Pipe Straps....118-119
Hex Keys....218
Hole Saws & Arbors....213
Hose & Spray Kits....43
Hose Bibbs & Ball Valves....143-144
Hose Clamps....159-160
HVAC,
Baseboard Diffusers....196
Baseboard Registers....189
Baseboard Return Grilles....202
Ceiling Diffusers....196-200
Condensate P-Traps....209
Condensate Pumps & Safety Switches....209-210
Condenser Pads....208
Curved Blade Registers....189-191
Dampers....201
Duct Rings....201
Fiberglass Backpans....198
Fixed Bar Filter Grilles....202
Floor Diffusers....199
Floor Registers....191
Floor Return Air Grilles....203
Inlet Collars for T-Bar Diffusers....200
Lock Slide Sets....200
Non-Metallic Registers....191-192
Push Pins for Inlet Collar....200
Register Sets....200
Return Air Filter Grilles....203-205
Return Air Grilles....205-208
Running Traps....209
Sidewall & Ceiling Registers....192-195
Spiral Duct Diffusers....200
T-Bar Plaster Frames....201
Thermostats....211
Toe Space Grilles....208
Wall Plates....211
Hydrant Setters....183
Hydronic Valves....153

I

Ice Maker,
Connectors....104-105
Kits....104

J

J-Bends....83-84

K

Keys,
Curb Stop....182
Gate Valve....182-183
Street....183
Valve....183
Kitchen & Bar Faucet Accessories,
Faucet Hole Covers....43
Hose & Spray Kits....43
Soap/Lotion Dispensers....43
Spray Heads....43
Spray Hoses & Guides....43-44
Water Dispensers....43

Kitchen & Bar Sink Accessories,
Air Gaps ... 71
Basket Strainers & Washers ... 71-73
Disposal Flanges ... 74
Sink Clips ... 70
Kitchen Faucets,
Pull-Down/Pull-Out ... 39
Single Handle ... 40
Two Handle ... 41
Kitchen Sinks,
Complete Kits ... 67
Double Bowl ... 69-70
Single Bowl ... 68-69
Knives & Blades ... 226

L

Laundry Faucets ... 176-177
Laundry Sinks ... 75-76
Lavatory Connectors ... 103-104
Lavatory Drains ... 65-66
Lavatory Faucets,
Single Handle ... 17-18
Two Handle ... 18-20, 177
Widespread ... 20
Lavatory Sinks,
Pedestal ... 64
Self-Rimming ... 62
Undermount ... 63
Wall-Mount ... 63
Lavatory Supply Kits ... 111, 115-116
Levels ... 226
Lift Rod Extensions ... 66
Lift Wires ... 100
Log Lighter Valves ... 149-150
Lubricants ... 181

M

Manhole Cover Hooks ... 183
Masonry Lines ... 226
Meter Box Lid Lifters ... 183
Mop Basins & Guards ... 75
Mop Hangers ... 75

N

Needle Valves ... 153-154
Non-Metallic Registers ... 191-192
Nose Pieces ... 125
Nut Drivers ... 218
Nuts,
Hex ... 228
Slip ... 91

O

Offset Drains ... 66
Outlet Waste,
Brass ... 82-83
Disposer Kits ... 83
Plastic ... 83, 85

P

P-Traps ... 77-79, 84-85
Pedestal Lavatories ... 64
Pipe,
Clamps ... 120-121
Straps ... 118-120
Support Brackets ... 121-122
Pipe/Tubing Tools ... 225
Plates,
FHA ... 122
Interlocking Safety Plates ... 122
Safety ... 123
Straps ... 123
Pliers ... 221-222
Plug Buttons ... 35
Plugs, Cleanout ... 159
Plungers ... 95
Polyfoam ... 235
Pressure Gauges ... 91
Pumps,
Battery Back Up Kits ... 157
Check Valves ... 157
Condensate ... 209-210
Drain/Utility ... 156, 158
Effluent ... 156
Float Switches ... 157
Foot Valves ... 157-158
Packaged ... 156-158
Sewage ... 156, 158
Sump ... 155, 158
Tanks ... 158

R

Registers,
Baseboard ... 189
Curved Blade ... 189-191
Floor ... 191
Non-Metallic ... 191-192
Sidewall ... 192-193
Sidewall/Ceiling ... 193-195
Repair Clamps ... 165
Return Air Filter Grilles ... 203-205
Return Air Grilles ... 205-208
Robe Hooks ... 35
Roman Tub Faucets ... 33
Roof Drains ... 137
Rough Plumbing,
Brass Fittings ... 124-134
Cast Iron ... 159-161
Drains ... 135-142
Plumbing Valves ... 148-154
Pumps ... 155-158
Repair ... 162-165
Specialty ... 93-95
Stop Valves ... 106-113
Supply ... 102-117
Supply Kits ... 113-116
Supply Tubes & Flex Connectors ... 102-106
Supports ... 118-123
Testing ... 91-92
Toilet Repair ... 96-101
Tubing ... 116
Tubular ... 77-90
Wall Faucets & Hydrants ... 143-147
Rough-in Valves ... 29
Running Traps ... 209

S

S-Traps ... 85
Sand & Mesh Cloths ... 234
Saws,
Cable ... 222
Hacksaws ... 223
Hole ... 213
Jab ... 223
Mini Hacksaws ... 223
Plumber ... 223
PVC ... 223
Screwdrivers ... 224-225
Screws,
Cap ... 227
Self Piercing ... 229
Self Tapping ... 229
Wood ... 228
Seat Discs ... 100
Service Sink Faucets ... 176
Service Sink P-Traps ... 136
Sewage Pumps ... 156, 158
Shower Arm Diverters ... 32
Shower Arms ... 26
Shower Bases ... 12
Shower Drains ... 139-141
Shower Elbows ... 16
Shower Faucets,
Commercial/Industrial ... 176
Single Handle ... 21-22
Two Handle ... 22
Shower Pan Liners ... 142
Shower Rods & Accessories ... 36
Showerheads ... 24-26
Sidewall & Ceiling Registers ... 192-195
Sillcocks ... 144
Sink Clips ... 70
Sink Traps ... 79
Sinks,
Bar ... 67-68
Floor ... 137
Floor Grates & Hoses ... 137
Kitchen ... 67-70
Laundry & Utility ... 75-76
Lavatory ... 62-64
Slide Bars ... 32
Snips ... 223-224
Soap Dishes ... 36
Soap/Lotion Dispensers ... 43
Spray Heads ... 43
Spray Hoses & Guides ... 43-44
Stems ... 35
Stop Valves ... 106-113
Stoppers ... 15
Strainers ... 141
Stud Guards & Shoes ... 123
Sump Pumps ... 155, 158
Supply Kits ... 113-116
Supply Stops ... 106-113

T

Tailpieces,
Branch ... 79-80
Flanged ... 80-81
Trap Primer ... 81
Tank Balls ... 100
Tank Bolt Sets ... 97
Tank Pal Clips ... 97
Tank Repair Kits ... 100
Tank to Bowl Gaskets ... 97-98
Tanks,
Pump ... 158
Thermal Expansion ... 162
Tape Measures ... 225-226
Tapes,
Duct ... 232
Electrical ... 232
Pipe Thread ... 232
Pipe Wrap ... 232
Test Caps & Plugs ... 91-92
Thermal Expansion Tanks ... 162
Thermostats,
Non-Programmable ... 211
Programmable ... 211
Toe Space Grilles ... 208
Toilet Flange Repair ... 98
Toilet Flappers ... 59-60
Toilet Repair Parts & Accessories,
Ballcocks ... 61
Closet Bolts & Screws ... 96-97
Closet Flanges ... 98-99
Fill Valves ... 60
Flush Levers ... 59, 61
Flush Valves ... 60-61
Lift Wires ... 100
Plungers ... 95
Seat Discs ... 100
Tank Balls ... 100
Tank Pal Clips ... 97
Tank Repair Kits ... 100
Tank to Bowl Bolts ... 97
Tank to Bowl Gaskets ... 97-98
Toilet Flange Repair ... 98

Toilet Flappers 59-60
Toilet Shims 95
Toilet/Urinal Spuds & Washers 95
Urinal Flange Kits 100
Wax Rings 100-101
Toilet Seats,
Children's 57
Elongated 56-57
Round 56-57
Toilet Shims 95
Toilet Tissue Holders 36-37
Toilet/Urinal Spuds & Washers 95
Toilets,
Children's 52
Complete Toilet Kits 45
Elongated 46-51
Flush Valve 52
Round Front 46-51
Tools,
Bits & Saws. 213-214
Cement Tools 216
Curb Stop Keys 182
Cutting Tools 222
Extension Cords & Worklights 214-215
Gate Valve Keys 182-183
Hammers 217
Hex Keys 218
Hydrant Setters 183
Hydrant Wrenches 183
Knives & Blades 214, 226
Manhole Cover Hooks 183
Material Handling 226
Measuring 225-226
Nut Drivers 218
Pipe/Tubing 225
Pliers 221-222
Saws 222-223
Screwdrivers 224-225
Snips 223-224
Wrenches 181-183, 219-221
Towel Bars 37
Towel Rings 37
Trap Adapters 79
Trap Covers 85-88
Trap Primer Valves 141-142
Tub & Shower Faucets,
Showerheads 24-26
Single Handle 23
Three Handle 24
Tub Spouts 27-28
Two Handle 24
Tub & Shower Valves,
Rough-in 29
Shower 28
Tub Spouts 27-28
Tubing 116
Tubular Repair Fittings 84
Tubular,
Brass 77-84
Escutcheons 88-90
Floor Ceiling Plates 90
Nuts 90-91
Plastic 84-85
Trap Covers 85-88
Washers 90

U

Unions,
Compression 128-129
Dielectric 125
Socket 95
Urinal Flange Kits 100
Urinals 55
Utility Knives 226
Utility Pumps 156, 158
Utility Worklights 215

V

Vacuum Breakers 32, 146
Valve Boxes & Accessories 184-187
Valve Setters 183
Valves,
Backwater 152
Ball 148-149
Boiler Drain 152
Check 150-151, 157
Foot 157-158
Gas 149
Gate 151
Hose Bibb 143
Hydronic 153
Log Lighter 149-150
Needle 153-154
Stop 147
Stop & Waste 147
Supply Stop 106-113
Trap Primer 141-142
Washing Machine 151-152
Water Heater Drain 163
Vents,
Air Admittance Valves 94-95
In-Line 94
Wall Boxes 94

W

Wall Bends 84
Wall Boxes 94
Wall Faucets & Hydrants,
Hose Bibbs 143-144
Repair Kits 145-146
Sillcocks 144
Stop Valves 147
Vacuum Breakers 146
Yard 146-147
Wall Hydrants 145
Wall Plates 211
Washers,
Fender 229
Flanged Tailpiece 90
Flat 228-229
Slip Joint 90
Slip Nut 90
Washing Machine,
Connectors 105-106
Tees 106
Valves 151-152
Waste Arms 84
Water Gauges 91
Water Hammer Arrestors 116-117
Water Heater Connectors 103, 106
Water Heater Repair,
Adapter Kits 163
Anode Rods 162
Clamps 165
Couplings 164-165
Dip Tubes 162
Drain Valves 163
Elements 163-164
Nipples 164
T&P Discharge Pipes 163
T&P Relief Valves 163
Thermal Expansion Tanks 162
Thermocouples 162
Thermostats 162
Tune-Up Kits 162
Waterworks,
Accessory Packs 179-180
Curb Stop Keys 182
Duc Lugs 181
Eye Bolts 181
Gate Valve Keys & Stem Extensions 182-183
Hydrant Setters 183
Manhole Cover Hooks 183
Meter Box Lid Lifters 183
Pipe Lubricants 181
Street Keys 183
T-Bolts 181
Valve Boxes 184-187
Valve Keys 183
Valve Setters 183
Wrenches 181-183
Wax Rings 100-101
Whirlpools 5-8
Wire Strippers 222
Wrenches,
Adjustable 219
Basin 219
Drain 219
Handle Pullers 219-220
Hydrant 183
Nut 220
Pipe 220
Plug 220
Ratchet 181-182
Seat 220
Spud 221
Strainer 221
Strap 221
Torque 221

Y

Yard Hydrants 146-147

ACF3001CRT 34
ACF3001LSCRT 34
IMJAP10 179
IMJAP12 179
IMJAP14 179
IMJAP16 179
IMJAPHDI10 179
IMJAPHDI12 179
IMJAPHDIM 179
IMJAPHDIP 179
IMJAPHDIU 179
IMJAPHDIX 179
IMJAPM 179
IMJAPP 179
IMJAPU 179
IMJAPX 179
IMJBGP10 179
IMJBGP12 179
IMJBGP14 179
IMJBGP16 179
IMJBGPM 179
IMJBGPP 179
IMJBGPU 179
IMJBGPX 179
IMJG10 180
IMJG12 180
IMJG14 180
IMJG16 180
IMJGA10 179
IMJGA12 179
IMJGA14 179
IMJGA16 179
IMJGAM 179
IMJGAP 179
IMJGAU 179
IMJGAX 179
IMJGM 180
IMJGP 180
IMJGU 180
IMJGX 180
IMJTBGP10 180
IMJTBGP12 180
IMJTBGPM 180
IMJTBGPP 180
IMJTBGPU 180
IMJTBGPX 180
IMJTG10 180
IMJTG12 180
IMJTGAP10 180
IMJTGAP12 180
IMJTGAPM 180
IMJTGAPP 180
IMJTGAPU 180
IMJTGAPX 180
IMJTGM 180
IMJTGP 180
IMJTGU 180
IMJTGX 180
IVB160BSE 186
IVB24BOTONLY 185
IVB36BOTONLY 185
IVB6BSE 186
IVB910SWR 184
IVB910TOP 184
IVB910WTR 184
IVB940DSLID 184
IVB940TOP18 184
IVBABS15 185
IVBABS24 185
IVBABS30 185
IVBABS36 185
IVBABS48 185
IVBABS60 185
IVBATS10 185
IVBATS16 185
IVBATS26 185
IVBATS26TF 185
IVBD198FRM 184
IVBD198S 184
IVBD198W 184
IVBEXT58 184
IVBEXT59 184
IVBEXT60 184
IVBLID40W 185
IVBLID6RIBSKT 186
IVBLIDF 186
IVBLIDG 186
IVBLIDI 186
IVBLIDR 186
IVBLIDS 186
IVBLIDW 186
IVBR514G 186
IVBR514J 186
IVBR514K 186
IVBR514M 186
IVBR514P 186
IVBR514U 186
IVBSBS15 184
IVBSBS24 184
IVBSBS36 184
IVBSTS10 184
IVBSTS16 184
IVBSTS26 184
IVBSV0088 186
MB111BN 43
MB111CP 43
MB111ORB 43
MB121BN 43
MB121CP 43
MB121ORB 43
MB121PN 43
MB131BLK 43
MB131BN 43
MB131BS 43
MB131ORB 43
MB131SS 43
MB131WH 43
MB141BN 71
MB141CP 71
MB141ORB 71
MB141PN 71
MB161BLK 74
MB161BS 74
MB161WH 74
MB162BN 74
MB162BS 74
MB162CP 74
MB162ORB 74
MB162PN 74
MB162SS 74
MB162WH 74
MB163CP 74
MB163ORB 74
MB163SS 74
MB171BN 71
MB171CP 71
MB171ORB 71
MB171PN 71
MB171SS 71
MB171WH 71
MB172BLK 71
MB172BS 71
MB172WH 71
MB173BN 71
MB173ORB 71
MB201BN 106
MB201ORB 106
MB201PB 106
MB201PN 106
MB202BN 106
MB202CP 106
MB202ORB 106
MB202PB 106
MB202PN 106
MB203BN 107
MB203ORB 107
MB203PB 107
MB203PN 107
MB204BN 107
MB204CP 107
MB204ORB 107
MB204PB 107
MB204PN 107
MB205BN 107
MB205CP 107
MB206BN 107
MB206CP 107
MB207BN 107
MB207CP 107
MB208BN 107
MB208CP 107
MB208ORB 107
MB208PN 107
MB211BN 108
MB211ORB 108
MB211PN 108
MB212BN 108
MB212CP 108
MB212ORB 108
MB212PB 108
MB213BN 113
MB213ORB 113
MB221BN 102
MB221CP 102
MB221ORB 102
MB221PB 102
MB221PN 102
MB231BN 115
MB231CP 115
MB231ORB 115
MB241BN 102
MB241CP 102
MB241ORB 102
MB241PB 102
MB241PN 102
MB242BN 102
MB242CP 102
MB242ORB 102
MB242PB 102
MB242PN 102
MB251BN 113
MB251CP 113
MB251ORB 113
MB251PN 113
MB254BN 113
MB254CP 113
MB254ORB 113
MB254PN 113
MB261BN 102
MB261CP 102
MB261ORB 102
MB271BN 88
MB271CP 88
MB271ORB 88
MB271PB 88
MB271PN 88
MB272BN 88
MB272CP 88
MB272ORB 88
MB272PB 88
MB272PN 88
MB273BN 89
MB273ORB 89
MB273PN 89
MB301BN 65
MB301CP 65
MB301ORB 65
MB301PB 65
MB301PN 65
MB311BN 65
MB311CP 65
MB311ORB 65
MB311PN 65
MB312BN 65
MB312CP 65
MB312ORB 65
MB313BN 65
MB313CP 65
MB313ORB 65
MB313PN 65
MB314BN 65
MB314CP 65
MB314ORB 65
MB321BN 65
MB321CP 65
MB321ORB 65
MB331BN 65
MB331CP 65
MB331ORB 65
MB332BN 66
MB332CP 66
MB332ORB 66
MB332PN 66
MB333BN 66
MB333CP 66
MB333ORB 66
MB333PN 66
MB341BN 81
MB341ORB 81
MB341PN 81
MB351NA 66
MB361BN 77
MB361CP 77
MB361ORB 77
MB361PN 77
MB362BN 77
MB362CP 77
MB362ORB 77
MB362PB 77
MB362PN 77
MB363BN 77
MB363CP 77
MB401ORB 59
MB402BN 59
MB402PN 59
MB422BN 59
MB422ORB 59
MB423BN 59
MB423CP 59
MB423ORB 59
MB423PN 59
MB424BN 59
MB424CP 59
MB424ORB 59
MB425BN 59
MB425CP 59
MB425ORB 59
MB501BN 25
MB501CP 25
MB501ORB 25
MB502 24
MB502BN 25
MB502CP 25
MB502ORB 25
MB503BN 25
MB503CP 25
MB503ORB 25
MB511BN 29
MB511CP 29
MB511ORB 29
MB512BN 29
MB512CP 29
MB512ORB 29
MB521BN 32
MB521CP 32
MB521ORB 32
MB522BN 32
MB522CP 32
MB531BN 31
MB531CP 31
MB531ORB 31
MB541BN 32
MB541CP 32
MB541ORB 32
MB542BN 31
MB542CP 31
MB542ORB 31
MB544BN 31
MB544CP 31
MB544ORB 31
MB551BN 26
MB551ORB 26
MB551PB 26
MB551PN 26
MB552BN 26
MB552CP 26
MB552ORB 26
MB553BN 26
MB553CP 26
MB553ORB 26
MB554CP 26
MB561BN 27
MB561ORB 27
MB562BN 27
MB562ORB 27
MB563BN 27
MB563ORB 27
MB563PB 27
MB564CP 27-28
MB601BN 138
MB601CP 138
MB601ORB 138
MB601PB 138
MB601PN 138
MB602BN 138
MB602CP 138
MB602ORB 138
MB602PN 138
MB603BN 138
MB603ORB 138
MB603PN 138
MB604BN 139
MB604CP 139
MB604ORB 139
MB604PN 139
MB605BN 139
MB605CP 139
MB605ORB 139
MB605PN 139
MB606BN 139
MB606CP 139
MB606ORB 139
MB607BN 139
MB607CP 139
MB607ORB 139
MB612BN 16
MB612CP 16
MB612ORB 16
MB612PB 16
MB612PN 16
MB621BN 15
MB621CP 15
MB621ORB 15
MB621PN 15
MB622BN 15
MB622CP 15
MB622ORB 15
MB622PN 15
MB631BN 14
MB631CP 14
MB631ORB 14
MB631PB 14
MB631PN 14
MB632BN 14
MB632CP 14
MB632ORB 14
MB632PB 14
MB632PN 14
MB633BN 15
MB633ORB 15
MB633PB 15
MB633PN 15
MB642BN 12
MB642CP 12
MB642ORB 12
MB643BN 12
MB643CP 12
MB643ORB 12
MB643PN 12
MB644BN 12
MB644CP 12
MB644ORB 12
MB644PN 12
PF002 136
PF003 136
PF025 97
PF035 97
PF05036BN 32
PF05036CP 32
PF05128BN 32
PF05128CP 32
PF05130BN 32
PF05130CP 32
PF05143BN 31
PF05143CP 31
PF05289BN 31
PF05289CP 31
PF05316BN 25
PF05316CP 25
PF05324BN 25
PF05324CP 25
PF05417WH 29-30
PF05464BN 30
PF05464CP 30
PF05509CP 24-25
PF05516CP 32

PF05615CP....30
PF05688BN....31
PF05688CP....31
PF05738BN....31
PF05738CP....31
PF05786CP....29-30
PF05844BN....30
PF05844CP....30
PF061DC....153
PF100....95
PF100C22F50....118
PF100DC....152
PF100DCC....151
PF100G20F10....118
PF100G24F10....118
PF100G24F100....118
PF100G24F50....118
PF100S24F10....118
PF100S24F100....118
PF100S24F50....118
PF101....95
PF1010AD....93
PF1010SSAD....93
PF1011WH....64
PF101DC....152
PF101G28F10....118
PF101G28F100....118
PF101G28F50....118
PF101MFC....152
PF101PNC....139
PF1020CP....22
PF1021WH....64
PF102DC....151
PF102F100....118
PF102F25....118
PF102F50....118
PF103....95
PF1030CP....24
PF1033CP....24
PF103DBFPC....143
PF103DC....143
PF103DLKC....143
PF1045BS....64
PF1045WH....64
PF104DBFPC....143
PF104DC....143
PF105....95
PF105DBFPC....143
PF105DC....143
PF105DLKC....143
PF106....95
PF106DBFPC....143
PF106DC....143
PF107....95
PF107DLKC....144
PF108....95
PF108202....94
PF108DC....143
PF109....95
PF1091....27-28
PF1092....27-28
PF1093....27-28
PF1095....27-28
PF1096....27-28
PF1097....27-28
PF109FBFPC....143
PF109FC....143
PF109FLKC....143
PF110100....24, 26
PF1103WH....64
PF110FBFPC....143
PF110FC....143
PF110FLKC....143
PF1119....176
PF111FC....144
PF111FLKC....144
PF1121WHP....64
PF1125WH....62
PF1131WHP....64
PF113FC....144
PF113FLKC....144
PF115FC....143
PF116FC....143
PF117DC....144
PF118GC....144
PF119DC....144
PF120DC....144
PF1212AD....93
PF1212SSAD....93
PF127033....81
PF127044....81
PF12CCJN....118
PF12CCJNPL....118
PF12GAJN....118
PF131J....91
PF131K....91
PF131M....91
PF131P....91
PF1400TBS....48-49
PF1400TWH....48-49
PF1401TBS....46
PF1401TWH....46-47
PF140330PK....43
PF1403TBS....46-47
PF1403TWH....46-48
PF140954PK....61
PF140NC....140
PF14104WH....64
PF14108WH....64
PF14110WH....30
PF141344PK....35
PF1414AD....93
PF141548PK....35
PF141554PK....35
PF141555PK....34
PF141558PK....34
PF141566PK....35
PF141570PK....35
PF1430SS....70-71
PF1431BRSS....70-71
PF1431SS....70-71
PF1432SS....70, 72-73
PF1433BRSS....70, 72-73
PF1433SS....70, 72-73
PF1434BRSS....70, 72-73
PF1434SS....70, 72-73
PF1435SS....70, 72
PF146814....105-106
PF146815....105-106
PF146816....105-106
PF149002N....116
PF149006N....116
PF149008N....116
PF149012N....116
PF149014N....116
PF149016N....116
PF149022N....116
PF149026N....116
PF149028N....116
PF149030N....116
PF149032N....116
PF149034N....116
PF14BSBN....32
PF14BSCP....32
PF1500WH....49
PF1501WH....46
PF1503WH....47
PF1512UBS....63
PF1512UWH....63
PF151ACP....70, 72, 74
PF151CP....70, 72, 74
PF1600PAWH....50
PF1601PAWH....50
PF1603PAWH....50
PF1604PAWH....51
PF1605PAWH....51
PF1606PAWH....51
PF1612PALWH....50-51
PF1612PARWH....50-51
PF1612PAWH....50-51
PF1616AD....93
PF1700BBHEWH....52
PF1704BBHEWH....52
PF1705HEWH....51
PF1710HEWH....51
PF1712BBHEWH....52
PF1712BBLHEWH....52
PF1712BBRHEWH....52
PF1713UBS....63
PF1713UWH....63
PF1714UABS....63
PF1714UAWH....63
PF1721WH....52
PF1723WH....52
PF1731WH....52
PF18012....16
PF1805WH....55
PF1812UBS....63
PF1812UWH....63
PF1815PTWH....55
PF1815WH....55
PF1818AD....93
PF1825PTWH....55
PF1835WH....55
PF19164BS....62
PF19164WH....62
PF19168WH....62
PF191RWH....62
PF194RBS....62
PF194RWH....62
PF198RBS....62
PF198RWH....62
PF1CCJNPL....118
PF2000....79
PF20015....28
PF2001BP....59
PF200CDP10....120
PF200CDU10....120
PF200CFP10....120
PF200CFU10....120
PF200CGU10....120
PF200D....148
PF200F....148
PF200G....148
PF200H....148
PF200J....148
PF200K....148
PF200PFU10....119
PF200PSDU12....120
PF200PSFP10....120
PF200PSFU10....120
PF200PSFU12....120
PF200PSGU10....120
PF200SD....148
PF200SDU10....120
PF200SF....148
PF200SFP10....120
PF200SFU10....120
PF200SG....148
PF200SGU10....120
PF200SGX10....120
PF200SH....148
PF200SJ....148
PF200SK....148
PF200WH....85-86
PF2010....79
PF20171WH....62
PF20174BS....62
PF20174WH....62
PF20178BS....62
PF20178WH....62
PF201WH....85-86
PF2020....79
PF202WH....86
PF2030....79
PF203WH....86
PF2040....79
PF2050....79
PF205WH....86
PF210200....61
PF210420....60
PF220J....118
PF220K....118
PF220M....118
PF220P....118
PF2424AD....93
PF244....176
PF245....75
PF250....131
PF250BRCP....70, 72, 74
PF250PC....70, 72, 74
PF2800BN....37
PF2800CP....37
PF2800ORB....37
PF2820BN....21
PF2820CP....21
PF2820ORB....21
PF2830BN....23
PF2830CP....23
PF2830ORB....23
PF2831BN....36
PF2831CP....36
PF2831ORB....36
PF2841BN....35
PF2841CP....35
PF2841ORB....35
PF2851BN....37
PF2851CP....37
PF2851ORB....37
PF2870BN....33
PF2870CP....33
PF2870ORB....33
PF2890BN....37
PF2890CP....37
PF2890ORB....37
PF296....137
PF299WH....86
PF3001....29
PF3001C....29
PF3001CLS....29
PF3001F....29
PF3001FLS....29
PF3001LS....29
PF3001P....29
PF3001PLS....29
PF301....176
PF302....177
PF30P50....142
PF30S100....142
PF30S40....142
PF30U50....142
PF310400....43
PF310400WH....43
PF310410....43
PF310410WH....43
PF310430....44
PF310440....44
PF31D....150
PF31F....150
PF31G....150
PF31H....150
PF31J....150
PF31K....150
PF31L....150
PF31M....150
PF31P....150
PF31SD....150
PF31SF....150
PF31SG....150
PF31SH....150
PF31SJ....150
PF31SK....150
PF33845....119
PF33846....119
PF33847....119
PF33848....119
PF34225....91
PF34226....91
PF34240....120
PF34241....120
PF34242....120
PF34243....120
PF34244....120
PF34245....120
PF34250....121
PF34251....121
PF34252....121
PF34253....121
PF34254....121
PF34255....121
PF34256....120
PF34257....120
PF34258....120
PF34260....121
PF34261....121
PF34262....121
PF34263....121
PF34264....121
PF34265....121
PF34CCJNPL....118
PF3812CRX....102
PF3812LR....102
PF3820CRX....102
PF3820LR....102
PF3830LR....102
PF3836LR....102
PF39002....92
PF39003....92
PF39004....92
PF39006....92
PF39008....92
PF39010....92
PF39012....92
PF400....14
PF4004BS....64
PF4004WH....64
PF4008BS....64
PF4008WH....64
PF401....15
PF402....15
PF402BS....16
PF4034A....99
PF4034P....99
PF40481....95
PF40P100....142
PF40P50....142
PF40S100....142
PF40S40....142
PF40SFCD....165
PF40SFCF....165
PF40SFCG....165
PF40SFCH....165
PF40SFCJ....165
PF40SFCK....165
PF40U50....142
PF4134A....99
PF4134P....99
PF418....176
PF42800....140
PF42801....140
PF42804....135
PF42805....135
PF42806....135
PF42807....135
PF42809....135
PF42813....135
PF42816....135
PF42817....135
PF42820....138
PF42821....138
PF42834....138
PF42835....138
PF42838....136
PF42839....136
PF42840....136
PF42842....141
PF42845....135
PF42846....135
PF42847....135
PF42848....136
PF42849....152
PF42849WS....152
PF42850....137
PF42851....137
PF42852....152
PF42852SKO....152
PF42852WS....152
PF42853....152
PF42853SKO....152
PF42853WS....152
PF42854....152
PF42855....137
PF42856....137
PF42857....137
PF42858....137
PF42859....138
PF42860....209
PF42861....209
PF42862....135
PF42863....135
PF42867....140
PF42868....135
PF42869....138
PF42870....137
PF42871....137
PF42872....140

PF42873....138
PF42874....138
PF42876....136
PF42879....136
PF42882....136
PF42883....136
PF42884....136
PF42885....136
PF42889....135
PF42890....136
PF42891....136
PF42895....137
PF42896....137
PF42899....141
PF42914....152
PF42915....152
PF42915SKO....152
PF42915WS....152
PF42916....152
PF42916SKO....152
PF42916WS....152
PF42917....152
PF42918....138
PF42919....135
PF42920....135
PF42924....136
PF42926....135
PF42927....135
PF42928....135
PF42929....135
PF42930....138
PF42931....138
PF42932....138
PF42933....140
PF42934....135
PF42935....135
PF42936....135
PF42937....138
PF42938....138
PF42939....138
PF42940....139
PF42941....139
PF42942....140
PF42943....140
PF42944....140
PF42945....140
PF42946....140
PF42947....141
PF42947SQ....140
PF42950....141
PF42951....141
PF42952....141
PF42957RD....140
PF42958RD....140
PF42959RD....140
PF431D....153
PF431F....153
PF431G....153
PF431H....153
PF431J....153
PF435F....153
PF436D....153
PF436F....153
PF437D....153
PF437F....153
PF437G....153
PF437H....153
PF438D....153
PF438F....153
PF438G....153
PF438H....153
PF439D....153
PF439F....153
PF453A....100
PF4820BN....21
PF4820CP....21
PF4820ORB....21
PF4830BN....23
PF4830CP....23
PF4830ORB....23
PF4870BN....33
PF4870CP....33
PF4870ORB....33
PF49114....60
PF5004BS....64
PF5004WH....64
PF5008BS....64
PF5008WH....64
PF500B....119
PF500C....119
PF500D....119
PF500F....119
PF500G....119
PF500H....119
PF500J....119
PF500K....119
PF500WND....119
PF500WNF....119
PF500WNG....119
PF500WNH....119
PF500WNJ....119
PF500WNK....119
PF506N....105
PF507N....105
PF50DC....147
PF50SDC....147
PF50SFC....147
PF5110BSM....46, 48
PF5110HEBS....46-47
PF5110HEWH....46-47, 49
PF5110WHM....46, 48
PF5112BSM....46, 48
PF5112FLPK....60
PF5112FRPK....59
PF5112HEBS....46-47, 49
PF5112HEWH....46-47, 49
PF5112LHEWH....46-47, 49
PF5112RHEWH....46-47, 49
PF5112RWHM....46, 48
PF5112TLWHPK....61
PF5112UHEWH....46-47, 49
PF5112UWHM....46, 48
PF5112WHM....46, 48
PF5114HEWH....47, 49
PF5114WH....46
PF5114WHM....46, 48
PF513D....121
PF513F....121
PF5200BN....21
PF5200CP....21
PF5200ORB....21
PF5220BN....21
PF5220CP....21
PF5220ORB....21
PF5230BN....23
PF5230CP....23
PF5230ORB....23
PF5270BN....33
PF5270CP....33
PF5270ORB....33
PF530JM....123
PF530JS....123
PF530JU....123
PF531JS....123
PF531JU....123
PF531JX....123
PF532JU....123
PF5331....123
PF5332....123
PF5333....123
PF5360BN....25
PF5360CP....25
PF536JS....123
PF536JU....123
PF540....118
PF5411WH....63
PF5414WH....63
PF5511WH....63
PF5514WH....63
PF5518WH....63
PF600....225
PF600C....119
PF600D....119
PF600F....119
PF600G....119
PF600H....119
PF600J....119
PF600K....119
PF600L....119
PF600M....119
PF600N....119
PF600P....119
PF600U....119
PF60DC....147
PF60FC....147
PF60SDC....147
PF60SFC....147
PF610C....119
PF610D....119
PF610F....119
PF610G....119
PF610H....119
PF610J....119
PF610K....119
PF6110WH....46-47, 49
PF6112RWH....46-47, 49
PF6112WH....46-47, 49
PF6114WH....46-47, 49
PF646443....70, 72-73
PF647003....70, 72-73
PF6700BN....37
PF6700CP....37
PF6700RB....37
PF6731BN....37
PF6731CP....37
PF6731RB....37
PF6741BN....35
PF6741CP....35
PF6741RB....35
PF6751BN....37
PF6751CP....37
PF6751RB....37
PF6770BN....37
PF6770CP....37
PF6770RB....37
PF6820BN....21
PF6820CP....21
PF6830BN....23
PF6830CP....23
PF6870BN....33
PF6870CP....33
PF7002DC....147
PF7002FC....147
PF7004DC....147
PF7004FC....147
PF7009DC....144
PF7009FC....144
PF7010DC....144
PF7013DC....152
PF7013FC....152
PF71DC....143
PF71FC....143
PF71QTD....143
PF71QTF....143
PF73ASD10....145
PF73ASD12....145
PF73ASD14....145
PF73ASDCC....145
PF73ASDP....145
PF73ASDU....145
PF73ASDX....145
PF73ASF10....145
PF73ASF12....145
PF73ASFF12....145
PF73ASFP....145
PF73ASFU....145
PF73ASFX....145
PF73ASHDL....145
PF73ASPX10....145
PF73ASPX12....145
PF73ASPXP....145
PF73ASPXU....145
PF73ASPXX....145
PF73ASRK1....145
PF73BRCP....70, 73
PF73CP....70, 73
PF73D10....145
PF73D12....145
PF73D14....145
PF73DP....145
PF73DU....145
PF73DX....145
PF74CART....145
PF74DC....144
PF74FC....144
PF74SDC....144
PF74SFC....144
PF74VBKIT....146
PF7523....100
PF75DC....152
PF75FC....152
PF760HECP....176
PF7610SBN....21
PF7610SCP....21
PF7611SBN....23
PF7611SCP....23
PF76DC....152
PF76FC....152
PF800A....136
PF800P....136
PF80DC....147
PF80FC....147
PF821200ANR....140
PF821200PNR....140
PF821ANBQ....139
PF821PCPQ....140
PF821PNBQ....140
PF821PORBQ....140
PF83BRSS....70, 73
PF83SS....70, 73
PF87CD....149
PF87CF....149
PF87CG....149
PF8820BN....22
PF8820CP....22
PF8830BN....23
PF8830CP....23
PF88AD....93
PF88CD....149
PF88CF....149
PF88CG....149
PF88SSAD....93
PF90104....96
PF90104BRSS....96
PF90124....96
PF90124BRSS....96
PF90154....96
PF90174BRSS....96
PF906JM....123
PF906JU....123
PF906K....137
PF906M....137
PF906P....137
PF910....137
PF91025....156, 158
PF910708....93
PF910710....93
PF91071014....93
PF912....137
PF912S....137
PF91335....156, 158
PF916J18....122
PF918J12....122
PF918J18....122
PF918J9....122
PF919M18....122
PF92000SJE....157
PF92010....157
PF92017....156, 158
PF92216JU....122
PF92218JU....122
PF92260....155, 158
PF922U....122
PF92305....156, 158
PF92331....155, 158
PF92333....155, 158
PF92341....155, 158
PF92342....155, 158
PF92352....155, 158
PF92370....155, 158
PF92511....155, 158
PF9280C....149
PF9280D....149
PF9280F....149
PF9281FDC....149
PF9281FDD....149
PF92910....157-158
PF92941....157-158
PF92952....157-158
PF93015....156, 158
PF93020....156, 158
PF9310WH....47-49
PF9312FLPK....60
PF9312FVPK....100
PF9312RWH....47-49
PF9312WH....47-49
PF934....137
PF93501....156, 158
PF93511....156, 158
PF935NU....122
PF938J18....122
PF93SS....70, 73
PF9400WH....49
PF9401WH....47
PF9403WH....48
PF9410WH....47-49
PF9412FLPK....60
PF9412FRPK....60
PF9412FVPK....60
PF9412LWH....47-49
PF9412RWH....47-49
PF9412TGPK....98
PF9412TLPK....61
PF9412UWH....47-49
PF9412WHC....47-49
PF9414WH....47-49
PF949M18....122
PF950S18....122
PF957....123
PF958....123
PF9800WH....50
PF9803WH....48
PF9810WH....48, 50
PF9812WH....48, 50
PF99509....157
PF99547....157
PF99549....157
PFA600....141
PFAAV160....94-95
PFAAV160A....94-95
PFAAV20....94-95
PFAAV20A....94-95
PFAAV500....94-95
PFAAV500A....94-95
PFAAV6....94-95
PFAAV6A....94-95
PFAAV6T....94-95
PFAAV6TA....94-95
PFAAVBX....94
PFAAVG....94
PFAF7500RK....146
PFAHUFK....100
PFAIUFK....100
PFAS5....61
PFASUFK....100
PFB14CLBS....11
PFB14CLWH....11
PFB14CRBS....11
PFB14CRWH....11
PFB14LS2BS....11
PFB14LS2WH....11
PFB14LSBS....11
PFB14LSWH....11
PFB14RS2BS....11
PFB14RS2WH....11
PFB14RSBS....11
PFB14RSWH....11
PFB16LBS....10
PFB16LS2BS....11
PFB16LS2WH....11
PFB16LSBS....11
PFB16LSWH....11
PFB16LWH....10
PFB16RBS....10
PFB16RS2BS....11
PFB16RS2WH....11
PFB16RSBS....11
PFB16RSWH....11
PFB16RWH....10
PFB54LWH....11
PFB54RWH....11
PFBC43....97
PFBCE....16
PFBE1....89
PFBE2....89
PFBE6X....89

PFBE7 89
PFBFVM 158
PFBG24S 75
PFBG24V 75
PFBG36S 75
PFBG36V 75
PFBHD 118
PFBHF 118
PFBHG 118
PFBHH 118
PFBHJ 118
PFBHK 118
PFBOGSKT 98
PFBP5CSKJ 159
PFBP5CSKK 159
PFBP5CSKL 159
PFBP5CSKM 159
PFBP5CSKN 159
PFBP5CSKP 159
PFBP5CSKS 159
PFBP5CSKU 159
PFBP5CSKX 159
PFBP5RH10 159
PFBP5RHH 159
PFBP5RHJ 159
PFBP5RHK 159
PFBP5RHL 159
PFBP5RHM 159
PFBP5RHN 159
PFBP5RHP 159
PFBP5RHS 159
PFBP5RHU 159
PFBP5RHX 159
PFBPUCP 66
PFBPUCPC 66
PFBRACKET 63
PFBSG 71
PFBVHBD 143
PFBVHBF 143
PFBVL2LCP 150
PFBVL2SCP 150
PFC100WHT 235
PFC114A10 96
PFC114A10RW 96
PFC15515 96-97
PFC200WHT 236
PFC2110 96
PFC2110RW 96
PFC2110RWLA 96
PFC300WHT 235
PFC301WHT 235
PFC3110 96
PFC3110RW 96
PFC401ALM 235
PFC401BIS 235
PFC401CLR 235
PFC401WHT 235
PFC44A10 96
PFC500ALU 235
PFC500CLR 235
PFC500WHT 235
PFC5110 93
PFC51LA10 93
PFC51LAM 93
PFC51LAP 93
PFC51LAS 93
PFC51LAU 93
PFC51LAX 93
PFC51M 93
PFC51P 93
PFC51S 93
PFC51U 93
PFC51X 93
PFC54A10 96
PFC54A10RW 96
PFC600CLR 236
PFC700RED 235
PFC71F 36
PFC71FB 36
PFC8110 96
PFC8110RW 96
PFC8110RWLA 96
PFC9110 96
PFCB20D 121
PFCB20DF 121
PFCB20DFG 121
PFCB20FG 121
PFCB26D 121
PFCB26DF 121
PFCB26FG 121
PFCBE20D 121
PFCBE26DF 121
PFCBRE20DFG 121
PFCBRE26DFG 121
PFCBVD 148
PFCBVF 148
PFCBVG 148
PFCBVH 148
PFCBVJ 148
PFCBVK 148
PFCCCD 164
PFCCCF 164
PFCF11 98
PFCF13 98
PFCF8 98
PFCFCOPKJ 98
PFCFCOPPK 98
PFCFCPJ 99
PFCFCPK 99
PFCFCPL 99
PFCFCPM 99
PFCFCPP 99
PFCFCRPMM 99
PFCFNHMN 99
PFCFNHPN 99
PFCFQCMK 99
PFCFQCOPKG 99
PFCFQCPK 99
PFCFQCPKT 99
PFCFQCPM 99
PFCFQCPP 99
PFCG 236
PFCHVBDF 122
PFCLIP 70
PFCMRH 124
PFCMRJ 124
PFCMRK 124
PFCNAN 127
PFCNB20DF 122
PFCNBN 127
PFCNCNN 127
PFCNDNN 127
PFCNEN 127
PFCS100 67
PFCS78N 127
PFCSAN 127
PFCSB6 122
PFCSBN 127
PFCSCN 127
PFCSDN 127
PFCSEN 127
PFCSH300 95
PFCSH4 95
PFCSH75 95
PFCSMAD 124
PFCSMAF 124
PFCSMAG 124
PFCSRH60BN 36
PFCSRH60CP 36
PFCSS300 95
PFCSS4 95
PFCSS75 95
PFCT100HEWH 45
PFCT101HEWH 45
PFCT103HEWH 45
PFCTSA 119
PFCTSB 119
PFCTSC 119
PFCTSD 119
PFCTSF 119
PFCTSG 119
PFCTSH 119
PFCTSJ 119
PFCTSK 119
PFCVBD 122
PFCVJH 157
PFCVK 157
PFCWP100 85
PFCWP101 85
PFCWP102 85
PFDAC4C 93
PFDAC4W 93
PFDAC5C 93
PFDAC5W 93
PFDAC7C 93
PFDAC7W 93
PFDCSHK 24, 26
PFDFVB 61
PFDUGD 125
PFDUGF 125
PFDUGFD 125
PFDUGG 125
PFDUGH 125
PFDUGJ 125
PFDUGK 125
PFE1 89
PFE10 89
PFE11 89
PFE16A 89
PFE2 89
PFE2PB 89
PFE32 90
PFE33 90
PFE34 90
PFE35 90
PFE36 89
PFE37 89
PFE40 89
PFE41 89
PFE42 89
PFE7 89
PFE7PB 89
PFE8 89
PFE9 89
PFE9A 89
PFEFU 61
PFEM7500RK 146
PFEP53J 159
PFEP53K 159
PFEP53L 159
PFEP53LAK 159
PFEP53LAL 159
PFEP53LAM 159
PFEP53LAN 159
PFEP53LAP 159
PFEP53M 159
PFEP53N 159
PFEP53P 159
PFEP53S 159
PFEP53U 159
PFETB400 81
PFETB401 81
PFETB402 81
PFETB403 81
PFETB404 81
PFETB405 81
PFETB406 81
PFETB407 81
PFETB408 81
PFETB409 81
PFETB410 81
PFETB500 81
PFETB501 81
PFETB502 81
PFETB503 81
PFETB504 81
PFETB505 81
PFETB600 82
PFETB601 82
PFETB602 82
PFETB603 82
PFETB604 82
PFETB605 82
PFETB606 82
PFETB607 82
PFETB608 82
PFETB609 82
PFETB610 82
PFETB611 82
PFETB612 82
PFETB613 82
PFETB614 82
PFETB615 82
PFETB616 82
PFETB617 82
PFETB618 82
PFETB700 82
PFETB701 82
PFETB702 82
PFETB703 82
PFETB704 82
PFETB800 82
PFETB801 82
PFETCHBJ 92
PFETCHBK 92
PFETCHBM 92
PFETCHBP 92
PFETCHBS 92
PFETCHBU 92
PFETCJ 91
PFETCK 91
PFETCM 91
PFETCP 91
PFETCS 91
PFETCU 91
PFETCX 91
PFETL 61
PFETP600 82
PFETP601 82
PFETP602 82
PFETP603 82
PFETP604 82
PFETP700 82
PFETP701 82
PFETP702 82
PFETPJ 92
PFETPK 92
PFETPM 92
PFETPP 92
PFEWB100 82
PFEWB101 83
PFEWB102 83
PFEWB103 83
PFEWB104 83
PFEWB105 83
PFEWB106 83
PFEWB107 82
PFEWB108 82
PFEWB109 83
PFEWB110 83
PFEWB111 83
PFEWB112 83
PFEWB200 83
PFEWP100 83
PFEWP101 83
PFEWP102 83
PFEWP103 83
PFEWP200 83
PFEWP201 83
PFEWP202 83
PFEXT200WH 86-87
PFF170 90
PFF171 90
PFF171C 90
PFF172 90
PFF172C 90
PFF173 90
PFF173C 90
PFF174 90
PFF174C 90
PFF175 90
PFF175C 90
PFF176 90
PFF6 95
PFFAC4C 93
PFFAC4W 93
PFFAC5C 93
PFFAC5W 93
PFFAC7C 93
PFFAC7W 93
PFFCB 131
PFFCC 131
PFFCD 131
PFFCE 131
PFFCEFT 131
PFFFU516B 132
PFFFUCB 132
PFFFUCC 132
PFFFUCD 132
PFFFUDD 132
PFFFUDF 132
PFFHC 43
PFFHCP 43
PFFHCWH 43
PFFPC 132
PFFPD 132
PFFSRFNB 132
PFFTC 132
PFFTD 132
PFFUB 132
PFFUC 132
PFFUCD 132
PFFUD 132
PFFUE 132
PFFUED 132
PFFW92B 135
PFFW93B 135
PFGABDFG 122
PFGAPCP 71
PFGB12SF2 177
PFGB16PF2 177
PFGB16SF2 177
PFGB18PF2 177
PFGB18SF2 177
PFGB20 122
PFGB20DF 122
PFGB24PF2 177
PFGB24SF2 177
PFGB26 122
PFGB26DF 122
PFGB30PF2 177
PFGB30SF2 177
PFGB32PF2 177
PFGB32SF2 177
PFGB36PF2 177
PFGB36SF2 177
PFGB42PF2 177
PFGB42SF2 177
PFGB48SF2 177
PFGD100 66
PFGD101 66
PFGG100K 91
PFGG15K1 91
PFGG30K 91
PFGG60K 91
PFH60 104
PFHS18 118
PFHS26 118
PFJBB100 83
PFJBB101 83
PFJBB200 83
PFJBB201 83
PFJBB300 83
PFJBB400 83
PFJBB401 83
PFJBB402 83
PFJBB403 84
PFL54X 60
PFLFNB 132
PFLL18CP 37
PFLL24CP 37
PFLLDRHCP 35
PFLLRSHCP 36
PFLLRTPHCP 36
PFLLSDCP 36
PFLLTPCP 37
PFLLTRCCP 37
PFLLWR 100
PFLLWT 100
PFLT2024 76
PFLT2123 76
PFLT2123W 76
PFLT2522D 75
PFLT4024 76
PFLT4024W 76
PFLTBLK 176
PFM90037 235
PFMB2424 75
PFMB2424S 75
PFMB3624S 75
PFMBRFEDD 131
PFMFEBB 131
PFMFECB 131
PFMFECC 131
PFMFECD 131
PFMFEDC 131

PFMFEED....131
PFMFEFF....131
PFMFU78F....133
PFMFUBA....133
PFMFUBB....133
PFMFUBC....133
PFMFUBD....133
PFMFUCA....133
PFMFUCB....133
PFMFUCC....133
PFMFUCD....133
PFMFUCF....133
PFMFUDB....133
PFMFUDC....133
PFMFUDD....133
PFMFUDF....133
PFMFUFF....133
PFMM500L....116
PFMSH....24-25
PFMUSTLD....133
PFNCBL....96-97
PFNHC10....160
PFNHCJ....160
PFNHCK....160
PFNHCM....160
PFNHCP....160
PFNHCS....160
PFNHCU....160
PFNHCX....160
PFNHHHDC10....161
PFNHHHDCJ....161
PFNHHHDCK....161
PFNHHHDCM....161
PFNHHHDCP....161
PFNHHHDCS....161
PFNHHHDCU....161
PFNHHHDCX....161
PFNHHMDC10....161
PFNHHMDCJ....161
PFNHHMDCK....161
PFNHHMDCM....161
PFNHHMDCP....161
PFNHHMDCS....161
PFNHHMDCU....161
PFNHHMDCX....161
PFNHRCKJ....160
PFNHRCMK....160
PFNHRCPM....160
PFNHWBC12....161
PFNHWBC15....161
PFOD100....66
PFOFFUED....132
PFOMFUED....133
PFOMFUEF....133
PFP1500....141
PFP2500....141
PFP56ACP....149
PFP56APB....149
PFP57ACP....149
PFP57APB....149
PFP600....141
PFP80SUD....95
PFP80SUF....95
PFP80SUG....95
PFP80SUH....95
PFP80SUJ....95
PFP80SUK....95
PFP80SUL....95
PFP80SUM....95
PFP80VSSFK....94
PFP80VSSFL....94
PFP80VSSFM....94
PFP80VSSFP....94
PFP80VSSFU....94
PFP80VSSFX....94
PFPA4SVCSK....160
PFPA6SVCSK....160
PFPAL516....97
PFPB41A....26
PFPCCD....165
PFPCCF....165
PFPCCG....165
PFPCCH....165
PFPCCJ....165
PFPCCK....165
PFPCCL....165
PFPCCM....165
PFPCCP....165
PFPCCU....165
PFPCSBN....127
PFPCSCN....127
PFPCSDN....127
PFPCSEN....127
PFPCVF....150
PFPCVG....150
PFPCVH....150
PFPCVJ....150
PFPCVK....150
PFPDUU....116
PFPE1WH....88
PFPE2CP....88
PFPE2WH....88
PFPE3CP....88
PFPE3WH....88
PFPE4CP....88
PFPE4WH....88
PFPE5CP....88
PFPE5WH....88
PFPE6CP....88
PFPE6WH....88
PFPE7CP....88
PFPE7WH....88
PFPE8CP....88
PFPE8WH....88
PFPE9CP....88
PFPE9WH....88
PFPG100K....91
PFPG100L....91
PFPG100N....91
PFPG15K1....91
PFPG160K....91
PFPG160L....91
PFPG200K....91
PFPG200L....91
PFPG200N....91
PFPG300K....91
PFPG300L....91
PFPG300N....91
PFPG30K....91
PFPG30L....91
PFPG5L....91
PFPG60K....91
PFPG60L....91
PFPHUFK....100
PFPIUFK....100
PFPO200....66
PFPR500....141
PFPS09126....123
PFPS0916....123
PFPS12126....123
PFPS12164....123
PFPS12166....123
PFPS169....123
PFPS18126....123
PFPS18166....123
PFPS24126....123
PFPS2416....123
PFPS24166....123
PFPSBVD....149
PFPSBVF....149
PFPSBVG....149
PFPSBVH....149
PFPSBVJ....149
PFPSBVK....149
PFPSBVL....149
PFPSBVM....149
PFPSBVP....149
PFPSUFK....100
PFPT22010....118
PFPT24010CC....118
PFPT26010....118
PFPTB100....77
PFPTB101....78
PFPTB102....78
PFPTB103....77
PFPTB104....78
PFPTB105....78
PFPTB106....78
PFPTB107....77
PFPTB108....78
PFPTB109....78
PFPTB110....78
PFPTB111....78
PFPTB112....78
PFPTB200....78
PFPTB201....78
PFPTB202....78
PFPTB300....78
PFPTB301....78
PFPTB400....78
PFPTB401....78
PFPTB402....78
PFPTB403....78
PFPTB500....79
PFPTB501....79
PFPTB502....79
PFPTB503....79
PFPTBVD....149
PFPTBVF....149
PFPTBVG....149
PFPTBVJ....149
PFPTBVK....149
PFPTBVM....149
PFPTP100....84
PFPTP101....84
PFPTP102....84
PFPTP103....84
PFPTP104....85
PFPTP105....85
PFPTP200....85
PFPWH....90
PFPWJ....90
PFPWJH....90
PFR602FLD....149
PFR602MDC....149
PFR602MDD....149
PFR850PD....148
PFR850PF....148
PFR850PG....148
PFR858PD....148
PFR858PF....148
PFR858PG....148
PFRB12X....135
PFRB1310....135
PFRCDM....165
PFRCDU....165
PFRCFM....165
PFRCFU....165
PFRCGM....165
PFRCGU....165
PFRCHM....165
PFRCHU....165
PFRCJM....165
PFRCJU....165
PFRCKM....165
PFRCKU....165
PFRGHWN....133
PFRKLK....112
PFRR....98
PFS11D....151
PFS194RBS....62
PFS194RWH....62
PFS20174BS....62
PFS20174WH....62
PFS40....26
PFS41....26
PFS42....88
PFS5838BS....9
PFS5838WH....9
PFS6030LSKBS....10
PFS6030LSKWH....10
PFS6030RSKBS....10
PFS6030RSKWH....10
PFS6032ABS....9
PFS6032AWH....9
PFS6032LSKBS....10
PFS6032LSKWH....10
PFS6032RSKBS....10
PFS6032RSKWH....10
PFS6036ABS....9
PFS6036AWH....9
PFS6036LSKBS....10
PFS6036LSKWH....10
PFS6036RSKBS....10
PFS6036RSKWH....10
PFS6042ABS....9
PFS6042AWH....9
PFS6042LSKBS....10
PFS6042LSKWH....10
PFS6042RSKBS....10
PFS6042RSKWH....10
PFS6060BS....10
PFS6060SKBS....10
PFS6060SKWH....10
PFS6060WH....10
PFS6636LSKBS....10
PFS6636LSKWH....10
PFS6636RSKBS....10
PFS6636RSKWH....10
PFS7040BS....9
PFS7040WH....9
PFS7236ABS....9
PFS7236AWH....9
PFS7236LSKBS....9
PFS7236LSKWH....9
PFS7236RSKBS....9
PFS7236RSKWH....9
PFS7242ABS....8
PFS7242AWH....8
PFS7242LSKBS....9
PFS7242LSKWH....9
PFS7242RSKBS....9
PFS7242RSKWH....9
PFSB3232WH....12
PFSB3434WH....12
PFSB3636NEOWH....12
PFSB3636WH....12
PFSB4234WH....12
PFSB4242WH....12
PFSB4832WH....12
PFSB4834WH....12
PFSB5434WH....12
PFSB6034WH....12
PFSBSTR....141
PFSC1SBK....86-87
PFSC1SWH....86-87
PFSCOFFWH....86-87
PFSCPT1SBK....86-87
PFSCPT1SWH....86-87
PFSCPT2SBK....86-87
PFSCPT2SOFFBK....86-87
PFSCPT2SOFFWH....86-87
PFSCPT2SWH....86-87
PFSCPTBK....86, 88
PFSCPTWH....86, 88
PFSCR60....36
PFSCR72....36
PFSCVD....151
PFSCVF....151
PFSCVG....151
PFSCVH....151
PFSCVJ....151
PFSCVK....151
PFSE78ODCP....89
PFSE78ODWH....89
PFSEDCP....89
PFSEDWH....89
PFSEECP....89
PFSEEWH....89
PFSEFCP....89
PFSEFWH....89
PFSEGCP....89
PFSEGWH....89
PFSEJCP....89
PFSEJWH....89
PFSEKCP....89
PFSEKWH....89
PFSF1....98
PFSFN78....132
PFSFNB....132
PFSFNC....132
PFSFND....132
PFSFNE....132
PFSFNF....132
PFSHD15BN....26
PFSHD15CP....26
PFSHD15RB....26
PFSHSC....43
PFSJP1....90
PFSJP125....90
PFSJP3....90
PFSK36....183
PFSK60....183
PFSNH....90
PFSNJ....90
PFSNJH....90
PFSNRBJ....90
PFSNVCC....129
PFSNVCD....129
PFSNWH....90
PFSNWJ....90
PFSNWJH....90
PFSP0916....122
PFSP316100....123
PFSP416100....123
PFSP5161002....123
PFSP5161003....123
PFSR151561A....67
PFSR151562A....67
PFSR171962....67
PFSR171963....67
PFSR172273....67
PFSR2521553C....68
PFSR2521553L....68
PFSR2521553R....68
PFSR252263....68
PFSR252263BP....68
PFSR252264....68
PFSR252264BP....68
PFSR2522653....68
PFSR2522654....68
PFSR252273....68
PFSR252274....68
PFSR252283A....68
PFSR252284A....68
PFSR3321653....69
PFSR3321654....69
PFSR332263....69
PFSR332263BP....69
PFSR332264....69
PFSR332264BP....69
PFSR3322653....69
PFSR3322654....69
PFSR332273....69
PFSR332274....69
PFSR332283....69
PFSR332284....69
PFSRFCP....36
PFSRFNFC....132
PFSRFNFD....132
PFSRFNFE....132
PFSSCPK....141
PFSSE1....88
PFSSE2....88
PFSSHC62602....159
PFSSHC62606....159
PFSSHC63152....160
PFSSHC63248....160
PFSSHC6706....159
PFSSHC6708....159
PFSSHC6710....159
PFSSHC6712....159
PFSSHC6716....159
PFSSHC6720....159
PFSSHC6724....159
PFSSHC6728....159
PFSSHC6732....159
PFSSHC6736....159
PFSSHC6740....159
PFSSHC6744....159
PFSSHC6748....159
PFSSHC6752....159
PFSSHC6756....159
PFSSHC6764....159
PFSSHC6772....159
PFSSHC6780....159
PFSSHC6788....159
PFSSHC6796....159
PFSSHC6799....159
PFSSHC6806....160
PFSSHC6808....160
PFSSHC6810....160
PFSSHC68104....160
PFSSHC6812....160
PFSSHC6816....160
PFSSHC6820....160

PFSSHC6824....160
PFSSHC6828....160
PFSSHC6832....160
PFSSHC6836....160
PFSSHC6840....160
PFSSHC6844....160
PFSSHC6848....160
PFSSHC6852....160
PFSSHC6856....160
PFSSHC6864....160
PFSSHC6872....160
PFSSHC6880....160
PFSSHC6888....160
PFSSHC6896....160
PFSSHE....137
PFSTB100....79
PFSTB101....79
PFSTB102....79
PFSTB103....79
PFSTP100....85
PFSTP101....85
PFSTP102....85
PFSVL2CP....150
PFSVL2PB....150
PFSVQTG10....161
PFSVQTG12....161
PFSVQTG15....161
PFSVQTGK....161
PFSVQTGM....161
PFSVQTGP....161
PFSVQTGS....161
PFSVQTGU....161
PFSVQTGX....161
PFSVS2CP....150
PFSVS2PB....150
PFT10....90
PFT11D....152
PFT250....104
PFT300B....151
PFT300C....151
PFT300D....151
PFT300F....151
PFT300G....151
PFT300H....151
PFT300J....151
PFT300K....151
PFT300L....151
PFT300M....151
PFT300P....151
PFT300SD....151
PFT300SF....151
PFT300SG....151
PFT300SH....151
PFT300SJ....151
PFT300SK....151
PFT382RH....160
PFT383RH....160
PFT384CS....160
PFT384RH....160
PFT386RH....160
PFT523RH....160
PFT524RH....160
PFTBG....97
PFTBSP....100
PFTCJ....92
PFTCK....92
PFTCM....92
PFTCP....92
PFTG92352....155, 158
PFTG92352P....155, 158
PFTGFPK....97
PFTK....12
PFTLCP....61
PFTPB100....80
PFTPB101....80
PFTPB102....80
PFTPB103....80
PFTPB104....80
PFTPB105....80
PFTPB106....80
PFTPB107....80
PFTPB108....80
PFTPB109....80
PFTPB110....80
PFTPB111....80
PFTPB112....80
PFTPB113....80
PFTPB114....80
PFTPB200....80
PFTPB201....80
PFTPB202....80
PFTPB300....79
PFTPB301....79
PFTPB302....79
PFTPB303....79
PFTPB304....79
PFTPB305....79
PFTPB306....79
PFTPB307....79
PFTPB308....79
PFTPB309....79
PFTPB310....80
PFTPD....92
PFTPP100....80
PFTPP101....80
PFTPP102....80
PFTPP103....80
PFTPP104....80
PFTPP105....80
PFTPP106....80
PFTPP200....81
PFTPP201....81
PFTPP300....80
PFTPP301....80
PFTPP302....80
PFTPP400....80
PFTPP401....80
PFTPP402....80
PFTRAPID....142
PFTRAPSD....142
PFTRC100....84
PFTRC101....84
PFTRC102....84
PFTRC103....84
PFTRC104....84
PFTRC105....84
PFTS32BN....27
PFTS32CP....27
PFTS33....28
PFTS33BN....28
PFTS33CP....28
PFTSBB1000WH....57-58
PFTSCOF2000BL....57-58
PFTSCOF2000WH....57-58
PFTSCOFA2000WH....57-58
PFTSCOFC2000WH....57-58
PFTSCOFE2000WH....57-58
PFTSCOFH2000WH....57-58
PFTSE1000BS....56
PFTSE1000WH....56
PFTSE2000BS....56
PFTSE2000WH....56
PFTSEC1000WH....56
PFTSEC2000BS....56
PFTSEC2000WH....56
PFTSHEC1000BS....56
PFTSHEC1000WH....56
PFTSHEC2000BS....56
PFTSHEC2000WH....56
PFTSWE1001WH....57
PFTSWE2001WH....56
PFTSWEC1000BO....57
PFTSWEC1000BS....57
PFTSWEC1000WH....57
PFTSWEC2000BO....56
PFTSWEC2000BS....56
PFTSWEC2000WH....56
PFUC109....68
PFUC206....69
PFUC208....70
PFUC301A....68
PFUC303....67
PFUC307A....68
PFUC308A....69
PFUC405A....68
PFUC907....69
PFUC907R....70
PFUCCLIP....70
PFULW....100
PFUTB....100
PFVB....146
PFVBMD....146
PFW6032ALSKBS....8
PFW6032ALSKWH....8
PFW6032ARSKBS....8
PFW6032ARSKWH....8
PFW6036ALSKBS....7
PFW6036ALSKWH....7
PFW6036ARSKBS....7
PFW6036ARSKWH....7
PFW6042ALSKBS....7
PFW6042ALSKWH....7
PFW6042ARSKBS....7
PFW6042ARSKWH....7
PFW6060SKPLABS....8
PFW6060SKPLAWH....8
PFW6636ALSKBS....7
PFW6636ALSKWH....7
PFW6636ARSKBS....7
PFW6636ARSKWH....7
PFW7236ALSKBS....7
PFW7236ALSKWH....7
PFW7236ARSKBS....7
PFW7236ARSKWH....7
PFW7242ALSKBS....6
PFW7242ALSKWH....6
PFW7242ARSKBS....6
PFW7242ARSKWH....6
PFWAB101....84
PFWAB107....84
PFWAB112....84
PFWAB113....84
PFWAB201....84
PFWAB206....84
PFWBB102....84
PFWBB201....84
PFWBB204....84
PFWG24S....75
PFWG300L....91
PFWG36S....75
PFWGI300L....91
PFWMBKT....63
PFWMH4PR....105-106
PFWMH5PR....105-106
PFWMH6PR....105-106
PFWO101....13
PFWO201....14
PFWO210....13
PFWO215....13
PFWO250....14
PFWO251....13
PFWO300....13
PFWO304....13
PFWO305....13
PFWO320....12
PFWO321....12
PFWO322....12
PFWO350....12
PFWO351....12
PFWO352....12
PFWO354....12
PFWO355....12
PFWO357....12
PFWO400....13
PFWO401....14
PFWO402....14
PFWO500....16
PFWO502....13
PFWO503....13
PFWO505....13
PFWO600....16
PFWO900....15
PFWO901....15
PFWO902....15
PFWO903....15
PFWO904....14
PFWO950....16
PFWPLUSA5838BS....6
PFWPLUSA5838WH....6
PFWPLUSA6032BS....6
PFWPLUSA6032WH....6
PFWPLUSA6036BS....6
PFWPLUSA6036WH....6
PFWPLUSA6042BS....6
PFWPLUSA6042WH....6
PFWPLUSA6060LBS....8
PFWPLUSA6060LWH....8
PFWPLUSA6060RBS....8
PFWPLUSA6060RWH....8
PFWPLUSA7040BS....6
PFWPLUSA7040WH....6
PFWPLUSA7236BS....5
PFWPLUSA7236WH....5
PFWPLUSA7242BS....5
PFWPLUSA7242WH....5
PFWR....101
PFWR4WHWB....100
PFWRBO....101
PFWRU....101
PFWRWB....100
PFWRWH....101
PFWRWHWB....100
PFWRWHXW....101
PFWRWHXWWB....100
PFWRXW....101
PFWSC1040ACP....18
PFWSC1040CP....18
PFWSC1120CP....177
PFWSC1140CP....18
PFWSC1140LCP....18
PFWSC1190CP....41
PFWSC1240ABN....19
PFWSC1240ACP....19
PFWSC1240BN....19
PFWSC1240CP....19
PFWSC13405GCP....19
PFWSC13405LCP....19
PFWSC1340GCP....19
PFWSC1340LCP....19
PFWSC13905CP....42
PFWSC1390CP....42
PFWSC2840BN....19
PFWSC2840CP....19
PFWSC2840ORB....19
PFWSC2860BN....20
PFWSC2860CP....20
PFWSC2860ORB....20
PFWSC30065CP....17
PFWSC3006CP....17
PFWSC30165CP....17
PFWSC3016BN....17
PFWSC3016CP....17
PFWSC3016ORB....17
PFWSC47445CP....17
PFWSC4744BN....17
PFWSC4744CP....17
PFWSC4744SCP....17
PFWSC4746BN....18
PFWSC4746CP....18
PFWSC4746SCP....17
PFWSC4840BN....19
PFWSC4840CP....19
PFWSC4840ORB....19
PFWSC4860BN....20
PFWSC4860CP....20
PFWSC4860ORB....20
PFWSC5240BN....19
PFWSC5240CP....19
PFWSC5240ORB....19
PFWSC5260BN....20
PFWSC5260CP....20
PFWSC5260ORB....20
PFWSC6840BN....19
PFWSC6840CP....19
PFWSC6850BN....18
PFWSC6850CP....18
PFWSC6860BN....20
PFWSC6860CP....20
PFWSC6890BN....42
PFWSC6890CP....42
PFWSC8851BN....18
PFWSC8851CP....18
PFWTI75....106
PFWTS....70, 73
PFX113174....33-34
PFX113175....33-34
PFX119....158
PFX141137PK....35
PFX141199PK....34
PFX143128PK....33-34
PFX146022....103-104
PFX146023....103-104
PFX146024....103-104
PFX146172....102-103
PFX146198....104-105
PFX146202....104-105
PFX146205....104-105
PFX146207....104-105
PFX146222....103, 106
PFX146224....103, 106
PFX146232....103, 106
PFX146302....103-104
PFX146303....103-104
PFX146304....103-104
PFX146306....103-104
PFX146322....103-104
PFX146323....103-104
PFX146324....103-104
PFX146326....103-104
PFX146330....103-104
PFX146332....103-104
PFX146334....103-104
PFX146342....103-104
PFX146343....103-104
PFX146344....103-104
PFX146350....104-105
PFX146352....104-105
PFX146354....104-105
PFX146365....104-105
PFX146423....103-104
PFX146424....103-104
PFX146430....103-104
PFX146432....103-104
PFX146462....102-103
PFX146463....102-103
PFX146471....102-103
PFX146472....102-103
PFX146473....102-103
PFX146474....102-103
PFX146492....102-103
PFX20....158
PFX26....158
PFX277....33-34
PFX300....176
PFX304....20
PFX3045....20
PFX308....20
PFX3085....20
PFX3145L....18
PFX314L....18
PFX31D....150
PFX31F....150
PFX31G....150
PFX31H....150
PFX31J....150
PFX31K....150
PFX31L....150
PFX31M....150
PFX31P....150
PFX31SD....150
PFX31SF....150
PFX31SG....150
PFX31SH....150
PFX31SJ....150
PFX31SK....150
PFX32....158
PFX34....158
PFX3C322C....108, 110
PFX3C322R....108, 110
PFX3T322C....108, 111
PFX3T322R....108, 111
PFX44....158
PFX462D....148
PFX462F....148
PFX462G....148
PFX472D....149
PFX472F....149
PFX472G....149
PFX5061C....33-34
PFX60SDC....147
PFX60SFC....147
PFX62....158
PFX750C....176
PFX75DC....152
PFX75FC....152
PFX76DC....152

PFX76FC....152
PFX81....158
PFX86....158
PFXAC31C....108, 110
PFXAC32C....108, 110
PFXAC32CLK....109-110
PFXAC32CLON....109-110
PFXAC32R....108, 110
PFXAF7501....146
PFXAF7502....146
PFXAF7503....146
PFXAF7504....146
PFXAF7505....146
PFXAF7506....146
PFXAF7507....146
PFXAFHDL....146
PFXAP32C....108, 110
PFXARBDCN....128
PFXAS31C....108, 110
PFXAS31R....108, 110
PFXAS32C....108, 110
PFXAS32R....108, 110
PFXAT22C....108, 110
PFXAT32C....108, 110
PFXAV32C....108, 110
PFXAV32R....108, 110
PFXAZ32CC12....114
PFXB304....42
PFXB3045....42
PFXBCCCM....164
PFXBCCCS....164
PFXBCCDM....164
PFXBCCDS....164
PFXBCCFM....164
PFXBCCFS....164
PFXBCCGM....164
PFXBCCGS....164
PFXBCCHM....164
PFXBCCHS....164
PFXBCCJM....164
PFXBCCJS....164
PFXBFHDFN....133
PFXBFHEFN....133
PFXBFHFFN....133
PFXBFVF....157
PFXBFVG....157
PFXBFVH....157
PFXBFVJ....157
PFXBFVK....157
PFXBFVM....157
PFXBMHEFN....133
PFXBRIBN....129
PFXBRICN....129
PFXBRIDN....129
PFXBRIEN....129
PFXBVHBD....143
PFXBVHBF....143
PFXC1080CP....41
PFXC1080LSCP....41
PFXC1180CP....41
PFXC1180LSCP....41
PFXC1880CP....41
PFXC1901BN....40
PFXC1901CP....40
PFXC1911BN....40
PFXC1911CP....40
PFXC3101CP....40
PFXC3111CP....40
PFXC3121CP....40
PFXC4101BN....40
PFXC4111BN....40
PFXC4111CP....40
PFXC4121BN....40
PFXC4121CP....40
PFXC5150BN....39
PFXC5150CP....39
PFXC5150ORB....39
PFXC6011BN....39
PFXC6011CP....39
PFXC6011RB....39
PFXC6880BN....41
PFXC6880CP....41
PFXC6880LSBN....41
PFXC6880LSCP....41
PFXC7011BN....39
PFXC7011CP....39
PFXC800....177
PFXC80012....177
PFXC800U....177
PFXC9011BN....39
PFXC9011CP....39
PFXCAC32C....109, 111
PFXCAC32CC12....111, 114
PFXCAC32CL12....111, 115
PFXCAC32CLK....109, 111
PFXCAC32CLKC12 111, 114
PFXCAC32CLKL12 111, 115
PFXCARBDBN....128
PFXCAS32C....109, 111
PFXCAS32CC12....111, 114
PFXCAS32CL12....111, 115
PFXCAS32CLK....109, 111
PFXCAS32CLKC12....111, 114
PFXCAS32CLKL12....111, 115
PFXCAT22C....109, 111
PFXCAT22CC12....114
PFXCAT22CL12....111, 115
PFXCAT22CLK....109, 111
PFXCAT22CLKC12....114
PFXCAT22CLKL12....111, 115
PFXCAT32C....109, 111
PFXCAT32CL12....111, 115
PFXCAT32CLK....109, 111
PFXCAT32CLKL12....111, 115
PFXCAT33C....109, 111
PFXCATT22CLKRL12 111, 115
PFXCAZ32C....109, 111
PFXCAZ32CC12....111, 114
PFXCAZ32CL12....111, 115
PFXCAZ32CLK....111-112
PFXCAZ32CLKL12....111, 115
PFXCBCCKS....165
PFXCCBN....126
PFXCCCN....126
PFXCCDN....126
PFXCCEN....126
PFXCCMS22....125
PFXCCMS33....125
PFXCCS22....125
PFXCCS32....125
PFXCCS33....125
PFXCCS44....125
PFXCCS55....125
PFXCCS66....125
PFXCCS77....125
PFXCCUEN....128
PFXCE7878....127
PFXCEBBN....127
PFXCECCN....127
PFXCEDDN....127
PFXCEECCPN....127
PFXCEECN....127
PFXCEEEN....127
PFXCH4D....129
PFXCH9C....129
PFXCH9D....129
PFXCH9F....129
PFXCH9G....129
PFXCHBDC....130
PFXCHBFD....130
PFXCHCAPD....130
PFXCHCAPF....130
PFXCHCAPG....130
PFXCHCC....130
PFXCHCD....130
PFXCHFM18N....103, 106
PFXCHFM24N....103, 106
PFXCHFT18N....103, 106
PFXCHFT24N....103, 106
PFXCHFU18N....103, 106
PFXCHFW18NA....103, 106
PFXCHFW24NA....103, 106
PFXCHGFT24N....103, 106
PFXCHGT18....103, 106
PFXCHGT24....103, 106
PFXCHHGT24....103, 106
PFXCHHT18....103, 106
PFXCHJT18....103, 106
PFXCHNC12....130
PFXCHNCCL....130
PFXCHNCJ....130
PFXCHNCK....130
PFXCHNCL....130
PFXCHNCM....130
PFXCHNCN....130
PFXCHNCP....130
PFXCHNCR....130
PFXCHNCS....130
PFXCHNCT....130
PFXCHNCU....130
PFXCHNCX....130
PFXCHND10....130
PFXCHND12....130
PFXCHND18....130
PFXCHND36....130
PFXCHNDCL....130
PFXCHNDJ....130
PFXCHNDK....130
PFXCHNDL....130
PFXCHNDM....130
PFXCHNDN....130
PFXCHNDP....130
PFXCHNDR....130
PFXCHNDS....130
PFXCHNDT....130
PFXCHNDU....130
PFXCHNDX....130
PFXCHNFCL....130
PFXCHNFJ....130
PFXCHNFK....130
PFXCHNFL....131
PFXCHNFM....130
PFXCHNFN....131
PFXCHNFP....130
PFXCHNFR....131
PFXCHNFS....131
PFXCHNFT....131
PFXCHNFU....130
PFXCHNGCL....130
PFXCHNGK....130
PFXCHNGL....131
PFXCHNGM....130
PFXCHNGP....130
PFXCHNGS....130
PFXCHNGT....131
PFXCHNGU....130
PFXCHNHK....131
PFXCHNHL....131
PFXCHNHN....131
PFXCHNHP....131
PFXCHNHR....131
PFXCHNHS....131
PFXCHNHU....131
PFXCHNJCL....131
PFXCHNJK....131
PFXCHNJL....131
PFXCHNJP....131
PFXCHNKCL....131
PFXCHNKM....131
PFXCHRCDC....130
PFXCHS9D....129
PFXCHS9F....129
PFXCHS9G....129
PFXCHTC....131
PFXCHTD....131
PFXCHUD....131
PFXCN78....127
PFXCPCN....127
PFXCPFAD....124
PFXCPFAF....124
PFXCPFAG....124
PFXCPFAH....124
PFXCPFAJ....124
PFXCPFAK....124
PFXCPFDE9D....124
PFXCPFDE9DSS....124
PFXCPMAD....124
PFXCPMAF....124
PFXCPMAG....124
PFXCPMAH....124
PFXCPMAJ....124
PFXCPMAK....124
PFXCPSUD....124
PFXCPSUF....124
PFXCTBN....128
PFXCTCCBN....128
PFXCTCCPN....128
PFXCTCN....128
PFXCTDN....128
PFXCTEN....128
PFXCTFCCBN....126
PFXCTFCCCN....126
PFXCU78N....128
PFXCUACCN....129
PFXCUBECPCN....129
PFXCUBN....128
PFXCUCBN....128
PFXCUCN....128
PFXCUDCN....128
PFXCUDN....128
PFXCUECCPN....128
PFXCUECN....128
PFXCUEDN....128
PFXDC321R....110, 112
PFXDC322C....110, 112
PFXDC322R....110, 112
PFXDEDN....105
PFXDEN....105, 126
PFXDNGKP....125
PFXDNGLU....125
PFXDNGMU....125
PFXDNGPU....125
PFXDNGTGP....125
PFXDNGTHP....125
PFXDNGTJP....125
PFXDNGTKP....125
PFXDNGTLU....125
PFXDNGTMU....125
PFXDNGTPU....125
PFXDNGUU....125
PFXDNTDM....125
PFXDNTFM....125
PFXDNTGP....125
PFXDNTHP....125
PFXDNTJP....125
PFXDNTKP....125
PFXDNTLU....125
PFXDNTMU....125
PFXDNTPU....125
PFXDT322R....110, 112
PFXEM7501....147
PFXEM75015....147
PFXEM7502....147
PFXEM7503....147
PFXEM7504....147
PFXEM7505....147
PFXEM7506....147
PFXEM7508....147
PFXEM7510....147
PFXEMHDL....146
PFXFCECCN....127
PFXFCECDN....127
PFXFCECPCDN....127
PFXFCU78FN....129
PFXFCUBAN....129
PFXFCUBBN....129
PFXFCUBCN....129
PFXFCUBDN....129
PFXFCUCBN....129
PFXFCUCCN....129
PFXFCUCDCPN....126
PFXFCUCDN....129
PFXFCUDCN....129
PFXFCUDDN....129
PFXFCUECN....129
PFXFCUEDN....129
PFXFFHDFN....133
PFXFFHFFN....133
PFXFFHSDFN....134
PFXFFHSFFN....133
PFXFHBBBN....134
PFXFHBCCN....134
PFXFHFHSFFN....134
PFXFMHDFN....133
PFXFMHFFN....133
PFXGCCDL....165
PFXGCCFL....165
PFXGCCGL....165
PFXGCCHL....165
PFXGCCJL....165
PFXGCCKL....165
PFXGCCLL....165
PFXGCCML....165
PFXGCCPL....165
PFXGHCC12W....133
PFXGHCFN....133
PFXHAC32C....111-112
PFXHAC32CLK....111-112
PFXHAT32CC12....114
PFXHAT32CL12....111, 115
PFXHAT32CLK....111-112
PFXHAT32CLKL12....111, 115
PFXHAT33CLKL12....111, 116
PFXHATT22CLKL12....111, 115
PFXHATT33CLK....111-112
PFXHG10....161
PFXHG12....161
PFXHGK....161
PFXHGM....161
PFXHGP....161
PFXHGS....161
PFXHGU....161
PFXHGX....161
PFXHWFFN....133
PFXIBCCKS....164
PFXIMK15CA....104
PFXIMK25PA....104
PFXLNPCN....125
PFXMBRHBEF....134
PFXMCACCCPN....128
PFXMCADCCPN....128
PFXMCEBAN....126
PFXMCEBBN....126
PFXMCEBCN....126
PFXMCECAN....126
PFXMCECBN....126
PFXMCECCN....126
PFXMCECDN....126
PFXMCEDCN....126
PFXMCEDDN....126
PFXMCEEDN....126
PFXMCRADCN....128
PFXMCU78FN....128
PFXMCU78GN....128
PFXMCUAAN....128
PFXMCUBAN....128
PFXMCUBBN....128
PFXMCUBCN....128
PFXMCUBDN....128
PFXMCUCAN....128
PFXMCUCBCP....126
PFXMCUCBN....128
PFXMCUCCN....128
PFXMCUCDCPN....126
PFXMCUCDN....128
PFXMCUCFN....128
PFXMCUCPCCN....128
PFXMCUDBN....128
PFXMCUDDN....128
PFXMCUDFN....128
PFXMCUECN....128
PFXMCUEDN....128
PFXMCUEFN....128
PFXMFHDFN....133
PFXMFHFFN....133
PFXMFMHFDFN....133
PFXMHAAN....134
PFXMHBABN....134
PFXMHBBAN....134
PFXMHBBBN....134
PFXMHBBCN....134
PFXMHBBDN....134
PFXMHBCBN....134
PFXMHBCCN....134
PFXMHBCDN....134
PFXMHBDCN....134
PFXMHBDDN....134
PFXMHBDFN....134
PFXMHBEFN....134
PFXMHBGGN....134
PFXMHFFN....133
PFXMMHDFN....133
PFXMMHFFN....133
PFXNV104A....154
PFXNV105A....154
PFXNV106A....154

PFXNV200A....153
PFXPG100K....91
PFXPGLF100K....91
PFXQ3C322C....108, 110
PFXQAC31C....109-110
PFXQAC32C....109-110
PFXQAC32CLK....109-110
PFXQAJ34C....109-110
PFXQAP32C....109-110
PFXQAPP32C....110, 113
PFXQAQ32BN....109, 111
PFXQAQ32C....109, 111
PFXQAQ32ORB....109, 111
PFXQAS32C....109-110
PFXQAT22C....109-110
PFXQAT32C....109-110
PFXQAV32C....109-110
PFXQSC32C....110, 112
PFXQSF22C....110, 112
PFXQSP32C....110, 112
PFXQSPP32C....110, 113
PFXQSQ32BN....111, 113
PFXQSQ32C....111, 113
PFXQSQ32ORB....111, 113
PFXQSS32C....110, 112
PFXQST22C....110, 112
PFXQST32C....110, 112
PFXQSV32C....110, 112
PFXR850PD....148
PFXR850PF....148
PFXR850PG....148
PFXR858PD....148
PFXR858PF....148
PFXR858PG....148
PFXRCAP....148
PFXSC32C....110, 113
PFXSC32CA....110, 112
PFXSCVD....150
PFXSCVF....150
PFXSCVG....150
PFXSCVH....150
PFXSCVJ....150
PFXSCVK....150
PFXSD6C60ET....105
PFXSD6C72ET....105
PFXSP32C....110, 113
PFXSS32C....110, 113
PFXSSIEN....129
PFXST22C....110, 113
PFXST32C....110, 113
PFXSV32C....110, 113
PFXSV32R....110, 113
PFXT12....162
PFXT12I....162
PFXT300D....151
PFXT300F....151
PFXT300G....151
PFXT300H....151
PFXT300J....151
PFXT300K....151
PFXT300L....151
PFXT300M....151
PFXT300P....151
PFXT300SD....151
PFXT300SF....151
PFXT300SG....151
PFXT300SH....151
PFXT300SJ....151
PFXT300SK....151
PFXT300SL....151
PFXT300SM....151
PFXT5....162
PFXT5I....162
PFXU308....41
PFXU3085....41
PFXWHACFD....117
PFXWHACSD....117
PFXWHACTC....117
PFXWHACTD....117
PFXWHAPD....117
PFXWHAPPD....117
PFXWHAPPTD....117
PFXWHAPTD....117
PFXWHASD....117
PFXWHATD....117
PFXWHATSD....116
PFXWHAUTB....117
PFXWHAUTC....117
PFXWHAUTD....117
PMEL4500HI....164
PMEL4500LO....163
PMTC18....162
PMTC24....162
PROPFAS4....61
PS000202....228
PS000203....228
PS000204....228
PS000205....228
PS000206....228
PS000312....228
PS000313....228
PS000314....228
PS000315....228
PS000316....228
PS000317....228
PS000318....228
PS000319....228
PS000324....228
PS000325....228
PS000326....228
PS000327....228
PS000328....228
PS000329....228
PS000335....228
PS000336....228
PS000337....228
PS000338....228
PS000339....228
PS000340....228
PS000341....228
PS000342....228
PS000343....228
PS000344....228
PS000345....228
PS000412....227
PS000414....227
PS000427....227
PS000431....227
PS000439....227
PS000440....227
PS000441....227
PS000442....227
PS000443....227
PS000446....227
PS000448....227
PS000453....227
PS000454....227
PS000456....227
PS000461....227
PS000462....227
PS000470....227
PS000471....227
PS000472....227
PS000473....227
PS000474....227
PS000475....227
PS000476....227
PS000477....227
PS000478....227
PS000479....227
PS000484....227
PS000485....227
PS000486....227
PS000487....227
PS000488....227
PS000489....227
PS000490....227
PS000491....227
PS000492....227
PS000494....227
PS000496....227
PS000497....227
PS000498....227
PS000503....227
PS000504....227
PS000505....227
PS000506....227
PS000702....228
PS000703....228
PS000704....228
PS000731....228
PS000732....228
PS000733....228
PS000734....228
PS000735....228
PS000736....228
PS000814....228
PS000824....229
PS000825....229
PS000826....229
PS000827....229
PS000828....229
PS000829....229
PS000830....229
PS000854....229
PS000855....229
PS000856....229
PS000857....229
PS000858....229
PS000859....229
PS000860....229
PS000861....229
PS000909....228
PS000910....228
PS000911....228
PS000913....228
PS000915....228
PS000916....228
PS000918....228
PS0402....234
PS0403....234
PS0404....234
PS0503....234
PS0504....234
PS0602....234
PS0603....234
PS0604....234
PS0605....234
PS0606....234
PS0644....230
PS0645....230
PS0646....230
PS0648....230
PS0649....230
PS0650....230
PS0651....230
PS0652....230
PS0653....230
PS0654....230
PS0655....230
PS10001....230
PS10007....231
PS1CW10P....189
PS1CW10U....189
PS1CW10X....189
PS1CW1212....189
PS1CW12P....189
PS1CW12U....189
PS1CW12X....189
PS1CW14U....189
PS1CW14X....189
PS1CWML10U....193
PS1CWML1212....193
PS1CWML12U....193
PS1CWML12X....193
PS1CWML14X....193
PS1CWMLXP....193
PS1CWXP....189
PS1WW10U....193
PS1WW12U....193
PS1WW14U....193
PS1WW16U....193
PS1WWXP....193
PS2CW1010....189
PS2CW10U....189
PS2CW1212....189
PS2CW12U....189
PS2CW12X....189
PS2W3W10P....193
PS2W3W10U....193
PS2W3W10X....193
PS2W3W1210....193
PS2W3W1212....193
PS2W3W12P....193
PS2W3W12U....193
PS2W3W12X....193
PS2W3W14P....193
PS2W3W14U....193
PS2W3W14X....193
PS2W3W16U....193
PS2W3W16X....193
PS2W3W24U....193
PS2W3W30U....193
PS2W3WUP....193
PS2W3WUU....193
PS2W3WXP....193
PS2W3WXU....193
PS2W3WXX....193
PS2WW1010....194
PS2WW10P....194
PS2WW10S....194
PS2WW10U....194
PS2WW10X....194
PS2WW1210....194
PS2WW1212....194
PS2WW12P....194
PS2WW12S....194
PS2WW12U....194
PS2WW12X....194
PS2WW1410....194
PS2WW14P....194
PS2WW14U....194
PS2WW14X....194
PS2WW16P....194
PS2WW16U....194
PS2WW16X....194
PS2WW18U....194
PS2WW18X....194
PS2WW20U....194
PS2WW20X....194
PS2WW24U....194
PS2WW24X....194
PS2WWML10P....194
PS2WWML10U....194
PS2WWML10X....194
PS2WWML12P....194
PS2WWML12U....194
PS2WWML12X....194
PS2WWML14P....194
PS2WWML14U....194
PS2WWML14X....194
PS2WWML16U....194
PS2WWMLXP....194
PS2WWMLXU....194
PS2WWUP....194
PS2WWUU....194
PS2WWXP....194
PS2WWXU....194
PS2WWXX....194
PS3CW1010....190
PS3CW10P....190
PS3CW10U....190
PS3CW10X....190
PS3CW1212....190
PS3CW12P....190
PS3CW12U....190
PS3CW12X....190
PS3CW14P....190
PS3CW14U....190
PS3CW14X....190
PS3CWUU....190
PS3CWXP....190
PS3CWXU....190
PS3CWXX....190
PS3W3W10U....194
PS3W3W12P....194
PS3W3WXP....194
PS3WW1010....194
PS3WW10P....194
PS3WW10U....194
PS3WW10X....194
PS3WW1212....194
PS3WW12P....194
PS3WW12U....194
PS3WW12X....194
PS3WW1410....194
PS3WW1414....194
PS3WW14P....194
PS3WW14U....194
PS3WW14X....194
PS3WW16X....194
PS3WWML10P....195
PS3WWML10U....195
PS3WWML12U....195
PS3WWML12X....195
PS3WWML1410....195
PS3WWML14U....195
PS3WWML14X....195
PS3WWMLXP....195
PS3WWMLXX....195
PS3WWUU....194
PS3WWXP....194
PS3WWXU....194
PS3WWXX....194
PS41101....182
PS41102....182
PS41103....182
PS41104....182
PS41105....182
PS41106....182
PS41107....182
PS41108....182
PS41109....182
PS41110....182
PS41111....182
PS41112....182
PS41114....182
PS41115....182
PS41116....182
PS4CW1010....190
PS4CW1212....190
PS4CW1414....190
PS4CWML1010....195
PS4CWML1212....195
PS4CWMLXX....195
PS4CWUU....190
PS4CWXX....190
PS4WW1010....195
PS4WW1212....195
PS4WW1414....195
PS4WW1616....195
PS4WW1818....195
PS4WWML1010....195
PS4WWML1212....195
PS4WWML1414....195
PS4WWMLUU....195
PS4WWMLXX....195
PS4WWUU....195
PS4WWXX....195
PS546....230
PS546BP....230
PS548....230
PS548BP....230
PS549....230
PS550....230
PS551....230
PS552....230
PS67191....230
PS67192....230
PS67193....230
PS67194....230
PS67195....230
PS67196....230
PS67198....230
PS9546....230
PS9548....230
PSA1CW1010....190
PSA1CW10P....190
PSA1CW10U....190
PSA1CW10X....190
PSA1CW1212....190
PSA1CW12P....190
PSA1CW12U....190
PSA1CW12X....190
PSA1CW14U....190
PSA1CW14X....190
PSA1CWUU....190
PSA1CWXP....190
PSA1CWXX....190
PSA2CW1010....190
PSA2CW10U....190
PSA2CW10X....190
PSA2CW1212....190
PSA2CW12U....190
PSA2CW12X....190
PSA2CW14X....190

PSA2CWXX....190
PSA3CW1010....191
PSA3CW10P....191
PSA3CW10U....191
PSA3CW1212....191
PSA3CW12U....191
PSA3CW12X....191
PSA3CW1414....191
PSA3CW14P....191
PSA3CW14U....191
PSA3CW14X....191
PSA3CWUU....191
PSA3CWXP....191
PSA3CWXU....191
PSA3CWXX....191
PSA3W1010....196
PSA3W1212....196
PSA3WUU....196
PSA3WXX....196
PSA4COBW1010....191
PSA4COBW1212....191
PSA4COBW1414....191
PSA4COBWUU....191
PSA4COBWXX....191
PSA4CW1010....191
PSA4CW1212....191
PSA4CW1414....191
PSA4CW1616....191
PSA4CWUU....191
PSA4CWXX....191
PSA4W1010....196
PSA4W1212....196
PSA4W1414....196
PSA4WUU....196
PSA4WXX....196
PSAASW1010....192
PSAASW10P....192
PSAASW10U....192
PSAASW10X....192
PSAASW1212....192
PSAASW12P....192
PSAASW12U....192
PSAASW12X....192
PSAASW1410....192
PSAASW1414....192
PSAASW14P....192
PSAASW14U....192
PSAASW14X....192
PSAASW1610....192
PSAASW1616....192
PSAASW16P....192
PSAASW16U....192
PSAASW16X....192
PSAASW1810....192
PSAASW1812....192
PSAASW1818....192
PSAASW18U....192
PSAASW18X....192
PSAASW2020....192
PSAASW20P....192
PSAASW20U....192
PSAASW20X....192
PSAASW2412....192
PSAASW2414....192
PSAASW24P....192
PSAASW24U....192
PSAASW24X....192
PSAASW28U....192
PSAASW28X....192
PSAASW30U....192
PSAASW30X....192
PSAASWUU....192
PSAASWXP....192
PSAASWXU....192
PSAASWXX....192
PSAEC51212....207
PSAEC51414....207
PSAEC52210....207
PSAEC52414....207
PSAEC5FG2014....203
PSAEC5FG2412....203
PSAEC5FG2414....203
PSAEC5FG2420....203
PSAEC5FG3014....203
PSAEC5FG3020....203
PSAEC5FG3024....203
PSAEC5ITB2222....207
PSAEC5TB2210....208
PSAEC5TB2222....208
PSAH45FGW1010....203
PSAH45FGW1212....203
PSAH45FGW1224....203
PSAH45FGW1414....203
PSAH45FGW14X....203
PSAH45FGW1818....203
PSAH45FGW1824....203
PSAH45FGW2020....203
PSAH45FGW2025....203
PSAH45FGW2412....203
PSAH45FGW2418....203
PSAH45FGW2430....203
PSAH45FGW3018....203
PSAH45FTB2020....208
PSAH45FTB2424....208
PSAH45FTB2448....208
PSAH45TB....208
PSAH45TB1010....208
PSAH45TB1212....208
PSAH45TB1414....208
PSAH45TBXX....208
PSAH45W1010....207
PSAH45W10U....207
PSAH45W1212....207
PSAH45W1224....207
PSAH45W12U....207
PSAH45W12X....207
PSAH45W1410....207
PSAH45W1414....207
PSAH45W1420....207
PSAH45W14X....207
PSAH45W1616....207
PSAH45W1818....207
PSAH45W1824....207
PSAH45W2010....207
PSAH45W2012....207
PSAH45W2014....207
PSAH45W2016....207
PSAH45W2020....207
PSAH45W20X....207
PSAH45W2410....207
PSAH45W2412....207
PSAH45W2414....207
PSAH45W2416....207
PSAH45W2418....207
PSAH45W2420....207
PSAH45W2424....207
PSAH45W24U....207
PSAH45W24X....207
PSAH45W2814....207
PSAH45W3010....207
PSAH45W3012....207
PSAH45W3014....207
PSAH45W3016....207
PSAH45W3018....207
PSAH45W3020....207
PSAH45W30X....207
PSAH45W3610....207
PSAH45W3612....207
PSAH45W3614....207
PSAH45W36X....207
PSAH45W4824....207
PSAH45WUU....207
PSAH45WXP....207
PSAH45WXX....207
PSAK10H....230
PSAK14J....230
PSAMCTBXX....196
PSAMODOB1010....196
PSAMODOB1212....196
PSAMODOB1414....196
PSAMODOB1616....196
PSAMODOB2020....196
PSAMODOBXX....196
PSARGW1010....207
PSARGW1212....207
PSARGW1410....207
PSARGWUU....207
PSARGWXX....207
PSAVHOBW1010....192
PSAVHOBW10U....192
PSAVHOBW10X....192
PSAVHOBW1212....192
PSAVHOBW12U....192
PSAVHOBW12X....192
PSAVHOBW14U....192
PSAVHOBW14X....192
PSAVHOBW16U....192
PSAVHOBW16X....192
PSAVHOBW18U....192
PSAVHOBW18X....192
PSAVHOBW20U....192
PSAVHOBW24U....192
PSAVHOBW24X....192
PSAVHOBWUU....192
PSAVHOBWXU....192
PSAVHOBWXX....192
PSAVHW1010....192
PSAVHW1212....192
PSAVHW14X....192
PSBBDB18....196
PSBBDW15....196
PSBBDW18....196
PSBBR783W10U....189
PSBBR783W14U....189
PSBBRD10U....189
PSBBRD14U....189
PSBBRW18....202
PSBIT10D100....229
PSBIT10D500....229
PSBIT10F100....229
PSBIT10F1000....229
PSBIT10F500....229
PSBIT10F5000....229
PSBIT10G100....229
PSBIT10G500....229
PSBIT8D100....229
PSBIT8D1000....229
PSBIT8D500....229
PSBIT8F100....229
PSBIT8F1000....229
PSBIT8F500....229
PSBRG3W14U....202
PSBRG3W30U....202
PSCDBXW1414....199
PSCDBXW1616....199
PSCDBXW1818....199
PSCDBXW2020....199
PSCDBXW2222....199
PSCDBXW2424....199
PSCP15....209
PSCP15WS....209
PSCP15WS20T....209
PSCP20LPWS....209
PSCP20WS....209
PSCP20WS20T....209
PSCP20WS230....210
PSCP24WS....210
PSCP45WS....210
PSCP72OFSS....209
PSCPE24242....208
PSCPE24243....208
PSCPE24302....208
PSCPE24362....208
PSCPE24363....208
PSCPE30302....208
PSCPE30303....208
PSCPE30362....208
PSCPE32322....208
PSCPE32323....208
PSCPE32442....208
PSCPE36362....208
PSCPE36363....208
PSCPE36402....208
PSCPE36483....208
PSCPE38422....208
PSCPE52523....208
PSCPLS....181
PSCPMS115....210
PSCPMS230....210
PSCPMSOP230....210
PSCTB11....230
PSCTB14....230
PSCTB24....230
PSCTB36....230
PSCTB48....230
PSCTBV....230
PSCTBV1000....230
PSCTN36....230
PSCTN48....230
PSDB10....201
PSDB12....201
PSDB14....201
PSDBU....201
PSDBW....201
PSDBX....201
PSDFDBK10....199
PSDFDBK12....199
PSDFDBK14....199
PSDFDBP10....199
PSDFDBP12....199
PSDFDBP14....199
PSDFDBU10....199
PSDFDBU12....199
PSDFDBU14....199
PSDFDWU10....199
PSDFDWU14....199
PSDLUG....181
PSDR10....201
PSDR12....201
PSDR14....201
PSDRU....201
PSDRX....201
PSDTC260B....232
PSDTC260S....232
PSDTU260S....232
PSFBFG2W1010....202
PSFBFG2W1212....202
PSFBFG2W1414....202
PSFBFG2W1420....202
PSFBFG2W1424....202
PSFBFG2W1425....202
PSFBFG2W1430....202
PSFBFG2W1616....202
PSFBFG2W1625....202
PSFBFG2W1816....202
PSFBFG2W1818....202
PSFBFG2W2010....202
PSFBFG2W2012....202
PSFBFG2W2014....202
PSFBFG2W2016....202
PSFBFG2W2020....202
PSFBFG2W2025....202
PSFBFG2W2030....202
PSFBFG2W2410....202
PSFBFG2W2412....202
PSFBFG2W2414....202
PSFBFG2W2416....202
PSFBFG2W2420....202
PSFBFG2W2424....202
PSFBFG2W2512....202
PSFBFG2W2514....202
PSFBFG2W2516....202
PSFBFG2W2520....202
PSFBFG2W3010....202
PSFBFG2W3012....202
PSFBFG2W3014....202
PSFBFG2W3016....202
PSFBFG2W3018....202
PSFBFG2W3020....202
PSFBFG2W3024....202
PSFBFG2W3614....202
PSFBFG2W4020....202
PSFDBK10....199
PSFDBK12....199
PSFDBK14....199
PSFDBP10....199
PSFDBP12....199
PSFDBP14....199
PSFDBPX....199
PSFDBU10....199
PSFDBU12....199
PSFDBU14....199
PSFDBX14....199
PSFDWK10....199
PSFDWK12....199
PSFDWK14....199
PSFDWP10....199
PSFDWP12....199
PSFDWP14....199
PSFDWPX....199
PSFDWU10....199
PSFDWU12....199
PSFDWU14....199
PSFDWX14....199
PSFG3W1212....203
PSFG3W1414....203
PSFG3W1420....203
PSFG3W1424....203
PSFG3W1425....203
PSFG3W14U....203
PSFG3W1616....203
PSFG3W1620....203
PSFG3W1625....203
PSFG3W1818....203
PSFG3W2012....203
PSFG3W2014....203
PSFG3W2016....203
PSFG3W2020....203
PSFG3W2025....203
PSFG3W2412....203
PSFG3W2424....203
PSFG3W2520....203
PSFGBP....198
PSFGFHBIW2020....205
PSFGFHBW2020....204
PSFGTBIW2020....204
PSFGTBW2020....205
PSFGW1010....204
PSFGW1020....204
PSFGW10U....204
PSFGW1212....204
PSFGW1220....204
PSFGW1224....204
PSFGW1230....204
PSFGW1236....204
PSFGW12U....204
PSFGW1410....204
PSFGW1412....204
PSFGW1414....204
PSFGW1420....204
PSFGW1424....204
PSFGW1425....204
PSFGW1430....204
PSFGW14X....204
PSFGW1612....204
PSFGW1616....204
PSFGW1620....204
PSFGW1624....204
PSFGW1625....204
PSFGW1630....204
PSFGW1812....204
PSFGW1818....204
PSFGW1824....204
PSFGW1830....204
PSFGW18X....204
PSFGW2010....204
PSFGW2012....204
PSFGW2014....204
PSFGW2016....204
PSFGW2020....204
PSFGW2024....204
PSFGW2025....204
PSFGW2030....204
PSFGW2040....204
PSFGW20X....204
PSFGW2222....204
PSFGW2410....204
PSFGW2412....204
PSFGW2414....204
PSFGW2416....204
PSFGW2418....204
PSFGW2420....204
PSFGW2424....204
PSFGW2430....204
PSFGW2436....204
PSFGW24X....204
PSFGW2514....204
PSFGW2516....204
PSFGW2520....204
PSFGW2525....204
PSFGW2532....204
PSFGW3010....204
PSFGW3012....204
PSFGW3014....204
PSFGW3016....204
PSFGW3018....204

PSFGW3020 204
PSFGW3024 204
PSFGW3025 204
PSFGW3030 204
PSFGW30X 204
PSFGW3225 204
PSFGW4020 204
PSFRDB10P 191
PSFRDB10U 191
PSFRDBP12 191
PSFRDBP14 191
PSFRDBPX 191
PSFRDBU12 191
PSFRDBU14 191
PSFRDBUX 191
PSFRDBX12 191
PSFRDBX14 191
PSFRDBXX 191
PSFRDWP10 191
PSFRDWU10 191
PSFRGBP10 203
PSFRGBP12 203
PSFRGBP14 203
PSFRGBP30 203
PSFRGBU10 203
PSFRGBU12 203
PSFRGBU14 203
PSFRGBU18 203
PSFRGBU20 203
PSFRGBU24 203
PSFRGBU30 203
PSFRGBX10 203
PSFRGBX12 203
PSFRGBX14 203
PSFRGBX16 203
PSFRGBX20 203
PSFRGBX24 203
PSFRGBX30 203
PSFRGB1010 203
PSFRGB1012 203
PSFRGB1014 203
PSFRGB1016 203
PSFRGB1020 203
PSFRGB1024 203
PSFRGB1030 203
PSFRGB1212 203
PSFRGB1214 203
PSFRGB1220 203
PSFRGB1224 203
PSFRGB1230 203
PSFRGB14P 203
PSFRGB1414 203
PSFRGB1420 203
PSFRGB1424 203
PSFRGB1430 203
PSFRGB1616 203
PSFRGB1620 203
PSFRGB1624 203
PSFRGB2020 203
PSFRGB36U 203
PSG12152 234
PSG12153 234
PSG12154 234
PSG12252 234
PSG12253 234
PSG12254 234
PSG14102PK 233
PSG14103PK 233
PSG14104PK 233
PSG14302PK 233
PSG14303PK 233
PSG14304PK 233
PSG14452 234
PSG14453 234
PSG14454 234
PSG16323 234
PSG17552 233
PSG17553 233
PSG17554 233
PSG18156 233
PSG20152 233
PSG20153 233
PSG20154 233
PSG20352 233
PSG20353 233
PSG20354 233
PSG20452 233
PSG20453 233
PSG20454 233
PSG21106 233
PSGDDSD14P 200
PSGDDSD14U 200
PSGDDSD18P 200
PSGDDSD18U 200
PSGDDSD26U 200
PSGTTD260 232
PSGTTD520 232
PSHDFBD 231
PSHDFBF 231
PSHDFBG 231
PSHDFBH 231
PSHDFBJ 231
PSHDFBK 231
PSHFSW1010 205
PSHFSW10U 205
PSHFSW1212 205
PSHFSW12U 205
PSHFSW12X 205
PSHFSW1410 205
PSHFSW1414 205
PSHFSW14U 205
PSHFSW14X 205
PSHFSW1616 205
PSHFSW16X 205
PSHFSW1818 205
PSHFSW2010 205
PSHFSW2012 205
PSHFSW2014 205
PSHFSW2016 205
PSHFSW2020 205
PSHFSW2025 205
PSHFSW20U 205
PSHFSW20X 205
PSHFSW2410 205
PSHFSW2412 205
PSHFSW2414 205
PSHFSW2416 205
PSHFSW2420 205
PSHFSW2424 205
PSHFSW24X 205
PSHFSW2520 205
PSHFSW3010 205
PSHFSW3012 205
PSHFSW3014 205
PSHFSW3016 205
PSHFSW3020 205
PSHFSW30U 205
PSHFSW30X 205
PSHFSW3612 205
PSHFSW3614 205
PSHFSWUU 205
PSHFSWXX 205
PSHVD10 199
PSHVD12 199
PSHVD14 199
PSHVD310 199
PSHVD312 199
PSHVD314 199
PSHVD32424 197
PSHVD3I10 197
PSHVD3I12 197
PSHVD3IBD10 200
PSHVD3IBD12 200
PSHVD3IBDU 200
PSHVD3IBDX 200
PSHVD3IU 197
PSHVD3IX 197
PSHVD3U 199
PSHVD3X 199
PSHVDU 199
PSHVDX 199
PSHYD1GALREG 236
PSHYD5GALFAS 236
PSHYD5GALREG 236
PSIDU 201
PSLFSI2424 197
PSLSRS1B 200
PSLSRS2B 200
PSLSWSHR 200
PSLUBXL1G 181
PSLUBXL1Q 181
PSLUBXL5G 181
PSMJARTBFN 181
PSMJARTBFP 181
PSMJARTBFR 181
PSMJTHBNEM 181
PSMJTHBNFN 181
PSMJTHBNFP 181
PSMJTHBNFR 181
PSMJTHBNFS 181
PSMJTHBNFU 181
PSMJTHBNFW 181
PSMJTHBNGU 181
PSMTTD260 232
PSMTTD520 232
PSMTTF520 232
PSOBD1010 201
PSOBD1212 201
PSOBD1414 201
PSOBDUU 201
PSOBDXX 201
PSP2WW10X 191
PSP2WW12U 191
PSP2WW14U 191
PSP2WW14X 191
PSP2WWUU 191
PSP2WWXP 191
PSP3WW10U 191
PSP3WW10X 191
PSP3WW12U 191
PSP3WW14X 191
PSP3WWXP 191
PSP4WW1010 192
PSP4WW1212 192
PSP4WWUU 192
PSP4WWXX 192
PSPC50LB 236
PSPCBRST10 198
PSPCBRST12 198
PSPCBRST14 198
PSPCBRST16 198
PSPCBRST18 198
PSPCBRSTU 198
PSPCBRSTX 198
PSPCBSST10 197
PSPCBSST12 197
PSPCBSST14 197
PSPCBSST16 197
PSPCBSSTU 197
PSPCBSSTX 197
PSPFBR 198
PSPFBS 198
PSPFGFBR 205
PSPLEBE 181
PSPLEBF 181
PSPRDI2424 198
PSPRF 208
PSPRF2412 208
PSPSBSST10 198
PSPSBSST12 198
PSPSBSSTU 198
PSPSBSSTX 198
PSPSDI2424 198
PSPSI 198
PSPWT110 232
PSPWT210 232
PSPWT210Y 232
PSPWT220 232
PSPWT410 232
PSPWT410Y 232
PSRAD10 201
PSRAD12 201
PSRADU 201
PSRADW10 200
PSRADW12 200
PSRADW14 200
PSRADW16 200
PSRADWX 200
PSRADX 201
PSRCDW10 200
PSRCDW12 200
PSRCDW14 200
PSRCDWU 200
PSRCDWX 200
PSRDR10 201
PSRDR12 201
PSRDR14 201
PSRDRU 201
PSRDRX 201
PSRG3W1010 206
PSRG3W1020 206
PSRG3W1024 206
PSRG3W10P 206
PSRG3W10U 206
PSRG3W1210 206
PSRG3W1212 206
PSRG3W1224 206
PSRG3W12P 206
PSRG3W12U 206
PSRG3W12X 206
PSRG3W1410 206
PSRG3W1414 206
PSRG3W1420 206
PSRG3W1424 206
PSRG3W14U 206
PSRG3W14X 206
PSRG3W1610 206
PSRG3W1616 206
PSRG3W1620 206
PSRG3W1624 206
PSRG3W16X 206
PSRG3W1812 206
PSRG3W1818 206
PSRG3W18X 206
PSRG3W2010 206
PSRG3W2012 206
PSRG3W2014 206
PSRG3W2016 206
PSRG3W2018 206
PSRG3W2020 206
PSRG3W2024 206
PSRG3W20U 206
PSRG3W20X 206
PSRG3W2410 206
PSRG3W2412 206
PSRG3W2414 206
PSRG3W2416 206
PSRG3W2420 206
PSRG3W2424 206
PSRG3W2430 206
PSRG3W24U 206
PSRG3W24X 206
PSRG3W3010 206
PSRG3W3012 206
PSRG3W3014 206
PSRG3W30U 206
PSRG3W30X 206
PSRG3W36X 206
PSRG3WUU 206
PSRG3WXX 206
PSRG783W12U 202
PSRG783W12X 202
PSRG783W14U 202
PSRG783W14X 202
PSRG783W16X 202
PSRG783W20X 202
PSRG783W2412 202
PSRG783W24U 202
PSRG783W24X 202
PSRG783W3010 202
PSRG783W3012 202
PSRG783W30U 202
PSRG783W30X 202
PSRG783W36U 202
PSRG783W36X 202
PSRG78W14X 202
PSRG78W30X 202
PSRGW1010 206
PSRGW1014 206
PSRGW1020 206
PSRGW1024 206
PSRGW10P 206
PSRGW10U 206
PSRGW10X 206
PSRGW1210 206
PSRGW1212 206
PSRGW1216 206
PSRGW1218 206
PSRGW1220 206
PSRGW1224 206
PSRGW1230 206
PSRGW12P 206
PSRGW12U 206
PSRGW12X 206
PSRGW1410 206
PSRGW1412 206
PSRGW1414 206
PSRGW1416 206
PSRGW1420 206
PSRGW1424 206
PSRGW1425 206
PSRGW1430 206
PSRGW14P 206
PSRGW14U 206
PSRGW14X 206
PSRGW1610 206
PSRGW1612 206
PSRGW1616 206
PSRGW1620 206
PSRGW1624 206
PSRGW1625 206
PSRGW16U 206
PSRGW16X 206
PSRGW1812 206
PSRGW1818 206
PSRGW1824 206
PSRGW1830 206
PSRGW18P 206
PSRGW18U 206
PSRGW18X 206
PSRGW2010 206
PSRGW2012 206
PSRGW2014 206
PSRGW2016 206
PSRGW2020 206
PSRGW2024 206
PSRGW2025 206
PSRGW2030 206
PSRGW20U 206
PSRGW20X 206
PSRGW2410 206
PSRGW2412 206
PSRGW2414 206
PSRGW2416 206
PSRGW2418 206
PSRGW2420 206
PSRGW2424 206
PSRGW2430 206
PSRGW24U 206
PSRGW24X 206
PSRGW2516 206
PSRGW2520 206
PSRGW3010 206
PSRGW3012 206
PSRGW3014 206
PSRGW3016 206
PSRGW3018 206
PSRGW3020 206
PSRGW3024 206
PSRGW3030 206
PSRGW30U 206
PSRGW30X 206
PSRGW3610 206
PSRGW3612 206
PSRGW3614 206
PSRGW3624 206
PSRGWUU 206
PSRGWX14 206
PSRGWXP 206
PSRGWXU 206
PSRGWXX 206
PSSICR10 200
PSSICR12 200
PSSICR14 200
PSSICRU 200
PSSICRW 200
PSSICRX 200
PSSIPP 200
PSSMF2424 201
PSSPD10 197
PSSPD12 197
PSSPD14 197
PSSPDI2424 197
PSSPDU 197
PSSPDX 197
PSSQCDW12 196

PSTC30....162
PSTC36....162
PSTS11NP....211
PSTS11P52....211
PSTS21NP....211
PSTS21P52....211
PSTSBK10....208
PSTSBK12....208
PSTSBK14....208
PSTSBP10....208
PSTSL11NP....211
PSTSL11P52....211
PSTSL21NP....211
PSTSL21P52....211
PSTSWK10....208
PSTSWK12....208
PSTSWK14....208
PSTTD260....232
PSTTD520....232
PSTTF260....232
PSTTF520....232
PSTTG520....232
PSVAFW1010....193
PSVAFW10P....193
PSVAFW10U....193
PSVAFW10X....193
PSVAFW1210....193
PSVAFW1212....193
PSVAFW12P....193
PSVAFW12U....193
PSVAFW12X....193
PSVAFW1410....193
PSVAFW1414....193
PSVAFW14P....193
PSVAFW14U....193
PSVAFW14X....193
PSVAFW1612....193
PSVAFW1616....193
PSVAFW16P....193
PSVAFW16U....193
PSVAFW16X....193
PSVAFW1810....193
PSVAFW1818....193
PSVAFW18U....193
PSVAFW18X....193
PSVAFW2010....193
PSVAFW2012....193
PSVAFW2014....193
PSVAFW2020....193
PSVAFW20U....193
PSVAFW20X....193
PSVAFW2424....193
PSVAFW24U....193
PSVAFW24X....193
PSVAFW3010....193
PSVAFW3012....193
PSVAFW3018....193
PSVAFW30U....193
PSVAFWUU....193
PSVAFWXP....193
PSVAFWXU....193
PSVAFWXX....193
PSVB165S....186
PSVB165W....186
PSVB461AW....185
PSVB461SS....185
PSVB461SW....185
PSVB562AW....185
PSVB562SW....185
PSVB564SW....185
PSVB664SW....185
PSVB8450....186
PSVBC....185
PSVBM1007CO....187
PSVBM1007SC....187
PSVBM1007SCSWR....187
PSVBM1007SWR....187
PSVBTUCSONPS....187
PSVBTUCSONWV....187
PSVOBW1010....192
PSVOBW10U....192
PSVOBW1212....192
PSVOBW12U....192
PSVOBW12X....192
PSVOBW1414....192
PSVOBW14U....192
PSVOBW14X....192
PSVOBW16U....192
PSVOBW16X....192
PSVOBW18U....192
PSVOBW18X....192
PSVOBW20U....192
PSVOBW20X....192
PSVOBW24U....192
PSVOBW24X....192
PSVOBWUU....192
PSVOBWXU....192
PSVOBWXX....192
PSW12101....162
PSW12102....162
PSW12103....162
PSW12104....162
PSW12301....163
PSW12302....163
PSW12303....163
PSW12304....163
PSW12305....164
PSW12306....164
PSW12307....164
PSW12308....164
PSW12309....164
PSW12310....164
PSW12311....164
PSW12312....163
PSW12313....163
PSW12314....163
PSW12317....163
PSW12320....164
PSW12321....164
PSW12322....164
PSW12323....164
PSW12324....164
PSW12325....163
PSW12501....162
PSW12503....162
PSW12504....163
PSW12505....164
PSW12506....164
PSW12507....163
PSW12508....164
PSW12509....163
PSW12601....163
PSW12701....162
PSW12702....162
PSW12704....162
PSW12705....162
PSW12708....162
PSW12901....162
PSWALLPLT....211
PSXET....232
PSZIP10D1000....229
PSZIP10F100....229
PSZIP10F1000....229
PSZIP10F5000....229
PSZIP7D100....229
PSZIP7D1000....229
PSZIP7D15000....229
PSZIP7D5000....229
PSZIP8D100....229
PSZIP8D1000....229
PSZIP8D12000....229
PSZIP8F100....229
PSZIP8F1000....229
PSZIP8F10000....229
PSZIP8F5000....229
PSZIP8G1000....229
PSZIP8G500....229
PSZIP8G5000....229
PSZIP8J1000....229
PSZIP8J250....229
PSZIP8J5000....229
PSZIP8JW250....229
PSZIP8K100....229
PSZIP8K1000....229
PSZIP8K250....229
PSZIP8KW250....229
PSZIP8KW50....229
PSZIP8KWFH250....229
RAP10501....226
RAP10502....226
RAP10520....226
RAP10543....226
RAP11002....236
RAP11003....236
RAP11214....220
RAP11218....220
RAP11224....220
RAP11312....221
RAP11414....220
RAP11418....220
RAP11424....220
RAP11502....221
RAP11514....220
RAP12501....217
RAP12504....217
RAP12507....217
RAP12509....217
RAP12518....217
RAP12525....217
RAP12530....217
RAP13002....218
RAP13003....218
RAP13004....218
RAP13511....225
RAP13512....225
RAP13513....225
RAP13514....225
RAP13515....225
RAP14500....226
RAP14503....218
RAP14504....218
RAP14506....218
RAP14507....218
RAP14508....218
RAP14509....218
RAP14550....218
RAP14551....218
RAP14552....218
RAP14553....218
RAP14560PK....218
RAP15502....223
RAP15507....223
RAP15508....223
RAP15510....222
RAP15515....223
RAP15520....223
RAP15525....223
RAP15610....222
RAP15615....222
RAP16001....224
RAP16002....224
RAP16003....224
RAP16004....224
RAP16007....224
RAP16009....224
RAP16012....224
RAP16013....225
RAP16014....224
RAP16030....224
RAP16031....224
RAP16032....224
RAP16033....224
RAP16034....224
RAP16501....223
RAP16504....224
RAP16505....224
RAP16506....224
RAP16507....224
RAP16508....224
RAP16512....223
RAP17002....225
RAP17004....225
RAP17006....226
RAP17007....225
RAP18001....221
RAP18002....221
RAP18003....221
RAP18004....221
RAP18006....219
RAP18007....219
RAP18008....219
RAP18009....219
RAP18010....219
RAP18011....219
RAP18024....222
RAP18541....222
RAP18550....221
RAP18551....221
RAP18552....221
RAP30501....215
RAP30502....215
RAP31201....214
RAP31202....214
RAP31203....214
RAP31204....215
RAP31206....214
RAP31207....214
RAP31401....214
RAP31402....214
RAP31601....214
RAP31602....214
RAP32001....215
RAP33001....215
RAP33002....215
RAP33003....215
RAP41002....183
RAP41003....181
RAP41007....181
RAP41008....181
RAP41017....183
RAP41023....182
RAP41024....182
RAP41025....182
RAP41026....182
RAP41027....183
RAP41028....183
RAP41030....182
RAP41031....182
RAP41032....182
RAP41033....182
RAP41034....182
RAP41035....182
RAP41037....183
RAP41038....183
RAP41039....183
RAP41201....215
RAP42009....182
RAP42014....183
RAP42015....183
RAP42040....182
RAP44020....216
RAP44022....216
RAP44024....216
RAP44026....216
RAP44028....216
RAP44030....216
RAP44032....216
RAP44034....216
RAP44036....216
RAP44040....226
RAP44042....226
RAP50105....144
RAP50115....219
RAP50125....220
RAP50130....221
RAP50145....221
RAP50150....220
RAP50175....219
RAP50185....231
RAP50190....225
RAP50200....223
RAP50205....219
RAP50210....220
RAP50215....221
RAP50220....220
RAP50230....219
RAP50245....222
RAP50315....225
RAP50325....225
RAP50330....222
RAP50505....220
RAP60001....222
RAP60002....222
RAP64010....226
RAP75001....218
RAP75003....218
RAP75004....218
RAP75005....218
RAP75006....218
RAP75007....218
RAP75009....218
RAP75010....218
RAW1L....213
RAW2L....213
RAWHS1....213
RAWHS112....213
RAWHS114....213
RAWHS1316....213
RAWHS134....213
RAWHS138....213
RAWHS2....213
RAWHS212....213
RAWHS214....213
RAWHS234....213
RAWHS258....213
RAWHS2916....213
RAWHS3....213
RAWHS312....213
RAWHS4....213
RAWHS412....213
RAWHS5....213
RAWHS512....213
RAWHS6....213
RAWHS78....213
RAWRB606HD....214
RAWRB610....214
RAWRB614....214
RAWRB614HD....214
RAWRB618....214
RAWRB624....214
RAWRB814....214
RAWRB818....214
RAWRB906HD....214
RAWRB910....214
RAWRB914HD....214
RAWRB918HD....214



FNW



FNW Hangers, Supports & Strut Accs.



Mirabelle Price Book



Mirabelle Custom Showering



Mirabelle Decorative Faucets & Accs.



Mirabelle Stainless Steel Sinks



Monogram Brass



Park Harbor



PROFLO



Mirabelle Designer Bathing

FERGUSON®

WE'RE MORE THAN JUST PLUMBING.

To view these catalogs and more,
visit us at FERGUSON.COM



PROFLO ACCUFIT



ProSelect



ProSelect Grilles, Registers & Diffusers



Raptor



FNW™ MONOGRAM BRASS® PROFLO PROSELECT™ RAPTOR™

FERGUSON®
FERGUSON.COM

WOLSELEY Canada
WOLSELEYINC.CA

©2016 Ferguson Enterprises, Inc.

2016-PL-001