

# PUMPS AND ACCESSORIES



**PROFLO**®



# Pumps and Accessories

## Table of Contents

<b>PRODUCT CATEGORY</b>	<b>PAGE</b>
Submersible Utility Pumps.....	6
Thermoplastic Sump Pumps .....	7-8
Stainless Steel Sump Pumps .....	9
Cast Iron Sump Pumps.....	10-12
Sump Pumps & Transfer Pumps .....	13
Backup Sump Pumps .....	14
Pre-Assembled Sump Pumps .....	15-16
Remote Drain Pump Kits .....	17
Cast Iron Sewage Pumps.....	18
Cast Iron & Stainless Steel Sewage Pumps...	19
Sewage Pump Kits.....	20-22
Descaler Pump Kits.....	23
Pump Accessories .....	24-25
Sewage Basin Accessories .....	26

# POWER TO THE PUMPS

We have one mission: To make pumps built to last. We didn't reinvent the pump, we just made it stronger, more reliable and—most importantly—affordable.

## 1 - MOTOR HOUSING

Our one-piece motor housing makes the pump stronger and dissipates heat with greater efficiency.

## 2 - SPLIT CAPACITOR

It's like having two gears—one for startup, another for efficient, continuous operation. More power, less energy.

## 3 - SOLID COPPER

No coated wiring here. Only 100% solid copper motor windings featured in all PROFLO pumps.

## 4 - SUPERIOR MOTOR

We design, build, test and install our own motors to ensure every PROFLO pump is built to last.

## 5 - DOUBLE SEALS

Dual seals on the bottom of each motor plate ensures water from entering the motor housing and causing failure.

## 6 - INTAKE SCREEN

All utility and sump pumps include a removable intake screen for easy cleaning.

## 7 - SHAFT SEAL

This is no regular shaft seal—this is a heavy duty stainless steel jacketed shaft seal. We put quality first.

## QUALITY TESTED


Every pump is approved by:



## FOR TECHNICAL ASSISTANCE

Contact the PROFLO Pump Assistance Line at

888-6-PROFLO  
888-677-6356



# SUBMERSIBLE UTILITY PUMPS




## 1/5 HP THERMOPLASTIC UTILITY PUMP

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Tough thermoplastic construction
- Large 1-1/4" discharge for high-capacity pumping
- Garden hose adapter included
- Can be used as a sump pump by adding an optional float switch (PF92000SJE or PF92010)

### PERFORMANCE

HEAD	GPM	GPH
0'	26	1560
5'	21	1260
10'	14	840
15'	10	600
20'	7	420
25'	1	60



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Cord Length	Solids Handling	Warranty
PF91025	1/5	3.6	Thermoplastic	1-1/4"	Top	10'	1/8"	3 Years




## 1/3 HP THERMOPLASTIC UTILITY PUMP

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Tough thermoplastic construction
- Large 1-1/4" discharge for high-capacity pumping
- Garden hose adapter included
- Can be used as a sump pump by adding an optional float switch (PF92000SJE or PF92010)

### PERFORMANCE

HEAD	GPM	GPH
0'	40	2400
5'	34	2040
10'	28	1680
15'	22	1320
20'	12	720
25'	2	120



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Cord Length	Solids Handling	Warranty
PF91335	1/3	4.1	Thermoplastic	1-1/4"	Top	25'	1/8"	3 Years

# THERMOPLASTIC SUMP PUMPS




## 1/4 HP THERMOPLASTIC SUMP PUMP WITH VERTICAL FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Tough thermoplastic construction
- Large 1-1/4" or 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	30	1800
5'	22	1320
10'	20	1200
15'	16	960
20'	9	540
25'	2	120



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92260	1/4	3.8	Thermoplastic	1-1/4" - 1-1/2"	Top	Vertical	10'	1/8"	3 Years




## 1/3 HP THERMOPLASTIC SUMP PUMP WITH TETHERED FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Tough thermoplastic construction
- Large 1-1/4" or 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	40	2400
5'	34	2040
10'	28	1680
15'	22	1320
20'	12	720
25'	2	120



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92330	1/3	4.1	Thermoplastic	1-1/4" - 1-1/2"	Top	Tethered	10'	1/8"	3 Years

# THERMOPLASTIC SUMP PUMPS




## 1/3 HP THERMOPLASTIC SUMP PUMP WITH VERTICAL FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pumps will lift water up to 25' of vertical height
- Tough thermoplastic construction
- Large 1-1/4" or 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	40	2400
5'	34	2040
10'	28	1680
15'	22	1320
20'	12	720
25'	2	120



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92342	1/3	4.1	Thermoplastic	1-1/4" - 1-1/2"	Top	Vertical	10'	1/8"	3 Years




## 1/3 HP THERMOPLASTIC SUMP PUMP WITH TETHERED FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motors
- Pumps will lift water up to 25' of vertical height
- Tough thermoplastic construction
- Large 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	48	2880
5'	44	2640
10'	40	2400
15'	36	2160
20'	23	1380
25'	16	960



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92370	1/3	4.1	Thermoplastic	1-1/2"	Side	Tethered	10'	3/8"	3 Years

# STAINLESS STEEL SUMP PUMPS




**NEW**

## STAINLESS/CAST IRON SUMP PUMP

- Rugged stainless steel and cast iron pump body for durability
- Vertical float switch
- 2" NPT Discharge
- 2" x 1-1/2" NPT Adapter
- Handles up to 1/2" solids
- Non-clogging stainless steel vortex impeller
- Integrated carrying handle

### PERFORMANCE

LIFT	GPM	GPH
0'	80	4800
15'	61	3660
30'	38	2280
45'	2	2700



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92751	3/4	7.5	Cast Iron	1-1/2" - 2"	Side	Vertical	10'	1/2"	5 Years




**NEW**

## STAINLESS/CAST IRON SUMP PUMP

- Rugged stainless steel and cast iron pump body for durability
- Vertical float switch
- 2" NPT Discharge
- 2" x 1-1/2" NPT Adapter
- Handles up to 1/2" solids
- Non-clogging stainless steel vortex impeller
- Integrated carrying handle

### PERFORMANCE

LIFT	GPM	GPH
0'	86	5160
15'	68	4080
30'	43	2580
45'	3	180



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92151	1	12	Cast Iron	1-1/2" - 2"	Side	Vertical	10'	1/2"	5 Years

# CAST IRON SUMP PUMPS




## 3/10 HP CAST IRON SUMP PUMP WITH TETHERED FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Rugged cast iron construction
- Large 1-1/2" discharge for high-capacity pumping
- Stainless steel impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	46	2760
5'	36	2160
10'	30	1800
15'	25	1500
20'	12	720
25'	1	60



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92331	3/10	4.1	Cast Iron	1-1/2"	Side	Tethered	10'	3/8"	5 Years




## 3/10 HP CAST IRON SUMP PUMP WITH VERTICAL FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Rugged cast iron construction
- Large 1-1/2" discharge for high-capacity pumping
- Stainless steel impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	46	2760
5'	36	2160
10'	30	1800
15'	25	1500
20'	12	720
25'	1	60



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92341	3/10	4.1	Cast Iron	1-1/2"	Side	Vertical	10'	3/8"	5 Years




## 1/3 HP CAST IRON SUMP PUMP WITH VERTICAL FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Tough cast iron construction
- Large 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	60	3600
5'	56	3360
10'	50	3000
15'	35	2100
20'	15	900
25'	6	360



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92352	1/3	5.9	Cast Iron	1-1/2"	Side	Vertical	10'	1/2"	5 Years
<b>NEW</b> PF9235225	1/3	5.9	Cast Iron	1-1/2"	Side	Vertical	25'	1/2"	5 Years




## 1/2 HP CAST IRON SUMP PUMP WITH VERTICAL FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Rugged cast iron construction
- Large 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	70	4200
5'	66	3960
10'	58	3480
15'	48	2880
20'	25	1500
25'	10	600



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92511	1/2	7.6	Cast Iron	1-1/2"	Side	Vertical	10'	1/2"	5 Years

# CAST IRON SUMP & EFFLUENT PUMPS




## 1/2 HP CAST IRON SUMP PUMP WITH TETHERED FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Pump will lift water up to 25' of vertical height
- Rugged cast iron construction
- Large 1-1/2" discharge for high-capacity pumping
- Thermoplastic impeller
- Can be used as a utility pump by removing the float switch

### PERFORMANCE

HEAD	GPM	GPH
0'	70	4200
5'	66	3960
10'	58	3480
15'	48	2880
20'	25	1500
25'	10	600



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92501	1/2	7.6	Cast Iron	1-1/2"	Side	Tethered	10'	1/2"	5 Years




## 1/3 HP CAST IRON EFFLUENT PUMP WITH TETHERED FLOAT SWITCH

- Continuous duty, thermally protected split capacitor motor
- Rugged cast iron construction
- Non-clogging, stainless steel vortex impeller
- Handles 5/8" solids
- Pump will lift water up to 25' vertical height
- 1-1/2" discharge for high-capacity pumping

### PERFORMANCE

HEAD	GPM	GPH
0'	60	3600
5'	56	3360
10'	50	3000
15'	35	2100
20'	15	800
25'	6	360



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92305	1/3	7.6	Cast Iron	1-1/2"	Side	Tethered	10'	5/8"	3 Years

# SUMP PUMPS & TRANSFER PUMPS




## 1/3 HP THERMOPLASTIC PEDESTAL SUMP PUMP

- Thermoplastic base
- Fully adjustable automatic switch
- Non-corrosive, plated steel drive shaft
- Metal switch arm for strength and durability
- 1-1/4" discharge for high-capacity pumping
- For use in sump basins 12" or larger

### PERFORMANCE

HEAD	GPM	GPH
0'	50	3000
5'	45	2700
10'	38	2280
15'	35	2100
20'	15	900



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Base Material	Discharge Size	Column Material	Impeller Material	Cord Length	Warranty
PF92333	1/3	2.76	Thermoplastic	1-1/4"	Thermoplastic	Stainless Steel	10'	3 Years




**NEW**

## CAST IRON PORTABLE TRANSFER PUMP

- Multi-purpose transfer pump
- Cast iron construction
- 3/4" NPT suction and discharge
- Includes brass garden hose adapters
- Includes suction strainer
- Two heavy-duty carrying handles
- Easy prime plug
- 25' Power cord
- Built-in on/off switch
- 1/2 HP fan cooled motor

### PERFORMANCE

LIFT	GPM	GPH
0'	25	1500
30'	19	1140
60'	13	780
90'	7	420
110'	3	180



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Cord Length	Solids Handling	Warranty
PF90060	1/2	8.4	Cast Iron	3/4"	Side	10'	1/8"	1 Year

# BACKUP SUMP PUMPS




## EMERGENCY BACKUP SUMP PUMP KIT

- 12V DC pump with vertical switch
- Alarm/control unit with fuse and mute feature
- Thermoplastic battery box
- Mounting hardware included
- 2 amp AC charger with power cord
- Primary pump not included

### PERFORMANCE

HEAD	GPM	GPH
0'	23	1380
5'	22	1320
10'	18	1080
15'	13	780
20'	8	480



### TECHNICAL SPECIFICATIONS


Model	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Cord Length	Solids Handling	Warranty
PF92910	12	Thermoplastic	1-1/4" or 1-1/2"	Top	Vertical	10'	1/8"	3 Years



**NEW**

## 12 VOLT HIGH PERFORMANCE BATTERY BACKUP SYSTEM

- Battery Backup System
- 12 Volt high output DC pump
- SJE Vertical float switch
- 1-1/2" NPT discharge size
- 1-1/2" check valve
- Electric control panel with indicator lights
- 87 decibel alarm with mute
- Reverse polarity protection
- Battery charge percentage indicator
- Low battery alarm
- Manual test button
- Indicator lights
- 5 amp DC charger
- Thermoplastic battery box
- Battery sold separately



### PERFORMANCE

LIFT	GPM	GPH
0'	45	2700
5'	42	2520
10'	36	2160
15'	25	1500
20'	12	720

### TECHNICAL SPECIFICATIONS

Model	Amps	Construction	Discharge Size	Discharge Type	Switch Type	Solids Handling	Warranty
PF92950	12	Thermoplastic	1-1/2"	Top	Vertical	3/8"	3 Years

# PRE-ASSEMBLED SUMP PUMPS




## PRE-ASSEMBLED PRIMARY / BACKUP SUMP PUMP KIT

PF92941 Kit Includes:

- 12V DC back-up pump with vertical switch
- Primary Pump (PF92341) with vertical switch
- Alarm/control unit with fuse and mute feature
- Thermoplastic battery box
- 2 amp AC charger with 10" power cord
- Pre-assembled kit is ready to install

### PERFORMANCE

HEAD	DC PUMP	PF92341
	GPM (at listed discharge height)	
0'	23	46
5'	22	36
10'	18	30
15'	13	25
20'	8	12
25'	-	1



### TECHNICAL SPECIFICATIONS PF92941

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Solids Handling	Warranty
DC PUMP	-	12	Thermoplastic	1-1/4" or 1-1/2"	Top	1/8"	3 Years
PF92341	3/10	4.1	Cast Iron	1-1/2"	Side	3/8"	3 Years




## PRE-ASSEMBLED PRIMARY / BACKUP SUMP PUMP KIT

PF92952 Kit Includes

- 12V DC back-up pump with vertical switch
- Primary Pump (PF92352) with vertical switch
- Alarm/control unit with fuse and mute feature
- Thermoplastic battery box
- 2 amp AC charger with power cord
- Pre-assembled kit is ready to install

### PERFORMANCE

HEAD	DC PUMP	PF92352
	GPM (at listed discharge height)	
0'	23	60
5'	22	56
10'	18	50
15'	13	35
20'	8	15
25'	-	6



### TECHNICAL SPECIFICATIONS PF92952

Model	HP	Amps	Construction	Discharge Size	Discharge Type	Solids Handling	Warranty
DC PUMP	12V	12	Thermoplastic	1-1/4" or 1-1/2"	Top	1/8"	3 Years
PF92352	1/3	5.9	Cast Iron	1-1/2"	Side	1/2"	3 Years

# PRE-ASSEMBLED SUMP PUMPS




## PRE-ASSEMBLED SUMP PUMP WITH BASE

- Pump is mounted to base to prevent clogging and switch malfunction
- Reliable vertical or tethered float switch
- 10' power cords
- Pump will lift water up to 25' of vertical height

### PERFORMANCE

HEAD	PF92342PB	PF92330PB
	GPM (at listed discharge height)	
0'	40	40
5'	34	34
10'	28	28
15'	22	22
20'	12	12
25'	2	2



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Switch Type	Discharge Size	Solids Handling	Warranty
PF92342PB	1/3	4.1	Thermoplastic	Vertical	1-1/4" or 1-1/2"	1/8"	3 Years
PF92330PB	1/3	4.1	Thermoplastic	Tethered	1-1/4" or 1-1/2"	1/8"	3 Years




## PRE-ASSEMBLED TO-GO SUMP PUMP

Kit Includes:

- Pump is mounted to base to prevent clogging and switch malfunction
- Reliable vertical float switch
- 10' power cords
- Pump will lift water up to 25' of vertical height
- Pre-plumbed with check valve and discharge pipe

### PERFORMANCE

HEAD	PFTG92352	PFTG92352P
	GPM (at listed discharge height)	
0'	60	60
5'	56	56
10'	50	50
15'	35	35
20'	15	15
25'	6	6



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Discharge Pipe	Solids Handling	Warranty
PFTG92352	1/3	5.9	Cast Iron	1-1/2"	ABS	1/2"	5 Years
PFTG92352P	1/3	5.9	Cast Iron	1-1/2"	PVC	1/2"	5 Years



## REMOTE DRAIN PUMP KIT - PF92017

Pre-assembled kit is ready for installation

Works great for laundry tubs, washing machines, wet bars and dehumidifiers

### Pump Features:

- Model PF92341 sump pump
- .3 HP continuous duty, thermally protected split capacitor motor
- Vertical float switch
- Rugged cast iron construction
- Stainless steel impeller
- Handles 3/8" solids
- Pumps up to 46 gallons per minute / 2760 gallons per hour

### Basin Features:

- Structural foam construction
- Molded reusable PVC seal
- 6 gallon capacity
- Size: 15" x 15" x 13.5"
- 1-1/2" inlet discharge & vent

### Check Valve Features:

- Model PFCVJH check valve
- Prevents backflow of water and sewer gases
- Flexible 1-1/4" or 1-1/2" rubber slip X slip connections
- PVC body
- All stainless steel clamps
- Connections fit PVC, ABS, copper or steel pipe
- Vertical or horizontal installation
- 125 psi @ 176°F



Basin



PF92341 Sump Pump



PFCVJH Check Valve

Custom kits available upon request

# CAST IRON SEWAGE PUMPS




## 1/2 HP CAST IRON SEWAGE PUMP

- Continuous duty, thermally protected split capacitor motor
- Rugged cast iron construction
- Stainless steel, non-clogging vortex impeller
- Will easily handle 2" solids
- Pump will lift water up to 25' of vertical height
- 2" discharge for high-capacity pumping

### PERFORMANCE

HEAD	GPM	GPH
0'	80	4800
5'	68	4080
10'	60	3600
15'	44	2640
20'	13	780
25'	2	120



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Switch Type	Cord Length	Solids Handling	Warranty
PF93501	1/2	7.6	Cast Iron	2"	Tethered	10'	2"	3 Years




## 1/2 HP CAST IRON SEWAGE PUMP

- Continuous duty, thermally protected split capacitor motor
- Rugged cast iron construction
- Stainless steel, non-clogging vortex impeller
- Will easily handle 2" solids
- Pump will lift water up to 25' of vertical height
- 2" discharge for high-capacity pumping

### PERFORMANCE

HEAD	GPM	GPH
0'	80	4800
5'	68	4080
10'	60	3600
15'	44	2640
20'	13	780
25'	2	120



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Switch Type	Cord Length	Solids Handling	Warranty
PF93511	1/2	7.6	Cast Iron	2"	Vertical	10'	2"	3 Years

# CAST IRON & STAINLESS STEEL SEWAGE PUMPS




## 1/2 HP CAST IRON & STAINLESS STEEL SEWAGE PUMP

- Continuous duty, thermally protected split capacitor motor
- Stainless steel and cast iron construction
- Stainless steel, non-clogging vortex impeller
- Will easily handle 2" solids
- Pump will lift water up to 30' of vertical height
- 2" discharge for high-capacity pumping

### PERFORMANCE

HEAD	GPM	GPH
0'	140	8400
5'	123	7380
10'	97	5820
15'	72	4320
20'	49	2940
25'	25	1500
30'	3	180



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Switch Type	Cord Length	Solids Handling	Warranty
PF93781	1/2	12	Cast Iron/Stainless Steel	2"	Tethered	15'	2"	3 Years




## 1/2 HP CAST IRON & STAINLESS STEEL SEWAGE PUMP

- Continuous duty, thermally protected split capacitor motors
- Stainless steel and cast iron construction
- Stainless steel, non-clogging vortex impeller
- Will easily handle 2" solids
- Pumps will lift water up to 30' of vertical height
- 2" discharge for high-capacity pumping

### PERFORMANCE

HEAD	GPM	GPH
0'	140	8400
5'	123	7380
10'	97	5820
15'	72	4320
20'	49	2940
25'	25	1500
30'	3	180



### TECHNICAL SPECIFICATIONS

Model	HP	Amps	Construction	Discharge Size	Switch Type	Cord Length	Solids Handling	Warranty
PF93782	1/2	12	Cast Iron/Stainless Steel	2"	Vertical	15'	2"	3 Years

<b>NEW</b> PF9378225	1/2	12	Cast Iron/Stainless Steel	2"	Vertical	25'	2"	3 Years
----------------------	-----	----	---------------------------	----	----------	-----	----	---------

# SEWAGE PUMP KITS



PF93015



PF93020



Basin



Hub

## SEWAGE PUMP KITS - PF93015 & PF93020

Pre-assembled kit is ready for installation

### Pump Features:

- Kit PF93015 includes pump PF93501
- Kit PF93020 includes pump PF93511
- 1/2 HP continuous duty, thermally protected split capacitor motor
- Tethered or vertical float switch
- Rugged cast iron construction
- Stainless steel, non-clogging vortex impeller
- Pumps will lift water up to 25' of vertical height
- 2" discharge will easily handle 2" solids
- 80 gallons per minute / 4800 gallons per hour

### Basin Features:


- Structural foam construction
- Air tight molded reusable pvc gasket
- Corrosion resistant
- Size: 18" x 30"
- 4" inlet hub / 2" discharge & vent
- 30 gallon capacity
- Built-in torque stops

### Hub Features:


- Fits 4" DWV schedule 40/80 pipe
- Water and vapor tight seal with no caulking



PF93501 Sewage Pump



PF93511 Sewage Pump



Custom kits available upon request



## SEWAGE PUMP KITS - PF93024 & PF93026

Pre-assembled kit is ready for installation



PF93024



PF93026

### Pump Features:

- Kit PF93024 includes pump PF93501 pump
- Kit PF93026 includes pump PF93511 pump
- 1/2 HP continuous duty, thermally protected split capacitor motor
- Tethered or vertical float switch
- Rugged cast iron construction
- Stainless steel, non-clogging vortex impeller
- Will easily handle 2" solids
- Pumps will lift water up to 25' of vertical height
- 2" discharge for high-capacity pumping
- 80 gallons per minute / 4800 gallons per hour

### Basin Features:


- Tough polyethylene construction
- Corrosion resistant
- 24" x 24" - 45 gallon capacity
- Gasket sealed liquid and airtight cover with 8 bolts
- Built-in anti float collar prevents basin from floating
- Pre-plumbed with 2" PVC
- 2" NPT discharge and vent
- Integrated 360° lifting handle
- Molded torque stops prevent pump from turning
- Solid 1 piece lid




Basin



PF93501 Sewage Pump



PF93511 Sewage Pump



# SEWAGE PUMP KITS



PF93082



PF93084



Basin

## SEWAGE PUMP KITS - PF93082 & PF93084

Pre-assembled kit is ready for installation

### Pump Features:


- Kit PF93082 includes PF93781 pump
- Kit PF93084 includes PF93782 pump
- 1/2 HP continuous duty, thermally protected split capacitor motor
- Tethered or vertical float switch
- Stainless steel and cast iron construction
- Stainless steel, non-clogging vortex impeller
- Will easily handle 2" solids
- Pumps will lift water up to 30' of vertical height
- 2" discharge for high-capacity pumping
- 140 gallons per minute / 8400 gallons per hour

### Basin Features:


- Tough polyethylene construction
- Corrosion resistant
- 24" x 24" - 45 gallon capacity
- Gasket sealed liquid and airtight cover with 8 bolts
- Built-in anti float collar prevents basin from floating
- Pre-plumbed with 2" PVC
- 2" NPT discharge and vent
- Integrated 360° lifting handle
- Molded torque stops prevent pump from turning
- 2 piece split lid



PF93781 Sewage Pump



PF93782 Sewage Pump



Custom kits available upon request




**NEW**

## DESCALER PUMP KIT - PF91655

For use with Tankless Water Heaters

### Pump Features:

- Descaler Pump Kit
- Energy efficient 55 watt mag drive pump
- 3/4" Garden hose adapter
- 3.5 Gallon pail
- Screw top lid.
- Two - 6' clear poly hoses
- Bucket filter
- **Descaler chemical is not included**





## TETHERED FLOAT SWITCH - PF92000SJE

- Mechanically activated, non-mercury, wide angle switch for use with utility, sump and sewage pumps
- 10' cord with piggyback plug
- 120 Volts AC
- Maximum Pump Running Current: 10 amps
- Includes mounting clamp



## VERTICAL FLOAT SWITCH - PF92010

- Mechanically activated, non-mercury, switch for use with utility, sump and sewage pumps
- 10' cord with piggyback plug
- 120 Volts AC
- Maximum Pump Running Current: 10 amps
- Includes mounting bracket and clamp



## SUMP PUMP BASE - PF99500

- Use instead of bricks to raise the pump off the bottom of the basin
- Easily mounts to pump base
- Made from durable ABS
- Helps prevent clogging and switch malfunction
- Fits all PROFLO submersible pumps (excludes sewage pumps)

## CHECK VALVES - BARB / SLIP



PF99509



PF99549

MODEL	MATERIAL	INLET	OUTLET
PF99509	ABS	1-1/2" MPT	1-1/4" BARB OR 1-1/2" SLIP
PF99549	PVC	1-1/2" MPT	1-1/4" BARB OR 1-1/2" SLIP

## CHECK VALVES - PVC



PFPCVC300J  
PFPCVC300K



PFPCV700J  
PFPCV700K



PFPCVC500HJ



PFPCVS400J  
PFPCVS400K



PFPCVS600J  
PFPCVS600K

MODEL	DESCRIPTION	INLET	OUTLET
PFPCVC300J	1-1/2" compression check valve	1-1/2" compression	1-1/2" compression
PFPCVC300K	2" compression check valve	2" compression	2" compression
PFPCV700J	1-1/2" solvent weld check valve	1-1/2" socket	1-1/2" socket
PFPCV700K	2" solvent weld check valve	2" socket	2" socket
PFPCVC500HJ	1-1/2" or 1-1/4" sump pump check valve	1-1/4" or 1-1/2" compression	1-1/4" or 1-1/2" compression
PFPCVS400J	1-1/2" check/ball valve combination	1-1/2" socket (Union)	1-1/2" socket (Union)
PFPCVS400K	2" check/ball valve combination	2" socket (Union)	2" socket (Union)
PFPCVS600J	1-1/2" spring check valve	1-1/2" socket (Union)	1-1/2" socket (Union)
PFPCVS600K	2" spring check valve	2" socket (Union)	2" socket (Union)

# SEWAGE BASIN ACCESSORIES

NEW



## SNAP IN HUB - PF99277

- 4" Snap in hub.
- Rubber construction
- Provides tight seal when installing inlet pipe into sewage basin
- Corrosion resistant material

NEW



## POLY EXTENSIONS (18X6 AND 18X12) - PF99294 & PF99295

- 18" x 6" Poly Extension (PF99294) or 18" x 12" Poly Extension (PF99295)
- Durable polyethylene construction
- Hardware included
- Increases the height of a 18" diameter sewage basin by 6" or 12"
- Corrosion resistant and durable.
- Easy to install

NEW



## UNIVERSAL SUMP PUMP HOSE KIT - PF99624

- 24' poly drainage tubing (1-1/4" hose diameter)
- Includes 1-1/4" and 1-1/2" adapters
- Rust resistant hose clamp
- For permanent or temporary use
- Easy installation



