

FEATURED PRODUCT



\$129.99

JDV22N

HAND-HELD DIGITAL VACUUM GAUGE



\$189.00

JDS20000

DIGITAL SCALE IN CASE



\$679.00

JF6DP

REFRIGERANT RECOVERY MACHINE



50TH ANNIVERSARY SWEEPSTAKES

AMERICAN MUSCLE WIN A CAMARO



DETAILS AT JBIND.COM

FEATURES & BENEFITS:

DV-22N FEATURES:

- Extended range MEMS sensor with easy-to-read backlit display
- Allows for direct connection to the A/C unit without a hose
- Audible and visual alarms when target vacuum level is achieved
- Intuitive user menu with custom setting options
- Low battery indicator with automatic shutoff
- Measures in Microns, PSIA, inHg, Pascals, Torr, mTorr and mBar
- Vacuum Reading Range 100,000 to 10 microns
- Operates with AA batteries (included)
- 1 year warranty

DS-20000 FEATURES:

- 220 lb (100 kg) capacity
- Highly sensitive, solid state load cell (0.25 oz/10 gm)
- Easy-to-read LCD screen
- Field repairable with replaceable cable, weighing platform and handheld remote
- Displays weight in decimal/pounds, pounds/ounces, and kilograms
- Automatic shutoff option to conserve battery life
- Rugged carrying case (included)
- Operates with 9v battery (included)
- 2 year warranty

F6-DP FEATURES:

- Micro-channel condenser provides exceptional heat exchange
- Full one horsepower dual piston compressor for industry leading recovery rates
- Oversized cooling fan for superior heat dissipation
- Self-purging without the need to change hoses
- Full size protected gauges for suction and tank pressure
- Filter/drier included
- Heavy duty handle with comfortable rubber grip and detachable power cord
- For use with all Class III, IV and V refrigerants, including R410A
- 3 Year OTC warranty

SHOP NOW >>

©2018 Ferguson Enterprises, Inc.
Promo Ends 07/31/18

