



PROSELECT



CONDENSATE PUMPS

- Newly improved compact design that doesn't sacrifice reservoir capacity for size
- Minimizes biofilm buildup with a unique trap and filter system
- Fan-assisted cooling system allows for semi-enclosed IP24 splashproof casing
- Single-screw quick-release reservoir for routine maintenance
- Built-in bubble level ensures consistent installation wherever, whenever
- Patent-pending impeller configuration

SPECIFICATIONS

Model	Listings	HP	Volts	Hz	Amps	Watts	Gallons Per Hour @ Height				Shutoff	Capacity (US Gal)	Weight (lbs)
							1'	5'	9'	15'			
PSCP215	CSA/UL	1/35	115	60	1.6	85	60	42	28	5	16'	0.45	4.10
PSCP215WS	CSA/UL	1/35	115	60	1.6	85	60	42	28	5	16'	0.45	4.10
PSCP215WS20T*	CSA/UL	1/35	115	60	1.6	85	60	42	28	5	16'	0.45	4.10
PSCP220WS	CSA/UL	1/35	115	60	1.6	85	130	105	80	45	21'	0.45	4.10
PSCP220WS20T*	CSA/UL	1/35	115	60	1.6	85	130	105	80	45	21'	0.45	4.10
PSCP220WS230	CSA/UL	1/40	230	60	0.7	75	95	80	60	20	17'	0.45	4.10

* Includes 20ft of 3/8" ID vinyl tube

WARRANTY & CODES

This PROSELECT product carries a 1-year limited warranty.

