

# FEATURED PRODUCT



## 102 X 77 SPOT INFRARED IMAGER

INSTANT IMAGE, FASTEST SCANNING



M225720 102x77 SPOT INFRARED IMAGER  
\$299.99



### Simply Point, Pull and Detect

- Instant Start-Up for Easy Detection
- Just Pull the Trigger to Scan Large Areas Quickly
- 15 Second Image Hold for Fast Diagnostics
- Runs on a Standard 9V Alkaline Battery

### High Resolution 102x77 Thermal Image

- DUAL SENSE™ Pixels Are Ultra-Responsive, Adjusting Individually to Eliminate Blurring of Hot and Cold Details
- Crisp Image Easily Identifies Heat, Water, Air, Electrical Resistance & More

### Measure Temperature: 14°F - 646°F

- One Simple On-Screen Temperature Reading
- Option to Switch Between F° or C°
- 56:1 Distance-to-Spot Provides Precise Measurements From Further Away Or Greater Detail Up Close

CONTACT YOUR LOCAL BRANCH >>

Purchase a **M225720** and get a **M230920**  
(\$99 value) **FREE** after eRebate.

#### M230920 Features:

- **Optimized 2.7" LCD Display:** Digital Technology and Larger Screen Deliver Crisp, Clear Image
- **9mm Digital Inspection Scope:** Best-In-Class Image Quality in Tight Space
- **Four Surround LED Lights:** Superior Brightness Without Shadow or Glare



©2017 Ferguson Enterprises, Inc.  
Promo Ends 01/31/18

